

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332713-940

Luminaire Tested: **SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332713-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8280.6 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332713-940
CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332713-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	94	91	87	92	88	84	81	76	73	71	64	62	61	54	52	51	46				
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43	39				
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24				
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21				
7	59	46	38	33	54	44	36	31	38	32	28	33	28	25	28	24	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	15				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332713-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	2.0
10°-20°	471.5	5.7
20°-30°	694.0	8.4
30°-40°	806.8	9.7
40°-50°	806.8	9.7
50°-60°	705.8	8.5
60°-70°	524.1	6.3
70°-80°	297.8	3.6
80°-90°	89.9	1.1
90°-100°	88.4	1.1
100°-110°	261.7	3.2
110°-120°	444.2	5.4
120°-130°	585.7	7.1
130°-140°	657.8	7.9
140°-150°	646.4	7.8
150°-160°	543.7	6.6
160°-170°	361.7	4.4
170°-180°	126.7	1.5
0°-30°	1332.9	16.1
0°-40°	2139.7	25.8
0°-60°	3652.3	44.1
0°-90°	4564.1	55.1
90°-120°	794.3	9.6
90°-150°	2684.3	32.4
90°-180°	3716.0	44.9
0°-180°	8280.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	3	14	23	29	31	8
95°	62	71	79	82	82	69
105°	241	243	247	250	253	256
115°	452	452	450	449	448	445
125°	658	658	657	655	653	586
135°	848	854	855	853	850	656
145°	1031	1035	1036	1035	1032	645
155°	1181	1181	1180	1184	1180	543
165°	1286	1283	1280	1286	1282	362
175°	1338	1332	1331	1338	1331	127
180°	1340	1340	1340	1340	1340	



TEST NUMBER: P332713-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	30.2	30.5	30.8	31.0	31.2	31.5	31.6	31.7	31.7	31.9	32.2
90°	3.1	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2
92.5°	22.2	25.1	28.0	30.9	33.8	35.8	37.2	38.4	39.8	41.0	41.8
95°	62.2	64.2	66.3	68.4	70.4	72.3	73.9	75.5	77.1	78.7	79.5
97.5°	108.6	110.2	111.9	113.5	115.2	117.0	118.9	120.7	122.6	124.5	125.4
100°	145.1	146.0	146.9	147.8	148.7	150.3	152.3	154.4	156.4	158.5	159.0
102.5°	183.2	183.5	183.9	184.2	184.7	185.7	187.6	189.6	191.5	193.3	193.9
105°	241.4	241.7	241.8	242.1	242.3	242.9	243.8	244.7	245.7	246.6	247.3
107.5°	302.5	302.8	303.1	303.4	303.6	303.8	304.0	304.1	304.3	304.3	305.1
110°	343.9	344.4	344.8	345.4	345.8	345.9	345.7	345.4	345.2	345.0	344.6



TEST NUMBER: P332713-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	387.0	387.2	387.3	387.4	387.4	387.3	386.8	386.5	386.0	385.6	385.5
115°	451.7	451.7	451.7	451.7	451.7	451.5	451.0	450.6	450.0	449.6	449.4
117.5°	512.6	512.8	513.0	513.2	513.4	513.3	512.9	512.6	512.3	512.0	511.2
120°	553.2	554.1	555.1	556.0	556.9	557.1	556.3	555.6	554.9	554.3	553.1
122.5°	595.5	595.8	596.2	596.6	597.0	597.0	596.6	596.4	596.0	595.7	594.9
125°	657.8	657.8	657.8	657.8	657.8	657.7	657.5	657.3	657.0	656.8	656.4
127.5°	714.4	715.2	715.8	716.5	717.2	717.4	716.9	716.6	716.2	715.9	715.4
130°	754.2	754.9	755.5	756.3	757.0	757.3	757.3	757.3	757.3	757.3	756.9
132.5°	794.8	795.3	795.9	796.3	796.8	797.0	796.8	796.7	796.5	796.3	795.8
135°	848.5	849.9	851.2	852.7	854.0	854.7	854.7	854.7	854.7	854.7	854.3
137.5°	906.9	907.6	908.2	908.8	909.5	910.0	910.3	910.7	911.1	911.4	910.9
140°	945.8	946.3	946.8	947.3	947.7	947.9	947.9	947.9	947.9	947.9	947.7
142.5°	981.5	982.0	982.4	982.8	983.4	983.5	983.3	983.1	982.9	982.8	982.7
145°	1030.8	1031.7	1032.7	1033.6	1034.5	1035.1	1035.3	1035.5	1035.7	1036.0	1035.7
147.5°	1079.7	1080.8	1081.9	1083.0	1084.1	1084.6	1084.4	1084.2	1084.1	1083.9	1083.7
150°	1109.6	1110.4	1111.4	1112.3	1113.2	1113.7	1113.7	1113.7	1113.7	1113.7	1113.7
152.5°	1137.7	1138.3	1138.8	1139.3	1140.0	1140.3	1140.5	1140.7	1140.9	1141.0	1141.6
155°	1181.0	1181.0	1181.0	1181.0	1181.0	1180.9	1180.7	1180.4	1180.2	1180.0	1180.9
157.5°	1217.5	1217.1	1216.7	1216.3	1215.8	1215.6	1215.6	1215.5	1215.5	1215.4	1216.1
160°	1239.0	1238.9	1238.6	1238.3	1238.1	1237.9	1237.7	1237.4	1237.2	1237.0	1237.7
162.5°	1258.9	1258.3	1257.8	1257.1	1256.5	1256.2	1255.9	1255.7	1255.4	1255.2	1256.4
165°	1285.7	1285.0	1284.2	1283.6	1282.9	1282.3	1281.8	1281.4	1280.9	1280.5	1281.8
167.5°	1306.2	1305.2	1304.2	1303.2	1302.3	1301.8	1301.9	1301.9	1302.0	1302.0	1303.4
170°	1317.8	1316.6	1315.5	1314.3	1313.1	1312.7	1313.0	1313.1	1313.4	1313.7	1315.0
172.5°	1326.1	1325.1	1324.1	1323.1	1322.2	1321.7	1321.8	1321.9	1321.9	1322.0	1323.5
175°	1337.5	1336.3	1335.2	1334.0	1332.8	1332.1	1331.9	1331.7	1331.5	1331.2	1332.8
177.5°	1341.2	1340.2	1339.3	1338.5	1337.5	1337.0	1337.0	1337.0	1337.0	1337.0	1338.4
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5



TEST NUMBER: P332713-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	32.5	32.7	33.0	33.2	33.3	33.3	33.4	33.5
90°	25.6	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	42.7	43.5	44.3	44.9	45.2	45.5	45.7	46.0
95°	80.1	80.8	81.5	81.9	81.9	81.9	81.9	81.9
97.5°	126.2	127.0	127.9	128.2	128.2	128.2	128.2	128.2
100°	159.4	159.9	160.3	160.6	160.6	160.6	160.6	160.6
102.5°	194.6	195.3	195.9	196.3	196.5	196.7	196.9	197.1
105°	248.0	248.6	249.3	250.0	250.7	251.4	252.1	252.8
107.5°	305.7	306.3	306.9	307.3	307.2	307.2	307.1	307.1
110°	344.0	343.6	343.1	343.2	343.9	344.6	345.4	346.0



TEST NUMBER: P332713-940

CATALOG NUMBER: SA4XXDIP-C1195D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	385.4	385.3	385.2	385.2	385.4	385.5	385.7	385.8
115°	449.2	448.9	448.7	448.4	448.3	448.0	447.8	447.5
117.5°	510.4	509.6	508.8	508.3	507.7	507.3	506.8	506.4
120°	552.0	550.8	549.7	549.3	549.7	550.2	550.7	551.2
122.5°	594.1	593.3	592.5	591.7	590.9	590.1	589.2	588.4
125°	655.9	655.4	655.0	654.5	654.1	653.6	653.1	652.6
127.5°	715.0	714.5	714.0	713.6	713.3	712.8	712.5	712.1
130°	756.3	755.9	755.5	754.7	753.9	753.0	752.0	751.1
132.5°	795.3	794.9	794.4	794.0	793.6	793.3	792.9	792.6
135°	853.8	853.3	852.8	852.3	851.6	850.9	850.2	849.5
137.5°	910.3	909.6	909.1	908.8	909.0	909.1	909.3	909.4
140°	947.4	947.3	947.0	946.8	946.6	946.3	946.1	945.8
142.5°	982.7	982.6	982.6	982.5	982.5	982.4	982.4	982.3
145°	1035.5	1035.3	1035.1	1034.6	1033.9	1033.2	1032.5	1031.9
147.5°	1083.5	1083.3	1083.1	1082.9	1082.7	1082.4	1082.2	1082.0
150°	1113.7	1113.7	1113.7	1113.6	1113.3	1113.1	1112.9	1112.7
152.5°	1142.1	1142.7	1143.3	1143.3	1142.6	1142.0	1141.4	1140.9
155°	1181.9	1182.8	1183.7	1183.7	1182.8	1181.9	1180.9	1180.0
157.5°	1216.8	1217.5	1218.2	1218.2	1217.4	1216.6	1215.8	1215.0
160°	1238.3	1239.0	1239.7	1239.5	1238.3	1237.2	1236.1	1234.9
162.5°	1257.7	1258.9	1260.2	1260.3	1259.1	1257.9	1256.8	1255.6
165°	1283.3	1284.6	1286.0	1286.2	1285.3	1284.4	1283.4	1282.5
167.5°	1304.8	1306.2	1307.5	1307.5	1306.1	1304.7	1303.2	1301.8
170°	1316.4	1317.8	1319.2	1319.0	1317.4	1315.8	1314.2	1312.6
172.5°	1325.1	1326.6	1328.2	1328.2	1326.5	1324.9	1323.3	1321.7
175°	1334.4	1336.1	1337.7	1337.7	1336.1	1334.4	1332.8	1331.2
177.5°	1339.6	1341.0	1342.2	1342.1	1340.6	1339.2	1337.7	1336.2
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5

(END OF REPORT)