

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332682-940

Luminaire Tested: **SA4XXDIP-C1195D590U940-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332682-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6440.1 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332682-940
CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P332682-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62	62	62	62	62	62	62	62	62	62	62	62	62																
1	99	94	90	86	93	88	84	81	77	74	72	67	65	63	58	56	54	50	50	50	50	50	50	50	50	50	50	50	50	50																
2	90	82	75	69	84	77	70	65	67	62	58	58	55	51	50	47	45	41	41	41	41	41	41	41	41	41	41	41	41	41	41															
3	82	71	63	57	76	67	60	54	59	53	48	51	47	43	44	40	38	34	34	34	34	34	34	34	34	34	34	34	34	34	34															
4	75	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32	29	29	29	29	29	29	29	29	29	29	29	29	29	29	29														
5	68	56	47	41	64	53	45	39	46	40	35	40	35	31	35	31	28	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25														
6	63	50	41	35	59	47	39	34	42	35	30	36	31	27	32	27	24	21	21	21	21	21	21	21	21	21	21	21	21	21	21	21	21													
7	58	45	37	31	54	43	35	29	38	31	27	33	28	24	29	25	21	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19	19													
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19	17	17	17	17	17	17	17	17	17	17	17	17	17	17	17	17													
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15												
10	47	34	27	22	44	33	26	21	29	23	19	26	21	17	23	18	16	14	14	14	14	14	14	14	14	14	14	14	14	14	14	14	14	14												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10266	10266	10266
5°	10297	10032	10061
10°	10234	9869	9861
15°	10142	9679	9625
20°	10004	9469	9396
25°	9848	9234	9144
30°	9679	9000	8885
35°	9488	8760	8658
40°	9335	8533	8422
45°	9109	8323	8219
50°	8917	8080	8004
55°	8719	7852	7753
60°	8410	7562	7524
65°	8071	7250	7242
70°	7660	6893	6914
75°	7091	6501	6617
80°	6453	6124	6326
85°	5641	5792	6154



TEST NUMBER: P332682-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.4	1.9
10°-20°	345.0	5.4
20°-30°	521.7	8.1
30°-40°	631.2	9.8
40°-50°	667.3	10.4
50°-60°	628.0	9.8
60°-70°	521.0	8.1
70°-80°	366.0	5.7
80°-90°	208.9	3.2
90°-100°	146.1	2.3
100°-110°	239.2	3.7
110°-120°	344.7	5.4
120°-130°	394.6	6.1
130°-140°	400.2	6.2
140°-150°	363.3	5.6
150°-160°	290.6	4.5
160°-170°	187.4	2.9
170°-180°	64.6	1.0
0°-30°	987.1	15.3
0°-40°	1618.2	25.1
0°-60°	2913.5	45.2
0°-90°	4009.3	62.3
90°-120°	730.1	11.3
90°-150°	1888.2	29.3
90°-180°	2431.0	37.7
0°-180°	6440.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1272	1272	1272	1272	1272	
5°	1273	1268	1259	1269	1269	121
15°	1220	1221	1218	1229	1229	344
25°	1116	1125	1129	1144	1146	514
35°	977	994	1008	1027	1032	611
45°	814	842	869	892	900	629
55°	638	668	710	738	748	568
65°	441	487	535	570	582	437
75°	245	298	357	396	410	260
85°	75	136	199	240	256	80
90°	24	87	152	195	209	16
95°	46	78	135	175	190	51
105°	166	199	253	290	286	175
115°	294	310	354	385	396	290
125°	408	410	443	470	480	364
135°	501	502	513	536	546	387
145°	576	576	576	585	592	360
155°	630	631	629	631	630	291
165°	665	662	662	666	662	188
175°	680	677	678	682	676	65
180°	680	680	680	680	680	



TEST NUMBER: P332682-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6
2.5°	1276.1	1275.3	1274.6	1273.8	1273.1	1271.7	1269.6	1267.7	1265.6	1263.6	1265.3
5°	1272.9	1272.0	1271.0	1270.2	1269.2	1267.6	1265.3	1263.1	1261.0	1258.7	1261.2
7.5°	1262.1	1261.6	1261.0	1260.4	1259.9	1258.6	1256.9	1255.0	1253.1	1251.3	1254.2
10°	1253.0	1252.7	1252.4	1252.1	1251.8	1250.8	1249.2	1247.7	1246.1	1244.5	1247.3
12.5°	1240.5	1240.5	1240.4	1240.3	1240.3	1239.7	1238.6	1237.5	1236.4	1235.4	1238.0
15°	1220.3	1220.6	1220.9	1221.2	1221.6	1221.2	1220.3	1219.3	1218.3	1217.5	1220.3
17.5°	1192.7	1193.6	1194.5	1195.5	1196.4	1196.9	1196.7	1196.4	1196.2	1196.1	1199.0
20°	1173.3	1174.2	1175.2	1176.2	1177.1	1177.7	1178.0	1178.4	1178.7	1179.0	1182.1
22.5°	1151.6	1152.8	1154.1	1155.2	1156.5	1157.4	1157.9	1158.5	1159.0	1159.6	1162.8
25°	1116.3	1118.2	1120.2	1122.0	1123.9	1125.3	1126.3	1127.2	1128.2	1129.2	1132.7
27.5°	1077.0	1079.9	1082.6	1085.4	1088.2	1090.3	1091.7	1093.2	1094.7	1096.1	1099.3
30°	1050.8	1053.4	1055.9	1058.5	1061.0	1063.4	1065.5	1067.7	1070.0	1072.2	1075.7
32.5°	1022.3	1025.4	1028.4	1031.4	1034.5	1037.2	1039.7	1042.2	1044.6	1047.1	1051.1
35°	976.8	980.6	984.4	988.2	991.9	995.4	998.6	1001.7	1005.0	1008.1	1012.5
37.5°	930.9	935.3	939.7	944.1	948.4	952.5	956.4	960.4	964.3	968.2	972.8
40°	901.3	905.4	909.5	913.6	917.7	922.0	926.5	930.9	935.3	939.8	944.5
42.5°	867.2	871.7	876.4	881.0	885.6	890.6	895.7	900.9	906.1	911.3	916.6
45°	814.5	820.5	826.5	832.5	838.5	844.5	850.5	856.6	862.6	868.6	874.0
47.5°	764.0	770.3	776.5	782.7	788.9	795.5	802.5	809.4	816.4	823.3	828.8
50°	727.6	734.6	741.5	748.5	755.5	762.4	769.4	776.3	783.3	790.2	796.6
52.5°	691.2	698.1	705.1	712.0	719.0	726.5	734.4	742.4	750.4	758.4	764.7
55°	637.9	644.5	651.2	657.8	664.5	672.5	682.1	691.5	701.1	710.5	716.8
57.5°	578.4	586.7	594.9	603.1	611.3	620.1	629.5	639.0	648.5	657.8	665.4
60°	539.7	547.9	556.1	564.4	572.6	581.9	592.4	602.8	613.2	623.7	631.0
62.5°	502.0	511.0	520.0	529.1	538.0	547.7	558.2	568.6	579.1	589.5	596.7
65°	441.4	451.6	461.6	471.8	481.9	492.3	503.1	513.9	524.6	535.4	543.3
67.5°	383.0	393.8	404.6	415.3	426.1	437.2	448.7	460.2	471.7	483.3	491.3
70°	343.1	353.9	364.7	375.4	386.2	397.6	409.6	421.6	433.6	445.7	454.2
72.5°	304.4	315.4	326.5	337.4	348.5	360.3	373.2	385.9	398.7	411.5	419.8
75°	245.0	256.6	268.3	280.0	291.8	304.3	317.5	330.8	344.1	357.4	366.2
77.5°	189.4	201.8	214.2	226.6	239.0	252.2	266.1	280.0	293.9	307.8	316.8
80°	155.2	167.8	180.5	193.1	205.8	219.1	233.0	247.0	260.9	274.8	284.3
82.5°	121.0	134.2	147.4	160.5	173.7	187.3	201.2	215.1	229.0	242.9	252.6
85°	75.4	88.7	102.0	115.3	128.6	142.4	156.6	170.9	185.1	199.4	208.8
87.5°	42.4	55.6	68.8	81.9	95.1	108.7	122.7	136.8	150.8	164.9	174.2
90°	24.3	38.2	52.1	66.0	79.9	94.1	108.6	123.1	137.7	152.1	162.0
92.5°	28.1	39.5	51.0	62.4	73.9	86.9	101.4	115.9	130.4	144.9	154.5
95°	46.5	53.1	59.7	66.3	72.9	82.8	95.8	108.9	122.0	135.1	144.3
97.5°	76.2	87.6	99.0	110.4	121.7	127.5	127.8	128.0	128.2	128.5	136.9
100°	99.1	109.3	119.6	129.8	140.1	143.7	140.4	137.1	133.8	130.6	137.2
102.5°	125.9	134.6	143.4	152.0	160.8	170.1	180.2	190.3	200.3	210.4	197.9
105°	165.9	172.9	179.9	186.9	193.9	203.6	215.9	228.1	240.4	252.7	261.6
107.5°	205.5	211.0	216.5	222.0	227.6	236.2	248.1	259.9	271.7	283.6	291.9
110°	231.1	235.9	240.7	245.4	250.2	258.5	270.2	282.0	293.7	305.5	313.0



TEST NUMBER: P332682-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.0	260.6	265.1	269.7	274.2	281.9	292.7	303.6	314.5	325.4	332.4
115°	294.4	297.6	300.8	304.0	307.2	313.8	323.8	333.8	343.8	353.8	361.0
117.5°	330.2	332.4	334.6	336.7	338.9	344.8	354.5	364.2	373.8	383.5	390.0
120°	353.5	354.9	356.3	357.8	359.1	364.4	373.4	382.5	391.6	400.6	407.2
122.5°	376.3	376.7	377.2	377.7	378.2	382.8	391.6	400.5	409.3	418.1	424.5
125°	407.5	407.7	407.8	408.0	408.0	412.0	419.6	427.4	435.1	442.7	449.1
127.5°	438.2	438.0	437.7	437.6	437.4	440.6	447.2	453.8	460.3	466.9	472.6
130°	457.0	456.7	456.6	456.4	456.2	458.8	464.1	469.6	474.9	480.4	486.2
132.5°	475.3	475.2	475.1	474.9	474.8	477.0	481.5	486.0	490.4	494.9	500.5
135°	501.3	501.2	501.1	501.0	500.9	502.1	504.8	507.5	510.1	512.8	518.1
137.5°	525.7	525.4	525.1	524.9	524.6	525.2	526.8	528.3	529.9	531.5	536.4
140°	541.5	541.4	541.4	541.3	541.2	541.4	541.9	542.4	543.0	543.6	548.0
142.5°	554.6	555.0	555.3	555.6	556.0	556.2	556.1	556.1	556.0	555.9	559.8
145°	576.2	576.2	576.2	576.3	576.3	576.3	576.3	576.3	576.3	576.3	578.3
147.5°	593.6	593.9	594.2	594.6	594.9	594.9	594.9	594.8	594.6	594.5	594.9
150°	606.2	606.4	606.5	606.6	606.7	606.8	606.6	606.5	606.5	606.3	606.3
152.5°	615.6	616.0	616.3	616.5	616.9	616.9	616.7	616.5	616.3	616.1	616.3
155°	630.3	630.4	630.4	630.5	630.7	630.5	630.3	629.9	629.5	629.2	629.6
157.5°	642.7	642.7	642.6	642.6	642.5	642.2	641.9	641.5	641.1	640.7	641.3
160°	650.1	649.7	649.3	649.1	648.7	648.5	648.4	648.3	648.1	648.0	648.7
162.5°	656.6	656.1	655.7	655.3	654.9	654.6	654.4	654.3	654.2	654.2	654.8
165°	664.8	664.2	663.7	663.1	662.5	662.3	662.3	662.3	662.3	662.3	663.2
167.5°	671.3	670.7	670.1	669.6	669.0	668.6	668.6	668.5	668.4	668.3	669.4
170°	675.0	674.3	673.6	673.0	672.3	672.0	672.1	672.2	672.3	672.4	673.3
172.5°	677.4	676.7	676.1	675.4	674.8	674.4	674.6	674.7	674.8	674.8	675.8
175°	680.1	679.4	678.7	678.1	677.3	677.1	677.2	677.3	677.4	677.5	678.5
177.5°	681.3	680.6	680.0	679.4	678.8	678.5	678.7	678.9	679.0	679.2	680.0
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332682-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6	1271.6
2.5°	1267.1	1268.9	1270.7	1271.4	1271.1	1270.9	1270.7	1270.4
5°	1263.8	1266.3	1268.8	1270.0	1269.6	1269.4	1269.0	1268.7
7.5°	1257.0	1259.9	1262.8	1264.0	1263.6	1263.4	1263.0	1262.8
10°	1250.2	1253.0	1255.9	1257.1	1256.9	1256.5	1256.2	1255.9
12.5°	1240.5	1243.1	1245.7	1247.1	1247.0	1246.9	1246.8	1246.8
15°	1223.2	1226.0	1228.8	1230.1	1229.8	1229.5	1229.1	1228.8
17.5°	1201.9	1204.8	1207.7	1209.1	1208.8	1208.5	1208.3	1208.0
20°	1185.4	1188.5	1191.7	1193.2	1193.2	1193.2	1193.2	1193.2
22.5°	1165.9	1169.1	1172.2	1174.1	1174.7	1175.1	1175.6	1176.2
25°	1136.1	1139.6	1143.1	1145.0	1145.3	1145.6	1145.9	1146.2
27.5°	1102.6	1105.8	1109.0	1110.8	1111.3	1111.6	1112.0	1112.3
30°	1079.1	1082.6	1086.1	1088.2	1088.8	1089.4	1090.0	1090.7
32.5°	1055.1	1059.1	1063.1	1065.4	1066.0	1066.7	1067.3	1067.9
35°	1017.0	1021.4	1025.8	1028.5	1029.5	1030.5	1031.4	1032.3
37.5°	977.2	981.7	986.2	989.0	990.0	991.0	992.0	993.0
40°	949.2	954.0	958.8	961.8	963.0	964.3	965.5	966.8
42.5°	921.8	927.0	932.3	935.4	936.5	937.5	938.4	939.5
45°	879.3	884.8	890.1	893.6	895.2	896.7	898.3	899.9
47.5°	834.5	840.0	845.6	849.3	851.2	853.1	855.0	856.9
50°	802.9	809.2	815.6	819.7	821.6	823.5	825.4	827.2
52.5°	771.1	777.4	783.6	787.8	789.7	791.6	793.4	795.4
55°	723.2	729.5	735.8	739.9	741.8	743.8	745.6	747.5
57.5°	672.9	680.5	688.0	692.6	694.4	696.2	697.9	699.7
60°	638.2	645.5	652.7	657.6	660.2	662.7	665.3	667.8
62.5°	604.0	611.4	618.6	623.5	626.1	628.6	631.1	633.6
65°	551.2	559.1	567.0	572.2	574.8	577.3	579.9	582.4
67.5°	499.4	507.4	515.4	520.7	523.2	525.6	528.1	530.6
70°	462.8	471.3	479.8	485.3	487.4	489.6	491.9	494.1
72.5°	428.1	436.4	444.7	450.0	452.5	455.0	457.4	459.9
75°	375.1	384.0	392.8	398.7	401.5	404.4	407.2	410.1
77.5°	325.8	334.8	343.8	349.8	352.8	355.9	358.9	361.9
80°	293.8	303.3	312.8	318.8	321.3	323.9	326.4	329.0
82.5°	262.4	272.2	281.9	288.2	291.0	293.7	296.5	299.3
85°	218.3	227.8	237.3	243.6	246.8	249.9	253.2	256.3
87.5°	183.5	192.8	202.1	208.1	211.0	213.8	216.7	219.5
90°	171.8	181.7	191.5	197.9	200.6	203.4	206.2	208.9
92.5°	164.1	173.7	183.3	189.4	192.0	194.6	197.2	199.7
95°	153.6	162.7	171.9	178.1	181.0	184.0	186.9	189.9
97.5°	145.2	153.6	161.9	167.5	170.3	173.2	176.0	178.9
100°	143.8	150.4	157.1	161.6	163.9	166.2	168.5	170.9
102.5°	185.5	173.0	160.6	155.6	158.1	160.6	163.1	165.6
105°	270.5	279.5	288.4	292.1	290.5	289.0	287.5	286.0
107.5°	300.1	308.4	316.7	322.2	324.9	327.6	330.3	333.1
110°	320.5	328.0	335.5	340.7	343.6	346.4	349.3	352.1



TEST NUMBER: P332682-940

CATALOG NUMBER: SA4XXDIP-C1195D590U940-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	339.4	346.3	353.3	358.3	361.2	364.3	367.2	370.1
115°	368.2	375.4	382.5	387.3	389.5	391.7	393.9	396.1
117.5°	396.5	403.1	409.7	414.2	416.7	419.1	421.6	424.1
120°	413.8	420.3	426.9	431.2	433.5	435.9	438.2	440.5
122.5°	431.1	437.5	444.0	448.2	450.3	452.4	454.4	456.5
125°	455.4	461.8	468.1	472.3	474.3	476.4	478.3	480.4
127.5°	478.2	483.8	489.5	493.3	495.3	497.4	499.4	501.5
130°	492.0	497.8	503.6	507.5	509.3	511.2	513.2	515.1
132.5°	506.0	511.6	517.2	520.8	522.6	524.4	526.3	528.1
135°	523.4	528.7	534.0	537.7	539.8	541.9	544.0	546.2
137.5°	541.3	546.1	551.0	554.2	555.7	557.2	558.7	560.3
140°	552.4	556.9	561.3	564.5	566.1	567.8	569.5	571.2
142.5°	563.7	567.5	571.3	573.9	575.3	576.7	578.0	579.3
145°	580.3	582.4	584.3	586.1	587.6	589.1	590.6	592.1
147.5°	595.2	595.6	595.9	596.6	597.7	598.9	600.0	601.1
150°	606.3	606.3	606.3	606.4	606.5	606.6	606.7	606.8
152.5°	616.4	616.6	616.8	616.9	616.8	616.7	616.6	616.6
155°	630.1	630.5	631.0	631.1	630.7	630.4	630.1	629.7
157.5°	641.9	642.5	643.0	643.0	642.5	641.9	641.3	640.7
160°	649.3	650.1	650.8	650.8	650.1	649.3	648.7	648.0
162.5°	655.5	656.1	656.8	656.8	656.0	655.2	654.5	653.7
165°	664.1	664.9	665.9	665.8	664.8	663.8	662.8	661.7
167.5°	670.4	671.4	672.3	672.3	671.2	670.0	668.9	667.8
170°	674.2	675.1	676.1	675.9	674.8	673.7	672.5	671.5
172.5°	676.7	677.6	678.5	678.3	677.2	675.9	674.7	673.4
175°	679.6	680.6	681.6	681.4	680.1	678.7	677.3	676.0
177.5°	680.7	681.4	682.2	682.0	680.9	679.8	678.7	677.6
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1

(END OF REPORT)