

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332695-940

Luminaire Tested: **SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332695-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7063.6 lumens  
Efficiency: N/A  
Efficacy: 116.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332695-940  
CATALOG NUMBER: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332695-940

CATALOG NUMBER: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	93	89	95	91	87	84	80	78	75	70	68	67	61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62	62	59	56	54	52	49	45
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	41	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332695-940

CATALOG NUMBER: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.3	2.4
10°-20°	471.5	6.7
20°-30°	694.0	9.8
30°-40°	806.8	11.4
40°-50°	806.8	11.4
50°-60°	705.8	10.0
60°-70°	524.1	7.4
70°-80°	297.8	4.2
80°-90°	88.6	1.3
90°-100°	59.5	0.8
100°-110°	176.1	2.5
110°-120°	298.9	4.2
120°-130°	394.2	5.6
130°-140°	442.7	6.3
140°-150°	435.0	6.2
150°-160°	365.9	5.2
160°-170°	243.4	3.4
170°-180°	85.2	1.2
0°-30°	1332.9	18.9
0°-40°	2139.7	30.3
0°-60°	3652.3	51.7
0°-90°	4562.8	64.6
90°-120°	534.5	7.6
90°-150°	1806.3	25.6
90°-180°	2501.0	35.4
0°-180°	7063.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	2	10	15	19	21	7
95°	42	48	53	55	55	47
105°	162	163	166	168	170	172
115°	304	304	303	302	301	300
125°	443	443	442	441	439	394
135°	571	575	575	574	572	442
145°	694	696	697	696	694	434
155°	795	795	794	796	794	366
165°	865	863	862	865	863	244
175°	900	897	896	900	896	85
180°	901	901	901	901	901	



TEST NUMBER: P332695-940

CATALOG NUMBER: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	30.1	30.1	30.2	30.3	30.4	30.4	30.4	30.4	30.4	30.4	30.6
90°	2.1	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2
92.5°	14.9	16.9	18.8	20.8	22.7	24.2	25.0	25.9	26.8	27.6	28.2
95°	41.8	43.2	44.6	46.0	47.4	48.7	49.8	50.8	51.9	53.0	53.4
97.5°	73.0	74.2	75.3	76.4	77.5	78.7	80.0	81.2	82.5	83.8	84.4
100°	97.6	98.2	98.8	99.4	100.0	101.1	102.5	103.9	105.2	106.6	107.0
102.5°	123.2	123.5	123.8	124.0	124.2	125.0	126.3	127.5	128.9	130.1	130.5
105°	162.5	162.6	162.7	162.9	163.1	163.5	164.1	164.7	165.3	165.9	166.4
107.5°	203.6	203.8	203.9	204.1	204.3	204.5	204.6	204.6	204.7	204.8	205.3
110°	231.5	231.8	232.0	232.4	232.6	232.7	232.6	232.5	232.3	232.1	231.8



TEST NUMBER: P332695-940

CATALOG NUMBER: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.5	260.5	260.6	260.6	260.7	260.6	260.3	260.0	259.8	259.5	259.4
115°	304.0	304.0	304.0	304.0	304.0	303.8	303.4	303.2	302.8	302.6	302.4
117.5°	344.9	345.1	345.2	345.3	345.4	345.4	345.2	344.9	344.7	344.6	344.0
120°	372.3	372.9	373.5	374.2	374.8	374.8	374.3	373.9	373.4	373.0	372.2
122.5°	400.7	400.9	401.2	401.4	401.7	401.7	401.5	401.3	401.1	400.8	400.3
125°	442.6	442.6	442.6	442.6	442.6	442.6	442.5	442.3	442.1	442.0	441.7
127.5°	480.7	481.2	481.7	482.1	482.6	482.7	482.4	482.2	482.0	481.7	481.4
130°	507.5	508.0	508.5	508.9	509.3	509.6	509.6	509.6	509.6	509.6	509.3
132.5°	534.8	535.2	535.6	535.8	536.2	536.3	536.2	536.1	535.9	535.8	535.5
135°	571.0	571.9	572.8	573.7	574.7	575.2	575.2	575.2	575.2	575.2	574.8
137.5°	610.3	610.7	611.1	611.5	612.0	612.3	612.6	612.9	613.1	613.3	613.0
140°	636.5	636.8	637.1	637.4	637.8	637.8	637.8	637.8	637.8	637.8	637.8
142.5°	660.5	660.8	661.1	661.4	661.7	661.8	661.6	661.6	661.4	661.3	661.3
145°	693.7	694.3	694.9	695.5	696.2	696.5	696.7	696.8	697.0	697.1	697.0
147.5°	726.6	727.3	728.0	728.8	729.5	729.9	729.7	729.6	729.4	729.3	729.2
150°	746.6	747.3	747.9	748.5	749.1	749.4	749.4	749.4	749.4	749.4	749.4
152.5°	765.6	766.0	766.3	766.7	767.0	767.3	767.4	767.6	767.7	767.9	768.2
155°	794.7	794.7	794.7	794.7	794.7	794.6	794.5	794.3	794.2	794.1	794.6
157.5°	819.3	818.9	818.7	818.4	818.1	818.0	818.0	818.0	817.9	817.9	818.3
160°	833.7	833.6	833.5	833.3	833.1	832.9	832.9	832.7	832.5	832.4	832.9
162.5°	847.1	846.8	846.3	846.0	845.5	845.3	845.1	845.0	844.8	844.6	845.5
165°	865.1	864.7	864.2	863.7	863.3	862.9	862.6	862.3	861.9	861.7	862.6
167.5°	879.0	878.2	877.6	877.0	876.4	876.0	876.0	876.1	876.1	876.1	877.1
170°	886.7	886.0	885.2	884.4	883.7	883.3	883.5	883.7	883.8	884.0	884.8
172.5°	892.3	891.7	891.0	890.4	889.7	889.4	889.5	889.5	889.5	889.6	890.6
175°	900.0	899.2	898.4	897.7	896.9	896.4	896.3	896.1	896.0	895.8	896.9
177.5°	902.5	901.9	901.3	900.6	900.0	899.7	899.7	899.7	899.7	899.7	900.5
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332695-940

CATALOG NUMBER: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	30.8	30.9	31.1	31.3	31.3	31.4	31.5	31.5
90°	17.2	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	28.7	29.2	29.9	30.2	30.4	30.6	30.8	30.9
95°	53.9	54.4	54.8	55.1	55.1	55.1	55.1	55.1
97.5°	84.9	85.4	86.1	86.3	86.3	86.3	86.3	86.3
100°	107.3	107.6	107.9	108.1	108.1	108.1	108.1	108.1
102.5°	131.0	131.3	131.8	132.1	132.2	132.3	132.5	132.6
105°	166.8	167.3	167.7	168.3	168.7	169.2	169.6	170.1
107.5°	205.7	206.1	206.5	206.8	206.7	206.7	206.7	206.6
110°	231.5	231.2	230.9	231.0	231.5	231.9	232.4	232.8





TEST NUMBER: P332695-940

CATALOG NUMBER: SA4XXDIP-C1195D810U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	259.3	259.3	259.2	259.2	259.3	259.4	259.5	259.6
115°	302.2	302.1	301.9	301.8	301.7	301.5	301.3	301.1
117.5°	343.5	343.0	342.4	342.0	341.7	341.3	341.1	340.7
120°	371.4	370.6	369.9	369.6	370.0	370.2	370.6	370.9
122.5°	399.8	399.3	398.8	398.2	397.6	397.1	396.5	396.0
125°	441.4	441.0	440.8	440.4	440.1	439.8	439.5	439.2
127.5°	481.1	480.8	480.5	480.2	479.9	479.7	479.5	479.2
130°	509.0	508.6	508.4	507.9	507.3	506.7	506.0	505.4
132.5°	535.2	534.8	534.6	534.3	534.0	533.8	533.5	533.3
135°	574.5	574.2	573.9	573.5	573.0	572.6	572.1	571.7
137.5°	612.5	612.2	611.7	611.5	611.6	611.7	611.8	612.0
140°	637.6	637.4	637.2	637.1	636.9	636.8	636.6	636.5
142.5°	661.2	661.2	661.2	661.1	661.1	661.1	661.0	661.0
145°	696.8	696.7	696.5	696.2	695.7	695.3	694.8	694.4
147.5°	729.1	729.0	728.8	728.7	728.5	728.3	728.3	728.1
150°	749.4	749.4	749.4	749.3	749.2	749.0	748.9	748.7
152.5°	768.6	768.9	769.3	769.3	768.9	768.5	768.1	767.7
155°	795.2	795.9	796.5	796.5	795.9	795.2	794.6	794.1
157.5°	818.8	819.3	819.7	819.7	819.2	818.7	818.1	817.6
160°	833.3	833.7	834.2	834.1	833.3	832.5	831.8	831.0
162.5°	846.3	847.1	848.0	848.0	847.2	846.5	845.7	844.9
165°	863.5	864.4	865.4	865.5	864.9	864.2	863.6	863.1
167.5°	878.0	879.0	879.9	879.9	878.9	877.9	877.0	876.0
170°	885.8	886.7	887.7	887.6	886.5	885.5	884.3	883.2
172.5°	891.6	892.7	893.8	893.8	892.7	891.5	890.5	889.4
175°	898.0	899.0	900.2	900.2	899.0	898.0	896.9	895.8
177.5°	901.4	902.3	903.2	903.1	902.1	901.2	900.2	899.1
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3

(END OF REPORT)