

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921274

Luminaire Tested: DFN2DIP-4P3F0-020D030US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921274
REPORT IS A COMBINATION OF REPORTS P899039 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US940-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4133.1 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921274

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921274

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	791	791	791
5°	792	779	785
10°	785	768	774
15°	773	755	757
20°	757	737	740
25°	741	715	720
30°	721	695	695
35°	702	672	668
40°	678	648	643
45°	655	624	617
50°	630	599	587
55°	603	570	559
60°	573	535	527
65°	540	500	490
70°	498	456	449
75°	440	404	411
80°	370	337	340
85°	260	223	223

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 851 cd/sqm

TEST NUMBER: P921274

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	1.6
10°-20°	183.8	4.4
20°-30°	270.1	6.5
30°-40°	313.7	7.6
40°-50°	313.3	7.6
50°-60°	273.2	6.6
60°-70°	201.9	4.9
70°-80°	114.2	2.8
80°-90°	32.6	0.8
90°-100°	52.3	1.3
100°-110°	166.3	4.0
110°-120°	284.7	6.9
120°-130°	374.4	9.1
130°-140°	420.2	10.2
140°-150°	412.1	10.0
150°-160°	345.7	8.4
160°-170°	229.2	5.5
170°-180°	80.1	1.9
0°-30°	519.1	12.6
0°-40°	832.8	20.1
0°-60°	1419.3	34.3
0°-90°	1768.0	42.8
90°-120°	503.4	12.2
90°-150°	1710.0	41.4
90°-180°	2365.0	57.2
0°-180°	4133.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	694	691	684	689	688	66
15°	661	657	648	651	647	186
25°	598	592	581	582	581	275
35°	516	509	498	494	491	322
45°	420	415	405	398	395	324
55°	318	314	306	298	294	284
65°	214	210	204	198	194	212
75°	112	111	107	103	105	120
85°	27	27	26	24	23	30
90°	1	9	25	24	24	4
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	

TEST NUMBER: P921274

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	693.9	693.9	693.9	693.9	693.9
2.5°	697.9	694.6	687.2	693.9	692.7
5°	693.9	691.3	683.9	689.3	688.0
7.5°	689.3	685.3	678.0	683.3	682.0
10°	682.0	677.3	669.3	674.6	672.6
12.5°	671.9	668.0	660.0	663.3	661.9
15°	660.6	656.7	647.9	650.6	647.3
17.5°	646.6	642.7	633.9	637.2	633.9
20°	631.2	627.2	617.9	619.9	617.2
22.5°	615.9	609.9	601.2	601.2	599.9
25°	597.9	592.5	581.2	582.5	581.2
27.5°	577.8	573.2	564.5	562.6	559.2
30°	557.9	552.5	542.5	540.6	537.8
32.5°	536.5	532.5	521.8	517.8	515.1
35°	515.9	509.2	498.5	494.5	491.1
37.5°	492.5	486.4	475.7	471.1	467.7
40°	468.4	463.1	452.4	446.5	443.7
42.5°	445.1	439.7	429.1	422.4	418.4
45°	419.7	415.1	405.0	397.7	395.0
47.5°	395.0	390.4	379.7	372.3	368.4
50°	369.0	365.7	356.3	347.0	343.7
52.5°	343.7	338.9	330.3	323.0	318.3
55°	317.6	313.6	305.6	297.7	294.3
57.5°	291.6	288.3	279.6	271.6	268.9
60°	265.6	263.0	253.6	246.2	244.2
62.5°	240.2	235.5	228.9	222.2	219.5
65°	214.2	210.2	203.6	197.5	194.2
67.5°	187.5	184.1	178.2	173.5	170.9
70°	162.8	160.2	154.1	149.5	146.9
72.5°	137.5	134.8	131.4	126.8	124.8
75°	112.1	110.8	107.4	103.4	104.8
77.5°	89.4	86.8	85.3	83.4	81.4
80°	66.8	66.1	64.7	62.7	61.3
82.5°	45.4	45.4	44.8	42.1	42.1
85°	27.3	26.7	26.0	24.0	23.4
87.5°	12.0	10.7	9.4	7.4	6.7
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9

TEST NUMBER: P921274

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1

TEST NUMBER: P921274

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.71	6.51	6.73	7.54	8.91	5.27	6.07	6.29	7.10	8.47
	3H	7.37	8.08	8.39	9.12	10.51	6.88	7.59	7.90	8.63	10.02
	4H	7.95	8.63	8.99	9.66	11.06	7.45	8.13	8.49	9.17	10.57
	6H	8.34	8.97	9.39	10.01	11.42	7.84	8.47	8.89	9.51	10.92
	8H	8.44	9.04	9.50	10.10	11.50	7.94	8.54	8.99	9.59	11.00
	12H	8.49	9.05	9.55	10.10	11.53	7.98	8.54	9.04	9.60	11.03
4H	2H	6.17	6.84	7.21	7.88	9.28	5.81	6.49	6.86	7.53	8.92
	3H	8.02	8.59	9.07	9.65	11.06	7.61	8.18	8.67	9.24	10.66
	4H	8.73	9.25	9.79	10.30	11.74	8.30	8.82	9.36	9.88	11.31
	6H	9.24	9.68	10.30	10.76	12.19	8.80	9.25	9.87	10.33	11.76
	8H	9.38	9.80	10.45	10.87	12.31	8.94	9.36	10.01	10.43	11.88
	12H	9.45	9.83	10.54	10.91	12.36	9.00	9.38	10.09	10.46	11.91
8H	4H	8.91	9.33	9.98	10.40	11.85	8.54	8.96	9.61	10.03	11.47
	6H	9.54	9.88	10.63	11.00	12.44	9.15	9.50	10.25	10.61	12.05
	8H	9.76	10.06	10.86	11.15	12.61	9.36	9.66	10.46	10.76	12.22
	12H	9.88	10.15	10.98	11.24	12.74	9.47	9.74	10.57	10.83	12.33
12H	4H	8.90	9.27	9.98	10.36	11.81	8.53	8.91	9.62	9.99	11.44
	6H	9.57	9.87	10.67	10.97	12.43	9.19	9.50	10.29	10.59	12.05
	8H	9.80	10.07	10.90	11.16	12.66	9.42	9.69	10.52	10.78	12.28