

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332525-940

Luminaire Tested: **SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332525-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4649.7 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332525-940
CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332525-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	33	32	31	24				
2	85	78	72	67	76	70	65	60	55	51	48	41	39	37	29	27	26	20				
3	77	68	61	55	69	61	55	50	48	44	41	36	34	31	25	24	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15				
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	17	13				
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	15	11				
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	15	13	10				
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9				
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8				
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4252	4252	4252
5°	4265	4214	4245
10°	4238	4180	4200
15°	4187	4120	4131
20°	4119	4046	4050
25°	4041	3963	3951
30°	3947	3864	3828
35°	3847	3761	3710
40°	3744	3643	3577
45°	3639	3528	3460
50°	3520	3425	3318
55°	3392	3291	3184
60°	3265	3142	3047
65°	3121	2999	2879
70°	2960	2809	2700
75°	2711	2583	2514
80°	2413	2315	2255
85°	2112	2029	1991



TEST NUMBER: P332525-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	1.1
10°-20°	139.8	3.0
20°-30°	205.7	4.4
30°-40°	239.2	5.1
40°-50°	239.2	5.1
50°-60°	209.2	4.5
60°-70°	155.4	3.3
70°-80°	88.3	1.9
80°-90°	28.0	0.6
90°-100°	327.3	7.0
100°-110°	681.1	14.6
110°-120°	610.1	13.1
120°-130°	513.2	11.0
130°-140°	427.9	9.2
140°-150°	326.9	7.0
150°-160°	229.8	4.9
160°-170°	135.2	2.9
170°-180°	44.0	0.9
0°-30°	395.1	8.5
0°-40°	634.2	13.6
0°-60°	1082.6	23.3
0°-90°	1354.2	29.1
90°-120°	1618.5	34.8
90°-150°	2886.5	62.1
90°-180°	3295.0	70.9
0°-180°	4649.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	524	50
15°	501	499	493	495	494	141
25°	454	451	445	445	444	209
35°	390	387	382	379	376	244
45°	319	316	309	305	303	246
55°	241	240	234	229	226	216
65°	163	161	157	153	151	162
75°	87	85	83	81	81	92
85°	23	23	22	22	22	25
90°	1	7	16	18	19	3
95°	29	93	726	359	217	33
105°	104	151	584	1257	1252	111
115°	183	230	521	1001	1203	182
125°	256	304	518	851	960	227
135°	304	361	514	756	858	235
145°	350	401	511	637	701	220
155°	398	430	497	563	587	183
165°	434	447	476	504	512	122
175°	452	453	457	463	461	43
180°	453	453	453	453	453	



TEST NUMBER: P332525-940
 CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	528.1	527.9	527.6	527.4	527.2	526.6	525.8	525.0	524.2	523.3	524.1
5°	526.3	525.9	525.6	525.2	524.9	524.1	523.1	522.1	521.0	520.0	521.0
7.5°	521.5	521.0	520.7	520.3	520.0	519.2	518.0	516.9	515.8	514.6	515.4
10°	517.0	516.7	516.3	515.9	515.6	514.8	513.5	512.3	511.1	509.9	510.6
12.5°	511.3	511.0	510.6	510.1	509.8	509.0	507.7	506.4	505.1	503.8	504.6
15°	501.0	500.6	500.2	499.9	499.5	498.6	497.2	495.8	494.4	493.0	493.6
17.5°	488.6	488.1	487.7	487.2	486.7	485.8	484.5	483.1	481.8	480.5	480.8
20°	479.5	479.0	478.6	478.0	477.6	476.7	475.3	473.9	472.4	471.0	471.4
22.5°	469.7	469.0	468.4	467.8	467.2	466.2	464.8	463.4	462.0	460.6	461.1
25°	453.7	453.1	452.5	451.7	451.1	450.1	448.8	447.5	446.2	444.9	445.0
27.5°	435.5	434.8	434.2	433.5	432.8	431.9	430.6	429.4	428.2	427.0	426.8
30°	423.4	422.6	421.9	421.1	420.4	419.4	418.1	416.9	415.7	414.5	414.1
32.5°	410.5	409.8	409.1	408.5	407.8	406.8	405.6	404.2	403.0	401.6	401.2
35°	390.4	389.8	389.1	388.4	387.8	386.8	385.5	384.1	382.9	381.6	380.9
37.5°	369.3	368.6	368.0	367.5	366.8	365.9	364.4	363.0	361.6	360.2	359.4
40°	355.3	354.6	353.9	353.1	352.4	351.3	349.9	348.5	347.1	345.7	344.7
42.5°	340.5	340.1	339.7	339.2	338.8	337.7	336.2	334.6	333.1	331.5	330.4
45°	318.7	318.0	317.4	316.7	316.0	315.0	313.4	311.9	310.5	309.0	307.9
47.5°	295.8	295.3	294.9	294.4	294.0	293.1	291.7	290.3	288.9	287.5	286.3
50°	280.3	279.9	279.6	279.1	278.7	277.9	276.6	275.3	273.9	272.7	271.3
52.5°	265.1	264.6	264.1	263.7	263.2	262.3	260.9	259.6	258.2	256.8	255.7
55°	241.0	240.8	240.4	240.1	239.9	239.1	237.7	236.5	235.1	233.8	232.7
57.5°	218.0	217.8	217.4	217.1	216.8	216.0	214.6	213.4	212.0	210.8	209.7
60°	202.2	201.7	201.3	200.7	200.3	199.5	198.2	197.0	195.8	194.6	193.8
62.5°	186.6	186.3	185.8	185.5	185.0	184.2	182.9	181.6	180.3	179.1	178.3
65°	163.4	162.9	162.4	161.9	161.5	160.8	159.8	158.9	157.9	157.0	156.0
67.5°	139.9	139.5	139.0	138.6	138.1	137.5	136.6	135.7	134.8	133.8	133.0
70°	125.4	124.7	124.0	123.4	122.7	122.0	121.3	120.6	119.8	119.0	118.2
72.5°	109.9	109.1	108.5	107.9	107.2	106.6	105.9	105.4	104.8	104.2	103.5
75°	86.9	86.5	86.1	85.5	85.1	84.6	84.2	83.6	83.2	82.8	82.4
77.5°	65.1	64.9	64.6	64.5	64.3	63.9	63.6	63.1	62.7	62.3	62.2
80°	51.9	51.6	51.4	51.1	50.8	50.6	50.4	50.2	50.0	49.8	49.6
82.5°	39.1	39.0	38.8	38.7	38.5	38.4	38.4	38.4	38.3	38.3	38.3
85°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.3	22.1	21.9	21.9
87.5°	8.9	9.3	9.7	9.8	9.9	9.8	10.8	10.8	11.1	11.3	11.1
90°	0.9	2.7	5.4	6.2	7.1	7.1	12.5	12.5	14.3	16.1	15.2
92.5°	10.2	14.8	23.2	34.0	47.0	65.5	110.8	179.9	247.1	282.4	235.2
95°	29.3	32.0	40.9	52.5	73.9	111.3	188.7	334.7	547.5	725.5	746.0
97.5°	52.7	52.7	60.4	71.1	89.3	120.7	180.4	300.9	512.4	764.1	937.2
100°	67.7	67.7	73.9	84.5	101.5	130.0	182.5	283.1	464.7	715.7	943.6
102.5°	81.9	83.3	88.8	98.8	115.0	142.0	189.6	278.1	432.7	655.2	890.2
105°	104.2	106.8	111.3	122.0	137.9	163.8	206.5	280.4	405.0	584.0	793.2
107.5°	128.8	130.5	134.9	146.3	161.7	187.1	226.3	293.6	400.0	544.1	714.8
110°	145.1	146.9	151.3	162.0	178.1	202.1	241.2	303.5	401.4	530.6	675.6



TEST NUMBER: P332525-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.8	162.6	167.7	177.7	193.7	217.8	255.5	314.2	405.7	524.1	653.6
115°	183.4	186.0	192.3	201.2	218.1	242.1	277.8	331.2	413.9	520.8	632.9
117.5°	206.9	209.4	214.9	224.7	240.5	265.5	299.3	348.4	422.7	519.9	623.7
120°	222.6	224.4	230.6	240.3	255.5	280.4	314.2	360.5	429.1	519.9	618.7
122.5°	236.8	238.5	244.8	253.9	270.5	294.6	328.5	371.9	435.5	519.2	613.0
125°	255.5	259.0	264.4	274.2	291.1	316.0	348.0	389.1	445.1	518.1	603.6
127.5°	272.1	274.9	281.3	292.5	310.1	335.3	366.2	403.8	452.7	516.1	590.9
130°	281.3	284.9	291.9	305.3	322.3	348.0	378.4	413.0	458.4	515.4	583.1
132.5°	290.5	293.4	302.6	315.3	333.7	358.0	388.3	422.3	463.4	514.7	576.0
135°	303.5	307.1	316.0	331.2	349.8	373.0	402.3	434.4	470.9	513.6	565.3
137.5°	316.6	319.9	329.8	344.1	363.6	385.7	413.0	443.0	475.4	513.4	556.0
140°	325.8	328.5	338.3	353.4	372.1	393.5	420.2	448.6	478.9	512.7	551.1
142.5°	335.8	338.5	347.5	361.9	380.0	400.6	426.6	452.9	481.8	512.7	546.8
145°	349.8	352.5	361.4	373.9	390.8	410.4	433.5	457.5	483.4	511.0	539.5
147.5°	365.7	366.6	374.4	387.3	401.3	418.9	440.7	461.6	484.3	507.7	532.9
150°	375.7	376.6	383.7	394.4	407.7	424.6	444.3	463.8	484.3	505.6	527.9
152.5°	385.0	385.1	392.3	402.2	414.1	429.6	447.1	465.2	482.9	502.0	522.2
155°	397.9	398.8	404.1	413.0	422.8	436.2	451.3	466.5	480.7	496.8	513.6
157.5°	410.5	410.5	415.5	422.5	431.1	441.6	454.3	466.5	478.4	491.2	504.9
160°	418.4	418.4	422.0	428.2	435.3	445.1	455.8	466.5	476.3	487.0	498.6
162.5°	425.5	424.8	427.7	433.2	439.6	447.3	457.2	466.5	474.1	482.7	492.8
165°	433.5	433.5	435.3	439.8	444.3	449.5	457.5	464.7	470.0	476.3	483.4
167.5°	441.6	440.7	441.6	445.0	447.5	451.5	457.4	462.5	465.7	469.8	474.8
170°	445.1	444.3	445.1	447.8	449.5	452.2	456.6	461.1	462.9	465.6	469.1
172.5°	448.6	447.8	447.9	449.9	450.9	452.9	455.9	459.7	460.0	461.3	464.1
175°	452.2	451.3	451.3	452.2	453.1	453.1	454.9	457.5	456.6	456.6	458.4
177.5°	453.8	453.1	452.4	453.1	453.1	453.1	453.8	455.2	453.8	453.8	454.5
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332525-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	524.9	525.7	526.4	526.7	526.6	526.6	526.5	526.4
5°	522.1	523.1	524.1	524.5	524.3	524.1	524.0	523.8
7.5°	516.2	517.1	517.9	518.3	518.2	518.0	517.9	517.8
10°	511.4	512.1	512.9	513.2	513.0	512.7	512.6	512.4
12.5°	505.4	506.2	507.1	507.4	507.1	506.8	506.6	506.3
15°	494.1	494.6	495.3	495.3	495.1	494.8	494.5	494.3
17.5°	481.2	481.5	481.9	482.0	481.8	481.6	481.4	481.3
20°	471.6	471.9	472.2	472.3	472.0	471.8	471.6	471.4
22.5°	461.5	462.1	462.6	462.7	462.4	462.0	461.6	461.4
25°	445.1	445.1	445.2	445.1	444.7	444.3	444.0	443.6
27.5°	426.5	426.3	426.1	425.7	425.3	424.8	424.3	423.8
30°	413.8	413.4	413.0	412.6	412.1	411.6	411.2	410.7
32.5°	400.7	400.3	399.8	399.4	399.0	398.4	398.0	397.5
35°	380.2	379.6	378.9	378.4	377.9	377.5	376.9	376.5
37.5°	358.7	358.0	357.3	356.7	356.1	355.4	354.8	354.2
40°	343.8	342.9	342.0	341.3	340.7	340.3	339.8	339.4
42.5°	329.3	328.2	327.2	326.5	326.1	325.8	325.5	325.2
45°	306.9	305.9	304.9	304.2	303.9	303.6	303.4	303.1
47.5°	285.2	284.0	282.9	282.0	281.2	280.5	279.8	279.1
50°	270.0	268.8	267.4	266.4	265.9	265.4	264.7	264.2
52.5°	254.5	253.3	252.2	251.2	250.5	249.8	249.1	248.3
55°	231.6	230.4	229.3	228.5	227.9	227.4	226.8	226.2
57.5°	208.7	207.6	206.5	205.7	205.2	204.6	204.1	203.5
60°	192.9	192.1	191.2	190.6	190.1	189.6	189.1	188.7
62.5°	177.5	176.7	175.9	175.3	174.9	174.4	174.0	173.4
65°	155.2	154.2	153.3	152.6	152.1	151.6	151.1	150.7
67.5°	132.1	131.2	130.3	129.7	129.7	129.5	129.4	129.2
70°	117.5	116.8	116.0	115.5	115.2	114.9	114.7	114.4
72.5°	103.0	102.4	101.7	101.3	101.0	100.8	100.5	100.2
75°	81.9	81.6	81.2	81.0	80.9	80.8	80.7	80.6
77.5°	62.1	62.0	61.9	61.7	61.4	61.2	60.9	60.7
80°	49.4	49.2	49.0	49.0	48.8	48.7	48.6	48.5
82.5°	38.1	38.0	37.9	37.8	37.7	37.5	37.5	37.4
85°	21.9	21.9	21.9	21.9	21.8	21.8	21.6	21.5
87.5°	11.3	11.5	11.7	11.7	11.9	12.0	11.9	11.9
90°	16.1	16.9	17.8	17.8	18.7	19.6	18.7	18.7
92.5°	174.9	131.6	104.7	86.9	76.4	71.6	68.6	68.6
95°	659.6	521.7	402.3	316.0	272.4	244.8	228.8	217.2
97.5°	974.6	923.3	836.2	743.3	679.4	625.8	599.1	580.6
100°	1073.6	1091.4	1047.8	981.9	904.5	850.2	823.4	816.4
102.5°	1068.6	1156.9	1169.6	1142.1	1094.6	1055.3	1027.2	1021.5
105°	997.0	1151.0	1239.1	1275.7	1277.5	1270.3	1257.8	1252.5
107.5°	895.4	1059.4	1183.5	1262.8	1306.8	1327.1	1336.1	1338.4
110°	834.1	988.1	1117.2	1215.1	1278.4	1315.7	1331.8	1339.8



TEST NUMBER: P332525-940

CATALOG NUMBER: SA4XXDIP-C350D1035U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	789.3	925.4	1047.4	1145.3	1217.1	1262.3	1284.8	1297.7
115°	744.2	853.7	957.9	1043.3	1113.7	1167.1	1195.5	1202.7
117.5°	722.1	812.8	894.7	967.1	1027.2	1072.0	1100.8	1106.3
120°	712.1	795.0	866.2	929.3	980.1	1019.3	1042.4	1052.2
122.5°	703.6	783.5	848.4	903.7	946.6	980.1	999.7	1009.5
125°	689.0	765.5	827.0	875.9	911.6	937.4	954.3	959.7
127.5°	671.2	744.4	805.7	852.1	887.9	910.9	925.1	930.4
130°	657.0	727.3	787.8	835.0	871.5	893.8	908.0	913.4
132.5°	642.0	708.1	767.1	814.4	850.2	875.2	888.8	894.1
135°	621.3	679.2	733.5	778.0	813.7	838.6	852.8	858.2
137.5°	602.7	651.7	697.4	737.6	770.9	795.5	807.3	813.7
140°	592.0	633.8	673.9	711.2	742.4	762.1	774.5	781.6
142.5°	582.0	618.8	653.3	685.6	713.2	731.4	742.4	747.4
145°	567.9	598.2	624.9	649.9	672.1	687.2	696.2	700.6
147.5°	556.3	580.4	601.8	621.3	637.8	650.8	657.5	659.1
150°	549.3	569.7	587.5	603.6	617.8	629.4	634.7	635.6
152.5°	541.4	559.0	575.4	588.6	600.7	610.1	613.3	614.2
155°	529.7	543.9	557.2	567.9	576.8	584.0	586.7	586.7
157.5°	517.0	529.0	540.2	548.8	555.4	560.8	562.4	562.4
160°	509.2	519.0	528.8	535.9	541.3	546.6	547.5	547.5
162.5°	501.3	509.7	517.4	523.8	527.7	533.1	534.0	533.2
165°	490.5	495.9	502.0	506.5	510.1	513.6	512.7	511.8
167.5°	480.0	484.1	489.1	491.8	493.6	495.9	495.7	495.0
170°	473.6	476.3	479.8	482.5	484.3	485.2	484.3	484.3
172.5°	467.9	469.8	472.0	473.9	475.0	475.9	475.0	473.6
175°	460.2	461.1	462.9	462.9	462.9	464.7	462.9	461.1
177.5°	455.2	455.9	455.9	456.6	455.9	456.6	455.2	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1

(END OF REPORT)