

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921275

Luminaire Tested: DFN2DIP-4P3F0-020D030US940-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921275
REPORT IS A COMBINATION OF REPORTS P900559 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US940-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4414.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921275
CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P921275
 CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	791	791	791
5°	792	779	785
10°	785	768	774
15°	773	755	757
20°	757	737	740
25°	741	715	720
30°	721	695	695
35°	702	672	668
40°	678	648	643
45°	655	624	617
50°	630	599	587
55°	603	570	559
60°	573	535	527
65°	540	500	490
70°	498	456	449
75°	440	404	411
80°	370	337	340
85°	260	223	223

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 655 cd/sqm



TEST NUMBER: P921275

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	1.5
10°-20°	183.8	4.2
20°-30°	270.1	6.1
30°-40°	313.7	7.1
40°-50°	313.3	7.1
50°-60°	273.2	6.2
60°-70°	201.9	4.6
70°-80°	114.2	2.6
80°-90°	31.8	0.7
90°-100°	29.8	0.7
100°-110°	111.0	2.5
110°-120°	294.3	6.7
120°-130°	488.2	11.1
130°-140°	518.5	11.7
140°-150°	481.9	10.9
150°-160°	387.5	8.8
160°-170°	249.7	5.7
170°-180°	85.9	1.9
0°-30°	519.1	11.8
0°-40°	832.8	18.9
0°-60°	1419.3	32.2
0°-90°	1767.2	40.0
90°-120°	435.1	9.9
90°-150°	1923.7	43.6
90°-180°	2647.0	60.0
0°-180°	4414.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	694	691	684	689	688	66
15°	661	657	648	651	647	186
25°	598	592	581	582	581	275
35°	516	509	498	494	491	322
45°	420	415	405	398	395	324
55°	318	314	306	298	294	284
65°	214	210	204	198	194	212
75°	112	111	107	103	105	120
85°	27	27	26	24	23	30
90°	1	8	13	16	18	4
95°	42	21	25	29	28	50
105°	199	218	40	47	50	212
115°	376	387	403	101	54	370
125°	531	540	552	557	559	474
135°	657	668	674	680	679	508
145°	762	762	773	777	774	477
155°	840	834	841	845	840	387
165°	884	881	883	887	883	250
175°	905	900	902	906	900	86
180°	903	903	903	903	903	



TEST NUMBER: P921275

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	693.9	693.9	693.9	693.9	693.9
2.5°	697.9	694.6	687.2	693.9	692.7
5°	693.9	691.3	683.9	689.3	688.0
7.5°	689.3	685.3	678.0	683.3	682.0
10°	682.0	677.3	669.3	674.6	672.6
12.5°	671.9	668.0	660.0	663.3	661.9
15°	660.6	656.7	647.9	650.6	647.3
17.5°	646.6	642.7	633.9	637.2	633.9
20°	631.2	627.2	617.9	619.9	617.2
22.5°	615.9	609.9	601.2	601.2	599.9
25°	597.9	592.5	581.2	582.5	581.2
27.5°	577.8	573.2	564.5	562.6	559.2
30°	557.9	552.5	542.5	540.6	537.8
32.5°	536.5	532.5	521.8	517.8	515.1
35°	515.9	509.2	498.5	494.5	491.1
37.5°	492.5	486.4	475.7	471.1	467.7
40°	468.4	463.1	452.4	446.5	443.7
42.5°	445.1	439.7	429.1	422.4	418.4
45°	419.7	415.1	405.0	397.7	395.0
47.5°	395.0	390.4	379.7	372.3	368.4
50°	369.0	365.7	356.3	347.0	343.7
52.5°	343.7	338.9	330.3	323.0	318.3
55°	317.6	313.6	305.6	297.7	294.3
57.5°	291.6	288.3	279.6	271.6	268.9
60°	265.6	263.0	253.6	246.2	244.2
62.5°	240.2	235.5	228.9	222.2	219.5
65°	214.2	210.2	203.6	197.5	194.2
67.5°	187.5	184.1	178.2	173.5	170.9
70°	162.8	160.2	154.1	149.5	146.9
72.5°	137.5	134.8	131.4	126.8	124.8
75°	112.1	110.8	107.4	103.4	104.8
77.5°	89.4	86.8	85.3	83.4	81.4
80°	66.8	66.1	64.7	62.7	61.3
82.5°	45.4	45.4	44.8	42.1	42.1
85°	27.3	26.7	26.0	24.0	23.4
87.5°	12.0	10.7	9.4	7.4	6.7
90°	0.6	7.8	13.0	16.4	17.6
92.5°	16.4	13.7	15.7	17.0	17.6
95°	42.4	20.9	25.4	28.8	28.1
97.5°	76.4	22.9	33.3	35.3	35.9
100°	115.7	26.1	37.3	42.4	43.8
102.5°	158.7	157.5	38.5	45.7	47.7
105°	198.6	218.2	39.9	47.0	49.7
107.5°	245.0	261.3	41.2	48.3	51.0
110°	289.4	303.1	114.3	49.0	51.6



TEST NUMBER: P921275

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.3	343.0	331.9	50.3	52.3
115°	375.6	386.7	403.1	100.6	53.6
117.5°	414.2	427.2	438.4	344.9	173.8
120°	457.3	467.1	478.8	486.7	398.5
122.5°	493.8	504.4	517.5	521.3	522.0
125°	531.1	539.6	552.1	556.6	558.6
127.5°	565.1	574.2	584.1	590.6	591.2
130°	597.1	607.6	614.7	621.9	621.3
132.5°	629.7	638.3	645.4	651.3	650.7
135°	657.2	667.7	673.5	680.1	678.8
137.5°	685.9	693.8	700.3	706.9	704.9
140°	714.0	719.3	726.4	732.3	729.1
142.5°	737.6	742.2	750.6	755.8	752.6
145°	762.4	761.7	772.8	777.4	774.1
147.5°	783.9	781.9	793.1	796.3	793.7
150°	804.9	800.3	810.7	814.6	811.4
152.5°	822.4	817.3	827.1	831.0	826.4
155°	839.5	833.7	841.4	845.3	840.2
157.5°	853.2	848.0	853.9	858.4	853.2
160°	865.0	861.0	865.0	868.9	864.2
162.5°	875.4	871.5	874.8	879.3	873.4
165°	884.5	880.7	882.6	887.2	882.6
167.5°	891.7	887.8	889.7	894.4	888.5
170°	897.6	893.7	895.0	899.6	893.7
172.5°	901.5	897.6	898.9	903.5	897.6
175°	904.7	900.2	901.5	906.1	899.6
177.5°	906.1	901.5	902.2	906.8	900.9
180°	902.9	902.9	902.9	902.9	902.9



TEST NUMBER: P921275
 CATALOG NUMBER: DFN2DIP-4P3F0-020D030US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.43	6.20	6.46	7.25	8.66	4.98	5.76	6.02	6.80	8.21
	3H	7.08	7.77	8.12	8.83	10.25	6.59	7.28	7.63	8.34	9.76
	4H	7.66	8.32	8.72	9.37	10.81	7.16	7.82	8.22	8.88	10.31
	6H	8.05	8.66	9.12	9.72	11.16	7.55	8.16	8.62	9.22	10.66
	8H	8.15	8.73	9.22	9.80	11.24	7.65	8.23	8.72	9.30	10.74
	12H	8.19	8.74	9.27	9.81	11.28	7.68	8.23	8.76	9.30	10.77
4H	2H	5.87	6.54	6.94	7.59	9.02	5.52	6.18	6.59	7.24	8.67
	3H	7.73	8.28	8.80	9.36	10.81	7.32	7.87	8.39	8.95	10.40
	4H	8.43	8.94	9.51	10.01	11.48	8.01	8.52	9.09	9.59	11.06
	6H	8.94	9.37	10.03	10.47	11.93	8.51	8.94	9.60	10.04	11.50
	8H	9.09	9.49	10.17	10.58	12.06	8.65	9.05	9.74	10.14	11.62
	12H	9.15	9.52	10.26	10.62	12.10	8.70	9.07	9.81	10.17	11.65
8H	4H	8.62	9.02	9.71	10.11	11.59	8.24	8.65	9.33	9.74	11.21
	6H	9.24	9.58	10.35	10.71	12.18	8.86	9.19	9.97	10.32	11.80
	8H	9.46	9.75	10.58	10.86	12.36	9.06	9.36	10.18	10.47	11.97
	12H	9.58	9.84	10.70	10.95	12.48	9.17	9.43	10.29	10.54	12.07
12H	4H	8.60	8.97	9.71	10.07	11.55	8.23	8.60	9.34	9.70	11.18
	6H	9.27	9.56	10.39	10.68	12.17	8.90	9.19	10.01	10.30	11.80
	8H	9.50	9.76	10.62	10.87	12.40	9.12	9.38	10.24	10.49	12.02