

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332516-940

Luminaire Tested: **SA4XXDIP-C350D810U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332516-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3934.8 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332516-940  
CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332516-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34				34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29				29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24				24
3	78	69	62	56	70	63	56	52	50	46	42	39	36	34	29	27	25	20				20
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	26	23	22	18				18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15				15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	18	17	13				13
7	56	44	36	31	50	40	33	28	32	27	24	26	22	19	19	17	15	12				12
8	52	40	32	27	46	36	29	25	30	24	21	23	20	17	18	15	13	11				11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10				10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9				9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4252	4252	4252
5°	4265	4214	4245
10°	4238	4180	4200
15°	4187	4120	4131
20°	4119	4046	4050
25°	4041	3963	3951
30°	3947	3864	3828
35°	3847	3761	3710
40°	3744	3643	3577
45°	3639	3528	3460
50°	3520	3425	3318
55°	3392	3291	3184
60°	3265	3142	3047
65°	3121	2999	2879
70°	2960	2809	2700
75°	2711	2583	2514
80°	2413	2315	2255
85°	2112	2029	1991



TEST NUMBER: P332516-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.6	1.3
10°-20°	139.8	3.6
20°-30°	205.7	5.2
30°-40°	239.2	6.1
40°-50°	239.2	6.1
50°-60°	209.2	5.3
60°-70°	155.4	3.9
70°-80°	88.3	2.2
80°-90°	27.4	0.7
90°-100°	256.3	6.5
100°-110°	533.5	13.6
110°-120°	477.9	12.1
120°-130°	402.0	10.2
130°-140°	335.1	8.5
140°-150°	256.1	6.5
150°-160°	180.0	4.6
160°-170°	105.9	2.7
170°-180°	34.4	0.9
0°-30°	395.1	10.0
0°-40°	634.2	16.1
0°-60°	1082.6	27.5
0°-90°	1353.7	34.4
90°-120°	1267.7	32.2
90°-150°	2260.9	57.5
90°-180°	2581.0	65.6
0°-180°	3934.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	524	50
15°	501	499	493	495	494	141
25°	454	451	445	445	444	209
35°	390	387	382	379	376	244
45°	319	316	309	305	303	246
55°	241	240	234	229	226	216
65°	163	161	157	153	151	162
75°	87	85	83	81	81	92
85°	23	23	22	22	22	25
90°	1	6	13	14	15	2
95°	23	72	568	281	170	26
105°	82	118	457	985	981	87
115°	144	180	408	784	942	142
125°	200	238	406	667	752	178
135°	238	283	402	592	672	184
145°	274	314	400	499	549	172
155°	312	336	389	441	460	144
165°	340	350	373	395	401	96
175°	354	355	358	363	361	34
180°	355	355	355	355	355	



TEST NUMBER: P332516-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	528.1	527.9	527.6	527.4	527.2	526.6	525.8	525.0	524.2	523.3	524.1
5°	526.3	525.9	525.6	525.2	524.9	524.1	523.1	522.1	521.0	520.0	521.0
7.5°	521.5	521.0	520.7	520.3	520.0	519.2	518.0	516.9	515.8	514.6	515.4
10°	517.0	516.7	516.3	515.9	515.6	514.8	513.5	512.3	511.1	509.9	510.6
12.5°	511.3	511.0	510.6	510.1	509.8	509.0	507.7	506.4	505.1	503.8	504.6
15°	501.0	500.6	500.2	499.9	499.5	498.6	497.2	495.8	494.4	493.0	493.6
17.5°	488.6	488.1	487.7	487.2	486.7	485.8	484.5	483.1	481.8	480.5	480.8
20°	479.5	479.0	478.6	478.0	477.6	476.7	475.3	473.9	472.4	471.0	471.4
22.5°	469.7	469.0	468.4	467.8	467.2	466.2	464.8	463.4	462.0	460.6	461.1
25°	453.7	453.1	452.5	451.7	451.1	450.1	448.8	447.5	446.2	444.9	445.0
27.5°	435.5	434.8	434.2	433.5	432.8	431.9	430.6	429.4	428.2	427.0	426.8
30°	423.4	422.6	421.9	421.1	420.4	419.4	418.1	416.9	415.7	414.5	414.1
32.5°	410.5	409.8	409.1	408.5	407.8	406.8	405.6	404.2	403.0	401.6	401.2
35°	390.4	389.8	389.1	388.4	387.8	386.8	385.5	384.1	382.9	381.6	380.9
37.5°	369.3	368.6	368.0	367.5	366.8	365.9	364.4	363.0	361.6	360.2	359.4
40°	355.3	354.6	353.9	353.1	352.4	351.3	349.9	348.5	347.1	345.7	344.7
42.5°	340.5	340.1	339.7	339.2	338.8	337.7	336.2	334.6	333.1	331.5	330.4
45°	318.7	318.0	317.4	316.7	316.0	315.0	313.4	311.9	310.5	309.0	307.9
47.5°	295.8	295.3	294.9	294.4	294.0	293.1	291.7	290.3	288.9	287.5	286.3
50°	280.3	279.9	279.6	279.1	278.7	277.9	276.6	275.3	273.9	272.7	271.3
52.5°	265.1	264.6	264.1	263.7	263.2	262.3	260.9	259.6	258.2	256.8	255.7
55°	241.0	240.8	240.4	240.1	239.9	239.1	237.7	236.5	235.1	233.8	232.7
57.5°	218.0	217.8	217.4	217.1	216.8	216.0	214.6	213.4	212.0	210.8	209.7
60°	202.2	201.7	201.3	200.7	200.3	199.5	198.2	197.0	195.8	194.6	193.8
62.5°	186.6	186.3	185.8	185.5	185.0	184.2	182.9	181.6	180.3	179.1	178.3
65°	163.4	162.9	162.4	161.9	161.5	160.8	159.8	158.9	157.9	157.0	156.0
67.5°	139.9	139.5	139.0	138.6	138.1	137.5	136.6	135.7	134.8	133.8	133.0
70°	125.4	124.7	124.0	123.4	122.7	122.0	121.3	120.6	119.8	119.0	118.2
72.5°	109.9	109.1	108.5	107.9	107.2	106.6	105.9	105.4	104.8	104.2	103.5
75°	86.9	86.5	86.1	85.5	85.1	84.6	84.2	83.6	83.2	82.8	82.4
77.5°	65.1	64.9	64.6	64.5	64.3	63.9	63.6	63.1	62.7	62.3	62.2
80°	51.9	51.6	51.4	51.1	50.8	50.6	50.4	50.2	50.0	49.8	49.6
82.5°	39.1	39.0	38.8	38.7	38.5	38.4	38.4	38.4	38.3	38.3	38.3
85°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.3	22.1	21.9	21.9
87.5°	8.9	9.1	9.5	9.5	9.6	9.5	10.3	10.2	10.4	10.6	10.4
90°	0.7	2.1	4.2	4.9	5.6	5.6	9.7	9.7	11.1	12.6	11.9
92.5°	7.9	11.6	18.1	26.7	36.8	51.3	86.8	140.8	193.6	221.1	184.2
95°	23.0	25.1	32.1	41.1	57.9	87.1	147.8	262.2	428.8	568.3	584.3
97.5°	41.3	41.3	47.3	55.6	70.0	94.5	141.2	235.7	401.4	598.5	734.1
100°	53.0	53.0	57.9	66.3	79.5	101.8	142.9	221.8	364.0	560.6	739.0
102.5°	64.1	65.3	69.6	77.4	90.1	111.3	148.5	217.8	338.9	513.2	697.2
105°	81.6	83.6	87.1	95.5	108.1	128.3	161.8	219.6	317.3	457.4	621.3
107.5°	100.9	102.2	105.7	114.6	126.6	146.6	177.3	230.0	313.3	426.1	559.9
110°	113.7	115.0	118.5	126.9	139.5	158.3	189.0	237.7	314.4	415.5	529.2



TEST NUMBER: P332516-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.9	127.3	131.3	139.2	151.7	170.6	200.1	246.1	317.8	410.5	511.9
115°	143.7	145.7	150.6	157.6	170.9	189.7	217.6	259.4	324.2	407.9	495.7
117.5°	162.0	164.0	168.4	176.0	188.4	207.9	234.4	272.9	331.1	407.2	488.5
120°	174.3	175.7	180.6	188.2	200.1	219.6	246.1	282.4	336.1	407.2	484.6
122.5°	185.5	186.9	191.7	198.9	211.8	230.8	257.3	291.3	341.1	406.6	480.1
125°	200.1	202.9	207.1	214.7	228.0	247.5	272.6	304.7	348.7	405.8	472.7
127.5°	213.1	215.3	220.3	229.1	242.9	262.6	286.9	316.3	354.6	404.3	462.8
130°	220.3	223.1	228.7	239.2	252.4	272.6	296.3	323.5	359.1	403.7	456.7
132.5°	227.6	229.8	237.1	247.0	261.4	280.4	304.2	330.7	363.0	403.1	451.1
135°	237.7	240.6	247.5	259.4	274.0	292.1	315.1	340.3	368.8	402.3	442.7
137.5°	248.0	250.6	258.2	269.6	284.7	302.0	323.5	347.0	372.3	402.2	435.5
140°	255.2	257.3	264.9	276.8	291.4	308.2	329.1	351.4	375.1	401.6	431.6
142.5°	263.0	265.1	272.2	283.5	297.6	313.8	334.1	354.7	377.4	401.6	428.3
145°	274.0	276.1	283.1	292.8	306.1	321.5	339.6	358.4	378.6	400.2	422.5
147.5°	286.4	287.1	293.3	303.3	314.3	328.1	345.2	361.6	379.3	397.7	417.4
150°	294.3	295.0	300.5	308.9	319.3	332.6	347.9	363.3	379.3	396.0	413.5
152.5°	301.5	301.7	307.2	315.0	324.4	336.5	350.2	364.4	378.2	393.2	409.0
155°	311.7	312.4	316.6	323.5	331.2	341.6	353.5	365.3	376.5	389.1	402.3
157.5°	321.6	321.6	325.5	330.9	337.6	345.8	355.9	365.3	374.7	384.8	395.5
160°	327.7	327.7	330.5	335.4	341.0	348.7	357.0	365.3	373.0	381.4	390.5
162.5°	333.3	332.7	334.9	339.3	344.3	350.3	358.1	365.3	371.4	378.1	386.0
165°	339.6	339.6	341.0	344.5	347.9	352.1	358.4	364.0	368.2	373.0	378.6
167.5°	345.8	345.2	345.8	348.5	350.4	353.7	358.3	362.3	364.8	368.0	371.9
170°	348.7	347.9	348.7	350.7	352.1	354.2	357.7	361.1	362.6	364.6	367.5
172.5°	351.4	350.7	350.9	352.4	353.2	354.7	357.1	360.1	360.3	361.3	363.6
175°	354.2	353.5	353.5	354.2	354.9	354.9	356.3	358.4	357.7	357.7	359.1
177.5°	355.4	354.9	354.4	354.9	354.9	354.9	355.4	356.6	355.4	355.4	356.0
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9



TEST NUMBER: P332516-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	524.9	525.7	526.4	526.7	526.6	526.6	526.5	526.4
5°	522.1	523.1	524.1	524.5	524.3	524.1	524.0	523.8
7.5°	516.2	517.1	517.9	518.3	518.2	518.0	517.9	517.8
10°	511.4	512.1	512.9	513.2	513.0	512.7	512.6	512.4
12.5°	505.4	506.2	507.1	507.4	507.1	506.8	506.6	506.3
15°	494.1	494.6	495.3	495.3	495.1	494.8	494.5	494.3
17.5°	481.2	481.5	481.9	482.0	481.8	481.6	481.4	481.3
20°	471.6	471.9	472.2	472.3	472.0	471.8	471.6	471.4
22.5°	461.5	462.1	462.6	462.7	462.4	462.0	461.6	461.4
25°	445.1	445.1	445.2	445.1	444.7	444.3	444.0	443.6
27.5°	426.5	426.3	426.1	425.7	425.3	424.8	424.3	423.8
30°	413.8	413.4	413.0	412.6	412.1	411.6	411.2	410.7
32.5°	400.7	400.3	399.8	399.4	399.0	398.4	398.0	397.5
35°	380.2	379.6	378.9	378.4	377.9	377.5	376.9	376.5
37.5°	358.7	358.0	357.3	356.7	356.1	355.4	354.8	354.2
40°	343.8	342.9	342.0	341.3	340.7	340.3	339.8	339.4
42.5°	329.3	328.2	327.2	326.5	326.1	325.8	325.5	325.2
45°	306.9	305.9	304.9	304.2	303.9	303.6	303.4	303.1
47.5°	285.2	284.0	282.9	282.0	281.2	280.5	279.8	279.1
50°	270.0	268.8	267.4	266.4	265.9	265.4	264.7	264.2
52.5°	254.5	253.3	252.2	251.2	250.5	249.8	249.1	248.3
55°	231.6	230.4	229.3	228.5	227.9	227.4	226.8	226.2
57.5°	208.7	207.6	206.5	205.7	205.2	204.6	204.1	203.5
60°	192.9	192.1	191.2	190.6	190.1	189.6	189.1	188.7
62.5°	177.5	176.7	175.9	175.3	174.9	174.4	174.0	173.4
65°	155.2	154.2	153.3	152.6	152.1	151.6	151.1	150.7
67.5°	132.1	131.2	130.3	129.7	129.7	129.5	129.4	129.2
70°	117.5	116.8	116.0	115.5	115.2	114.9	114.7	114.4
72.5°	103.0	102.4	101.7	101.3	101.0	100.8	100.5	100.2
75°	81.9	81.6	81.2	81.0	80.9	80.8	80.7	80.6
77.5°	62.1	62.0	61.9	61.7	61.4	61.2	60.9	60.7
80°	49.4	49.2	49.0	49.0	48.8	48.7	48.6	48.5
82.5°	38.1	38.0	37.9	37.8	37.7	37.5	37.5	37.4
85°	21.9	21.9	21.9	21.9	21.8	21.8	21.6	21.5
87.5°	10.6	10.8	10.9	10.9	11.1	11.1	11.1	11.1
90°	12.6	13.3	13.9	13.9	14.6	15.3	14.6	14.6
92.5°	137.0	103.1	82.0	68.0	59.8	56.1	53.7	53.7
95°	516.7	408.6	315.1	247.5	213.4	191.7	179.2	170.1
97.5°	763.3	723.2	655.0	582.2	532.2	490.2	469.2	454.8
100°	840.9	854.8	820.6	769.1	708.4	665.8	645.0	639.4
102.5°	837.0	906.2	916.1	894.6	857.4	826.5	804.5	800.0
105°	781.0	901.5	970.5	999.2	1000.6	995.0	985.3	981.1
107.5°	701.3	829.7	926.9	989.1	1023.6	1039.5	1046.4	1048.2
110°	653.4	773.9	875.0	951.7	1001.2	1030.6	1043.1	1049.4





TEST NUMBER: P332516-940

CATALOG NUMBER: SA4XXDIP-C350D810U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	618.2	724.9	820.4	897.1	953.2	988.7	1006.3	1016.5
115°	582.9	668.7	750.2	817.2	872.3	914.1	936.4	942.0
117.5°	565.6	636.6	700.7	757.5	804.5	839.6	862.2	866.6
120°	557.8	622.7	678.4	727.9	767.7	798.3	816.5	824.1
122.5°	551.1	613.7	664.5	707.8	741.5	767.7	783.0	790.7
125°	539.7	599.7	647.7	686.1	714.0	734.2	747.4	751.6
127.5°	525.8	583.0	631.0	667.4	695.4	713.5	724.6	728.8
130°	514.6	569.6	617.1	654.0	682.6	700.1	711.2	715.4
132.5°	502.8	554.6	600.9	637.8	665.8	685.5	696.2	700.3
135°	486.7	532.0	574.5	609.4	637.3	656.8	668.0	672.2
137.5°	472.1	510.4	546.3	577.7	603.8	623.0	632.2	637.3
140°	463.7	496.4	527.8	557.1	581.5	596.8	606.6	612.2
142.5°	455.8	484.7	511.7	537.0	558.7	572.8	581.5	585.4
145°	444.9	468.6	489.5	509.0	526.5	538.2	545.3	548.8
147.5°	435.8	454.6	471.4	486.7	499.5	509.7	515.0	516.2
150°	430.2	446.2	460.2	472.7	483.9	492.9	497.1	497.8
152.5°	424.1	437.8	450.7	461.0	470.5	477.9	480.4	481.1
155°	414.8	426.1	436.5	444.9	451.8	457.4	459.5	459.5
157.5°	404.9	414.3	423.1	429.8	435.1	439.3	440.5	440.5
160°	398.9	406.5	414.2	419.7	423.9	428.1	428.8	428.8
162.5°	392.7	399.2	405.3	410.3	413.3	417.5	418.2	417.7
165°	384.1	388.3	393.2	396.7	399.5	402.3	401.6	400.9
167.5°	375.9	379.2	383.1	385.1	386.6	388.3	388.3	387.6
170°	371.0	373.0	375.9	377.9	379.3	380.0	379.3	379.3
172.5°	366.5	368.0	369.7	371.2	372.0	372.7	372.0	371.0
175°	360.5	361.1	362.6	362.6	362.6	364.0	362.6	361.1
177.5°	356.6	357.1	357.1	357.7	357.1	357.7	356.6	355.4
180°	354.9	354.9	354.9	354.9	354.9	354.9	354.9	354.9

(END OF REPORT)