

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332577-940

Luminaire Tested: **SA4XXDIP-C575D1205U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332577-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6511.4 lumens  
Efficiency: N/A  
Efficacy: 131.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332577-940  
CATALOG NUMBER: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332577-940

CATALOG NUMBER: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	67	77	71	66	62	57	54	50	44	42	40	32	31	29	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	34	29	27	25	20
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	26	23	22	17
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16	13
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	17	15	12
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6990	6990	6990
5°	7012	6928	6978
10°	6968	6871	6906
15°	6884	6774	6791
20°	6772	6653	6659
25°	6644	6515	6495
30°	6488	6352	6293
35°	6326	6182	6099
40°	6157	5989	5879
45°	5981	5799	5688
50°	5786	5630	5456
55°	5576	5410	5234
60°	5365	5165	5007
65°	5129	4932	4732
70°	4865	4617	4440
75°	4457	4242	4133
80°	3966	3808	3710
85°	3473	3344	3279



TEST NUMBER: P332577-940

CATALOG NUMBER: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.6	1.3
10°-20°	229.8	3.5
20°-30°	338.2	5.2
30°-40°	393.2	6.0
40°-50°	393.2	6.0
50°-60°	343.9	5.3
60°-70°	255.4	3.9
70°-80°	145.1	2.2
80°-90°	45.9	0.7
90°-100°	47.4	0.7
100°-110°	302.1	4.6
110°-120°	577.9	8.9
120°-130°	733.6	11.3
130°-140°	784.9	12.1
140°-150°	734.0	11.3
150°-160°	591.9	9.1
160°-170°	381.8	5.9
170°-180°	131.6	2.0
0°-30°	649.5	10.0
0°-40°	1042.7	16.0
0°-60°	1779.8	27.3
0°-90°	2226.2	34.2
90°-120°	927.4	14.2
90°-150°	3179.9	48.8
90°-180°	4285.0	65.8
0°-180°	6511.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	862	861	82
15°	824	820	810	814	812	232
25°	746	741	731	732	729	343
35°	642	637	627	622	619	401
45°	524	519	508	501	498	404
55°	396	394	384	376	372	355
65°	268	265	258	251	248	266
75°	143	139	136	133	132	152
85°	38	37	36	36	35	41
90°	3	14	23	29	31	5
95°	57	24	23	29	30	73
105°	312	318	323	330	295	326
115°	582	585	584	586	586	573
125°	818	822	821	824	825	730
135°	1015	1015	1018	1021	1023	782
145°	1171	1174	1174	1175	1177	731
155°	1284	1285	1282	1285	1283	592
165°	1354	1349	1349	1356	1348	383
175°	1385	1379	1380	1388	1377	132
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P332577-940

CATALOG NUMBER: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	868.2	867.8	867.5	867.1	866.7	865.9	864.5	863.2	861.7	860.4	861.7
5°	865.3	864.7	864.1	863.4	862.8	861.7	860.0	858.3	856.6	854.9	856.6
7.5°	857.2	856.6	856.0	855.4	854.8	853.5	851.7	849.8	847.8	846.0	847.4
10°	850.0	849.4	848.8	848.2	847.6	846.2	844.3	842.2	840.3	838.2	839.5
12.5°	840.6	840.0	839.4	838.7	838.1	836.8	834.6	832.5	830.4	828.2	829.6
15°	823.7	823.0	822.4	821.8	821.2	819.7	817.4	815.1	812.8	810.5	811.4
17.5°	803.3	802.5	801.7	800.9	800.1	798.7	796.5	794.3	792.1	790.0	790.5
20°	788.3	787.5	786.8	786.0	785.2	783.6	781.3	779.0	776.7	774.4	774.8
22.5°	772.1	771.2	770.2	769.1	768.1	766.4	764.1	761.8	759.5	757.2	758.0
25°	745.9	744.8	743.8	742.7	741.6	740.0	737.8	735.7	733.5	731.4	731.6
27.5°	716.0	714.9	713.7	712.7	711.5	710.0	707.9	706.0	703.9	702.0	701.6
30°	696.0	694.7	693.5	692.2	691.1	689.4	687.4	685.4	683.4	681.4	680.8
32.5°	674.8	673.8	672.6	671.5	670.5	668.8	666.7	664.6	662.5	660.3	659.6
35°	641.9	640.8	639.7	638.6	637.6	635.9	633.7	631.6	629.5	627.3	626.2
37.5°	607.0	606.0	605.0	604.0	603.1	601.5	599.1	596.8	594.5	592.2	591.0
40°	584.2	583.0	581.8	580.6	579.3	577.6	575.2	572.9	570.6	568.3	566.8
42.5°	559.8	559.1	558.4	557.6	556.9	555.2	552.7	550.1	547.5	545.0	543.2
45°	523.9	522.8	521.7	520.7	519.6	517.8	515.3	512.8	510.4	507.9	506.2
47.5°	486.2	485.5	484.8	484.0	483.3	481.8	479.6	477.2	474.9	472.7	470.7
50°	460.7	460.1	459.5	458.9	458.3	456.9	454.8	452.5	450.4	448.3	446.1
52.5°	435.8	435.1	434.3	433.5	432.8	431.3	429.0	426.8	424.5	422.1	420.3
55°	396.2	395.7	395.3	394.8	394.4	393.1	390.9	388.7	386.6	384.4	382.5
57.5°	358.5	357.9	357.4	356.9	356.3	355.1	352.9	350.8	348.7	346.5	344.7
60°	332.3	331.6	330.8	330.0	329.3	327.9	325.9	323.9	321.9	319.9	318.5
62.5°	306.8	306.2	305.5	304.9	304.3	302.8	300.8	298.6	296.5	294.4	293.1
65°	268.5	267.8	267.0	266.3	265.5	264.3	262.8	261.2	259.7	258.2	256.5
67.5°	230.0	229.3	228.5	227.8	227.1	226.0	224.5	223.1	221.6	220.1	218.6
70°	206.1	205.0	203.9	202.9	201.8	200.6	199.4	198.1	196.9	195.6	194.5
72.5°	180.6	179.5	178.4	177.3	176.2	175.2	174.2	173.3	172.3	171.2	170.2
75°	142.9	142.1	141.4	140.6	139.8	139.1	138.3	137.5	136.8	136.0	135.4
77.5°	107.0	106.6	106.3	106.0	105.7	105.1	104.4	103.8	103.1	102.5	102.2
80°	85.3	84.9	84.4	84.0	83.5	83.1	82.8	82.5	82.2	81.9	81.6
82.5°	64.3	64.0	63.8	63.6	63.4	63.2	63.2	63.1	63.0	63.0	62.8
85°	37.5	37.5	37.5	37.5	37.5	37.3	37.0	36.7	36.4	36.1	36.1
87.5°	15.1	15.4	15.8	16.2	16.6	16.9	17.1	17.4	17.7	17.9	18.2
90°	3.1	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2
92.5°	13.0	13.2	13.4	13.5	13.6	14.6	16.4	18.3	20.2	21.9	23.4
95°	57.0	49.1	41.3	33.5	25.7	21.8	22.1	22.3	22.6	22.8	24.2
97.5°	121.0	125.9	130.8	135.6	140.5	130.1	104.4	78.7	53.1	27.4	27.5
100°	170.0	174.1	178.3	182.4	186.5	172.7	140.9	109.1	77.4	45.6	41.6
102.5°	224.6	227.7	230.7	233.7	236.7	236.2	232.1	227.9	223.8	219.6	177.5
105°	311.8	313.3	314.6	316.0	317.4	318.7	319.9	320.9	322.1	323.2	325.4
107.5°	392.9	393.6	394.3	394.9	395.7	396.8	398.3	399.9	401.4	403.1	404.0
110°	447.6	448.3	449.0	449.7	450.4	451.4	452.8	454.1	455.6	456.9	457.4



TEST NUMBER: P332577-940

CATALOG NUMBER: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	500.7	501.9	503.1	504.4	505.6	506.6	507.2	507.8	508.5	509.2	509.1
115°	582.3	583.0	583.7	584.3	585.1	585.3	585.1	584.9	584.6	584.3	584.9
117.5°	655.9	656.7	657.7	658.6	659.5	660.2	660.8	661.3	661.8	662.3	662.2
120°	705.6	706.5	707.5	708.4	709.3	709.6	709.4	709.2	708.9	708.7	709.2
122.5°	752.0	752.6	753.1	753.7	754.2	754.7	755.0	755.3	755.6	756.0	756.3
125°	818.5	819.5	820.4	821.3	822.2	822.4	822.0	821.5	821.1	820.6	821.3
127.5°	881.5	881.7	882.0	882.3	882.4	883.1	884.1	885.2	886.3	887.3	887.2
130°	922.1	922.4	922.7	922.8	923.1	923.5	924.3	924.9	925.6	926.3	926.5
132.5°	959.5	959.8	960.3	960.7	961.1	961.8	962.6	963.5	964.4	965.3	965.5
135°	1015.4	1015.2	1014.9	1014.7	1014.5	1014.9	1015.7	1016.6	1017.6	1018.5	1019.0
137.5°	1065.0	1065.1	1065.1	1065.2	1065.3	1065.9	1066.8	1067.9	1068.9	1069.9	1070.4
140°	1097.3	1097.7	1098.1	1098.7	1099.1	1099.6	1100.0	1100.5	1100.9	1101.4	1102.1
142.5°	1126.2	1127.1	1127.9	1128.7	1129.6	1130.2	1130.4	1130.7	1131.0	1131.2	1131.8
145°	1170.8	1171.5	1172.2	1172.9	1173.6	1173.9	1173.9	1173.9	1173.9	1173.9	1174.2
147.5°	1206.2	1207.6	1208.8	1210.1	1211.4	1211.9	1211.7	1211.5	1211.2	1211.0	1211.2
150°	1232.0	1232.9	1233.8	1234.8	1235.6	1236.0	1235.7	1235.6	1235.3	1235.0	1235.0
152.5°	1253.5	1254.3	1255.0	1255.7	1256.4	1256.6	1256.2	1255.8	1255.4	1255.0	1255.4
155°	1283.8	1284.0	1284.2	1284.4	1284.7	1284.4	1283.8	1283.1	1282.4	1281.7	1282.6
157.5°	1309.2	1309.1	1308.9	1308.9	1308.7	1308.2	1307.4	1306.7	1305.9	1305.1	1306.3
160°	1324.2	1323.5	1322.8	1322.1	1321.4	1321.0	1320.7	1320.4	1320.3	1320.0	1321.4
162.5°	1337.4	1336.6	1335.7	1334.8	1333.9	1333.4	1333.1	1332.9	1332.7	1332.5	1333.8
165°	1354.2	1353.1	1351.9	1350.8	1349.6	1349.1	1349.1	1349.1	1349.1	1349.1	1350.9
167.5°	1367.4	1366.3	1365.1	1363.9	1362.7	1362.0	1361.9	1361.7	1361.6	1361.5	1363.5
170°	1374.9	1373.6	1372.2	1370.8	1369.4	1368.9	1369.0	1369.3	1369.5	1369.8	1371.6
172.5°	1379.9	1378.5	1377.2	1375.7	1374.4	1373.8	1374.0	1374.3	1374.5	1374.8	1376.5
175°	1385.3	1383.9	1382.5	1381.2	1379.7	1379.2	1379.4	1379.7	1379.9	1380.1	1382.2
177.5°	1387.8	1386.5	1385.2	1383.9	1382.6	1382.2	1382.5	1382.9	1383.3	1383.7	1385.1
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332577-940

CATALOG NUMBER: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	862.9	864.2	865.4	865.9	865.8	865.7	865.6	865.4
5°	858.3	860.0	861.7	862.4	862.0	861.7	861.4	861.1
7.5°	848.7	850.1	851.4	852.0	851.9	851.7	851.5	851.2
10°	840.7	842.0	843.2	843.6	843.3	843.0	842.7	842.4
12.5°	831.0	832.3	833.7	834.1	833.7	833.2	832.9	832.4
15°	812.3	813.2	814.1	814.4	814.0	813.5	813.0	812.5
17.5°	791.1	791.7	792.3	792.4	792.1	791.8	791.5	791.2
20°	775.3	775.8	776.2	776.3	776.0	775.7	775.4	775.1
22.5°	758.8	759.6	760.5	760.6	760.1	759.6	759.0	758.4
25°	731.6	731.8	732.0	731.7	731.1	730.5	729.9	729.2
27.5°	701.2	700.8	700.4	699.9	699.1	698.4	697.6	696.8
30°	680.2	679.6	678.9	678.2	677.4	676.7	675.9	675.1
32.5°	658.8	658.1	657.4	656.6	655.9	655.1	654.2	653.5
35°	625.1	624.0	622.9	622.1	621.3	620.5	619.7	618.9
37.5°	589.9	588.6	587.5	586.4	585.4	584.3	583.4	582.3
40°	565.3	563.7	562.1	561.0	560.2	559.5	558.7	557.9
42.5°	541.4	539.6	537.8	536.6	536.2	535.7	535.1	534.6
45°	504.5	502.8	501.1	500.1	499.6	499.2	498.6	498.2
47.5°	468.9	466.9	465.0	463.5	462.4	461.1	459.9	458.8
50°	443.9	441.8	439.6	438.1	437.1	436.2	435.3	434.4
52.5°	418.3	416.4	414.6	413.0	411.8	410.6	409.5	408.3
55°	380.8	378.9	377.0	375.6	374.7	373.8	372.8	371.9
57.5°	343.0	341.3	339.5	338.1	337.2	336.4	335.5	334.6
60°	317.1	315.8	314.3	313.3	312.5	311.7	310.9	310.1
62.5°	291.9	290.5	289.3	288.3	287.5	286.8	286.0	285.2
65°	255.0	253.5	252.0	250.8	250.0	249.2	248.5	247.7
67.5°	217.1	215.7	214.2	213.3	213.1	212.9	212.7	212.5
70°	193.2	192.0	190.7	189.9	189.4	189.0	188.5	188.1
72.5°	169.2	168.3	167.3	166.6	166.1	165.7	165.2	164.7
75°	134.7	134.1	133.6	133.1	133.0	132.9	132.7	132.5
77.5°	102.0	101.8	101.7	101.4	100.9	100.6	100.1	99.8
80°	81.2	81.0	80.6	80.4	80.3	80.1	80.0	79.8
82.5°	62.6	62.4	62.2	62.1	62.0	61.8	61.6	61.4
85°	36.1	36.1	36.1	36.0	35.8	35.7	35.6	35.4
87.5°	18.5	18.7	19.0	19.2	19.3	19.4	19.4	19.5
90°	25.6	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	24.7	26.1	27.5	28.3	28.4	28.4	28.5	28.6
95°	25.6	26.9	28.4	29.2	29.3	29.6	29.8	30.1
97.5°	27.6	27.7	27.9	28.1	28.4	28.5	28.8	29.0
100°	37.7	33.9	30.0	28.1	28.4	28.5	28.8	29.0
102.5°	135.2	93.0	50.7	29.7	29.7	29.8	29.8	29.9
105°	327.4	329.5	331.5	328.4	320.1	311.8	303.6	295.3
107.5°	405.1	406.1	407.1	408.0	408.9	409.8	410.6	411.5
110°	457.9	458.3	458.8	459.3	460.0	460.7	461.5	462.1





TEST NUMBER: P332577-940

CATALOG NUMBER: SA4XXDIP-C575D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	509.0	508.9	508.8	509.2	510.1	511.0	511.8	512.6
115°	585.3	585.8	586.2	586.5	586.5	586.5	586.5	586.5
117.5°	662.1	662.0	661.9	661.8	661.7	661.6	661.6	661.5
120°	709.6	710.1	710.5	710.5	710.1	709.6	709.2	708.7
122.5°	756.5	756.8	757.1	757.0	756.5	756.1	755.5	755.1
125°	822.0	822.7	823.4	823.9	824.0	824.3	824.6	824.7
127.5°	887.1	886.9	886.8	886.6	886.4	886.3	886.1	885.9
130°	926.8	927.0	927.2	927.3	927.3	927.3	927.3	927.3
132.5°	965.7	966.0	966.2	966.2	966.0	965.8	965.6	965.5
135°	1019.4	1019.8	1020.4	1020.8	1021.3	1021.7	1022.2	1022.6
137.5°	1070.9	1071.4	1071.9	1072.1	1072.0	1071.8	1071.7	1071.6
140°	1102.8	1103.5	1104.2	1104.7	1104.8	1105.1	1105.3	1105.5
142.5°	1132.3	1132.7	1133.3	1133.5	1133.6	1133.6	1133.7	1133.7
145°	1174.4	1174.7	1174.8	1175.2	1175.6	1176.1	1176.6	1177.1
147.5°	1211.4	1211.6	1211.7	1211.9	1212.2	1212.5	1212.6	1212.9
150°	1235.0	1235.0	1235.0	1235.2	1235.4	1235.6	1235.9	1236.1
152.5°	1255.7	1256.1	1256.4	1256.5	1256.4	1256.2	1256.2	1256.0
155°	1283.5	1284.4	1285.4	1285.5	1284.8	1284.1	1283.4	1282.7
157.5°	1307.5	1308.7	1309.9	1309.9	1308.7	1307.5	1306.3	1305.1
160°	1322.8	1324.2	1325.5	1325.5	1324.2	1322.8	1321.4	1320.0
162.5°	1335.2	1336.6	1338.0	1337.9	1336.3	1334.8	1333.2	1331.6
165°	1352.7	1354.6	1356.4	1356.3	1354.2	1352.1	1350.1	1348.0
167.5°	1365.6	1367.5	1369.6	1369.4	1367.2	1364.9	1362.5	1360.2
170°	1373.4	1375.3	1377.2	1376.9	1374.6	1372.3	1370.0	1367.7
172.5°	1378.4	1380.3	1382.1	1381.8	1379.3	1376.8	1374.3	1371.8
175°	1384.3	1386.3	1388.4	1388.0	1385.3	1382.5	1379.7	1377.0
177.5°	1386.6	1388.0	1389.6	1389.2	1387.0	1384.7	1382.5	1380.4
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3

(END OF REPORT)