

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332552-940

Luminaire Tested: **SA4XXDIP-C575D590U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332552-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4106.7 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332552-940
CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332552-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54				
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51	46				
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	44	43	38				
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	39	36	32				
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31	28				
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24				
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	28	24	21	19				
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6990	6990	6990
5°	7012	6928	6978
10°	6968	6871	6906
15°	6884	6774	6791
20°	6772	6653	6659
25°	6644	6515	6495
30°	6488	6352	6293
35°	6326	6182	6099
40°	6157	5989	5879
45°	5981	5799	5688
50°	5786	5630	5456
55°	5576	5410	5234
60°	5365	5165	5007
65°	5129	4932	4732
70°	4865	4617	4440
75°	4457	4242	4133
80°	3966	3808	3710
85°	3473	3344	3279



TEST NUMBER: P332552-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	2.0
10°-20°	229.8	5.6
20°-30°	338.2	8.2
30°-40°	393.2	9.6
40°-50°	393.2	9.6
50°-60°	343.9	8.4
60°-70°	255.4	6.2
70°-80°	145.1	3.5
80°-90°	43.3	1.1
90°-100°	187.0	4.6
100°-110°	389.2	9.5
110°-120°	348.6	8.5
120°-130°	293.2	7.1
130°-140°	244.5	6.0
140°-150°	186.8	4.5
150°-160°	131.3	3.2
160°-170°	77.2	1.9
170°-180°	25.1	0.6
0°-30°	649.5	15.8
0°-40°	1042.7	25.4
0°-60°	1779.8	43.3
0°-90°	2223.6	54.1
90°-120°	924.8	22.5
90°-150°	1649.4	40.2
90°-180°	1883.0	45.9
0°-180°	4106.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	862	861	82
15°	824	820	810	814	812	232
25°	746	741	731	732	729	343
35°	642	637	627	622	619	401
45°	524	519	508	501	498	404
55°	396	394	384	376	372	355
65°	268	265	258	251	248	266
75°	143	139	136	133	132	152
85°	38	37	36	36	35	41
90°	0	4	9	10	11	3
95°	17	53	415	205	124	19
105°	60	86	334	719	716	63
115°	105	132	298	572	687	104
125°	146	173	296	486	548	130
135°	173	206	294	432	490	134
145°	200	229	292	364	400	125
155°	227	245	284	321	335	105
165°	248	255	272	288	292	70
175°	258	259	261	264	264	25
180°	259	259	259	259	259	



TEST NUMBER: P332552-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	868.2	867.8	867.5	867.1	866.7	865.9	864.5	863.2	861.7	860.4	861.7
5°	865.3	864.7	864.1	863.4	862.8	861.7	860.0	858.3	856.6	854.9	856.6
7.5°	857.2	856.6	856.0	855.4	854.8	853.5	851.7	849.8	847.8	846.0	847.4
10°	850.0	849.4	848.8	848.2	847.6	846.2	844.3	842.2	840.3	838.2	839.5
12.5°	840.6	840.0	839.4	838.7	838.1	836.8	834.6	832.5	830.4	828.2	829.6
15°	823.7	823.0	822.4	821.8	821.2	819.7	817.4	815.1	812.8	810.5	811.4
17.5°	803.3	802.5	801.7	800.9	800.1	798.7	796.5	794.3	792.1	790.0	790.5
20°	788.3	787.5	786.8	786.0	785.2	783.6	781.3	779.0	776.7	774.4	774.8
22.5°	772.1	771.2	770.2	769.1	768.1	766.4	764.1	761.8	759.5	757.2	758.0
25°	745.9	744.8	743.8	742.7	741.6	740.0	737.8	735.7	733.5	731.4	731.6
27.5°	716.0	714.9	713.7	712.7	711.5	710.0	707.9	706.0	703.9	702.0	701.6
30°	696.0	694.7	693.5	692.2	691.1	689.4	687.4	685.4	683.4	681.4	680.8
32.5°	674.8	673.8	672.6	671.5	670.5	668.8	666.7	664.6	662.5	660.3	659.6
35°	641.9	640.8	639.7	638.6	637.6	635.9	633.7	631.6	629.5	627.3	626.2
37.5°	607.0	606.0	605.0	604.0	603.1	601.5	599.1	596.8	594.5	592.2	591.0
40°	584.2	583.0	581.8	580.6	579.3	577.6	575.2	572.9	570.6	568.3	566.8
42.5°	559.8	559.1	558.4	557.6	556.9	555.2	552.7	550.1	547.5	545.0	543.2
45°	523.9	522.8	521.7	520.7	519.6	517.8	515.3	512.8	510.4	507.9	506.2
47.5°	486.2	485.5	484.8	484.0	483.3	481.8	479.6	477.2	474.9	472.7	470.7
50°	460.7	460.1	459.5	458.9	458.3	456.9	454.8	452.5	450.4	448.3	446.1
52.5°	435.8	435.1	434.3	433.5	432.8	431.3	429.0	426.8	424.5	422.1	420.3
55°	396.2	395.7	395.3	394.8	394.4	393.1	390.9	388.7	386.6	384.4	382.5
57.5°	358.5	357.9	357.4	356.9	356.3	355.1	352.9	350.8	348.7	346.5	344.7
60°	332.3	331.6	330.8	330.0	329.3	327.9	325.9	323.9	321.9	319.9	318.5
62.5°	306.8	306.2	305.5	304.9	304.3	302.8	300.8	298.6	296.5	294.4	293.1
65°	268.5	267.8	267.0	266.3	265.5	264.3	262.8	261.2	259.7	258.2	256.5
67.5°	230.0	229.3	228.5	227.8	227.1	226.0	224.5	223.1	221.6	220.1	218.6
70°	206.1	205.0	203.9	202.9	201.8	200.6	199.4	198.1	196.9	195.6	194.5
72.5°	180.6	179.5	178.4	177.3	176.2	175.2	174.2	173.3	172.3	171.2	170.2
75°	142.9	142.1	141.4	140.6	139.8	139.1	138.3	137.5	136.8	136.0	135.4
77.5°	107.0	106.6	106.3	106.0	105.7	105.1	104.4	103.8	103.1	102.5	102.2
80°	85.3	84.9	84.4	84.0	83.5	83.1	82.8	82.5	82.2	81.9	81.6
82.5°	64.3	64.0	63.8	63.6	63.4	63.2	63.2	63.1	63.0	63.0	62.8
85°	37.5	37.5	37.5	37.5	37.5	37.3	37.0	36.7	36.4	36.1	36.1
87.5°	14.5	14.6	14.8	14.8	14.7	14.6	15.2	15.0	15.1	15.2	15.1
90°	0.5	1.5	3.0	3.6	4.1	4.1	7.1	7.1	8.1	9.2	8.6
92.5°	5.8	8.5	13.2	19.4	26.8	37.5	63.3	102.7	141.2	161.3	134.4
95°	16.8	18.3	23.4	30.1	42.2	63.6	107.8	191.3	312.8	414.6	426.2
97.5°	30.1	30.1	34.5	40.6	51.1	69.0	103.1	171.9	292.8	436.7	535.6
100°	38.7	38.7	42.2	48.3	58.0	74.3	104.2	161.8	265.6	408.9	539.2
102.5°	46.8	47.6	50.7	56.4	65.7	81.1	108.3	158.9	247.2	374.4	508.6
105°	59.5	61.1	63.6	69.7	78.8	93.6	118.0	160.2	231.5	333.7	453.3
107.5°	73.6	74.5	77.1	83.6	92.4	106.9	129.3	167.7	228.6	310.9	408.5
110°	82.9	83.9	86.5	92.6	101.7	115.5	137.9	173.4	229.4	303.2	386.1



TEST NUMBER: P332552-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	91.8	92.9	95.9	101.6	110.7	124.4	146.0	179.6	231.8	299.5	373.4
115°	104.8	106.3	109.9	114.9	124.7	138.4	158.7	189.2	236.6	297.6	361.7
117.5°	118.2	119.7	122.8	128.4	137.4	151.7	171.0	199.1	241.5	297.0	356.4
120°	127.2	128.2	131.7	137.3	146.0	160.2	179.6	206.0	245.2	297.0	353.6
122.5°	135.3	136.3	139.9	145.1	154.5	168.4	187.7	212.5	248.9	296.7	350.3
125°	146.0	148.0	151.1	156.7	166.3	180.6	198.9	222.3	254.3	296.0	344.9
127.5°	155.4	157.1	160.8	167.1	177.2	191.5	209.3	230.8	258.7	294.9	337.7
130°	160.8	162.7	166.8	174.5	184.1	198.9	216.2	236.0	262.0	294.5	333.1
132.5°	166.0	167.6	173.0	180.2	190.6	204.6	221.9	241.3	264.8	294.1	329.1
135°	173.4	175.5	180.6	189.2	199.9	213.1	229.9	248.3	269.1	293.5	323.0
137.5°	180.9	182.8	188.4	196.6	207.8	220.3	236.0	253.2	271.6	293.4	317.7
140°	186.2	187.7	193.3	202.0	212.6	224.8	240.1	256.4	273.7	293.0	314.9
142.5°	191.9	193.4	198.6	206.8	217.1	228.9	243.8	258.8	275.3	293.0	312.5
145°	199.9	201.4	206.5	213.7	223.3	234.5	247.7	261.4	276.3	291.9	308.3
147.5°	208.9	209.5	213.9	221.2	229.3	239.4	251.8	263.8	276.7	290.2	304.5
150°	214.6	215.2	219.3	225.3	233.0	242.6	253.9	265.0	276.7	288.9	301.7
152.5°	220.0	220.1	224.1	229.8	236.7	245.5	255.5	265.8	275.9	286.9	298.4
155°	227.4	227.9	231.0	236.0	241.7	249.2	257.9	266.5	274.6	283.8	293.5
157.5°	234.6	234.6	237.5	241.4	246.3	252.3	259.7	266.5	273.4	280.7	288.6
160°	239.1	239.1	241.1	244.7	248.7	254.3	260.5	266.5	272.2	278.2	284.9
162.5°	243.2	242.7	244.3	247.5	251.2	255.6	261.3	266.5	270.9	275.8	281.6
165°	247.7	247.7	248.7	251.3	253.9	256.9	261.4	265.6	268.6	272.2	276.3
167.5°	252.3	251.8	252.3	254.2	255.7	258.0	261.4	264.3	266.2	268.5	271.3
170°	254.3	253.9	254.3	255.8	256.9	258.4	260.9	263.5	264.5	266.0	268.0
172.5°	256.4	255.8	255.9	257.1	257.7	258.8	260.6	262.7	262.9	263.6	265.2
175°	258.4	257.9	257.9	258.4	259.0	259.0	259.9	261.4	260.9	260.9	262.0
177.5°	259.3	259.0	258.5	259.0	259.0	259.0	259.3	260.1	259.3	259.3	259.8
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332552-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	862.9	864.2	865.4	865.9	865.8	865.7	865.6	865.4
5°	858.3	860.0	861.7	862.4	862.0	861.7	861.4	861.1
7.5°	848.7	850.1	851.4	852.0	851.9	851.7	851.5	851.2
10°	840.7	842.0	843.2	843.6	843.3	843.0	842.7	842.4
12.5°	831.0	832.3	833.7	834.1	833.7	833.2	832.9	832.4
15°	812.3	813.2	814.1	814.4	814.0	813.5	813.0	812.5
17.5°	791.1	791.7	792.3	792.4	792.1	791.8	791.5	791.2
20°	775.3	775.8	776.2	776.3	776.0	775.7	775.4	775.1
22.5°	758.8	759.6	760.5	760.6	760.1	759.6	759.0	758.4
25°	731.6	731.8	732.0	731.7	731.1	730.5	729.9	729.2
27.5°	701.2	700.8	700.4	699.9	699.1	698.4	697.6	696.8
30°	680.2	679.6	678.9	678.2	677.4	676.7	675.9	675.1
32.5°	658.8	658.1	657.4	656.6	655.9	655.1	654.2	653.5
35°	625.1	624.0	622.9	622.1	621.3	620.5	619.7	618.9
37.5°	589.9	588.6	587.5	586.4	585.4	584.3	583.4	582.3
40°	565.3	563.7	562.1	561.0	560.2	559.5	558.7	557.9
42.5°	541.4	539.6	537.8	536.6	536.2	535.7	535.1	534.6
45°	504.5	502.8	501.1	500.1	499.6	499.2	498.6	498.2
47.5°	468.9	466.9	465.0	463.5	462.4	461.1	459.9	458.8
50°	443.9	441.8	439.6	438.1	437.1	436.2	435.3	434.4
52.5°	418.3	416.4	414.6	413.0	411.8	410.6	409.5	408.3
55°	380.8	378.9	377.0	375.6	374.7	373.8	372.8	371.9
57.5°	343.0	341.3	339.5	338.1	337.2	336.4	335.5	334.6
60°	317.1	315.8	314.3	313.3	312.5	311.7	310.9	310.1
62.5°	291.9	290.5	289.3	288.3	287.5	286.8	286.0	285.2
65°	255.0	253.5	252.0	250.8	250.0	249.2	248.5	247.7
67.5°	217.1	215.7	214.2	213.3	213.1	212.9	212.7	212.5
70°	193.2	192.0	190.7	189.9	189.4	189.0	188.5	188.1
72.5°	169.2	168.3	167.3	166.6	166.1	165.7	165.2	164.7
75°	134.7	134.1	133.6	133.1	133.0	132.9	132.7	132.5
77.5°	102.0	101.8	101.7	101.4	100.9	100.6	100.1	99.8
80°	81.2	81.0	80.6	80.4	80.3	80.1	80.0	79.8
82.5°	62.6	62.4	62.2	62.1	62.0	61.8	61.6	61.4
85°	36.1	36.1	36.1	36.0	35.8	35.7	35.6	35.4
87.5°	15.2	15.2	15.3	15.3	15.4	15.6	15.4	15.4
90°	9.2	9.6	10.2	10.2	10.7	11.1	10.7	10.7
92.5°	99.9	75.2	59.8	49.7	43.6	40.9	39.1	39.1
95°	376.9	298.1	229.9	180.6	155.7	139.9	130.7	124.1
97.5°	556.9	527.6	477.9	424.7	388.3	357.6	342.3	331.7
100°	613.5	623.7	598.7	561.1	516.8	485.8	470.6	466.5
102.5°	610.6	661.1	668.3	652.6	625.4	603.0	586.9	583.6
105°	569.7	657.7	708.1	729.0	730.0	725.9	718.7	715.7
107.5°	511.7	605.3	676.3	721.6	746.7	758.3	763.4	764.7
110°	476.6	564.6	638.4	694.4	730.5	751.8	761.0	765.5



TEST NUMBER: P332552-940

CATALOG NUMBER: SA4XXDIP-C575D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.0	528.8	598.5	654.4	695.4	721.3	734.1	741.5
115°	425.3	487.9	547.3	596.2	636.3	666.9	683.1	687.2
117.5°	412.6	464.4	511.2	552.6	586.9	612.5	629.0	632.2
120°	407.0	454.2	494.9	531.0	560.1	582.5	595.7	601.3
122.5°	402.1	447.7	484.7	516.4	540.9	560.1	571.2	576.8
125°	393.7	437.5	472.5	500.5	520.8	535.7	545.3	548.3
127.5°	383.5	425.3	460.4	486.9	507.4	520.5	528.6	531.6
130°	375.4	415.6	450.1	477.2	498.0	510.7	518.9	521.9
132.5°	366.8	404.6	438.4	465.3	485.8	500.2	507.8	511.0
135°	355.1	388.2	419.1	444.6	464.9	479.2	487.3	490.4
137.5°	344.4	372.4	398.5	421.5	440.5	454.6	461.3	464.9
140°	338.2	362.2	385.0	406.4	424.3	435.4	442.6	446.7
142.5°	332.6	353.7	373.3	391.8	407.5	417.9	424.3	427.0
145°	324.5	341.8	357.1	371.3	384.1	392.7	397.8	400.3
147.5°	317.9	331.6	343.8	355.1	364.4	371.8	375.7	376.7
150°	313.9	325.6	335.7	344.9	353.0	359.6	362.7	363.2
152.5°	309.3	319.4	328.8	336.4	343.2	348.7	350.4	351.0
155°	302.6	310.8	318.4	324.5	329.7	333.7	335.2	335.2
157.5°	295.4	302.3	308.6	313.5	317.4	320.5	321.4	321.4
160°	291.0	296.6	302.1	306.2	309.2	312.4	312.8	312.8
162.5°	286.5	291.2	295.6	299.3	301.6	304.6	305.1	304.7
165°	280.3	283.3	286.9	289.4	291.5	293.5	293.0	292.5
167.5°	274.3	276.6	279.5	281.0	282.0	283.3	283.2	282.9
170°	270.6	272.2	274.2	275.7	276.7	277.2	276.7	276.7
172.5°	267.3	268.5	269.7	270.8	271.4	272.0	271.4	270.6
175°	263.0	263.5	264.5	264.5	264.5	265.6	264.5	263.5
177.5°	260.1	260.6	260.6	260.9	260.6	260.9	260.1	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)