

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332622-940

Luminaire Tested: **SA4XXDIP-C795D1205U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332622-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7326.7 lumens  
Efficiency: N/A  
Efficacy: 128.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332622-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332622-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42				
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	43	42	41	35				
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	37	36	34	29				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18				
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13				
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332622-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.5	1.5
10°-20°	314.1	4.3
20°-30°	462.3	6.3
30°-40°	537.4	7.3
40°-50°	537.5	7.3
50°-60°	470.1	6.4
60°-70°	349.1	4.8
70°-80°	198.4	2.7
80°-90°	61.2	0.8
90°-100°	47.4	0.6
100°-110°	302.1	4.1
110°-120°	577.9	7.9
120°-130°	733.6	10.0
130°-140°	784.9	10.7
140°-150°	734.0	10.0
150°-160°	591.9	8.1
160°-170°	381.8	5.2
170°-180°	131.6	1.8
0°-30°	887.8	12.1
0°-40°	1425.3	19.5
0°-60°	2432.8	33.2
0°-90°	3041.6	41.5
90°-120°	927.4	12.7
90°-150°	3179.9	43.4
90°-180°	4285.0	58.5
0°-180°	7326.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	3	14	23	29	31	5
95°	57	24	23	29	30	73
105°	312	318	323	330	295	326
115°	582	585	584	586	586	573
125°	818	822	821	824	825	730
135°	1015	1015	1018	1021	1023	782
145°	1171	1174	1174	1175	1177	731
155°	1284	1285	1282	1285	1283	592
165°	1354	1349	1349	1356	1348	383
175°	1385	1379	1380	1388	1377	132
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P332622-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.3	20.7	21.0	21.4	21.7	21.9	22.2	22.4	22.6	22.7	23.0
90°	3.1	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2
92.5°	13.0	13.2	13.4	13.5	13.6	14.6	16.4	18.3	20.2	21.9	23.4
95°	57.0	49.1	41.3	33.5	25.7	21.8	22.1	22.3	22.6	22.8	24.2
97.5°	121.0	125.9	130.8	135.6	140.5	130.1	104.4	78.7	53.1	27.4	27.5
100°	170.0	174.1	178.3	182.4	186.5	172.7	140.9	109.1	77.4	45.6	41.6
102.5°	224.6	227.7	230.7	233.7	236.7	236.2	232.1	227.9	223.8	219.6	177.5
105°	311.8	313.3	314.6	316.0	317.4	318.7	319.9	320.9	322.1	323.2	325.4
107.5°	392.9	393.6	394.3	394.9	395.7	396.8	398.3	399.9	401.4	403.1	404.0
110°	447.6	448.3	449.0	449.7	450.4	451.4	452.8	454.1	455.6	456.9	457.4



TEST NUMBER: P332622-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	500.7	501.9	503.1	504.4	505.6	506.6	507.2	507.8	508.5	509.2	509.1
115°	582.3	583.0	583.7	584.3	585.1	585.3	585.1	584.9	584.6	584.3	584.9
117.5°	655.9	656.7	657.7	658.6	659.5	660.2	660.8	661.3	661.8	662.3	662.2
120°	705.6	706.5	707.5	708.4	709.3	709.6	709.4	709.2	708.9	708.7	709.2
122.5°	752.0	752.6	753.1	753.7	754.2	754.7	755.0	755.3	755.6	756.0	756.3
125°	818.5	819.5	820.4	821.3	822.2	822.4	822.0	821.5	821.1	820.6	821.3
127.5°	881.5	881.7	882.0	882.3	882.4	883.1	884.1	885.2	886.3	887.3	887.2
130°	922.1	922.4	922.7	922.8	923.1	923.5	924.3	924.9	925.6	926.3	926.5
132.5°	959.5	959.8	960.3	960.7	961.1	961.8	962.6	963.5	964.4	965.3	965.5
135°	1015.4	1015.2	1014.9	1014.7	1014.5	1014.9	1015.7	1016.6	1017.6	1018.5	1019.0
137.5°	1065.0	1065.1	1065.1	1065.2	1065.3	1065.9	1066.8	1067.9	1068.9	1069.9	1070.4
140°	1097.3	1097.7	1098.1	1098.7	1099.1	1099.6	1100.0	1100.5	1100.9	1101.4	1102.1
142.5°	1126.2	1127.1	1127.9	1128.7	1129.6	1130.2	1130.4	1130.7	1131.0	1131.2	1131.8
145°	1170.8	1171.5	1172.2	1172.9	1173.6	1173.9	1173.9	1173.9	1173.9	1173.9	1174.2
147.5°	1206.2	1207.6	1208.8	1210.1	1211.4	1211.9	1211.7	1211.5	1211.2	1211.0	1211.2
150°	1232.0	1232.9	1233.8	1234.8	1235.6	1236.0	1235.7	1235.6	1235.3	1235.0	1235.0
152.5°	1253.5	1254.3	1255.0	1255.7	1256.4	1256.6	1256.2	1255.8	1255.4	1255.0	1255.4
155°	1283.8	1284.0	1284.2	1284.4	1284.7	1284.4	1283.8	1283.1	1282.4	1281.7	1282.6
157.5°	1309.2	1309.1	1308.9	1308.9	1308.7	1308.2	1307.4	1306.7	1305.9	1305.1	1306.3
160°	1324.2	1323.5	1322.8	1322.1	1321.4	1321.0	1320.7	1320.4	1320.3	1320.0	1321.4
162.5°	1337.4	1336.6	1335.7	1334.8	1333.9	1333.4	1333.1	1332.9	1332.7	1332.5	1333.8
165°	1354.2	1353.1	1351.9	1350.8	1349.6	1349.1	1349.1	1349.1	1349.1	1349.1	1350.9
167.5°	1367.4	1366.3	1365.1	1363.9	1362.7	1362.0	1361.9	1361.7	1361.6	1361.5	1363.5
170°	1374.9	1373.6	1372.2	1370.8	1369.4	1368.9	1369.0	1369.3	1369.5	1369.8	1371.6
172.5°	1379.9	1378.5	1377.2	1375.7	1374.4	1373.8	1374.0	1374.3	1374.5	1374.8	1376.5
175°	1385.3	1383.9	1382.5	1381.2	1379.7	1379.2	1379.4	1379.7	1379.9	1380.1	1382.2
177.5°	1387.8	1386.5	1385.2	1383.9	1382.6	1382.2	1382.5	1382.9	1383.3	1383.7	1385.1
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332622-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	23.4	23.6	23.9	24.1	24.2	24.3	24.3	24.4
90°	25.6	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	24.7	26.1	27.5	28.3	28.4	28.4	28.5	28.6
95°	25.6	26.9	28.4	29.2	29.3	29.6	29.8	30.1
97.5°	27.6	27.7	27.9	28.1	28.4	28.5	28.8	29.0
100°	37.7	33.9	30.0	28.1	28.4	28.5	28.8	29.0
102.5°	135.2	93.0	50.7	29.7	29.7	29.8	29.8	29.9
105°	327.4	329.5	331.5	328.4	320.1	311.8	303.6	295.3
107.5°	405.1	406.1	407.1	408.0	408.9	409.8	410.6	411.5
110°	457.9	458.3	458.8	459.3	460.0	460.7	461.5	462.1





TEST NUMBER: P332622-940

CATALOG NUMBER: SA4XXDIP-C795D1205U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	509.0	508.9	508.8	509.2	510.1	511.0	511.8	512.6
115°	585.3	585.8	586.2	586.5	586.5	586.5	586.5	586.5
117.5°	662.1	662.0	661.9	661.8	661.7	661.6	661.6	661.5
120°	709.6	710.1	710.5	710.5	710.1	709.6	709.2	708.7
122.5°	756.5	756.8	757.1	757.0	756.5	756.1	755.5	755.1
125°	822.0	822.7	823.4	823.9	824.0	824.3	824.6	824.7
127.5°	887.1	886.9	886.8	886.6	886.4	886.3	886.1	885.9
130°	926.8	927.0	927.2	927.3	927.3	927.3	927.3	927.3
132.5°	965.7	966.0	966.2	966.2	966.0	965.8	965.6	965.5
135°	1019.4	1019.8	1020.4	1020.8	1021.3	1021.7	1022.2	1022.6
137.5°	1070.9	1071.4	1071.9	1072.1	1072.0	1071.8	1071.7	1071.6
140°	1102.8	1103.5	1104.2	1104.7	1104.8	1105.1	1105.3	1105.5
142.5°	1132.3	1132.7	1133.3	1133.5	1133.6	1133.6	1133.7	1133.7
145°	1174.4	1174.7	1174.8	1175.2	1175.6	1176.1	1176.6	1177.1
147.5°	1211.4	1211.6	1211.7	1211.9	1212.2	1212.5	1212.6	1212.9
150°	1235.0	1235.0	1235.0	1235.2	1235.4	1235.6	1235.9	1236.1
152.5°	1255.7	1256.1	1256.4	1256.5	1256.4	1256.2	1256.2	1256.0
155°	1283.5	1284.4	1285.4	1285.5	1284.8	1284.1	1283.4	1282.7
157.5°	1307.5	1308.7	1309.9	1309.9	1308.7	1307.5	1306.3	1305.1
160°	1322.8	1324.2	1325.5	1325.5	1324.2	1322.8	1321.4	1320.0
162.5°	1335.2	1336.6	1338.0	1337.9	1336.3	1334.8	1333.2	1331.6
165°	1352.7	1354.6	1356.4	1356.3	1354.2	1352.1	1350.1	1348.0
167.5°	1365.6	1367.5	1369.6	1369.4	1367.2	1364.9	1362.5	1360.2
170°	1373.4	1375.3	1377.2	1376.9	1374.6	1372.3	1370.0	1367.7
172.5°	1378.4	1380.3	1382.1	1381.8	1379.3	1376.8	1374.3	1371.8
175°	1384.3	1386.3	1388.4	1388.0	1385.3	1382.5	1379.7	1377.0
177.5°	1386.6	1388.0	1389.6	1389.2	1387.0	1384.7	1382.5	1380.4
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3

(END OF REPORT)