

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332595-940

Luminaire Tested: **SA4XXDIP-C795D590U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332595-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D590U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5143.2 lumens  
Efficiency: N/A  
Efficacy: 127.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332595-940  
CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332595-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50				
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42				
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35				
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30				
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26				
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23				
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20				
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18				
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17				
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332595-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.5	2.2
10°-20°	314.1	6.1
20°-30°	462.3	9.0
30°-40°	537.4	10.4
40°-50°	537.5	10.4
50°-60°	470.1	9.1
60°-70°	349.1	6.8
70°-80°	198.4	3.9
80°-90°	59.2	1.2
90°-100°	23.3	0.5
100°-110°	148.3	2.9
110°-120°	283.7	5.5
120°-130°	360.1	7.0
130°-140°	385.3	7.5
140°-150°	360.3	7.0
150°-160°	290.6	5.6
160°-170°	187.4	3.6
170°-180°	64.6	1.3
0°-30°	887.8	17.3
0°-40°	1425.3	27.7
0°-60°	2432.8	47.3
0°-90°	3039.5	59.1
90°-120°	455.3	8.9
90°-150°	1561.1	30.4
90°-180°	2104.0	40.9
0°-180°	5143.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	2	7	11	14	15	4
95°	28	12	11	14	15	36
105°	153	156	159	162	145	160
115°	286	287	287	288	288	281
125°	402	404	403	404	405	359
135°	498	498	500	501	502	384
145°	575	576	576	577	578	359
155°	630	631	629	631	630	290
165°	665	662	662	666	662	188
175°	680	677	678	682	676	65
180°	680	680	680	680	680	



TEST NUMBER: P332595-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	20.1	20.2	20.2	20.2	20.3	20.4	20.4	20.4	20.4	20.4	20.6
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	6.4	6.5	6.5	6.6	6.7	7.1	8.1	9.0	9.9	10.8	11.5
95°	28.0	24.2	20.3	16.4	12.6	10.7	10.9	11.0	11.1	11.1	11.9
97.5°	59.4	61.8	64.2	66.6	69.0	63.8	51.3	38.7	26.0	13.5	13.5
100°	83.4	85.4	87.5	89.5	91.6	84.8	69.2	53.6	38.0	22.4	20.4
102.5°	110.3	111.7	113.2	114.8	116.3	116.0	114.0	111.9	109.9	107.8	87.1
105°	153.1	153.8	154.4	155.2	155.8	156.4	157.0	157.6	158.1	158.7	159.7
107.5°	192.9	193.2	193.6	193.9	194.2	194.7	195.6	196.4	197.1	197.9	198.4
110°	219.7	220.1	220.4	220.8	221.1	221.6	222.3	222.9	223.6	224.4	224.5



TEST NUMBER: P332595-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.4	247.0	247.6	248.3	248.7	249.0	249.3	249.7	249.9	249.9
115°	285.9	286.2	286.5	286.9	287.2	287.3	287.2	287.1	287.0	286.9	287.1
117.5°	322.0	322.4	322.9	323.3	323.8	324.1	324.4	324.7	324.9	325.1	325.1
120°	346.4	346.9	347.3	347.8	348.2	348.4	348.3	348.1	348.0	347.9	348.1
122.5°	369.2	369.4	369.7	370.0	370.2	370.5	370.7	370.8	371.0	371.1	371.2
125°	401.8	402.3	402.8	403.2	403.7	403.8	403.5	403.3	403.1	402.9	403.2
127.5°	432.7	432.8	433.0	433.1	433.2	433.5	434.1	434.5	435.1	435.6	435.5
130°	452.7	452.8	452.9	453.1	453.2	453.3	453.7	454.1	454.4	454.8	454.9
132.5°	471.0	471.2	471.4	471.6	471.8	472.2	472.6	473.0	473.4	473.9	473.9
135°	498.5	498.4	498.3	498.1	498.0	498.2	498.6	499.1	499.5	500.0	500.2
137.5°	522.8	522.8	522.9	522.9	523.0	523.3	523.7	524.2	524.8	525.2	525.5
140°	538.7	538.9	539.1	539.3	539.6	539.8	540.0	540.3	540.5	540.7	541.0
142.5°	552.9	553.3	553.8	554.1	554.6	554.8	554.9	555.1	555.2	555.4	555.6
145°	574.8	575.2	575.4	575.8	576.1	576.3	576.3	576.3	576.3	576.3	576.4
147.5°	592.2	592.8	593.4	594.1	594.7	594.9	594.9	594.8	594.6	594.5	594.6
150°	604.8	605.2	605.7	606.2	606.6	606.8	606.6	606.5	606.5	606.3	606.3
152.5°	615.4	615.7	616.1	616.4	616.8	616.9	616.7	616.5	616.3	616.1	616.3
155°	630.3	630.4	630.4	630.5	630.7	630.5	630.3	629.9	629.5	629.2	629.6
157.5°	642.7	642.7	642.6	642.6	642.5	642.2	641.9	641.5	641.1	640.7	641.3
160°	650.1	649.7	649.3	649.1	648.7	648.5	648.4	648.3	648.1	648.0	648.7
162.5°	656.6	656.1	655.7	655.3	654.9	654.6	654.4	654.3	654.2	654.2	654.8
165°	664.8	664.2	663.7	663.1	662.5	662.3	662.3	662.3	662.3	662.3	663.2
167.5°	671.3	670.7	670.1	669.6	669.0	668.6	668.6	668.5	668.4	668.3	669.4
170°	675.0	674.3	673.6	673.0	672.3	672.0	672.1	672.2	672.3	672.4	673.3
172.5°	677.4	676.7	676.1	675.4	674.8	674.4	674.6	674.7	674.8	674.8	675.8
175°	680.1	679.4	678.7	678.1	677.3	677.1	677.2	677.3	677.4	677.5	678.5
177.5°	681.3	680.6	680.0	679.4	678.8	678.5	678.7	678.9	679.0	679.2	680.0
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332595-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	20.7	20.9	21.0	21.0	21.1	21.1	21.2	21.2
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	12.1	12.8	13.5	13.8	13.9	13.9	14.0	14.0
95°	12.6	13.2	13.9	14.3	14.4	14.5	14.6	14.7
97.5°	13.6	13.6	13.7	13.8	13.9	14.0	14.1	14.3
100°	18.5	16.6	14.7	13.8	13.9	14.0	14.1	14.3
102.5°	66.3	45.7	24.9	14.5	14.6	14.6	14.6	14.6
105°	160.8	161.8	162.7	161.2	157.2	153.1	149.0	145.0
107.5°	198.9	199.4	199.8	200.3	200.7	201.2	201.6	202.1
110°	224.8	225.0	225.2	225.5	225.9	226.1	226.5	226.9





TEST NUMBER: P332595-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.9	249.9	249.8	249.9	250.4	250.8	251.3	251.6
115°	287.3	287.6	287.8	287.9	287.9	287.9	287.9	287.9
117.5°	325.0	325.0	324.9	324.9	324.9	324.9	324.8	324.8
120°	348.4	348.6	348.8	348.8	348.6	348.4	348.1	347.9
122.5°	371.4	371.5	371.7	371.6	371.4	371.1	371.0	370.7
125°	403.5	403.9	404.2	404.5	404.6	404.7	404.7	404.9
127.5°	435.5	435.4	435.3	435.2	435.2	435.1	435.0	434.9
130°	455.0	455.0	455.2	455.2	455.2	455.2	455.2	455.2
132.5°	474.1	474.2	474.3	474.3	474.2	474.1	474.0	473.9
135°	500.4	500.7	500.9	501.1	501.3	501.6	501.9	502.0
137.5°	525.8	526.0	526.2	526.3	526.3	526.2	526.1	526.0
140°	541.4	541.7	542.1	542.2	542.4	542.5	542.6	542.7
142.5°	555.8	556.1	556.3	556.5	556.5	556.5	556.5	556.6
145°	576.5	576.7	576.8	576.9	577.1	577.4	577.7	577.8
147.5°	594.7	594.8	594.9	594.9	595.1	595.2	595.3	595.4
150°	606.3	606.3	606.3	606.4	606.5	606.6	606.7	606.8
152.5°	616.4	616.6	616.8	616.9	616.8	616.7	616.6	616.6
155°	630.1	630.5	631.0	631.1	630.7	630.4	630.1	629.7
157.5°	641.9	642.5	643.0	643.0	642.5	641.9	641.3	640.7
160°	649.3	650.1	650.8	650.8	650.1	649.3	648.7	648.0
162.5°	655.5	656.1	656.8	656.8	656.0	655.2	654.5	653.7
165°	664.1	664.9	665.9	665.8	664.8	663.8	662.8	661.7
167.5°	670.4	671.4	672.3	672.3	671.2	670.0	668.9	667.8
170°	674.2	675.1	676.1	675.9	674.8	673.7	672.5	671.5
172.5°	676.7	677.6	678.5	678.3	677.2	675.9	674.7	673.4
175°	679.6	680.6	681.6	681.4	680.1	678.7	677.3	676.0
177.5°	680.7	681.4	682.2	682.0	680.9	679.8	678.7	677.6
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1

(END OF REPORT)