

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332597-940

Luminaire Tested: **SA4XXDIP-C795D590U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332597-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4922.1 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332597-940
CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332597-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	69	67	65	59	58	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9556	9556	9556
5°	9585	9469	9539
10°	9525	9393	9439
15°	9410	9260	9283
20°	9257	9094	9101
25°	9082	8905	8879
30°	8869	8682	8603
35°	8647	8451	8339
40°	8416	8186	8037
45°	8176	7927	7775
50°	7910	7695	7458
55°	7623	7396	7156
60°	7335	7061	6846
65°	7011	6739	6468
70°	6649	6314	6069
75°	6095	5798	5652
80°	5421	5202	5072
85°	4742	4566	4474



TEST NUMBER: P332597-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.5	2.3
10°-20°	314.1	6.4
20°-30°	462.3	9.4
30°-40°	537.4	10.9
40°-50°	537.5	10.9
50°-60°	470.1	9.6
60°-70°	349.1	7.1
70°-80°	198.4	4.0
80°-90°	58.7	1.2
90°-100°	187.0	3.8
100°-110°	389.2	7.9
110°-120°	348.6	7.1
120°-130°	293.2	6.0
130°-140°	244.5	5.0
140°-150°	186.8	3.8
150°-160°	131.3	2.7
160°-170°	77.2	1.6
170°-180°	25.1	0.5
0°-30°	887.8	18.0
0°-40°	1425.3	29.0
0°-60°	2432.8	49.4
0°-90°	3039.0	61.7
90°-120°	924.8	18.8
90°-150°	1649.4	33.5
90°-180°	1883.0	38.3
0°-180°	4922.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1184	1184	1184	1184	1184	
5°	1183	1179	1168	1178	1177	112
15°	1126	1122	1108	1113	1111	317
25°	1020	1013	1000	1000	997	469
35°	877	870	858	851	846	548
45°	716	709	694	684	681	552
55°	542	538	526	514	508	485
65°	367	362	353	344	339	363
75°	195	191	186	182	181	208
85°	51	51	49	49	48	56
90°	0	4	9	10	11	4
95°	17	53	415	205	124	19
105°	60	86	334	719	716	63
115°	105	132	298	572	687	104
125°	146	173	296	486	548	130
135°	173	206	294	432	490	134
145°	200	229	292	364	400	125
155°	227	245	284	321	335	105
165°	248	255	272	288	292	70
175°	258	259	261	264	264	25
180°	259	259	259	259	259	



TEST NUMBER: P332597-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1186.8	1186.2	1185.7	1185.3	1184.7	1183.6	1181.7	1179.8	1177.9	1176.2	1177.8
5°	1182.8	1182.0	1181.1	1180.3	1179.4	1177.8	1175.5	1173.1	1170.8	1168.5	1170.8
7.5°	1171.8	1170.9	1170.1	1169.2	1168.4	1166.7	1164.1	1161.5	1159.0	1156.4	1158.2
10°	1161.9	1161.1	1160.2	1159.4	1158.5	1156.7	1154.0	1151.3	1148.5	1145.8	1147.5
12.5°	1149.0	1148.2	1147.3	1146.5	1145.7	1143.7	1140.9	1137.9	1135.1	1132.1	1134.0
15°	1125.9	1125.0	1124.2	1123.3	1122.5	1120.5	1117.3	1114.2	1111.0	1107.9	1109.1
17.5°	1098.0	1096.9	1095.8	1094.8	1093.8	1091.7	1088.8	1085.7	1082.7	1079.8	1080.6
20°	1077.5	1076.4	1075.4	1074.3	1073.3	1071.1	1068.0	1064.8	1061.7	1058.5	1059.2
22.5°	1055.5	1054.1	1052.7	1051.3	1049.9	1047.7	1044.5	1041.3	1038.1	1035.0	1036.2
25°	1019.6	1018.2	1016.6	1015.2	1013.7	1011.5	1008.5	1005.6	1002.6	999.7	999.9
27.5°	978.7	977.1	975.6	974.1	972.6	970.4	967.7	965.0	962.2	959.5	958.9
30°	951.4	949.7	948.0	946.3	944.6	942.4	939.6	936.9	934.2	931.4	930.6
32.5°	922.5	921.0	919.4	917.9	916.4	914.2	911.3	908.4	905.5	902.6	901.6
35°	877.4	875.8	874.4	872.9	871.5	869.2	866.3	863.4	860.4	857.5	856.0
37.5°	829.7	828.4	827.1	825.7	824.3	822.1	818.9	815.7	812.6	809.4	807.8
40°	798.6	796.9	795.2	793.5	791.8	789.4	786.3	783.1	780.0	776.8	774.7
42.5°	765.3	764.2	763.2	762.2	761.2	758.9	755.5	752.0	748.4	744.9	742.5
45°	716.1	714.6	713.2	711.7	710.2	707.8	704.5	701.1	697.7	694.3	692.0
47.5°	664.7	663.7	662.7	661.6	660.7	658.6	655.5	652.4	649.3	646.1	643.5
50°	629.8	628.9	628.1	627.2	626.4	624.6	621.6	618.7	615.6	612.7	609.8
52.5°	595.7	594.7	593.6	592.6	591.6	589.5	586.4	583.3	580.1	577.0	574.4
55°	541.6	540.9	540.3	539.7	539.0	537.3	534.3	531.4	528.4	525.5	522.9
57.5°	490.0	489.3	488.6	487.9	487.1	485.3	482.4	479.5	476.6	473.7	471.3
60°	454.3	453.3	452.2	451.2	450.1	448.2	445.5	442.7	440.0	437.3	435.3
62.5°	419.5	418.6	417.7	416.8	415.9	414.0	411.1	408.1	405.3	402.3	400.6
65°	367.0	366.0	365.0	363.9	362.8	361.2	359.2	357.0	354.9	352.8	350.7
67.5°	314.3	313.3	312.4	311.4	310.5	309.0	306.9	304.9	302.9	300.9	298.8
70°	281.7	280.3	278.7	277.2	275.8	274.2	272.5	270.8	269.1	267.5	265.8
72.5°	246.8	245.3	243.9	242.4	240.9	239.5	238.2	236.7	235.4	234.1	232.7
75°	195.4	194.3	193.3	192.3	191.2	190.1	189.0	188.0	187.0	185.9	185.0
77.5°	146.2	145.8	145.3	144.9	144.4	143.7	142.8	141.9	140.9	140.0	139.7
80°	116.6	116.0	115.4	114.8	114.1	113.6	113.2	112.8	112.4	111.9	111.5
82.5°	87.8	87.6	87.2	86.9	86.7	86.5	86.4	86.3	86.2	86.1	85.9
85°	51.2	51.2	51.2	51.2	51.2	51.0	50.6	50.2	49.8	49.3	49.3
87.5°	19.8	19.9	20.0	20.0	19.9	19.7	20.2	20.0	20.0	20.1	20.0
90°	0.5	1.5	3.0	3.6	4.1	4.1	7.1	7.1	8.1	9.2	8.6
92.5°	5.8	8.5	13.2	19.4	26.8	37.5	63.3	102.7	141.2	161.3	134.4
95°	16.8	18.3	23.4	30.1	42.2	63.6	107.8	191.3	312.8	414.6	426.2
97.5°	30.1	30.1	34.5	40.6	51.1	69.0	103.1	171.9	292.8	436.7	535.6
100°	38.7	38.7	42.2	48.3	58.0	74.3	104.2	161.8	265.6	408.9	539.2
102.5°	46.8	47.6	50.7	56.4	65.7	81.1	108.3	158.9	247.2	374.4	508.6
105°	59.5	61.1	63.6	69.7	78.8	93.6	118.0	160.2	231.5	333.7	453.3
107.5°	73.6	74.5	77.1	83.6	92.4	106.9	129.3	167.7	228.6	310.9	408.5
110°	82.9	83.9	86.5	92.6	101.7	115.5	137.9	173.4	229.4	303.2	386.1



TEST NUMBER: P332597-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	91.8	92.9	95.9	101.6	110.7	124.4	146.0	179.6	231.8	299.5	373.4
115°	104.8	106.3	109.9	114.9	124.7	138.4	158.7	189.2	236.6	297.6	361.7
117.5°	118.2	119.7	122.8	128.4	137.4	151.7	171.0	199.1	241.5	297.0	356.4
120°	127.2	128.2	131.7	137.3	146.0	160.2	179.6	206.0	245.2	297.0	353.6
122.5°	135.3	136.3	139.9	145.1	154.5	168.4	187.7	212.5	248.9	296.7	350.3
125°	146.0	148.0	151.1	156.7	166.3	180.6	198.9	222.3	254.3	296.0	344.9
127.5°	155.4	157.1	160.8	167.1	177.2	191.5	209.3	230.8	258.7	294.9	337.7
130°	160.8	162.7	166.8	174.5	184.1	198.9	216.2	236.0	262.0	294.5	333.1
132.5°	166.0	167.6	173.0	180.2	190.6	204.6	221.9	241.3	264.8	294.1	329.1
135°	173.4	175.5	180.6	189.2	199.9	213.1	229.9	248.3	269.1	293.5	323.0
137.5°	180.9	182.8	188.4	196.6	207.8	220.3	236.0	253.2	271.6	293.4	317.7
140°	186.2	187.7	193.3	202.0	212.6	224.8	240.1	256.4	273.7	293.0	314.9
142.5°	191.9	193.4	198.6	206.8	217.1	228.9	243.8	258.8	275.3	293.0	312.5
145°	199.9	201.4	206.5	213.7	223.3	234.5	247.7	261.4	276.3	291.9	308.3
147.5°	208.9	209.5	213.9	221.2	229.3	239.4	251.8	263.8	276.7	290.2	304.5
150°	214.6	215.2	219.3	225.3	233.0	242.6	253.9	265.0	276.7	288.9	301.7
152.5°	220.0	220.1	224.1	229.8	236.7	245.5	255.5	265.8	275.9	286.9	298.4
155°	227.4	227.9	231.0	236.0	241.7	249.2	257.9	266.5	274.6	283.8	293.5
157.5°	234.6	234.6	237.5	241.4	246.3	252.3	259.7	266.5	273.4	280.7	288.6
160°	239.1	239.1	241.1	244.7	248.7	254.3	260.5	266.5	272.2	278.2	284.9
162.5°	243.2	242.7	244.3	247.5	251.2	255.6	261.3	266.5	270.9	275.8	281.6
165°	247.7	247.7	248.7	251.3	253.9	256.9	261.4	265.6	268.6	272.2	276.3
167.5°	252.3	251.8	252.3	254.2	255.7	258.0	261.4	264.3	266.2	268.5	271.3
170°	254.3	253.9	254.3	255.8	256.9	258.4	260.9	263.5	264.5	266.0	268.0
172.5°	256.4	255.8	255.9	257.1	257.7	258.8	260.6	262.7	262.9	263.6	265.2
175°	258.4	257.9	257.9	258.4	259.0	259.0	259.9	261.4	260.9	260.9	262.0
177.5°	259.3	259.0	258.5	259.0	259.0	259.0	259.3	260.1	259.3	259.3	259.8
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0



TEST NUMBER: P332597-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7	1183.7
2.5°	1179.5	1181.2	1182.9	1183.7	1183.5	1183.3	1183.1	1182.9
5°	1173.1	1175.5	1177.8	1178.8	1178.3	1177.9	1177.5	1177.1
7.5°	1160.1	1162.0	1163.8	1164.6	1164.4	1164.1	1163.9	1163.6
10°	1149.1	1150.8	1152.5	1153.2	1152.7	1152.3	1151.9	1151.5
12.5°	1135.9	1137.6	1139.5	1140.1	1139.6	1139.0	1138.4	1137.8
15°	1110.4	1111.6	1112.9	1113.2	1112.6	1112.0	1111.3	1110.7
17.5°	1081.4	1082.2	1083.0	1083.2	1082.7	1082.3	1081.9	1081.5
20°	1059.8	1060.4	1061.0	1061.1	1060.7	1060.3	1059.9	1059.4
22.5°	1037.2	1038.4	1039.6	1039.7	1038.9	1038.2	1037.4	1036.7
25°	1000.1	1000.3	1000.6	1000.2	999.4	998.5	997.7	996.8
27.5°	958.5	958.0	957.4	956.7	955.6	954.6	953.5	952.4
30°	929.7	928.9	928.0	927.1	926.0	925.0	923.9	922.9
32.5°	900.5	899.6	898.6	897.5	896.4	895.4	894.3	893.3
35°	854.5	853.0	851.5	850.2	849.2	848.2	847.1	846.1
37.5°	806.2	804.6	803.1	801.6	800.1	798.8	797.4	795.9
40°	772.6	770.5	768.4	766.8	765.7	764.7	763.7	762.6
42.5°	740.0	737.6	735.1	733.6	732.9	732.2	731.5	730.8
45°	689.6	687.3	685.0	683.6	682.9	682.2	681.6	681.0
47.5°	640.9	638.3	635.6	633.6	632.0	630.4	628.7	627.1
50°	606.8	603.9	600.9	598.8	597.5	596.3	595.0	593.8
52.5°	571.9	569.2	566.6	564.5	562.9	561.3	559.7	558.1
55°	520.4	517.9	515.3	513.4	512.2	511.0	509.6	508.4
57.5°	468.9	466.5	464.0	462.3	461.0	459.8	458.6	457.4
60°	433.5	431.6	429.6	428.2	427.1	426.1	425.0	424.0
62.5°	398.9	397.2	395.5	394.0	393.0	391.9	390.9	389.9
65°	348.7	346.5	344.4	342.9	341.8	340.7	339.7	338.6
67.5°	296.9	294.8	292.7	291.6	291.3	291.1	290.7	290.4
70°	264.1	262.4	260.7	259.6	259.0	258.3	257.7	257.1
72.5°	231.4	230.1	228.7	227.7	227.0	226.4	225.8	225.2
75°	184.2	183.3	182.5	182.0	181.8	181.6	181.4	181.2
77.5°	139.5	139.2	139.0	138.6	138.0	137.5	137.0	136.4
80°	111.1	110.7	110.2	109.9	109.7	109.5	109.3	109.1
82.5°	85.6	85.3	85.1	84.9	84.7	84.4	84.3	84.0
85°	49.3	49.3	49.3	49.2	49.0	48.8	48.6	48.3
87.5°	20.1	20.2	20.2	20.2	20.3	20.4	20.3	20.3
90°	9.2	9.6	10.2	10.2	10.7	11.1	10.7	10.7
92.5°	99.9	75.2	59.8	49.7	43.6	40.9	39.1	39.1
95°	376.9	298.1	229.9	180.6	155.7	139.9	130.7	124.1
97.5°	556.9	527.6	477.9	424.7	388.3	357.6	342.3	331.7
100°	613.5	623.7	598.7	561.1	516.8	485.8	470.6	466.5
102.5°	610.6	661.1	668.3	652.6	625.4	603.0	586.9	583.6
105°	569.7	657.7	708.1	729.0	730.0	725.9	718.7	715.7
107.5°	511.7	605.3	676.3	721.6	746.7	758.3	763.4	764.7
110°	476.6	564.6	638.4	694.4	730.5	751.8	761.0	765.5



TEST NUMBER: P332597-940

CATALOG NUMBER: SA4XXDIP-C795D590U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	451.0	528.8	598.5	654.4	695.4	721.3	734.1	741.5
115°	425.3	487.9	547.3	596.2	636.3	666.9	683.1	687.2
117.5°	412.6	464.4	511.2	552.6	586.9	612.5	629.0	632.2
120°	407.0	454.2	494.9	531.0	560.1	582.5	595.7	601.3
122.5°	402.1	447.7	484.7	516.4	540.9	560.1	571.2	576.8
125°	393.7	437.5	472.5	500.5	520.8	535.7	545.3	548.3
127.5°	383.5	425.3	460.4	486.9	507.4	520.5	528.6	531.6
130°	375.4	415.6	450.1	477.2	498.0	510.7	518.9	521.9
132.5°	366.8	404.6	438.4	465.3	485.8	500.2	507.8	511.0
135°	355.1	388.2	419.1	444.6	464.9	479.2	487.3	490.4
137.5°	344.4	372.4	398.5	421.5	440.5	454.6	461.3	464.9
140°	338.2	362.2	385.0	406.4	424.3	435.4	442.6	446.7
142.5°	332.6	353.7	373.3	391.8	407.5	417.9	424.3	427.0
145°	324.5	341.8	357.1	371.3	384.1	392.7	397.8	400.3
147.5°	317.9	331.6	343.8	355.1	364.4	371.8	375.7	376.7
150°	313.9	325.6	335.7	344.9	353.0	359.6	362.7	363.2
152.5°	309.3	319.4	328.8	336.4	343.2	348.7	350.4	351.0
155°	302.6	310.8	318.4	324.5	329.7	333.7	335.2	335.2
157.5°	295.4	302.3	308.6	313.5	317.4	320.5	321.4	321.4
160°	291.0	296.6	302.1	306.2	309.2	312.4	312.8	312.8
162.5°	286.5	291.2	295.6	299.3	301.6	304.6	305.1	304.7
165°	280.3	283.3	286.9	289.4	291.5	293.5	293.0	292.5
167.5°	274.3	276.6	279.5	281.0	282.0	283.3	283.2	282.9
170°	270.6	272.2	274.2	275.7	276.7	277.2	276.7	276.7
172.5°	267.3	268.5	269.7	270.8	271.4	272.0	271.4	270.6
175°	263.0	263.5	264.5	264.5	264.5	265.6	264.5	263.5
177.5°	260.1	260.6	260.6	260.9	260.6	260.9	260.1	259.3
180°	259.0	259.0	259.0	259.0	259.0	259.0	259.0	259.0

(END OF REPORT)