

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924002

Luminaire Tested: DFN2DIP-4P3F0-020D030US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924002
REPORT IS A COMBINATION OF REPORTS P899039 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US950-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4421.8 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924002

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924002

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	846	846	846
5°	847	834	840
10°	839	822	828
15°	827	808	810
20°	809	788	792
25°	792	765	770
30°	771	744	743
35°	751	719	715
40°	726	693	687
45°	701	668	660
50°	674	641	628
55°	645	609	598
60°	613	573	564
65°	578	535	524
70°	533	488	480
75°	471	432	440
80°	396	361	363
85°	278	239	238

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 907 cd/sqm

TEST NUMBER: P924002

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.9	1.6
10°-20°	196.6	4.4
20°-30°	288.9	6.5
30°-40°	335.6	7.6
40°-50°	335.2	7.6
50°-60°	292.2	6.6
60°-70°	216.0	4.9
70°-80°	122.2	2.8
80°-90°	34.8	0.8
90°-100°	56.0	1.3
100°-110°	178.0	4.0
110°-120°	304.6	6.9
120°-130°	400.5	9.1
130°-140°	449.6	10.2
140°-150°	440.9	10.0
150°-160°	369.8	8.4
160°-170°	245.3	5.5
170°-180°	85.7	1.9
0°-30°	555.4	12.6
0°-40°	891.0	20.2
0°-60°	1518.4	34.3
0°-90°	1891.5	42.8
90°-120°	538.5	12.2
90°-150°	1829.5	41.4
90°-180°	2530.0	57.2
0°-180°	4421.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	742	740	732	737	736	70
15°	707	702	693	696	692	199
25°	640	634	622	623	622	294
35°	552	545	533	529	525	345
45°	449	444	433	426	423	347
55°	340	336	327	318	315	304
65°	229	225	218	211	208	227
75°	120	119	115	111	112	128
85°	29	28	28	26	25	33
90°	1	10	27	25	26	4
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P924002

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	742.4	742.4	742.4	742.4	742.4
2.5°	746.7	743.2	735.2	742.4	741.1
5°	742.4	739.6	731.7	737.4	736.0
7.5°	737.4	733.1	725.3	731.1	729.6
10°	729.6	724.7	716.1	721.7	719.6
12.5°	718.8	714.6	706.1	709.6	708.2
15°	706.7	702.5	693.2	696.0	692.5
17.5°	691.7	687.5	678.2	681.7	678.2
20°	675.3	671.0	661.0	663.2	660.4
22.5°	658.9	652.5	643.2	643.2	641.8
25°	639.7	633.9	621.8	623.2	621.8
27.5°	618.2	613.2	604.0	601.9	598.3
30°	596.8	591.1	580.4	578.3	575.4
32.5°	573.9	569.7	558.3	554.0	551.1
35°	551.9	544.7	533.3	529.0	525.4
37.5°	526.9	520.4	509.0	504.0	500.4
40°	501.1	495.4	484.0	477.7	474.7
42.5°	476.1	470.4	459.1	451.9	447.6
45°	449.0	444.1	433.3	425.5	422.6
47.5°	422.6	417.7	406.2	398.3	394.1
50°	394.8	391.2	381.2	371.2	367.7
52.5°	367.7	362.6	353.4	345.5	340.6
55°	339.8	335.5	326.9	318.4	314.8
57.5°	312.0	308.4	299.1	290.6	287.6
60°	284.1	281.3	271.3	263.4	261.3
62.5°	257.0	252.0	244.9	237.7	234.9
65°	229.2	224.9	217.8	211.3	207.8
67.5°	200.6	197.0	190.6	185.6	182.8
70°	174.2	171.3	164.9	159.9	157.1
72.5°	147.1	144.2	140.6	135.7	133.6
75°	119.9	118.6	114.9	110.7	112.1
77.5°	95.7	92.8	91.3	89.2	87.1
80°	71.5	70.7	69.3	67.1	65.6
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.2	28.5	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P924002

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P924002

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.95	6.75	6.97	7.77	9.15	5.51	6.31	6.52	7.33	8.70
	3H	7.60	8.32	8.63	9.35	10.74	7.11	7.83	8.14	8.86	10.25
	4H	8.18	8.86	9.22	9.90	11.30	7.69	8.37	8.73	9.41	10.80
	6H	8.58	9.20	9.63	10.24	11.65	8.08	8.70	9.12	9.74	11.15
	8H	8.68	9.27	9.73	10.33	11.74	8.18	8.77	9.23	9.83	11.23
	12H	8.72	9.29	9.78	10.34	11.77	8.21	8.78	9.27	9.83	11.26
4H	2H	6.40	7.08	7.44	8.12	9.51	6.04	6.72	7.09	7.76	9.16
	3H	8.25	8.82	9.31	9.89	11.30	7.85	8.41	8.90	9.48	10.89
	4H	8.96	9.48	10.02	10.54	11.97	8.54	9.06	9.60	10.11	11.55
	6H	9.47	9.92	10.54	11.00	12.42	9.04	9.48	10.11	10.56	11.99
	8H	9.62	10.03	10.69	11.11	12.55	9.18	9.60	10.25	10.67	12.11
	12H	9.68	10.06	10.77	11.15	12.60	9.23	9.61	10.32	10.70	12.15
8H	4H	9.15	9.57	10.22	10.64	12.08	8.77	9.19	9.84	10.26	11.71
	6H	9.77	10.12	10.87	11.23	12.67	9.39	9.73	10.48	10.85	12.29
	8H	9.99	10.29	11.09	11.39	12.85	9.60	9.90	10.70	11.00	12.46
	12H	10.12	10.38	11.22	11.47	12.97	9.70	9.97	10.81	11.06	12.56
12H	4H	9.13	9.51	10.22	10.59	12.04	8.76	9.14	9.85	10.23	11.68
	6H	9.80	10.10	10.90	11.20	12.66	9.43	9.73	10.53	10.83	12.29
	8H	10.04	10.30	11.14	11.39	12.89	9.65	9.92	10.76	11.01	12.51

END OF REPORT