

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924007

Luminaire Tested: DFN2DIP-4P3F0-020D040US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924007
REPORT IS A COMBINATION OF REPORTS P900569 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D040US950-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5666.8 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924007

CATALOG NUMBER: DFN2DIP-4P3F0-020D040US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924007

CATALOG NUMBER: DFN2DIP-4P3F0-020D040US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74		57	57	57		41
1	94	90	86	83	85	81	78	75	65	63	61		50	48	47		36
2	86	78	72	67	77	71	66	62	57	53	50		44	41	39		32
3	78	69	62	56	70	62	56	51	50	46	42		39	36	33		28
4	71	61	53	47	64	55	49	43	44	40	36		34	31	28		25
5	65	54	46	40	59	49	42	37	40	35	31		31	27	25		23
6	60	48	41	35	54	44	37	32	36	31	27		28	24	21		20
7	56	44	36	30	50	40	33	28	32	27	23		25	22	19		19
8	51	39	32	27	46	36	29	25	29	24	21		23	19	17		17
9	48	36	29	24	43	33	26	22	27	22	19		21	18	15		16
10	45	33	26	21	40	30	24	20	25	20	17		19	16	14		15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	846	846	846
5°	847	834	840
10°	839	822	828
15°	827	808	810
20°	809	788	792
25°	792	765	770
30°	771	744	743
35°	751	719	715
40°	726	693	687
45°	701	668	660
50°	674	641	628
55°	645	609	598
60°	613	573	564
65°	578	535	524
70°	533	488	480
75°	471	432	440
80°	396	361	363
85°	278	239	238

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 879 cd/sqm

TEST NUMBER: P924007

CATALOG NUMBER: DFN2DIP-4P3F0-020D040US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.9	1.2
10°-20°	196.6	3.5
20°-30°	288.9	5.1
30°-40°	335.6	5.9
40°-50°	335.2	5.9
50°-60°	292.2	5.2
60°-70°	216.0	3.8
70°-80°	122.2	2.2
80°-90°	34.5	0.6
90°-100°	42.5	0.7
100°-110°	158.3	2.8
110°-120°	419.9	7.4
120°-130°	696.4	12.3
130°-140°	739.7	13.1
140°-150°	687.5	12.1
150°-160°	552.7	9.8
160°-170°	356.1	6.3
170°-180°	122.6	2.2
0°-30°	555.4	9.8
0°-40°	891.0	15.7
0°-60°	1518.4	26.8
0°-90°	1891.2	33.4
90°-120°	620.6	11.0
90°-150°	2744.1	48.4
90°-180°	3776.0	66.6
0°-180°	5666.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	742	740	732	737	736	70
15°	707	702	693	696	692	199
25°	640	634	622	623	622	294
35°	552	545	533	529	525	345
45°	449	444	433	426	423	347
55°	340	336	327	318	315	304
65°	229	225	218	211	208	227
75°	120	119	115	111	112	128
85°	29	28	28	26	25	33
90°	1	11	19	23	25	5
95°	60	30	36	41	40	72
105°	283	311	57	67	71	303
115°	536	552	575	144	76	527
125°	758	770	787	794	797	676
135°	938	952	961	970	968	724
145°	1088	1087	1102	1109	1104	680
155°	1198	1189	1200	1206	1198	552
165°	1262	1256	1259	1266	1259	356
175°	1291	1284	1286	1292	1283	123
180°	1288	1288	1288	1288	1288	

TEST NUMBER: P924007

CATALOG NUMBER: DFN2DIP-4P3F0-020D040US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	742.4	742.4	742.4	742.4	742.4
2.5°	746.7	743.2	735.2	742.4	741.1
5°	742.4	739.6	731.7	737.4	736.0
7.5°	737.4	733.1	725.3	731.1	729.6
10°	729.6	724.7	716.1	721.7	719.6
12.5°	718.8	714.6	706.1	709.6	708.2
15°	706.7	702.5	693.2	696.0	692.5
17.5°	691.7	687.5	678.2	681.7	678.2
20°	675.3	671.0	661.0	663.2	660.4
22.5°	658.9	652.5	643.2	643.2	641.8
25°	639.7	633.9	621.8	623.2	621.8
27.5°	618.2	613.2	604.0	601.9	598.3
30°	596.8	591.1	580.4	578.3	575.4
32.5°	573.9	569.7	558.3	554.0	551.1
35°	551.9	544.7	533.3	529.0	525.4
37.5°	526.9	520.4	509.0	504.0	500.4
40°	501.1	495.4	484.0	477.7	474.7
42.5°	476.1	470.4	459.1	451.9	447.6
45°	449.0	444.1	433.3	425.5	422.6
47.5°	422.6	417.7	406.2	398.3	394.1
50°	394.8	391.2	381.2	371.2	367.7
52.5°	367.7	362.6	353.4	345.5	340.6
55°	339.8	335.5	326.9	318.4	314.8
57.5°	312.0	308.4	299.1	290.6	287.6
60°	284.1	281.3	271.3	263.4	261.3
62.5°	257.0	252.0	244.9	237.7	234.9
65°	229.2	224.9	217.8	211.3	207.8
67.5°	200.6	197.0	190.6	185.6	182.8
70°	174.2	171.3	164.9	159.9	157.1
72.5°	147.1	144.2	140.6	135.7	133.6
75°	119.9	118.6	114.9	110.7	112.1
77.5°	95.7	92.8	91.3	89.2	87.1
80°	71.5	70.7	69.3	67.1	65.6
82.5°	48.6	48.6	47.9	45.0	45.0
85°	29.2	28.5	27.9	25.7	25.0
87.5°	12.9	11.4	10.0	7.9	7.2
90°	0.9	11.2	18.6	23.4	25.1
92.5°	23.4	19.6	22.3	24.2	25.1
95°	60.5	29.8	36.3	41.0	40.1
97.5°	109.0	32.6	47.5	50.4	51.2
100°	164.9	37.3	53.1	60.5	62.4
102.5°	226.4	224.7	55.0	65.2	68.0
105°	283.2	311.3	56.9	67.1	70.8
107.5°	349.5	372.7	58.8	69.0	72.7
110°	412.9	432.4	163.1	69.9	73.6

TEST NUMBER: P924007

CATALOG NUMBER: DFN2DIP-4P3F0-020D040US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	472.5	489.2	473.4	71.7	74.6
115°	535.8	551.6	575.0	143.5	76.5
117.5°	590.8	609.4	625.3	492.0	247.8
120°	652.3	666.3	683.1	694.3	568.5
122.5°	704.4	719.4	738.1	743.6	744.6
125°	757.6	769.8	787.4	794.0	796.8
127.5°	806.0	819.1	833.1	842.5	843.3
130°	851.7	866.7	876.8	887.1	886.3
132.5°	898.3	910.5	920.7	929.1	928.2
135°	937.5	952.5	960.8	970.1	968.3
137.5°	978.4	989.6	999.0	1008.3	1005.5
140°	1018.5	1026.0	1036.2	1044.6	1040.0
142.5°	1052.2	1058.7	1070.8	1078.1	1073.5
145°	1087.6	1086.6	1102.3	1108.9	1104.3
147.5°	1118.2	1115.4	1131.3	1135.9	1132.3
150°	1148.0	1141.6	1156.5	1162.1	1157.4
152.5°	1173.2	1165.8	1179.7	1185.3	1178.9
155°	1197.5	1189.2	1200.3	1205.9	1198.4
157.5°	1217.0	1209.6	1218.1	1224.6	1217.0
160°	1233.8	1228.2	1233.8	1239.3	1232.9
162.5°	1248.7	1243.2	1247.8	1254.3	1245.9
165°	1261.8	1256.2	1259.0	1265.5	1259.0
167.5°	1272.1	1266.3	1269.3	1275.8	1267.4
170°	1280.5	1274.8	1276.6	1283.2	1274.8
172.5°	1286.0	1280.5	1282.4	1288.9	1280.5
175°	1290.6	1284.1	1286.0	1292.5	1283.2
177.5°	1292.5	1286.0	1286.9	1293.5	1285.1
180°	1287.9	1287.9	1287.9	1287.9	1287.9

TEST NUMBER: P924007

CATALOG NUMBER: DFN2DIP-4P3F0-020D040US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.88	5.61	5.97	6.70	8.19	4.44	5.17	5.53	6.26	7.75
	3H	6.53	7.18	7.63	8.28	9.79	6.04	6.69	7.14	7.79	9.30
	4H	7.11	7.73	8.22	8.83	10.34	6.62	7.24	7.72	8.33	9.85
	6H	7.50	8.07	8.62	9.17	10.69	7.00	7.57	8.11	8.67	10.19
	8H	7.60	8.14	8.72	9.26	10.78	7.10	7.64	8.22	8.75	10.27
	12H	7.64	8.16	8.76	9.27	10.81	7.13	7.65	8.26	8.76	10.30
4H	2H	5.33	5.95	6.44	7.04	8.56	4.97	5.59	6.09	6.69	8.20
	3H	7.17	7.69	8.29	8.81	10.34	6.77	7.28	7.89	8.41	9.93
	4H	7.88	8.36	9.00	9.47	11.01	7.46	7.93	8.58	9.04	10.59
	6H	8.38	8.79	9.51	9.93	11.46	7.95	8.36	9.08	9.49	11.03
	8H	8.53	8.91	9.66	10.04	11.59	8.09	8.47	9.22	9.60	11.15
	12H	8.59	8.94	9.74	10.08	11.64	8.14	8.49	9.29	9.63	11.19
8H	4H	8.06	8.44	9.19	9.57	11.12	7.68	8.07	8.82	9.19	10.75
	6H	8.68	9.00	9.83	10.17	11.72	8.30	8.61	9.45	9.78	11.33
	8H	8.90	9.17	10.06	10.32	11.89	8.50	8.78	9.66	9.93	11.50
	12H	9.02	9.26	10.18	10.41	12.01	8.61	8.85	9.77	10.00	11.60
12H	4H	8.04	8.38	9.19	9.52	11.08	7.67	8.02	8.82	9.16	10.72
	6H	8.71	8.98	9.87	10.13	11.70	8.34	8.61	9.49	9.76	11.33
	8H	8.94	9.18	10.10	10.33	11.93	8.56	8.80	9.72	9.95	11.55

END OF REPORT