

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332977-940

Luminaire Tested: **SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332977-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6916.5 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332977-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332977-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	62	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12999	12999	12999
5°	13028	12869	12949
10°	12946	12714	12714
15°	12797	12447	12354
20°	12594	12095	11874
25°	12333	11685	11388
30°	12078	11251	10781
35°	11798	10801	10170
40°	11460	10290	9511
45°	11147	9782	8840
50°	10792	9198	8130
55°	10412	8590	7357
60°	9993	7923	6570
65°	9608	7089	5794
70°	9050	6170	4919
75°	8344	5115	3999
80°	7280	3896	3668
85°	6169	3548	3316



TEST NUMBER: P332977-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.2
10°-20°	421.8	6.1
20°-30°	609.1	8.8
30°-40°	690.4	10.0
40°-50°	666.7	9.6
50°-60°	554.4	8.0
60°-70°	382.8	5.5
70°-80°	194.0	2.8
80°-90°	53.2	0.8
90°-100°	75.9	1.1
100°-110°	224.9	3.3
110°-120°	381.7	5.5
120°-130°	503.2	7.3
130°-140°	565.2	8.2
140°-150°	555.4	8.0
150°-160°	467.1	6.8
160°-170°	310.8	4.5
170°-180°	108.8	1.6
0°-30°	1182.1	17.1
0°-40°	1872.5	27.1
0°-60°	3093.5	44.7
0°-90°	3723.5	53.8
90°-120°	682.4	9.9
90°-150°	2306.2	33.3
90°-180°	3193.0	46.2
0°-180°	6916.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1608	1602	1588	1599	1598	152
15°	1531	1519	1489	1486	1478	431
25°	1385	1361	1312	1291	1278	638
35°	1197	1156	1096	1055	1032	748
45°	976	929	857	799	774	753
55°	740	689	610	548	523	661
65°	503	449	371	320	303	497
75°	268	221	164	137	128	282
85°	67	43	38	36	36	75
90°	3	12	20	25	27	7
95°	53	61	68	70	70	59
105°	207	208	212	214	217	220
115°	388	388	386	385	384	383
125°	565	565	564	562	561	504
135°	729	734	734	732	730	564
145°	886	889	890	889	886	554
155°	1015	1015	1014	1017	1014	467
165°	1105	1102	1100	1105	1102	311
175°	1149	1145	1144	1149	1144	109
180°	1151	1151	1151	1151	1151	



TEST NUMBER: P332977-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1614.1	1613.2	1612.3	1611.5	1610.6	1608.9	1606.5	1604.1	1601.7	1599.3	1601.7
5°	1607.7	1606.6	1605.5	1604.4	1603.3	1601.1	1597.9	1594.6	1591.3	1588.0	1590.7
7.5°	1593.1	1592.0	1590.8	1589.7	1588.5	1585.8	1581.5	1577.3	1573.0	1568.7	1570.5
10°	1579.3	1578.0	1576.5	1575.2	1573.9	1570.7	1565.8	1560.9	1555.9	1551.0	1552.0
12.5°	1561.6	1560.0	1558.4	1556.8	1555.2	1551.5	1545.7	1539.9	1534.1	1528.3	1528.9
15°	1531.2	1528.7	1526.3	1523.8	1521.3	1516.7	1509.8	1503.0	1496.2	1489.3	1488.8
17.5°	1494.5	1490.9	1487.4	1483.8	1480.2	1474.4	1466.2	1457.9	1449.7	1441.5	1439.9
20°	1465.9	1462.3	1458.7	1455.2	1451.6	1445.2	1435.9	1426.6	1417.3	1407.9	1405.8
22.5°	1434.3	1430.3	1426.3	1422.4	1418.4	1411.3	1401.4	1391.4	1381.4	1371.5	1368.2
25°	1384.6	1379.6	1374.7	1369.8	1364.8	1356.7	1345.5	1334.3	1323.0	1311.8	1307.2
27.5°	1332.2	1326.1	1319.9	1313.7	1307.5	1298.4	1286.4	1274.4	1262.4	1250.4	1244.6
30°	1295.7	1288.9	1282.1	1275.2	1268.4	1258.5	1245.6	1232.7	1219.9	1207.0	1200.2
32.5°	1257.3	1249.6	1241.8	1234.1	1226.4	1215.8	1202.6	1189.3	1175.9	1162.6	1154.7
35°	1197.1	1188.4	1179.6	1170.8	1162.1	1150.8	1137.1	1123.5	1109.7	1096.0	1086.7
37.5°	1132.7	1123.7	1114.7	1105.6	1096.6	1084.5	1069.3	1054.2	1038.9	1023.8	1013.3
40°	1087.4	1078.3	1069.3	1060.2	1051.2	1038.9	1023.3	1007.6	992.0	976.4	964.9
42.5°	1044.0	1034.6	1025.0	1015.6	1006.1	993.2	977.0	960.6	944.4	928.1	916.4
45°	976.4	966.3	956.2	946.0	935.9	922.6	906.2	889.7	873.3	856.8	843.5
47.5°	906.7	896.2	885.7	875.3	864.8	851.0	833.9	816.8	799.7	782.7	768.7
50°	859.3	848.6	837.9	827.2	816.5	802.5	785.0	767.4	749.8	732.4	718.6
52.5°	811.0	800.5	790.1	779.6	769.1	754.9	736.9	719.0	701.0	683.1	669.1
55°	739.8	728.8	717.8	706.9	695.9	681.5	663.7	645.9	628.1	610.3	596.0
57.5°	669.2	657.8	646.4	635.0	623.7	609.1	591.7	574.1	556.5	539.0	524.6
60°	618.9	608.0	597.0	586.0	575.1	560.8	543.3	525.8	508.2	490.7	476.4
62.5°	573.5	562.1	550.7	539.3	528.0	513.3	495.3	477.3	459.3	441.4	428.2
65°	503.0	491.2	479.5	467.7	455.9	441.2	423.7	406.2	388.6	371.1	359.4
67.5°	429.8	418.5	407.2	395.9	384.6	370.9	354.5	338.3	322.0	305.8	295.6
70°	383.4	371.9	360.4	348.9	337.4	323.9	308.3	292.6	277.0	261.4	252.4
72.5°	334.1	323.7	313.3	302.9	292.5	279.9	265.2	250.4	235.7	221.0	213.2
75°	267.5	257.4	247.3	237.1	227.0	215.4	202.6	189.8	176.8	164.0	157.7
77.5°	200.0	191.4	182.8	174.2	165.6	156.0	145.6	135.3	124.8	114.4	110.8
80°	156.6	148.6	140.7	132.8	124.8	116.7	108.5	100.3	92.0	83.8	83.0
82.5°	119.1	111.8	104.5	97.2	90.0	83.9	79.3	74.5	69.8	65.1	64.5
85°	66.6	61.1	55.6	50.1	44.7	41.5	40.7	39.9	39.1	38.3	37.6
87.5°	23.2	21.9	20.6	19.3	17.9	17.3	17.4	17.6	17.7	17.7	17.7
90°	2.7	4.8	7.0	9.2	11.4	13.3	14.8	16.4	18.0	19.6	20.8
92.5°	19.1	21.6	24.0	26.5	29.0	30.9	31.9	33.0	34.2	35.2	35.9
95°	53.4	55.2	57.0	58.8	60.5	62.1	63.5	64.9	66.3	67.7	68.2
97.5°	93.3	94.7	96.1	97.6	99.0	100.5	102.1	103.7	105.4	107.0	107.7
100°	124.6	125.4	126.2	127.0	127.8	129.0	130.8	132.6	134.4	136.2	136.6
102.5°	157.4	157.7	158.0	158.3	158.6	159.6	161.2	162.8	164.4	166.1	166.7
105°	207.4	207.6	207.8	207.9	208.2	208.7	209.5	210.3	211.1	211.9	212.4
107.5°	259.9	260.1	260.4	260.6	260.8	261.0	261.2	261.3	261.4	261.5	262.1
110°	295.5	295.9	296.3	296.7	297.1	297.2	296.9	296.8	296.6	296.4	296.0



TEST NUMBER: P332977-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	332.5	332.6	332.7	332.8	332.9	332.7	332.3	332.0	331.6	331.3	331.2
115°	388.1	388.1	388.1	388.1	388.1	387.9	387.4	387.1	386.6	386.3	386.1
117.5°	440.4	440.6	440.7	440.9	441.0	441.0	440.7	440.4	440.1	439.9	439.2
120°	475.3	476.1	476.9	477.7	478.5	478.6	478.0	477.3	476.8	476.2	475.2
122.5°	511.6	511.9	512.2	512.6	512.8	512.9	512.6	512.3	512.0	511.8	511.1
125°	565.2	565.2	565.2	565.2	565.2	565.1	564.9	564.7	564.5	564.3	563.9
127.5°	613.8	614.4	614.9	615.5	616.2	616.3	616.0	615.6	615.4	615.0	614.7
130°	647.9	648.5	649.2	649.7	650.3	650.6	650.6	650.6	650.6	650.6	650.2
132.5°	682.9	683.3	683.7	684.1	684.6	684.7	684.6	684.4	684.2	684.1	683.7
135°	729.0	730.1	731.3	732.5	733.7	734.3	734.3	734.3	734.3	734.3	733.9
137.5°	779.2	779.7	780.2	780.8	781.4	781.8	782.1	782.5	782.7	783.1	782.6
140°	812.6	813.0	813.4	813.8	814.2	814.4	814.4	814.4	814.4	814.4	814.2
142.5°	843.2	843.6	844.0	844.5	844.8	844.9	844.8	844.6	844.5	844.3	844.3
145°	885.6	886.4	887.2	888.0	888.8	889.2	889.5	889.7	889.8	890.0	889.8
147.5°	927.6	928.5	929.5	930.5	931.4	931.8	931.7	931.5	931.3	931.2	931.0
150°	953.2	954.0	954.8	955.6	956.4	956.8	956.8	956.8	956.8	956.8	956.8
152.5°	977.5	977.9	978.4	978.9	979.4	979.6	979.8	980.0	980.2	980.3	980.8
155°	1014.7	1014.7	1014.7	1014.7	1014.7	1014.6	1014.3	1014.1	1014.0	1013.8	1014.6
157.5°	1046.0	1045.6	1045.3	1044.9	1044.6	1044.4	1044.3	1044.3	1044.3	1044.2	1044.8
160°	1064.5	1064.3	1064.1	1063.9	1063.7	1063.5	1063.3	1063.1	1062.9	1062.7	1063.3
162.5°	1081.6	1081.1	1080.6	1080.0	1079.5	1079.1	1079.0	1078.8	1078.6	1078.3	1079.4
165°	1104.6	1103.9	1103.4	1102.8	1102.2	1101.7	1101.3	1100.9	1100.5	1100.1	1101.3
167.5°	1122.2	1121.3	1120.5	1119.7	1118.8	1118.5	1118.5	1118.6	1118.6	1118.7	1119.8
170°	1132.1	1131.1	1130.2	1129.2	1128.2	1127.7	1128.0	1128.2	1128.4	1128.5	1129.8
172.5°	1139.2	1138.4	1137.6	1136.8	1136.0	1135.5	1135.6	1135.6	1135.7	1135.7	1137.0
175°	1149.1	1148.1	1147.1	1146.1	1145.1	1144.5	1144.3	1144.1	1143.9	1143.7	1145.1
177.5°	1152.3	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1149.8
180°	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8



TEST NUMBER: P332977-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2	1610.2
2.5°	1604.1	1606.5	1608.9	1610.1	1609.8	1609.6	1609.4	1609.2
5°	1593.4	1596.2	1598.9	1600.0	1599.5	1598.9	1598.4	1597.9
7.5°	1572.3	1574.0	1575.7	1576.2	1575.3	1574.4	1573.5	1572.6
10°	1553.2	1554.3	1555.3	1555.3	1554.3	1553.2	1552.0	1551.0
12.5°	1529.6	1530.3	1530.9	1530.4	1528.9	1527.4	1525.9	1524.4
15°	1488.3	1487.6	1487.1	1485.9	1484.0	1482.0	1480.2	1478.2
17.5°	1438.4	1436.9	1435.4	1433.2	1430.2	1427.4	1424.4	1421.5
20°	1403.6	1401.4	1399.2	1396.3	1392.8	1389.2	1385.6	1382.1
22.5°	1364.9	1361.6	1358.3	1355.2	1352.3	1349.4	1346.5	1343.6
25°	1302.4	1297.8	1293.2	1289.4	1286.7	1284.0	1281.2	1278.5
27.5°	1238.9	1233.1	1227.4	1222.5	1218.6	1214.6	1210.7	1206.8
30°	1193.3	1186.4	1179.6	1173.9	1169.6	1165.2	1160.8	1156.5
32.5°	1146.7	1138.8	1130.9	1124.8	1120.6	1116.4	1112.3	1108.1
35°	1077.4	1068.1	1058.7	1051.7	1046.7	1041.8	1036.9	1031.9
37.5°	1003.0	992.6	982.1	974.5	969.6	964.6	959.7	954.8
40°	953.4	941.9	930.4	922.2	917.3	912.3	907.4	902.5
42.5°	904.6	893.0	881.2	872.8	867.6	862.5	857.3	852.2
45°	830.0	816.5	803.2	794.0	789.1	784.1	779.2	774.3
47.5°	754.8	740.9	726.9	717.3	711.9	706.4	701.0	695.6
50°	704.9	691.3	677.5	668.1	662.9	657.6	652.5	647.3
52.5°	655.1	641.2	627.3	617.7	612.2	606.8	601.4	596.0
55°	581.8	567.6	553.3	543.6	538.3	533.2	528.0	522.7
57.5°	510.1	495.6	481.2	472.0	468.0	464.0	460.1	456.2
60°	462.2	447.9	433.7	424.4	420.0	415.6	411.3	406.9
62.5°	415.1	401.9	388.8	380.4	376.9	373.4	369.9	366.4
65°	347.5	335.7	324.0	316.5	313.2	309.9	306.6	303.3
67.5°	285.4	275.4	265.2	258.3	254.7	251.1	247.4	243.9
70°	243.3	234.3	225.2	219.3	216.6	213.8	211.1	208.4
72.5°	205.5	197.8	190.0	184.9	182.4	179.9	177.4	174.9
75°	151.4	145.1	138.8	134.8	133.1	131.5	129.8	128.2
77.5°	107.1	103.4	99.7	97.6	97.1	96.7	96.1	95.7
80°	82.2	81.4	80.5	80.0	79.7	79.5	79.2	78.9
82.5°	63.8	63.3	62.7	62.2	62.0	61.7	61.4	61.2
85°	37.1	36.6	36.0	35.8	35.8	35.8	35.8	35.8
87.5°	17.7	17.7	17.8	17.9	18.3	18.5	18.8	19.2
90°	21.9	23.2	24.3	25.1	25.5	25.9	26.3	26.7
92.5°	36.6	37.4	38.1	38.6	38.8	39.1	39.3	39.5
95°	68.8	69.5	70.0	70.4	70.4	70.4	70.4	70.4
97.5°	108.4	109.1	109.9	110.2	110.2	110.2	110.2	110.2
100°	137.0	137.3	137.8	137.9	137.9	137.9	137.9	137.9
102.5°	167.2	167.7	168.3	168.6	168.8	169.0	169.2	169.2
105°	213.0	213.7	214.2	214.8	215.3	216.0	216.6	217.1
107.5°	262.6	263.1	263.7	263.9	263.9	263.9	263.9	263.8
110°	295.6	295.2	294.8	294.9	295.5	296.0	296.7	297.3



TEST NUMBER: P332977-940

CATALOG NUMBER: SA4XXRDIP-C1020D1035U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	331.1	331.0	331.0	331.0	331.1	331.2	331.4	331.4
115°	385.8	385.7	385.5	385.3	385.1	384.9	384.7	384.5
117.5°	438.5	437.8	437.2	436.7	436.2	435.9	435.4	435.1
120°	474.2	473.2	472.3	471.9	472.3	472.7	473.1	473.5
122.5°	510.4	509.8	509.1	508.4	507.7	506.9	506.2	505.5
125°	563.5	563.1	562.7	562.3	562.0	561.5	561.2	560.7
127.5°	614.2	613.9	613.4	613.1	612.8	612.4	612.2	611.8
130°	649.9	649.4	649.1	648.5	647.6	646.8	646.0	645.2
132.5°	683.3	682.9	682.5	682.2	681.8	681.5	681.2	680.9
135°	733.5	733.1	732.7	732.2	731.6	731.0	730.4	729.9
137.5°	782.0	781.5	781.0	780.8	781.0	781.0	781.1	781.3
140°	814.0	813.8	813.6	813.4	813.2	813.0	812.8	812.6
142.5°	844.2	844.2	844.2	844.1	844.1	844.0	844.0	843.9
145°	889.7	889.5	889.2	888.9	888.2	887.7	887.1	886.4
147.5°	930.9	930.7	930.5	930.3	930.1	930.0	929.8	929.6
150°	956.8	956.8	956.8	956.7	956.5	956.3	956.1	955.9
152.5°	981.2	981.7	982.2	982.2	981.7	981.1	980.6	980.1
155°	1015.4	1016.1	1016.9	1016.9	1016.1	1015.4	1014.6	1013.8
157.5°	1045.4	1046.0	1046.6	1046.5	1045.9	1045.2	1044.6	1043.8
160°	1063.9	1064.5	1065.1	1064.9	1063.9	1062.9	1061.9	1061.0
162.5°	1080.5	1081.6	1082.6	1082.7	1081.7	1080.8	1079.8	1078.7
165°	1102.5	1103.7	1104.8	1105.0	1104.3	1103.5	1102.7	1101.9
167.5°	1121.0	1122.2	1123.4	1123.4	1122.1	1120.9	1119.6	1118.5
170°	1131.0	1132.1	1133.4	1133.2	1131.8	1130.4	1129.1	1127.7
172.5°	1138.4	1139.7	1141.1	1141.0	1139.7	1138.3	1136.9	1135.5
175°	1146.5	1147.9	1149.2	1149.2	1147.9	1146.5	1145.1	1143.7
177.5°	1150.9	1152.0	1153.2	1153.1	1151.8	1150.5	1149.2	1148.0
180°	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8

(END OF REPORT)