

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332956-940

Luminaire Tested: **SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332956-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4999.1 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	77				
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	72	70	67				
2	96	89	83	77	91	85	79	75	78	73	70	71	68	65	65	63	60	57				
3	88	79	71	65	84	75	69	63	69	64	59	64	59	56	58	55	52	49				
4	81	70	62	56	77	67	60	54	62	56	51	57	52	48	53	49	45	43				
5	75	63	55	49	71	60	53	47	56	50	45	52	46	42	48	43	40	37				
6	69	57	49	43	66	55	47	42	51	44	40	47	42	37	43	39	35	33				
7	64	52	43	38	61	50	42	37	46	40	35	43	37	33	40	35	32	30				
8	60	47	39	34	57	45	38	33	42	36	32	39	34	30	37	32	29	27				
9	56	43	36	30	53	42	35	30	39	33	28	36	31	27	34	29	26	24				
10	52	40	33	28	50	39	32	27	36	30	26	34	29	25	32	27	24	22				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12352	12352	12352	12352
5°	14327	12388	10950	12388
10°	16948	12336	9773	12336
15°	19578	12221	8398	12221
20°	21798	12064	7594	12064
25°	22502	11909	7050	11909
30°	19699	11723	6723	11723
35°	15334	11446	6525	11446
40°	11499	11129	6418	11129
45°	9079	10620	6361	10620
50°	7665	10034	6179	10034
55°	6681	9388	5847	9388
60°	6011	8719	5176	8719
65°	5299	7996	4451	7996
70°	4773	7246	4015	7246
75°	3999	6422	3425	6422
80°	3384	5472	3208	5472
85°	2862	4279	2862	4279



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.2	3.0
10°-20°	447.2	8.9
20°-30°	699.4	14.0
30°-40°	777.5	15.6
40°-50°	689.9	13.8
50°-60°	537.6	10.8
60°-70°	351.9	7.0
70°-80°	173.1	3.5
80°-90°	43.9	0.9
90°-100°	26.9	0.5
100°-110°	79.6	1.6
110°-120°	135.1	2.7
120°-130°	178.2	3.6
130°-140°	200.1	4.0
140°-150°	196.6	3.9
150°-160°	165.4	3.3
160°-170°	110.0	2.2
170°-180°	38.5	0.8
0°-30°	1294.9	25.9
0°-40°	2072.4	41.5
0°-60°	3299.8	66.0
0°-90°	3868.7	77.4
90°-120°	241.6	4.8
90°-150°	816.5	16.3
90°-180°	1130.0	22.6
0°-180°	4999.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1530	1530	1530	1530	1530	
5°	1768	1529	1351	1529	1768	179
15°	2342	1462	1005	1462	2342	666
25°	2526	1337	792	1337	2526	1121
35°	1556	1161	662	1161	1556	975
45°	795	930	557	930	795	630
55°	475	667	415	667	475	432
65°	277	419	233	419	277	279
75°	128	206	110	206	128	141
85°	31	46	31	46	31	35
90°	10	1	10	1	10	6
95°	25	19	25	19	25	26
105°	77	73	77	73	77	81
115°	136	137	136	137	136	135
125°	198	200	198	200	198	177
135°	258	258	258	258	258	200
145°	314	314	314	314	314	196
155°	359	359	359	359	359	165
165°	390	391	390	391	390	110
175°	405	407	405	407	405	38
180°	407	407	407	407	407	



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1613.8	1618.3	1613.8	1613.4	1608.5	1607.0	1605.0	1598.6	1586.7	1579.8	1581.3
5°	1768.0	1783.3	1774.8	1773.5	1760.0	1746.4	1737.8	1718.1	1697.1	1682.9	1671.2
7.5°	1946.2	1955.1	1949.7	1941.1	1919.1	1906.7	1886.7	1860.6	1823.1	1794.3	1768.1
10°	2067.5	2074.9	2072.5	2056.5	2040.4	2007.8	1989.2	1952.9	1905.4	1867.9	1832.6
12.5°	2186.9	2194.8	2173.1	2173.8	2143.5	2117.7	2088.4	2042.6	1987.8	1939.3	1895.3
15°	2342.5	2332.6	2332.6	2320.3	2286.3	2250.7	2220.4	2172.4	2103.3	2045.3	1984.3
17.5°	2464.3	2467.7	2462.7	2433.6	2407.0	2370.0	2314.6	2258.5	2194.4	2116.7	2054.2
20°	2537.3	2537.3	2531.7	2512.0	2477.5	2438.0	2378.3	2317.2	2235.9	2157.6	2087.3
22.5°	2566.9	2568.8	2562.3	2546.0	2515.0	2476.5	2425.5	2363.6	2279.7	2191.6	2104.5
25°	2526.2	2537.9	2539.1	2534.8	2525.6	2502.1	2458.4	2394.9	2319.7	2224.1	2130.4
27.5°	2319.3	2334.1	2347.1	2368.4	2396.7	2411.5	2413.5	2381.2	2315.6	2223.7	2129.3
30°	2113.2	2125.5	2165.6	2218.0	2258.6	2295.6	2327.7	2336.3	2299.4	2216.7	2117.5
32.5°	1884.4	1901.1	1941.2	1997.5	2065.3	2128.0	2199.9	2236.7	2235.7	2186.1	2094.3
35°	1555.9	1568.3	1605.3	1664.4	1745.8	1838.9	1952.9	2041.7	2102.0	2097.7	2041.7
37.5°	1254.8	1268.7	1306.1	1355.2	1434.1	1549.3	1659.7	1782.0	1893.7	1956.5	1937.7
40°	1091.1	1091.7	1128.1	1178.7	1252.6	1353.1	1473.3	1608.9	1733.4	1835.1	1854.8
42.5°	961.9	962.0	986.1	1040.5	1093.9	1188.4	1303.1	1437.8	1583.5	1701.0	1753.3
45°	795.2	800.8	820.5	853.2	895.1	975.2	1067.0	1192.2	1355.6	1494.9	1581.8
47.5°	673.4	681.5	694.1	720.8	754.1	807.5	883.5	996.0	1128.8	1282.1	1405.8
50°	610.3	611.5	627.5	642.3	671.3	713.8	780.4	874.1	996.1	1143.5	1280.9
52.5°	556.1	555.8	565.4	584.2	607.7	640.9	694.6	779.9	888.1	1020.2	1162.1
55°	474.7	477.8	485.2	499.9	517.8	541.3	583.8	647.9	733.0	845.8	974.6
57.5°	412.8	414.4	420.2	426.4	442.8	459.9	491.8	536.3	608.1	700.4	820.5
60°	372.3	372.9	374.8	384.1	397.0	413.0	434.6	472.2	532.6	617.1	712.0
62.5°	332.9	333.9	336.8	343.6	353.6	364.7	387.3	417.5	467.5	539.7	625.2
65°	277.4	278.0	282.3	284.8	292.8	302.6	319.3	339.7	374.2	434.6	499.4
67.5°	231.8	231.8	232.0	235.3	240.9	247.4	257.4	273.7	299.7	336.8	393.9
70°	202.2	202.2	203.4	205.3	208.4	213.9	219.5	231.8	250.9	281.1	324.9
72.5°	174.6	175.0	176.3	176.6	178.3	182.8	186.9	194.8	209.0	231.8	267.2
75°	128.2	130.1	133.1	135.6	138.7	138.1	142.4	147.3	151.7	165.2	185.6
77.5°	95.4	94.4	94.8	96.9	97.3	97.9	100.9	104.8	108.0	114.4	121.7
80°	72.8	72.8	74.5	75.2	74.5	75.2	78.3	80.2	81.4	83.8	90.6
82.5°	55.0	56.0	55.4	56.0	56.4	57.0	59.6	59.9	61.2	62.2	65.0
85°	30.9	31.5	32.0	30.9	30.9	30.9	32.0	32.6	33.9	33.3	34.5
87.5°	12.8	12.2	12.7	12.7	13.1	12.6	13.0	13.9	12.8	13.2	13.1
90°	9.5	9.3	9.2	9.0	8.9	8.6	8.2	7.8	7.3	7.0	6.3
92.5°	14.0	13.9	13.8	13.7	13.6	13.5	13.2	13.0	12.8	12.5	12.1
95°	24.9	24.9	24.9	24.9	24.9	24.8	24.6	24.3	24.2	24.0	23.5
97.5°	39.0	39.0	39.0	39.0	39.0	38.9	38.6	38.3	38.2	37.9	37.3
100°	48.9	48.9	48.9	48.9	48.9	48.8	48.6	48.5	48.3	48.2	47.6
102.5°	59.9	59.8	59.8	59.7	59.7	59.6	59.4	59.2	59.0	58.8	58.2
105°	76.9	76.7	76.5	76.2	76.1	75.8	75.6	75.4	75.2	75.0	74.7
107.5°	93.4	93.5	93.5	93.5	93.5	93.4	93.2	93.0	92.7	92.6	92.6
110°	105.2	105.0	104.9	104.6	104.4	104.3	104.5	104.7	104.8	105.0	105.0



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	117.3	117.3	117.3	117.3	117.2	117.2	117.2	117.3	117.3	117.3	117.4
115°	136.2	136.2	136.3	136.3	136.4	136.4	136.5	136.6	136.7	136.8	136.9
117.5°	154.0	154.2	154.3	154.4	154.6	154.8	155.0	155.2	155.5	155.7	155.8
120°	167.6	167.5	167.4	167.2	167.1	167.2	167.6	167.9	168.3	168.6	168.8
122.5°	179.0	179.2	179.5	179.8	179.9	180.2	180.5	180.7	180.9	181.2	181.3
125°	198.5	198.7	198.8	198.9	199.0	199.2	199.4	199.5	199.7	199.7	199.8
127.5°	216.6	216.7	216.9	217.0	217.0	217.1	217.3	217.5	217.6	217.8	217.8
130°	228.5	228.7	229.0	229.3	229.5	229.8	229.9	230.1	230.2	230.3	230.3
132.5°	241.0	241.2	241.3	241.4	241.5	241.7	241.7	241.9	242.0	242.2	242.3
135°	258.4	258.6	258.8	259.0	259.2	259.4	259.6	259.7	259.8	259.9	259.9
137.5°	276.6	276.5	276.5	276.4	276.4	276.5	276.7	276.9	277.1	277.2	277.1
140°	287.7	287.8	287.8	287.9	287.9	288.0	288.1	288.2	288.3	288.3	288.3
142.5°	298.8	298.8	298.8	298.8	298.8	298.8	298.9	298.9	298.9	298.9	299.0
145°	313.9	314.1	314.2	314.5	314.7	314.9	314.9	315.0	315.0	315.1	315.0
147.5°	329.1	329.1	329.2	329.3	329.4	329.4	329.5	329.6	329.6	329.7	329.8
150°	338.4	338.5	338.6	338.7	338.7	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	347.0	347.1	347.3	347.5	347.7	347.8	347.6	347.4	347.2	347.1	347.0
155°	358.9	359.2	359.4	359.7	360.0	360.0	359.7	359.4	359.2	358.9	359.0
157.5°	369.5	369.8	370.1	370.2	370.5	370.5	370.3	370.1	369.9	369.7	369.7
160°	375.6	375.9	376.3	376.7	377.0	377.1	376.8	376.7	376.5	376.2	376.3
162.5°	381.9	382.3	382.6	383.0	383.3	383.3	382.9	382.5	382.2	381.7	381.8
165°	390.1	390.4	390.7	390.9	391.2	391.1	390.7	390.3	389.9	389.5	389.6
167.5°	395.9	396.4	396.8	397.3	397.7	397.7	397.3	396.9	396.5	396.0	396.0
170°	399.2	399.8	400.2	400.7	401.2	401.3	400.8	400.4	399.9	399.6	399.5
172.5°	402.0	402.5	403.0	403.5	403.9	403.9	403.5	403.1	402.5	402.1	402.1
175°	404.9	405.4	405.9	406.4	406.9	406.9	406.4	405.9	405.4	404.9	405.0
177.5°	406.4	406.9	407.3	407.8	408.2	408.2	407.9	407.4	407.1	406.7	406.7
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1576.4	1569.5	1566.0	1558.1	1548.7	1543.8	1539.4	1532.9	1524.6	1515.7	1509.3
5°	1656.4	1641.6	1623.1	1600.9	1581.2	1562.1	1545.4	1528.7	1509.7	1490.0	1470.3
7.5°	1738.5	1709.4	1677.9	1641.6	1606.2	1574.0	1544.4	1516.1	1484.0	1455.3	1429.1
10°	1795.7	1756.2	1712.4	1666.3	1620.0	1579.9	1540.5	1504.8	1465.3	1430.1	1400.5
12.5°	1842.1	1795.7	1743.0	1685.5	1629.9	1581.4	1536.1	1489.4	1444.6	1406.5	1367.0
15°	1919.0	1855.5	1784.6	1715.6	1643.4	1577.4	1516.4	1462.2	1411.0	1357.5	1319.8
17.5°	1971.8	1896.6	1810.4	1727.4	1642.2	1564.4	1494.0	1429.4	1370.4	1315.6	1270.9
20°	2003.4	1920.2	1824.7	1730.4	1634.8	1551.6	1475.8	1404.3	1343.3	1284.1	1237.8
22.5°	2021.2	1929.1	1824.7	1725.9	1626.9	1536.8	1453.6	1379.1	1312.7	1253.5	1202.3
25°	2026.9	1928.2	1821.6	1708.2	1599.6	1504.1	1417.8	1337.0	1263.1	1203.9	1149.7
27.5°	2019.0	1902.8	1793.6	1677.2	1565.3	1464.5	1373.9	1289.1	1215.0	1151.6	1095.9
30°	2007.2	1882.6	1765.5	1644.7	1531.2	1434.5	1338.9	1257.6	1180.4	1114.5	1058.5
32.5°	1981.5	1858.0	1732.0	1608.2	1493.3	1393.6	1302.9	1221.0	1145.5	1078.1	1018.5
35°	1930.7	1805.5	1668.7	1541.8	1428.9	1325.3	1240.3	1161.4	1089.2	1017.2	954.2
37.5°	1863.8	1735.9	1599.8	1460.7	1347.8	1250.0	1172.0	1097.9	1027.5	961.6	892.0
40°	1800.6	1684.1	1543.6	1405.5	1289.6	1195.2	1123.2	1056.0	985.1	919.7	850.1
42.5°	1724.2	1625.0	1482.9	1344.3	1229.9	1139.1	1071.8	1006.1	941.6	878.3	805.7
45°	1596.6	1521.3	1388.2	1255.1	1139.8	1049.8	988.2	930.2	873.5	813.1	744.7
47.5°	1450.4	1399.5	1284.5	1148.2	1041.5	960.6	901.0	853.6	805.7	745.3	685.3
50°	1348.8	1316.1	1205.1	1080.7	978.9	904.3	843.3	798.9	758.8	700.9	647.3
52.5°	1240.3	1222.9	1129.2	1010.1	911.9	838.7	786.6	746.6	706.1	658.0	607.8
55°	1075.0	1084.3	1004.8	901.9	809.4	747.8	700.3	667.0	632.5	591.8	552.9
57.5°	906.2	940.0	886.5	796.2	709.5	652.6	616.8	588.8	559.8	526.1	492.9
60°	805.0	833.4	803.3	723.7	647.9	594.9	561.6	540.0	511.0	480.2	455.0
62.5°	706.4	736.7	718.9	654.7	584.2	538.7	509.3	489.2	467.6	440.8	414.5
65°	582.6	602.3	593.6	549.3	499.4	460.5	433.4	418.6	398.9	379.2	355.7
67.5°	446.2	484.3	479.2	455.7	412.5	382.2	364.4	351.3	333.4	318.7	302.8
70°	366.8	401.9	401.3	382.2	358.7	330.4	318.1	307.0	291.0	276.8	263.9
72.5°	300.2	332.4	337.2	322.5	306.5	285.1	273.2	265.6	250.0	240.3	229.8
75°	210.2	233.6	239.8	239.8	232.4	221.3	210.8	205.9	194.8	186.2	180.0
77.5°	137.9	152.7	162.3	164.4	165.6	161.8	153.3	149.8	141.2	138.2	132.3
80°	97.4	107.3	118.3	122.1	125.1	123.9	120.2	117.7	109.8	106.6	104.2
82.5°	67.3	72.8	81.9	90.0	89.2	92.4	89.2	87.2	81.1	80.0	77.6
85°	35.1	35.8	37.0	42.5	45.7	46.8	47.4	46.2	44.4	44.4	40.0
87.5°	13.0	12.4	13.3	13.1	13.5	15.2	16.6	16.9	15.6	14.3	13.0
90°	5.8	5.3	4.7	4.0	3.3	2.5	1.7	1.0	1.7	2.5	3.3
92.5°	11.7	11.3	10.9	10.3	9.4	8.5	7.7	6.8	7.7	8.5	9.4
95°	23.0	22.5	22.0	21.4	20.8	20.2	19.5	18.9	19.5	20.2	20.8
97.5°	36.7	36.1	35.6	35.0	34.5	34.1	33.5	33.0	33.5	34.1	34.5
100°	47.0	46.3	45.7	45.2	44.9	44.7	44.4	44.1	44.4	44.7	44.9
102.5°	57.7	57.1	56.5	56.2	56.1	55.9	55.8	55.7	55.8	55.9	56.1
105°	74.5	74.2	73.8	73.7	73.7	73.6	73.5	73.4	73.5	73.6	73.7
107.5°	92.5	92.5	92.4	92.4	92.3	92.2	92.1	92.0	92.1	92.2	92.3
110°	105.0	105.1	105.2	105.1	105.0	104.9	104.8	104.6	104.8	104.9	105.0



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	117.5	117.6	117.8	117.8	117.8	117.8	117.7	117.7	117.7	117.8	117.8
115°	137.1	137.1	137.3	137.4	137.4	137.4	137.4	137.4	137.4	137.4	137.4
117.5°	156.0	156.0	156.1	156.1	156.0	156.0	156.0	155.9	156.0	156.0	156.0
120°	169.0	169.2	169.4	169.4	169.1	168.8	168.5	168.3	168.5	168.8	169.1
122.5°	181.4	181.5	181.6	181.6	181.5	181.4	181.2	181.1	181.2	181.4	181.5
125°	199.9	200.0	200.0	200.1	200.1	200.1	200.1	200.1	200.1	200.1	200.1
127.5°	217.9	218.1	218.2	218.1	217.9	217.8	217.5	217.3	217.5	217.8	217.9
130°	230.3	230.3	230.3	230.2	230.1	229.8	229.6	229.4	229.6	229.8	230.1
132.5°	242.3	242.4	242.4	242.4	242.2	242.0	241.9	241.7	241.9	242.0	242.2
135°	259.9	259.9	259.9	259.8	259.3	258.9	258.5	258.1	258.5	258.9	259.3
137.5°	277.0	276.9	276.8	276.6	276.4	276.3	276.1	275.8	276.1	276.3	276.4
140°	288.3	288.3	288.3	288.3	288.1	287.9	287.8	287.7	287.8	287.9	288.1
142.5°	299.0	299.1	299.2	299.1	298.9	298.8	298.6	298.5	298.6	298.8	298.9
145°	315.0	314.9	314.9	314.7	314.3	314.1	313.8	313.5	313.8	314.1	314.3
147.5°	329.8	329.8	329.8	329.8	329.4	329.0	328.8	328.4	328.8	329.0	329.4
150°	338.8	338.8	338.8	338.6	338.3	338.0	337.8	337.5	337.8	338.0	338.3
152.5°	347.0	346.9	346.8	346.7	346.5	346.3	346.3	346.1	346.3	346.3	346.5
155°	359.0	359.1	359.2	359.2	359.2	359.2	359.2	359.2	359.2	359.2	359.2
157.5°	369.7	369.7	369.7	369.8	370.0	370.1	370.1	370.3	370.1	370.1	370.0
160°	376.4	376.5	376.5	376.6	376.7	376.7	376.7	376.8	376.7	376.7	376.7
162.5°	381.9	382.0	382.1	382.2	382.4	382.5	382.7	382.9	382.7	382.5	382.4
165°	389.8	389.9	390.0	390.2	390.4	390.7	390.8	391.0	390.8	390.7	390.4
167.5°	396.0	396.0	395.9	396.1	396.4	396.7	397.0	397.3	397.0	396.7	396.4
170°	399.4	399.3	399.3	399.4	399.8	400.1	400.5	400.8	400.5	400.1	399.8
172.5°	402.1	402.0	402.0	402.2	402.4	402.7	403.1	403.3	403.1	402.7	402.4
175°	405.0	405.1	405.2	405.4	405.7	406.1	406.4	406.8	406.4	406.1	405.7
177.5°	406.7	406.7	406.7	406.8	407.1	407.3	407.7	408.0	407.7	407.3	407.1
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1502.4	1497.4	1491.0	1483.6	1474.8	1466.9	1463.5	1466.4	1467.8	1463.9	1463.5
5°	1456.7	1441.3	1428.9	1410.4	1395.6	1383.3	1374.7	1371.0	1372.2	1362.4	1359.9
7.5°	1405.2	1387.0	1366.8	1344.8	1324.4	1306.3	1296.7	1291.6	1281.1	1276.7	1269.2
10°	1372.2	1347.6	1327.8	1301.9	1278.5	1257.0	1246.4	1237.8	1227.4	1222.4	1211.9
12.5°	1338.2	1309.6	1287.9	1261.0	1237.1	1211.0	1201.0	1185.1	1168.7	1158.3	1144.9
15°	1290.2	1255.7	1229.2	1197.1	1168.8	1139.2	1112.7	1083.1	1072.0	1048.6	1035.0
17.5°	1234.1	1199.1	1166.3	1123.3	1079.5	1042.8	1014.5	986.1	969.2	954.2	947.4
20°	1197.1	1165.1	1119.5	1069.5	1020.8	980.2	957.3	938.9	920.3	909.9	902.5
22.5°	1162.1	1121.1	1068.2	1014.3	965.6	933.8	914.4	895.5	880.4	870.4	860.6
25°	1103.4	1049.8	993.7	932.1	898.8	871.0	850.1	834.6	825.5	812.4	807.5
27.5°	1043.1	978.2	916.3	874.9	840.2	814.8	796.6	785.0	773.3	765.0	758.6
30°	996.8	930.9	875.4	835.9	800.8	779.8	765.0	751.4	742.2	735.4	730.5
32.5°	950.9	884.9	838.4	795.9	768.2	747.8	732.0	721.8	714.6	705.8	702.8
35°	884.6	826.0	785.3	747.2	718.8	700.3	688.0	677.4	671.3	668.9	667.0
37.5°	820.8	772.9	729.2	697.9	672.5	658.0	643.5	638.3	634.1	629.6	631.6
40°	780.4	735.4	696.6	663.3	642.9	627.0	618.3	612.2	608.4	608.4	608.4
42.5°	745.4	701.4	663.5	633.7	613.3	599.8	590.2	585.0	583.8	583.3	586.2
45°	691.1	650.3	612.2	587.5	570.2	556.6	551.1	546.8	546.8	549.3	549.8
47.5°	637.1	599.1	568.4	540.7	525.0	516.5	511.7	509.4	509.7	512.1	515.0
50°	604.1	566.5	536.3	511.7	496.9	488.8	484.6	483.3	484.6	484.6	488.8
52.5°	568.1	534.5	504.7	484.0	467.3	459.8	457.4	455.7	456.4	458.4	460.2
55°	515.3	485.2	456.8	437.0	424.7	419.8	414.3	414.8	413.7	414.8	414.8
57.5°	462.4	435.3	408.9	393.3	382.5	375.3	369.3	371.0	369.2	368.9	367.9
60°	428.5	398.9	377.9	363.7	351.3	345.2	339.7	340.9	339.0	337.8	335.4
62.5°	391.5	366.8	346.8	333.1	323.2	316.1	310.6	309.3	305.1	300.9	295.4
65°	337.8	317.4	299.6	286.7	277.4	271.9	267.5	263.9	254.6	244.7	239.8
67.5°	285.7	271.0	254.3	243.3	235.9	228.5	220.3	214.0	205.4	200.0	196.9
70°	252.1	237.9	223.7	213.3	205.3	198.5	189.2	184.9	178.8	176.3	173.3
72.5°	220.1	206.9	193.7	184.2	175.7	170.4	163.1	158.8	156.0	155.1	152.0
75°	171.4	160.9	151.1	142.4	135.6	131.9	128.9	125.7	124.5	119.0	115.9
77.5°	125.0	118.2	111.9	105.8	100.9	98.5	92.6	89.0	86.9	84.4	83.7
80°	97.4	92.5	86.3	82.6	75.8	73.4	70.9	70.3	69.6	69.0	68.4
82.5°	73.2	68.3	62.2	59.9	58.1	56.6	55.1	54.5	53.9	54.2	54.1
85°	37.0	34.5	34.5	33.9	33.3	32.6	32.0	32.0	31.5	32.0	31.5
87.5°	13.1	12.8	12.9	12.0	12.6	12.8	12.3	12.4	13.0	12.0	12.1
90°	4.0	4.7	5.3	5.8	6.3	7.0	7.3	7.8	8.2	8.6	8.9
92.5°	10.3	10.9	11.3	11.7	12.1	12.5	12.8	13.0	13.2	13.5	13.6
95°	21.4	22.0	22.5	23.0	23.5	24.0	24.2	24.3	24.6	24.8	24.9
97.5°	35.0	35.6	36.1	36.7	37.3	37.9	38.2	38.3	38.6	38.9	39.0
100°	45.2	45.7	46.3	47.0	47.6	48.2	48.3	48.5	48.6	48.8	48.9
102.5°	56.2	56.5	57.1	57.7	58.2	58.8	59.0	59.2	59.4	59.6	59.7
105°	73.7	73.8	74.2	74.5	74.7	75.0	75.2	75.4	75.6	75.8	76.1
107.5°	92.4	92.4	92.5	92.5	92.6	92.6	92.7	93.0	93.2	93.4	93.5
110°	105.1	105.2	105.1	105.0	105.0	105.0	104.8	104.7	104.5	104.3	104.4



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.8	117.8	117.6	117.5	117.4	117.3	117.3	117.3	117.2	117.2	117.2
115°	137.4	137.3	137.1	137.1	136.9	136.8	136.7	136.6	136.5	136.4	136.4
117.5°	156.1	156.1	156.0	156.0	155.8	155.7	155.5	155.2	155.0	154.8	154.6
120°	169.4	169.4	169.2	169.0	168.8	168.6	168.3	167.9	167.6	167.2	167.1
122.5°	181.6	181.6	181.5	181.4	181.3	181.2	180.9	180.7	180.5	180.2	179.9
125°	200.1	200.0	200.0	199.9	199.8	199.7	199.7	199.5	199.4	199.2	199.0
127.5°	218.1	218.2	218.1	217.9	217.8	217.8	217.6	217.5	217.3	217.1	217.0
130°	230.2	230.3	230.3	230.3	230.3	230.3	230.2	230.1	229.9	229.8	229.5
132.5°	242.4	242.4	242.4	242.3	242.3	242.2	242.0	241.9	241.7	241.7	241.5
135°	259.8	259.9	259.9	259.9	259.9	259.9	259.8	259.7	259.6	259.4	259.2
137.5°	276.6	276.8	276.9	277.0	277.1	277.2	277.1	276.9	276.7	276.5	276.4
140°	288.3	288.3	288.3	288.3	288.3	288.3	288.3	288.2	288.1	288.0	287.9
142.5°	299.1	299.2	299.1	299.0	299.0	298.9	298.9	298.9	298.9	298.8	298.8
145°	314.7	314.9	314.9	315.0	315.0	315.1	315.0	315.0	314.9	314.9	314.7
147.5°	329.8	329.8	329.8	329.8	329.8	329.7	329.6	329.6	329.5	329.4	329.4
150°	338.6	338.8	338.8	338.8	338.8	338.8	338.8	338.8	338.8	338.8	338.7
152.5°	346.7	346.8	346.9	347.0	347.0	347.1	347.2	347.4	347.6	347.8	347.7
155°	359.2	359.2	359.1	359.0	359.0	358.9	359.2	359.4	359.7	360.0	360.0
157.5°	369.8	369.7	369.7	369.7	369.7	369.7	369.9	370.1	370.3	370.5	370.5
160°	376.6	376.5	376.5	376.4	376.3	376.2	376.5	376.7	376.8	377.1	377.0
162.5°	382.2	382.1	382.0	381.9	381.8	381.7	382.2	382.5	382.9	383.3	383.3
165°	390.2	390.0	389.9	389.8	389.6	389.5	389.9	390.3	390.7	391.1	391.2
167.5°	396.1	395.9	396.0	396.0	396.0	396.0	396.5	396.9	397.3	397.7	397.7
170°	399.4	399.3	399.3	399.4	399.5	399.6	399.9	400.4	400.8	401.3	401.2
172.5°	402.2	402.0	402.0	402.1	402.1	402.1	402.5	403.1	403.5	403.9	403.9
175°	405.4	405.2	405.1	405.0	405.0	404.9	405.4	405.9	406.4	406.9	406.9
177.5°	406.8	406.7	406.7	406.7	406.7	406.7	407.1	407.4	407.9	408.2	408.2
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1460.4	1461.4	1458.0	1457.1	1458.0	1461.4	1460.4	1463.5	1463.9	1467.8	1466.4
5°	1355.0	1353.7	1350.6	1351.2	1350.6	1353.7	1355.0	1359.9	1362.4	1372.2	1371.0
7.5°	1264.7	1259.9	1261.2	1256.3	1261.2	1259.9	1264.7	1269.2	1276.7	1281.1	1291.6
10°	1209.4	1202.7	1197.1	1192.2	1197.1	1202.7	1209.4	1211.9	1222.4	1227.4	1237.8
12.5°	1134.0	1128.2	1120.7	1122.2	1120.7	1128.2	1134.0	1144.9	1158.3	1168.7	1185.1
15°	1027.0	1017.7	1003.0	1004.8	1003.0	1017.7	1027.0	1035.0	1048.6	1072.0	1083.1
17.5°	936.4	936.5	929.7	931.3	929.7	936.5	936.4	947.4	954.2	969.2	986.1
20°	889.6	885.2	885.8	884.0	885.8	885.2	889.6	902.5	909.9	920.3	938.9
22.5°	857.0	851.7	847.4	843.6	847.4	851.7	857.0	860.6	870.4	880.4	895.5
25°	802.0	798.3	792.7	791.5	792.7	798.3	802.0	807.5	812.4	825.5	834.6
27.5°	753.7	753.0	750.7	747.9	750.7	753.0	753.7	758.6	765.0	773.3	785.0
30°	725.6	724.3	723.1	721.2	723.1	724.3	725.6	730.5	735.4	742.2	751.4
32.5°	700.4	699.6	698.4	698.6	698.4	699.6	700.4	702.8	705.8	714.6	721.8
35°	664.5	663.9	662.7	662.1	662.7	663.9	664.5	667.0	668.9	671.3	677.4
37.5°	631.0	632.6	631.9	631.7	631.9	632.6	631.0	631.6	629.6	634.1	638.3
40°	607.8	608.4	609.7	609.0	609.7	608.4	607.8	608.4	608.4	608.4	612.2
42.5°	588.6	588.7	590.4	588.4	590.4	588.7	588.6	586.2	583.3	583.8	585.0
45°	554.2	557.9	557.2	557.2	557.2	557.9	554.2	549.8	549.3	546.8	546.8
47.5°	516.6	519.8	520.7	520.5	520.7	519.8	516.6	515.0	512.1	509.7	509.4
50°	492.0	490.7	492.6	492.0	492.6	490.7	492.0	488.8	484.6	484.6	483.3
52.5°	461.8	462.1	462.0	461.4	462.0	462.1	461.8	460.2	458.4	456.4	455.7
55°	415.4	416.1	414.8	415.4	414.8	416.1	415.4	414.8	414.8	413.7	414.8
57.5°	365.2	362.2	363.5	361.9	363.5	362.2	365.2	367.9	368.9	369.2	371.0
60°	329.2	324.2	323.0	320.6	323.0	324.2	329.2	335.4	337.8	339.0	340.9
62.5°	288.7	285.3	281.1	283.0	281.1	285.3	288.7	295.4	300.9	305.1	309.3
65°	234.9	232.4	230.5	233.0	230.5	232.4	234.9	239.8	244.7	254.6	263.9
67.5°	194.4	193.1	193.1	191.8	193.1	193.1	194.4	196.9	200.0	205.4	214.0
70°	173.3	171.4	171.4	170.1	171.4	171.4	173.3	173.3	176.3	178.8	184.9
72.5°	151.5	149.6	150.2	149.5	150.2	149.6	151.5	152.0	155.1	156.0	158.8
75°	112.2	109.1	109.1	109.8	109.1	109.1	112.2	115.9	119.0	124.5	125.7
77.5°	83.7	83.1	84.0	82.8	84.0	83.1	83.7	83.7	84.4	86.9	89.0
80°	68.4	67.8	67.2	69.0	67.2	67.8	68.4	68.4	69.0	69.6	70.3
82.5°	53.1	53.1	52.9	55.2	52.9	53.1	53.1	54.1	54.2	53.9	54.5
85°	32.0	30.9	32.0	30.9	32.0	30.9	32.0	31.5	32.0	31.5	32.0
87.5°	13.1	12.7	12.2	12.8	12.2	12.7	13.1	12.1	12.0	13.0	12.4
90°	9.0	9.2	9.3	9.5	9.3	9.2	9.0	8.9	8.6	8.2	7.8
92.5°	13.7	13.8	13.9	14.0	13.9	13.8	13.7	13.6	13.5	13.2	13.0
95°	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.9	24.8	24.6	24.3
97.5°	39.0	39.0	39.0	39.0	39.0	39.0	39.0	39.0	38.9	38.6	38.3
100°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.8	48.6	48.5
102.5°	59.7	59.8	59.8	59.9	59.8	59.8	59.7	59.7	59.6	59.4	59.2
105°	76.2	76.5	76.7	76.9	76.7	76.5	76.2	76.1	75.8	75.6	75.4
107.5°	93.5	93.5	93.5	93.4	93.5	93.5	93.5	93.5	93.4	93.2	93.0
110°	104.6	104.9	105.0	105.2	105.0	104.9	104.6	104.4	104.3	104.5	104.7



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	117.3	117.3	117.3	117.3	117.3	117.3	117.3	117.2	117.2	117.2	117.3
115°	136.3	136.3	136.2	136.2	136.2	136.3	136.3	136.4	136.4	136.5	136.6
117.5°	154.4	154.3	154.2	154.0	154.2	154.3	154.4	154.6	154.8	155.0	155.2
120°	167.2	167.4	167.5	167.6	167.5	167.4	167.2	167.1	167.2	167.6	167.9
122.5°	179.8	179.5	179.2	179.0	179.2	179.5	179.8	179.9	180.2	180.5	180.7
125°	198.9	198.8	198.7	198.5	198.7	198.8	198.9	199.0	199.2	199.4	199.5
127.5°	217.0	216.9	216.7	216.6	216.7	216.9	217.0	217.0	217.1	217.3	217.5
130°	229.3	229.0	228.7	228.5	228.7	229.0	229.3	229.5	229.8	229.9	230.1
132.5°	241.4	241.3	241.2	241.0	241.2	241.3	241.4	241.5	241.7	241.7	241.9
135°	259.0	258.8	258.6	258.4	258.6	258.8	259.0	259.2	259.4	259.6	259.7
137.5°	276.4	276.5	276.5	276.6	276.5	276.5	276.4	276.4	276.5	276.7	276.9
140°	287.9	287.8	287.8	287.7	287.8	287.8	287.9	287.9	288.0	288.1	288.2
142.5°	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.8	298.9	298.9
145°	314.5	314.2	314.1	313.9	314.1	314.2	314.5	314.7	314.9	314.9	315.0
147.5°	329.3	329.2	329.1	329.1	329.1	329.2	329.3	329.4	329.4	329.5	329.6
150°	338.7	338.6	338.5	338.4	338.5	338.6	338.7	338.7	338.8	338.8	338.8
152.5°	347.5	347.3	347.1	347.0	347.1	347.3	347.5	347.7	347.8	347.6	347.4
155°	359.7	359.4	359.2	358.9	359.2	359.4	359.7	360.0	360.0	359.7	359.4
157.5°	370.2	370.1	369.8	369.5	369.8	370.1	370.2	370.5	370.5	370.3	370.1
160°	376.7	376.3	375.9	375.6	375.9	376.3	376.7	377.0	377.1	376.8	376.7
162.5°	383.0	382.6	382.3	381.9	382.3	382.6	383.0	383.3	383.3	382.9	382.5
165°	390.9	390.7	390.4	390.1	390.4	390.7	390.9	391.2	391.1	390.7	390.3
167.5°	397.3	396.8	396.4	395.9	396.4	396.8	397.3	397.7	397.7	397.3	396.9
170°	400.7	400.2	399.8	399.2	399.8	400.2	400.7	401.2	401.3	400.8	400.4
172.5°	403.5	403.0	402.5	402.0	402.5	403.0	403.5	403.9	403.9	403.5	403.1
175°	406.4	405.9	405.4	404.9	405.4	405.9	406.4	406.9	406.9	406.4	405.9
177.5°	407.8	407.3	406.9	406.4	406.9	407.3	407.8	408.2	408.2	407.9	407.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1463.5	1466.9	1474.8	1483.6	1491.0	1497.4	1502.4	1509.3	1515.7	1524.6	1532.9
5°	1374.7	1383.3	1395.6	1410.4	1428.9	1441.3	1456.7	1470.3	1490.0	1509.7	1528.7
7.5°	1296.7	1306.3	1324.4	1344.8	1366.8	1387.0	1405.2	1429.1	1455.3	1484.0	1516.1
10°	1246.4	1257.0	1278.5	1301.9	1327.8	1347.6	1372.2	1400.5	1430.1	1465.3	1504.8
12.5°	1201.0	1211.0	1237.1	1261.0	1287.9	1309.6	1338.2	1367.0	1406.5	1444.6	1489.4
15°	1112.7	1139.2	1168.8	1197.1	1229.2	1255.7	1290.2	1319.8	1357.5	1411.0	1462.2
17.5°	1014.5	1042.8	1079.5	1123.3	1166.3	1199.1	1234.1	1270.9	1315.6	1370.4	1429.4
20°	957.3	980.2	1020.8	1069.5	1119.5	1165.1	1197.1	1237.8	1284.1	1343.3	1404.3
22.5°	914.4	933.8	965.6	1014.3	1068.2	1121.1	1162.1	1202.3	1253.5	1312.7	1379.1
25°	850.1	871.0	898.8	932.1	993.7	1049.8	1103.4	1149.7	1203.9	1263.1	1337.0
27.5°	796.6	814.8	840.2	874.9	916.3	978.2	1043.1	1095.9	1151.6	1215.0	1289.1
30°	765.0	779.8	800.8	835.9	875.4	930.9	996.8	1058.5	1114.5	1180.4	1257.6
32.5°	732.0	747.8	768.2	795.9	838.4	884.9	950.9	1018.5	1078.1	1145.5	1221.0
35°	688.0	700.3	718.8	747.2	785.3	826.0	884.6	954.2	1017.2	1089.2	1161.4
37.5°	643.5	658.0	672.5	697.9	729.2	772.9	820.8	892.0	961.6	1027.5	1097.9
40°	618.3	627.0	642.9	663.3	696.6	735.4	780.4	850.1	919.7	985.1	1056.0
42.5°	590.2	599.8	613.3	633.7	663.5	701.4	745.4	805.7	878.3	941.6	1006.1
45°	551.1	556.6	570.2	587.5	612.2	650.3	691.1	744.7	813.1	873.5	930.2
47.5°	511.7	516.5	525.0	540.7	568.4	599.1	637.1	685.3	745.3	805.7	853.6
50°	484.6	488.8	496.9	511.7	536.3	566.5	604.1	647.3	700.9	758.8	798.9
52.5°	457.4	459.8	467.3	484.0	504.7	534.5	568.1	607.8	658.0	706.1	746.6
55°	414.3	419.8	424.7	437.0	456.8	485.2	515.3	552.9	591.8	632.5	667.0
57.5°	369.3	375.3	382.5	393.3	408.9	435.3	462.4	492.9	526.1	559.8	588.8
60°	339.7	345.2	351.3	363.7	377.9	398.9	428.5	455.0	480.2	511.0	540.0
62.5°	310.6	316.1	323.2	333.1	346.8	366.8	391.5	414.5	440.8	467.6	489.2
65°	267.5	271.9	277.4	286.7	299.6	317.4	337.8	355.7	379.2	398.9	418.6
67.5°	220.3	228.5	235.9	243.3	254.3	271.0	285.7	302.8	318.7	333.4	351.3
70°	189.2	198.5	205.3	213.3	223.7	237.9	252.1	263.9	276.8	291.0	307.0
72.5°	163.1	170.4	175.7	184.2	193.7	206.9	220.1	229.8	240.3	250.0	265.6
75°	128.9	131.9	135.6	142.4	151.1	160.9	171.4	180.0	186.2	194.8	205.9
77.5°	92.6	98.5	100.9	105.8	111.9	118.2	125.0	132.3	138.2	141.2	149.8
80°	70.9	73.4	75.8	82.6	86.3	92.5	97.4	104.2	106.6	109.8	117.7
82.5°	55.1	56.6	58.1	59.9	62.2	68.3	73.2	77.6	80.0	81.1	87.2
85°	32.0	32.6	33.3	33.9	34.5	34.5	37.0	40.0	44.4	44.4	46.2
87.5°	12.3	12.8	12.6	12.0	12.9	12.8	13.1	13.0	14.3	15.6	16.9
90°	7.3	7.0	6.3	5.8	5.3	4.7	4.0	3.3	2.5	1.7	1.0
92.5°	12.8	12.5	12.1	11.7	11.3	10.9	10.3	9.4	8.5	7.7	6.8
95°	24.2	24.0	23.5	23.0	22.5	22.0	21.4	20.8	20.2	19.5	18.9
97.5°	38.2	37.9	37.3	36.7	36.1	35.6	35.0	34.5	34.1	33.5	33.0
100°	48.3	48.2	47.6	47.0	46.3	45.7	45.2	44.9	44.7	44.4	44.1
102.5°	59.0	58.8	58.2	57.7	57.1	56.5	56.2	56.1	55.9	55.8	55.7
105°	75.2	75.0	74.7	74.5	74.2	73.8	73.7	73.7	73.6	73.5	73.4
107.5°	92.7	92.6	92.6	92.5	92.5	92.4	92.4	92.3	92.2	92.1	92.0
110°	104.8	105.0	105.0	105.0	105.1	105.2	105.1	105.0	104.9	104.8	104.6



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	117.3	117.3	117.4	117.5	117.6	117.8	117.8	117.8	117.8	117.7	117.7
115°	136.7	136.8	136.9	137.1	137.1	137.3	137.4	137.4	137.4	137.4	137.4
117.5°	155.5	155.7	155.8	156.0	156.0	156.1	156.1	156.0	156.0	156.0	155.9
120°	168.3	168.6	168.8	169.0	169.2	169.4	169.4	169.1	168.8	168.5	168.3
122.5°	180.9	181.2	181.3	181.4	181.5	181.6	181.6	181.5	181.4	181.2	181.1
125°	199.7	199.7	199.8	199.9	200.0	200.0	200.1	200.1	200.1	200.1	200.1
127.5°	217.6	217.8	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.5	217.3
130°	230.2	230.3	230.3	230.3	230.3	230.3	230.2	230.1	229.8	229.6	229.4
132.5°	242.0	242.2	242.3	242.3	242.4	242.4	242.4	242.2	242.0	241.9	241.7
135°	259.8	259.9	259.9	259.9	259.9	259.9	259.8	259.3	258.9	258.5	258.1
137.5°	277.1	277.2	277.1	277.0	276.9	276.8	276.6	276.4	276.3	276.1	275.8
140°	288.3	288.3	288.3	288.3	288.3	288.3	288.3	288.1	287.9	287.8	287.7
142.5°	298.9	298.9	299.0	299.0	299.1	299.2	299.1	298.9	298.8	298.6	298.5
145°	315.0	315.1	315.0	315.0	314.9	314.9	314.7	314.3	314.1	313.8	313.5
147.5°	329.6	329.7	329.8	329.8	329.8	329.8	329.8	329.4	329.0	328.8	328.4
150°	338.8	338.8	338.8	338.8	338.8	338.8	338.6	338.3	338.0	337.8	337.5
152.5°	347.2	347.1	347.0	347.0	346.9	346.8	346.7	346.5	346.3	346.3	346.1
155°	359.2	358.9	359.0	359.0	359.1	359.2	359.2	359.2	359.2	359.2	359.2
157.5°	369.9	369.7	369.7	369.7	369.7	369.7	369.8	370.0	370.1	370.1	370.3
160°	376.5	376.2	376.3	376.4	376.5	376.5	376.6	376.7	376.7	376.7	376.8
162.5°	382.2	381.7	381.8	381.9	382.0	382.1	382.2	382.4	382.5	382.7	382.9
165°	389.9	389.5	389.6	389.8	389.9	390.0	390.2	390.4	390.7	390.8	391.0
167.5°	396.5	396.0	396.0	396.0	396.0	395.9	396.1	396.4	396.7	397.0	397.3
170°	399.9	399.6	399.5	399.4	399.3	399.3	399.4	399.8	400.1	400.5	400.8
172.5°	402.5	402.1	402.1	402.1	402.0	402.0	402.2	402.4	402.7	403.1	403.3
175°	405.4	404.9	405.0	405.0	405.1	405.2	405.4	405.7	406.1	406.4	406.8
177.5°	407.1	406.7	406.7	406.7	406.7	406.7	406.8	407.1	407.3	407.7	408.0
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1539.4	1543.8	1548.7	1558.1	1566.0	1569.5	1576.4	1581.3	1579.8	1586.7	1598.6
5°	1545.4	1562.1	1581.2	1600.9	1623.1	1641.6	1656.4	1671.2	1682.9	1697.1	1718.1
7.5°	1544.4	1574.0	1606.2	1641.6	1677.9	1709.4	1738.5	1768.1	1794.3	1823.1	1860.6
10°	1540.5	1579.9	1620.0	1666.3	1712.4	1756.2	1795.7	1832.6	1867.9	1905.4	1952.9
12.5°	1536.1	1581.4	1629.9	1685.5	1743.0	1795.7	1842.1	1895.3	1939.3	1987.8	2042.6
15°	1516.4	1577.4	1643.4	1715.6	1784.6	1855.5	1919.0	1984.3	2045.3	2103.3	2172.4
17.5°	1494.0	1564.4	1642.2	1727.4	1810.4	1896.6	1971.8	2054.2	2116.7	2194.4	2258.5
20°	1475.8	1551.6	1634.8	1730.4	1824.7	1920.2	2003.4	2087.3	2157.6	2235.9	2317.2
22.5°	1453.6	1536.8	1626.9	1725.9	1824.7	1929.1	2021.2	2104.5	2191.6	2279.7	2363.6
25°	1417.8	1504.1	1599.6	1708.2	1821.6	1928.2	2026.9	2130.4	2224.1	2319.7	2394.9
27.5°	1373.9	1464.5	1565.3	1677.2	1793.6	1902.8	2019.0	2129.3	2223.7	2315.6	2381.2
30°	1338.9	1434.5	1531.2	1644.7	1765.5	1882.6	2007.2	2117.5	2216.7	2299.4	2336.3
32.5°	1302.9	1393.6	1493.3	1608.2	1732.0	1858.0	1981.5	2094.3	2186.1	2235.7	2236.7
35°	1240.3	1325.3	1428.9	1541.8	1668.7	1805.5	1930.7	2041.7	2097.7	2102.0	2041.7
37.5°	1172.0	1250.0	1347.8	1460.7	1599.8	1735.9	1863.8	1937.7	1956.5	1893.7	1782.0
40°	1123.2	1195.2	1289.6	1405.5	1543.6	1684.1	1800.6	1854.8	1835.1	1733.4	1608.9
42.5°	1071.8	1139.1	1229.9	1344.3	1482.9	1625.0	1724.2	1753.3	1701.0	1583.5	1437.8
45°	988.2	1049.8	1139.8	1255.1	1388.2	1521.3	1596.6	1581.8	1494.9	1355.6	1192.2
47.5°	901.0	960.6	1041.5	1148.2	1284.5	1399.5	1450.4	1405.8	1282.1	1128.8	996.0
50°	843.3	904.3	978.9	1080.7	1205.1	1316.1	1348.8	1280.9	1143.5	996.1	874.1
52.5°	786.6	838.7	911.9	1010.1	1129.2	1222.9	1240.3	1162.1	1020.2	888.1	779.9
55°	700.3	747.8	809.4	901.9	1004.8	1084.3	1075.0	974.6	845.8	733.0	647.9
57.5°	616.8	652.6	709.5	796.2	886.5	940.0	906.2	820.5	700.4	608.1	536.3
60°	561.6	594.9	647.9	723.7	803.3	833.4	805.0	712.0	617.1	532.6	472.2
62.5°	509.3	538.7	584.2	654.7	718.9	736.7	706.4	625.2	539.7	467.5	417.5
65°	433.4	460.5	499.4	549.3	593.6	602.3	582.6	499.4	434.6	374.2	339.7
67.5°	364.4	382.2	412.5	455.7	479.2	484.3	446.2	393.9	336.8	299.7	273.7
70°	318.1	330.4	358.7	382.2	401.3	401.9	366.8	324.9	281.1	250.9	231.8
72.5°	273.2	285.1	306.5	322.5	337.2	332.4	300.2	267.2	231.8	209.0	194.8
75°	210.8	221.3	232.4	239.8	239.8	233.6	210.2	185.6	165.2	151.7	147.3
77.5°	153.3	161.8	165.6	164.4	162.3	152.7	137.9	121.7	114.4	108.0	104.8
80°	120.2	123.9	125.1	122.1	118.3	107.3	97.4	90.6	83.8	81.4	80.2
82.5°	89.2	92.4	89.2	90.0	81.9	72.8	67.3	65.0	62.2	61.2	59.9
85°	47.4	46.8	45.7	42.5	37.0	35.8	35.1	34.5	33.3	33.9	32.6
87.5°	16.6	15.2	13.5	13.1	13.3	12.4	13.0	13.1	13.2	12.8	13.9
90°	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3	7.8
92.5°	7.7	8.5	9.4	10.3	10.9	11.3	11.7	12.1	12.5	12.8	13.0
95°	19.5	20.2	20.8	21.4	22.0	22.5	23.0	23.5	24.0	24.2	24.3
97.5°	33.5	34.1	34.5	35.0	35.6	36.1	36.7	37.3	37.9	38.2	38.3
100°	44.4	44.7	44.9	45.2	45.7	46.3	47.0	47.6	48.2	48.3	48.5
102.5°	55.8	55.9	56.1	56.2	56.5	57.1	57.7	58.2	58.8	59.0	59.2
105°	73.5	73.6	73.7	73.7	73.8	74.2	74.5	74.7	75.0	75.2	75.4
107.5°	92.1	92.2	92.3	92.4	92.4	92.5	92.5	92.6	92.6	92.7	93.0
110°	104.8	104.9	105.0	105.1	105.2	105.1	105.0	105.0	105.0	104.8	104.7



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	117.7	117.8	117.8	117.8	117.8	117.6	117.5	117.4	117.3	117.3	117.3
115°	137.4	137.4	137.4	137.4	137.3	137.1	137.1	136.9	136.8	136.7	136.6
117.5°	156.0	156.0	156.0	156.1	156.1	156.0	156.0	155.8	155.7	155.5	155.2
120°	168.5	168.8	169.1	169.4	169.4	169.2	169.0	168.8	168.6	168.3	167.9
122.5°	181.2	181.4	181.5	181.6	181.6	181.5	181.4	181.3	181.2	180.9	180.7
125°	200.1	200.1	200.1	200.1	200.0	200.0	199.9	199.8	199.7	199.7	199.5
127.5°	217.5	217.8	217.9	218.1	218.2	218.1	217.9	217.8	217.8	217.6	217.5
130°	229.6	229.8	230.1	230.2	230.3	230.3	230.3	230.3	230.3	230.2	230.1
132.5°	241.9	242.0	242.2	242.4	242.4	242.4	242.3	242.3	242.2	242.0	241.9
135°	258.5	258.9	259.3	259.8	259.9	259.9	259.9	259.9	259.9	259.8	259.7
137.5°	276.1	276.3	276.4	276.6	276.8	276.9	277.0	277.1	277.2	277.1	276.9
140°	287.8	287.9	288.1	288.3	288.3	288.3	288.3	288.3	288.3	288.3	288.2
142.5°	298.6	298.8	298.9	299.1	299.2	299.1	299.0	299.0	298.9	298.9	298.9
145°	313.8	314.1	314.3	314.7	314.9	314.9	315.0	315.0	315.1	315.0	315.0
147.5°	328.8	329.0	329.4	329.8	329.8	329.8	329.8	329.8	329.7	329.6	329.6
150°	337.8	338.0	338.3	338.6	338.8	338.8	338.8	338.8	338.8	338.8	338.8
152.5°	346.3	346.3	346.5	346.7	346.8	346.9	347.0	347.0	347.1	347.2	347.4
155°	359.2	359.2	359.2	359.2	359.2	359.1	359.0	359.0	358.9	359.2	359.4
157.5°	370.1	370.1	370.0	369.8	369.7	369.7	369.7	369.7	369.7	369.9	370.1
160°	376.7	376.7	376.7	376.6	376.5	376.5	376.4	376.3	376.2	376.5	376.7
162.5°	382.7	382.5	382.4	382.2	382.1	382.0	381.9	381.8	381.7	382.2	382.5
165°	390.8	390.7	390.4	390.2	390.0	389.9	389.8	389.6	389.5	389.9	390.3
167.5°	397.0	396.7	396.4	396.1	395.9	396.0	396.0	396.0	396.0	396.5	396.9
170°	400.5	400.1	399.8	399.4	399.3	399.3	399.4	399.5	399.6	399.9	400.4
172.5°	403.1	402.7	402.4	402.2	402.0	402.0	402.1	402.1	402.1	402.5	403.1
175°	406.4	406.1	405.7	405.4	405.2	405.1	405.0	405.0	404.9	405.4	405.9
177.5°	407.7	407.3	407.1	406.8	406.7	406.7	406.7	406.7	406.7	407.1	407.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4	407.4



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1605.0	1607.0	1608.5	1613.4	1613.8	1618.3	1613.8
5°	1737.8	1746.4	1760.0	1773.5	1774.8	1783.3	1768.0
7.5°	1886.7	1906.7	1919.1	1941.1	1949.7	1955.1	1946.2
10°	1989.2	2007.8	2040.4	2056.5	2072.5	2074.9	2067.5
12.5°	2088.4	2117.7	2143.5	2173.8	2173.1	2194.8	2186.9
15°	2220.4	2250.7	2286.3	2320.3	2332.6	2332.6	2342.5
17.5°	2314.6	2370.0	2407.0	2433.6	2462.7	2467.7	2464.3
20°	2378.3	2438.0	2477.5	2512.0	2531.7	2537.3	2537.3
22.5°	2425.5	2476.5	2515.0	2546.0	2562.3	2568.8	2566.9
25°	2458.4	2502.1	2525.6	2534.8	2539.1	2537.9	2526.2
27.5°	2413.5	2411.5	2396.7	2368.4	2347.1	2334.1	2319.3
30°	2327.7	2295.6	2258.6	2218.0	2165.6	2125.5	2113.2
32.5°	2199.9	2128.0	2065.3	1997.5	1941.2	1901.1	1884.4
35°	1952.9	1838.9	1745.8	1664.4	1605.3	1568.3	1555.9
37.5°	1659.7	1549.3	1434.1	1355.2	1306.1	1268.7	1254.8
40°	1473.3	1353.1	1252.6	1178.7	1128.1	1091.7	1091.1
42.5°	1303.1	1188.4	1093.9	1040.5	986.1	962.0	961.9
45°	1067.0	975.2	895.1	853.2	820.5	800.8	795.2
47.5°	883.5	807.5	754.1	720.8	694.1	681.5	673.4
50°	780.4	713.8	671.3	642.3	627.5	611.5	610.3
52.5°	694.6	640.9	607.7	584.2	565.4	555.8	556.1
55°	583.8	541.3	517.8	499.9	485.2	477.8	474.7
57.5°	491.8	459.9	442.8	426.4	420.2	414.4	412.8
60°	434.6	413.0	397.0	384.1	374.8	372.9	372.3
62.5°	387.3	364.7	353.6	343.6	336.8	333.9	332.9
65°	319.3	302.6	292.8	284.8	282.3	278.0	277.4
67.5°	257.4	247.4	240.9	235.3	232.0	231.8	231.8
70°	219.5	213.9	208.4	205.3	203.4	202.2	202.2
72.5°	186.9	182.8	178.3	176.6	176.3	175.0	174.6
75°	142.4	138.1	138.7	135.6	133.1	130.1	128.2
77.5°	100.9	97.9	97.3	96.9	94.8	94.4	95.4
80°	78.3	75.2	74.5	75.2	74.5	72.8	72.8
82.5°	59.6	57.0	56.4	56.0	55.4	56.0	55.0
85°	32.0	30.9	30.9	30.9	32.0	31.5	30.9
87.5°	13.0	12.6	13.1	12.7	12.7	12.2	12.8
90°	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	13.2	13.5	13.6	13.7	13.8	13.9	14.0
95°	24.6	24.8	24.9	24.9	24.9	24.9	24.9
97.5°	38.6	38.9	39.0	39.0	39.0	39.0	39.0
100°	48.6	48.8	48.9	48.9	48.9	48.9	48.9
102.5°	59.4	59.6	59.7	59.7	59.8	59.8	59.9
105°	75.6	75.8	76.1	76.2	76.5	76.7	76.9
107.5°	93.2	93.4	93.5	93.5	93.5	93.5	93.4
110°	104.5	104.3	104.4	104.6	104.9	105.0	105.2



TEST NUMBER: P332956-940

CATALOG NUMBER: SA4XXRDIP-C1020D365U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	117.2	117.2	117.2	117.3	117.3	117.3	117.3
115°	136.5	136.4	136.4	136.3	136.3	136.2	136.2
117.5°	155.0	154.8	154.6	154.4	154.3	154.2	154.0
120°	167.6	167.2	167.1	167.2	167.4	167.5	167.6
122.5°	180.5	180.2	179.9	179.8	179.5	179.2	179.0
125°	199.4	199.2	199.0	198.9	198.8	198.7	198.5
127.5°	217.3	217.1	217.0	217.0	216.9	216.7	216.6
130°	229.9	229.8	229.5	229.3	229.0	228.7	228.5
132.5°	241.7	241.7	241.5	241.4	241.3	241.2	241.0
135°	259.6	259.4	259.2	259.0	258.8	258.6	258.4
137.5°	276.7	276.5	276.4	276.4	276.5	276.5	276.6
140°	288.1	288.0	287.9	287.9	287.8	287.8	287.7
142.5°	298.9	298.8	298.8	298.8	298.8	298.8	298.8
145°	314.9	314.9	314.7	314.5	314.2	314.1	313.9
147.5°	329.5	329.4	329.4	329.3	329.2	329.1	329.1
150°	338.8	338.8	338.7	338.7	338.6	338.5	338.4
152.5°	347.6	347.8	347.7	347.5	347.3	347.1	347.0
155°	359.7	360.0	360.0	359.7	359.4	359.2	358.9
157.5°	370.3	370.5	370.5	370.2	370.1	369.8	369.5
160°	376.8	377.1	377.0	376.7	376.3	375.9	375.6
162.5°	382.9	383.3	383.3	383.0	382.6	382.3	381.9
165°	390.7	391.1	391.2	390.9	390.7	390.4	390.1
167.5°	397.3	397.7	397.7	397.3	396.8	396.4	395.9
170°	400.8	401.3	401.2	400.7	400.2	399.8	399.2
172.5°	403.5	403.9	403.9	403.5	403.0	402.5	402.0
175°	406.4	406.9	406.9	406.4	405.9	405.4	404.9
177.5°	407.9	408.2	408.2	407.8	407.3	406.9	406.4
180°	407.4	407.4	407.4	407.4	407.4	407.4	407.4

(END OF REPORT)