

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924045

Luminaire Tested: DFN2DIP-4P3F0-040D030US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924045
REPORT IS A COMBINATION OF REPORTS P900564 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D030US950-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6077.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924045

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924045

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1797	1797	1797
5°	1799	1768	1780
10°	1780	1732	1721
15°	1755	1673	1631
20°	1721	1593	1521
25°	1686	1504	1414
30°	1641	1412	1279
35°	1596	1314	1161
40°	1550	1212	1025
45°	1497	1100	902
50°	1442	986	782
55°	1385	865	667
60°	1318	738	548
65°	1241	609	493
70°	1148	490	445
75°	1031	429	404
80°	862	356	348
85°	584	232	258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1497 cd/sqm

TEST NUMBER: P924045

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	2.4
10°-20°	405.8	6.7
20°-30°	569.7	9.4
30°-40°	621.0	10.2
40°-50°	570.8	9.4
50°-60°	448.2	7.4
60°-70°	291.8	4.8
70°-80°	150.2	2.5
80°-90°	40.1	0.7
90°-100°	31.9	0.5
100°-110°	118.7	2.0
110°-120°	314.9	5.2
120°-130°	522.3	8.6
130°-140°	554.8	9.1
140°-150°	515.6	8.5
150°-160°	414.5	6.8
160°-170°	267.1	4.4
170°-180°	91.9	1.5
0°-30°	1123.3	18.5
0°-40°	1744.3	28.7
0°-60°	2763.3	45.5
0°-90°	3245.3	53.4
90°-120°	465.5	7.7
90°-150°	2058.1	33.9
90°-180°	2832.0	46.6
0°-180°	6077.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	1	8	14	18	19	6
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	

TEST NUMBER: P924045

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2



TEST NUMBER: P924045

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9

TEST NUMBER: P924045

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.46	10.32	10.40	11.27	12.49	5.42	6.28	6.36	7.23	8.45
	3H	11.14	11.91	12.09	12.86	14.11	6.61	7.38	7.55	8.33	9.58
	4H	11.75	12.47	12.71	13.43	14.69	7.06	7.78	8.02	8.74	10.00
	6H	12.17	12.83	13.14	13.80	15.07	7.37	8.04	8.34	9.01	10.28
	8H	12.29	12.93	13.27	13.91	15.18	7.46	8.10	8.44	9.08	10.35
	12H	12.35	12.96	13.33	13.93	15.22	7.50	8.11	8.48	9.08	10.37
4H	2H	9.48	10.21	10.45	11.17	12.43	6.02	6.75	6.99	7.71	8.96
	3H	11.31	11.91	12.29	12.90	14.17	7.37	7.97	8.34	8.96	10.23
	4H	12.00	12.55	12.98	13.53	14.83	7.91	8.46	8.89	9.44	10.74
	6H	12.51	12.98	13.51	13.99	15.29	8.32	8.80	9.32	9.80	11.10
	8H	12.69	13.13	13.68	14.13	15.44	8.45	8.89	9.45	9.89	11.20
	12H	12.78	13.18	13.79	14.19	15.51	8.51	8.91	9.53	9.93	11.24
8H	4H	11.97	12.41	12.97	13.41	14.72	8.19	8.63	9.19	9.63	10.94
	6H	12.53	12.89	13.55	13.94	15.24	8.70	9.07	9.72	10.11	11.41
	8H	12.74	13.06	13.77	14.09	15.42	8.89	9.21	9.92	10.24	11.56
	12H	12.88	13.16	13.91	14.19	15.56	9.00	9.28	10.03	10.31	11.68
12H	4H	11.92	12.32	12.94	13.34	14.65	8.19	8.59	9.21	9.61	10.92
	6H	12.50	12.83	13.53	13.86	15.18	8.75	9.07	9.78	10.10	11.42
	8H	12.72	13.01	13.76	14.03	15.40	8.95	9.24	9.99	10.26	11.63

END OF REPORT