

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924085

Luminaire Tested: DFN2DIP-4P3F0-060D030US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924085
REPORT IS A COMBINATION OF REPORTS P900568 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-060D030US950-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7698.8 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924085

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924085

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2696	2696	2696
5°	2699	2651	2669
10°	2670	2598	2582
15°	2632	2510	2446
20°	2581	2390	2281
25°	2530	2256	2121
30°	2461	2118	1919
35°	2394	1971	1741
40°	2325	1818	1538
45°	2246	1650	1353
50°	2163	1479	1173
55°	2077	1297	1000
60°	1977	1107	822
65°	1862	914	739
70°	1722	734	668
75°	1547	643	606
80°	1293	534	522
85°	877	348	387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2246 cd/sqm

TEST NUMBER: P924085

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	2.9
10°-20°	608.7	7.9
20°-30°	854.5	11.1
30°-40°	931.5	12.1
40°-50°	856.2	11.1
50°-60°	672.4	8.7
60°-70°	437.7	5.7
70°-80°	225.3	2.9
80°-90°	59.2	0.8
90°-100°	31.9	0.4
100°-110°	118.7	1.5
110°-120°	314.9	4.1
120°-130°	522.3	6.8
130°-140°	554.8	7.2
140°-150°	515.6	6.7
150°-160°	414.5	5.4
160°-170°	267.1	3.5
170°-180°	91.9	1.2
0°-30°	1684.9	21.9
0°-40°	2616.4	34.0
0°-60°	4144.9	53.8
0°-90°	4867.1	63.2
90°-120°	465.5	6.0
90°-150°	2058.1	26.7
90°-180°	2832.0	36.8
0°-180°	7698.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2366	2366	2366	2366	2366	
5°	2366	2355	2327	2346	2340	224
15°	2250	2226	2154	2113	2092	634
25°	2042	1974	1833	1745	1713	939
35°	1760	1651	1462	1327	1280	1102
45°	1439	1295	1071	918	867	1111
55°	1094	927	696	567	527	978
65°	739	565	372	300	293	732
75°	394	244	171	156	154	417
85°	92	47	41	41	41	106
90°	1	8	14	18	19	7
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	

TEST NUMBER: P924085

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2365.7	2365.7	2365.7	2365.7	2365.7
2.5°	2376.4	2365.7	2342.1	2363.6	2359.3
5°	2365.7	2355.0	2327.1	2346.5	2340.1
7.5°	2346.5	2333.7	2303.7	2312.1	2301.4
10°	2320.7	2305.7	2263.1	2256.5	2243.7
12.5°	2288.7	2269.4	2211.5	2198.8	2175.1
15°	2250.1	2226.4	2153.8	2113.1	2091.7
17.5°	2205.2	2170.8	2080.9	2033.8	1999.6
20°	2153.8	2110.8	2003.9	1950.5	1903.2
22.5°	2098.1	2048.8	1924.6	1851.9	1819.9
25°	2042.5	1973.9	1832.6	1745.0	1712.7
27.5°	1976.2	1903.2	1747.0	1646.3	1597.1
30°	1905.5	1824.0	1652.7	1543.7	1485.8
32.5°	1836.9	1738.4	1563.0	1434.4	1380.8
35°	1759.9	1650.7	1462.4	1327.4	1280.2
37.5°	1685.0	1567.0	1368.1	1220.3	1166.8
40°	1605.7	1477.4	1269.5	1117.5	1061.9
42.5°	1524.4	1387.4	1171.1	1012.6	959.2
45°	1438.7	1295.2	1070.6	918.3	867.0
47.5°	1357.4	1205.5	974.2	822.1	775.0
50°	1267.5	1115.5	880.0	732.1	687.4
52.5°	1179.5	1019.0	790.0	648.7	608.1
55°	1094.0	927.0	695.8	567.4	526.7
57.5°	1006.3	834.9	612.4	492.5	458.1
60°	916.3	745.1	524.5	415.5	381.1
62.5°	828.6	657.4	449.5	346.9	329.8
65°	738.7	565.1	372.5	299.8	293.3
67.5°	653.0	479.5	299.8	263.3	256.9
70°	563.1	396.1	248.2	227.0	218.3
72.5°	477.5	318.9	207.6	190.6	186.2
75°	393.9	243.9	171.2	156.3	154.3
77.5°	310.5	173.3	134.9	126.3	122.0
80°	233.3	124.2	102.7	94.3	94.3
82.5°	162.7	83.6	70.6	66.3	66.3
85°	92.0	47.0	40.6	40.6	40.6
87.5°	34.3	17.1	17.1	15.0	15.0
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2

TEST NUMBER: P924085

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9

TEST NUMBER: P924085

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.71	12.66	12.55	13.52	14.59	7.67	8.62	8.51	9.48	10.55
	3H	13.39	14.24	14.25	15.11	16.21	8.86	9.72	9.72	10.58	11.68
	4H	14.00	14.81	14.88	15.68	16.79	9.32	10.12	10.19	10.99	12.10
	6H	14.43	15.17	15.31	16.05	17.17	9.64	10.38	10.52	11.26	12.38
	8H	14.56	15.26	15.45	16.16	17.28	9.73	10.43	10.62	11.33	12.45
	12H	14.62	15.29	15.52	16.18	17.33	9.77	10.44	10.67	11.34	12.48
4H	2H	11.74	12.54	12.62	13.42	14.53	8.28	9.08	9.16	9.96	11.07
	3H	13.58	14.24	14.46	15.15	16.28	9.63	10.30	10.52	11.21	12.33
	4H	14.27	14.88	15.17	15.78	16.93	10.18	10.79	11.08	11.69	12.84
	6H	14.79	15.31	15.70	16.24	17.39	10.60	11.12	11.51	12.05	13.20
	8H	14.96	15.45	15.88	16.37	17.54	10.73	11.22	11.64	12.14	13.30
	12H	15.06	15.50	16.00	16.44	17.61	10.80	11.23	11.73	12.17	13.35
8H	4H	14.25	14.73	15.16	15.66	16.82	10.47	10.96	11.38	11.88	13.04
	6H	14.81	15.21	15.75	16.18	17.34	10.98	11.39	11.92	12.35	13.51
	8H	15.02	15.38	15.98	16.34	17.52	11.17	11.53	12.12	12.48	13.66
	12H	15.17	15.48	16.12	16.43	17.66	11.29	11.60	12.24	12.55	13.78
12H	4H	14.20	14.64	15.14	15.58	16.75	10.48	10.92	11.41	11.86	13.03
	6H	14.79	15.14	15.74	16.10	17.28	11.03	11.39	11.98	12.34	13.53
	8H	15.01	15.32	15.96	16.27	17.50	11.24	11.55	12.19	12.50	13.74

END OF REPORT