

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332990-940

Luminaire Tested: **SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332990-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5464.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332990-940

CATALOG NUMBER: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332990-940

CATALOG NUMBER: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	79
1	105	100	96	93	100	96	93	89	88	85	83	80	78	76	74	72	71	67
2	96	88	82	77	91	84	79	74	78	73	69	71	68	65	65	63	60	57
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52	49
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45	42
5	74	62	54	48	71	60	52	46	55	49	44	51	46	42	47	43	39	37
6	68	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35	32
7	64	51	43	37	61	49	41	36	46	39	34	42	37	33	39	35	31	29
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	25	23
10	52	39	32	27	50	38	31	26	36	30	25	33	28	24	31	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15012	15012	15012
5°	15046	14862	14955
10°	14952	14684	14684
15°	14780	14375	14269
20°	14545	13970	13713
25°	14243	13495	13153
30°	13951	12995	12450
35°	13626	12476	11745
40°	13235	11884	10984
45°	12875	11298	10209
50°	12465	10623	9388
55°	12024	9920	8497
60°	11541	9150	7585
65°	11096	8187	6692
70°	10452	7124	5681
75°	9638	5908	4619
80°	8405	4500	4235
85°	7123	4085	3825



TEST NUMBER: P332990-940

CATALOG NUMBER: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	3.2
10°-20°	487.1	8.9
20°-30°	703.4	12.9
30°-40°	797.3	14.6
40°-50°	770.0	14.1
50°-60°	640.3	11.7
60°-70°	442.1	8.1
70°-80°	224.1	4.1
80°-90°	58.4	1.1
90°-100°	115.9	2.1
100°-110°	241.1	4.4
110°-120°	216.0	4.0
120°-130°	181.7	3.3
130°-140°	151.5	2.8
140°-150°	115.7	2.1
150°-160°	81.3	1.5
160°-170°	47.8	0.9
170°-180°	15.6	0.3
0°-30°	1365.2	25.0
0°-40°	2162.6	39.6
0°-60°	3572.8	65.4
0°-90°	4297.4	78.6
90°-120°	573.0	10.5
90°-150°	1021.9	18.7
90°-180°	1167.0	21.4
0°-180°	5464.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1860	1860	1860	1860	1860	
5°	1857	1850	1834	1847	1845	176
15°	1768	1754	1720	1717	1707	498
25°	1599	1572	1515	1491	1477	736
35°	1383	1336	1266	1219	1192	864
45°	1128	1073	990	922	894	869
55°	854	795	705	633	604	764
65°	581	518	429	370	350	573
75°	309	256	189	158	148	326
85°	77	50	44	41	41	86
90°	0	2	6	6	7	4
95°	10	33	257	127	77	12
105°	37	53	207	445	443	39
115°	65	81	184	354	426	64
125°	90	108	183	301	340	80
135°	108	128	182	268	304	83
145°	124	142	181	226	248	78
155°	141	152	176	199	208	65
165°	154	158	169	178	181	43
175°	160	160	162	164	163	15
180°	160	160	160	160	160	



TEST NUMBER: P332990-940

CATALOG NUMBER: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1864.1	1863.1	1862.2	1861.1	1860.1	1858.2	1855.5	1852.6	1849.9	1847.1	1849.9
5°	1856.7	1855.5	1854.2	1853.0	1851.7	1849.1	1845.4	1841.6	1837.8	1834.0	1837.1
7.5°	1840.0	1838.6	1837.3	1835.9	1834.6	1831.5	1826.6	1821.7	1816.7	1811.8	1813.8
10°	1824.0	1822.4	1820.9	1819.3	1817.7	1814.0	1808.4	1802.7	1797.0	1791.3	1792.5
12.5°	1803.5	1801.7	1799.8	1798.0	1796.2	1791.9	1785.2	1778.5	1771.7	1765.1	1765.9
15°	1768.4	1765.6	1762.8	1760.0	1757.1	1751.7	1743.8	1735.9	1728.0	1720.0	1719.4
17.5°	1726.1	1721.9	1717.8	1713.7	1709.6	1702.8	1693.3	1683.8	1674.3	1664.8	1663.0
20°	1693.0	1688.9	1684.8	1680.7	1676.6	1669.1	1658.4	1647.6	1636.8	1626.1	1623.5
22.5°	1656.5	1652.0	1647.3	1642.7	1638.1	1630.0	1618.5	1607.0	1595.4	1583.9	1580.1
25°	1599.0	1593.3	1587.6	1582.0	1576.3	1566.9	1554.0	1541.0	1528.0	1515.0	1509.7
27.5°	1538.6	1531.5	1524.4	1517.2	1510.0	1499.6	1485.7	1471.9	1457.9	1444.1	1437.4
30°	1496.6	1488.6	1480.7	1472.7	1464.9	1453.5	1438.6	1423.7	1408.9	1394.0	1386.1
32.5°	1452.1	1443.1	1434.2	1425.3	1416.4	1404.3	1388.8	1373.5	1358.1	1342.7	1333.6
35°	1382.6	1372.4	1362.4	1352.2	1342.1	1329.1	1313.3	1297.5	1281.7	1265.9	1255.1
37.5°	1308.3	1297.8	1287.4	1276.9	1266.5	1252.5	1235.0	1217.5	1200.0	1182.4	1170.4
40°	1255.9	1245.5	1235.0	1224.6	1214.1	1199.9	1181.9	1163.8	1145.8	1127.7	1114.5
42.5°	1205.8	1194.8	1183.8	1172.9	1162.0	1147.1	1128.3	1109.5	1090.7	1071.9	1058.4
45°	1127.7	1116.0	1104.3	1092.6	1080.9	1065.5	1046.6	1027.6	1008.6	989.6	974.1
47.5°	1047.1	1035.0	1023.0	1010.8	998.8	982.8	963.1	943.3	923.6	903.9	887.8
50°	992.5	980.1	967.8	955.5	943.1	926.8	906.5	886.3	866.0	845.8	830.0
52.5°	936.7	924.5	912.5	900.4	888.3	871.8	851.1	830.4	809.6	788.8	772.8
55°	854.3	841.7	829.0	816.4	803.7	787.1	766.5	746.0	725.4	704.8	688.4
57.5°	772.8	759.7	746.5	733.4	720.2	703.6	683.3	663.0	642.7	622.5	605.8
60°	714.8	702.1	689.5	676.8	664.1	647.7	627.5	607.3	586.9	566.7	550.3
62.5°	662.4	649.3	636.1	622.9	609.8	592.8	572.0	551.3	530.5	509.8	494.5
65°	580.9	567.3	553.8	540.1	526.6	509.6	489.4	469.1	448.9	428.6	415.0
67.5°	496.3	483.3	470.3	457.3	444.3	428.3	409.5	390.7	371.9	353.1	341.4
70°	442.8	429.5	416.3	403.0	389.7	374.0	356.0	338.0	319.9	301.8	291.4
72.5°	385.8	373.9	361.9	349.8	337.8	323.2	306.2	289.2	272.2	255.1	246.2
75°	309.0	297.3	285.5	273.8	262.2	248.9	234.0	219.1	204.3	189.4	182.1
77.5°	231.0	221.1	211.1	201.2	191.2	180.2	168.2	156.2	144.2	132.2	127.9
80°	180.8	171.7	162.5	153.3	144.1	134.8	125.3	115.8	106.3	96.8	95.9
82.5°	137.6	129.1	120.7	112.3	103.9	96.9	91.5	86.1	80.6	75.2	74.5
85°	76.9	70.5	64.2	57.9	51.5	48.0	47.0	46.0	45.1	44.1	43.5
87.5°	26.3	24.3	22.6	20.6	18.6	17.5	17.6	17.3	17.2	17.1	16.8
90°	0.4	1.0	1.9	2.2	2.5	2.5	4.4	4.4	5.1	5.7	5.4
92.5°	3.6	5.3	8.2	12.0	16.7	23.2	39.2	63.7	87.5	100.0	83.3
95°	10.4	11.3	14.5	18.6	26.1	39.4	66.8	118.5	193.9	256.8	264.1
97.5°	18.6	18.6	21.4	25.1	31.7	42.7	63.8	106.6	181.4	270.5	331.8
100°	24.0	24.0	26.1	30.0	35.9	46.0	64.6	100.2	164.5	253.4	334.0
102.5°	29.0	29.5	31.5	35.0	40.8	50.3	67.1	98.4	153.2	231.9	315.1
105°	36.9	37.8	39.4	43.2	48.9	58.0	73.1	99.2	143.4	206.7	280.8
107.5°	45.6	46.2	47.8	51.8	57.2	66.3	80.1	104.0	141.6	192.6	253.1
110°	51.4	52.0	53.6	57.3	63.0	71.5	85.4	107.5	142.1	187.8	239.2



TEST NUMBER: P332990-940

CATALOG NUMBER: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.9	57.5	59.4	62.9	68.6	77.0	90.4	111.3	143.7	185.6	231.4
115°	64.9	65.9	68.0	71.2	77.2	85.7	98.4	117.3	146.5	184.4	224.1
117.5°	73.2	74.1	76.1	79.5	85.2	94.0	105.9	123.3	149.6	184.0	220.8
120°	78.8	79.5	81.6	85.1	90.4	99.2	111.3	127.6	151.9	184.0	219.0
122.5°	83.8	84.4	86.7	89.9	95.8	104.3	116.3	131.7	154.2	183.8	217.0
125°	90.4	91.7	93.6	97.1	103.1	111.9	123.2	137.7	157.6	183.4	213.7
127.5°	96.3	97.3	99.6	103.5	109.8	118.7	129.7	142.9	160.3	182.7	209.2
130°	99.6	100.9	103.3	108.1	114.0	123.2	133.9	146.2	162.3	182.4	206.4
132.5°	102.9	103.9	107.2	111.6	118.2	126.7	137.5	149.5	164.1	182.3	203.9
135°	107.5	108.7	111.9	117.3	123.9	132.1	142.4	153.8	166.7	181.8	200.1
137.5°	112.1	113.2	116.7	121.8	128.7	136.5	146.2	156.9	168.3	181.8	196.9
140°	115.4	116.3	119.8	125.1	131.7	139.3	148.7	158.8	169.5	181.6	195.1
142.5°	118.9	119.8	123.1	128.1	134.5	141.8	151.1	160.3	170.6	181.6	193.6
145°	123.9	124.8	128.0	132.3	138.4	145.3	153.5	162.0	171.1	180.9	191.0
147.5°	129.5	129.7	132.6	137.1	142.0	148.3	156.0	163.5	171.5	179.8	188.7
150°	133.0	133.3	135.8	139.6	144.4	150.3	157.3	164.2	171.5	179.0	186.9
152.5°	136.3	136.3	138.8	142.4	146.6	152.1	158.3	164.7	170.9	177.7	184.9
155°	140.9	141.2	143.1	146.2	149.7	154.4	159.8	165.1	170.2	175.8	181.8
157.5°	145.3	145.3	147.1	149.5	152.6	156.3	160.9	165.1	169.3	173.9	178.8
160°	148.1	148.1	149.4	151.6	154.1	157.6	161.4	165.1	168.6	172.4	176.5
162.5°	150.6	150.4	151.4	153.4	155.6	158.4	161.8	165.1	167.8	170.9	174.5
165°	153.5	153.5	154.1	155.7	157.3	159.2	162.0	164.5	166.4	168.6	171.1
167.5°	156.3	156.0	156.3	157.5	158.4	159.9	161.9	163.7	164.9	166.3	168.1
170°	157.6	157.3	157.6	158.5	159.2	160.1	161.7	163.3	163.9	164.8	166.1
172.5°	158.8	158.5	158.5	159.3	159.6	160.3	161.4	162.7	162.9	163.3	164.3
175°	160.1	159.8	159.8	160.1	160.4	160.4	161.0	162.0	161.7	161.7	162.3
177.5°	160.7	160.4	160.2	160.4	160.4	160.4	160.7	161.1	160.7	160.7	161.0
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332990-940

CATALOG NUMBER: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6	1859.6
2.5°	1852.6	1855.5	1858.2	1859.5	1859.2	1858.9	1858.7	1858.5
5°	1840.3	1843.4	1846.6	1847.9	1847.3	1846.6	1846.0	1845.4
7.5°	1815.8	1817.8	1819.9	1820.3	1819.4	1818.4	1817.3	1816.3
10°	1793.8	1795.0	1796.4	1796.4	1795.0	1793.8	1792.5	1791.3
12.5°	1766.6	1767.4	1768.1	1767.5	1765.9	1764.1	1762.3	1760.5
15°	1718.8	1718.1	1717.5	1716.1	1713.9	1711.6	1709.5	1707.3
17.5°	1661.3	1659.5	1657.7	1655.2	1651.8	1648.4	1645.1	1641.7
20°	1621.0	1618.5	1616.0	1612.7	1608.6	1604.5	1600.3	1596.2
22.5°	1576.4	1572.5	1568.8	1565.2	1561.8	1558.4	1555.1	1551.8
25°	1504.2	1498.9	1493.5	1489.2	1486.0	1482.9	1479.7	1476.6
27.5°	1430.8	1424.2	1417.6	1411.9	1407.4	1402.8	1398.3	1393.7
30°	1378.1	1370.3	1362.4	1355.8	1350.8	1345.8	1340.7	1335.6
32.5°	1324.4	1315.2	1306.0	1299.0	1294.2	1289.4	1284.6	1279.8
35°	1244.3	1233.6	1222.8	1214.6	1208.9	1203.2	1197.5	1191.8
37.5°	1158.3	1146.3	1134.3	1125.4	1119.7	1114.0	1108.4	1102.7
40°	1101.2	1087.9	1074.6	1065.1	1059.4	1053.6	1048.0	1042.3
42.5°	1044.8	1031.3	1017.7	1008.0	1002.0	996.1	990.2	984.2
45°	958.6	943.1	927.6	916.9	911.3	905.6	899.9	894.2
47.5°	871.7	855.7	839.6	828.4	822.2	815.9	809.6	803.3
50°	814.1	798.3	782.5	771.6	765.6	759.6	753.6	747.5
52.5°	756.7	740.7	724.5	713.4	707.1	700.9	694.6	688.3
55°	671.9	655.5	639.0	627.8	621.8	615.7	609.8	603.7
57.5°	589.2	572.4	555.7	545.1	540.6	535.9	531.4	526.8
60°	533.8	517.4	500.9	490.2	485.1	480.0	474.9	469.8
62.5°	479.4	464.2	449.0	439.3	435.3	431.3	427.2	423.2
65°	401.4	387.8	374.2	365.4	361.7	357.8	354.1	350.3
67.5°	329.8	318.0	306.3	298.4	294.2	290.0	285.8	281.6
70°	281.0	270.5	260.1	253.3	250.1	247.0	243.8	240.7
72.5°	237.3	228.4	219.5	213.6	210.6	207.8	204.8	201.9
75°	174.9	167.6	160.2	155.7	153.8	151.9	150.0	148.1
77.5°	123.7	119.4	115.2	112.8	112.2	111.6	111.1	110.5
80°	95.0	94.0	93.0	92.4	92.1	91.8	91.5	91.1
82.5°	73.8	73.1	72.4	71.9	71.6	71.2	71.0	70.6
85°	42.9	42.3	41.6	41.3	41.3	41.3	41.3	41.3
87.5°	16.6	16.4	16.2	16.2	16.5	16.9	17.0	17.3
90°	5.7	6.0	6.3	6.3	6.6	7.0	6.6	6.6
92.5°	61.9	46.5	37.1	30.8	27.0	25.3	24.3	24.3
95°	233.5	184.7	142.4	111.9	96.4	86.7	81.0	76.9
97.5°	345.0	326.9	296.0	263.1	240.5	221.6	212.1	205.5
100°	380.0	386.4	371.0	347.6	320.2	301.0	291.5	289.0
102.5°	378.4	409.6	414.0	404.3	387.5	373.6	363.6	361.6
105°	352.9	407.5	438.7	451.7	452.3	449.7	445.3	443.4
107.5°	317.0	375.1	418.9	447.1	462.6	469.8	473.0	473.8
110°	295.3	349.8	395.6	430.2	452.5	465.8	471.4	474.3



TEST NUMBER: P332990-940

CATALOG NUMBER: SA4XXRDIP-C1195D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.4	327.6	370.8	405.5	430.9	446.9	454.9	459.4
115°	263.5	302.2	339.1	369.3	394.2	413.1	423.3	425.8
117.5°	255.7	287.8	316.7	342.4	363.6	379.5	389.7	391.6
120°	252.1	281.4	306.7	329.0	347.0	360.9	369.1	372.6
122.5°	249.1	277.4	300.3	319.9	335.1	347.0	353.9	357.4
125°	244.0	271.0	292.7	310.1	322.7	331.9	337.9	339.7
127.5°	237.6	263.5	285.3	301.7	314.3	322.4	327.5	329.4
130°	232.6	257.5	278.9	295.6	308.5	316.4	321.5	323.3
132.5°	227.3	250.7	271.6	288.3	301.0	309.9	314.7	316.6
135°	220.0	240.5	259.7	275.4	288.0	296.9	301.9	303.8
137.5°	213.4	230.7	246.9	261.1	273.0	281.6	285.8	288.0
140°	209.6	224.4	238.5	251.8	262.9	269.7	274.2	276.7
142.5°	206.1	219.1	231.2	242.7	252.5	259.0	262.9	264.6
145°	201.1	211.8	221.2	230.1	237.9	243.3	246.5	248.0
147.5°	197.0	205.5	213.0	220.0	225.8	230.4	232.7	233.4
150°	194.5	201.7	208.0	213.7	218.7	222.8	224.7	225.0
152.5°	191.7	198.0	203.8	208.4	212.7	216.0	217.1	217.5
155°	187.5	192.5	197.2	201.1	204.2	206.7	207.7	207.7
157.5°	183.1	187.3	191.3	194.3	196.6	198.6	199.1	199.1
160°	180.3	183.7	187.2	189.8	191.6	193.5	193.9	193.9
162.5°	177.5	180.5	183.2	185.5	186.8	188.7	189.0	188.8
165°	173.6	175.6	177.7	179.3	180.6	181.8	181.6	181.2
167.5°	170.0	171.4	173.2	174.1	174.7	175.6	175.5	175.2
170°	167.6	168.6	169.9	170.9	171.5	171.7	171.5	171.5
172.5°	165.7	166.3	167.1	167.8	168.2	168.4	168.2	167.6
175°	162.9	163.3	163.9	163.9	163.9	164.5	163.9	163.3
177.5°	161.1	161.4	161.4	161.7	161.4	161.7	161.1	160.7
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4

(END OF REPORT)