

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902277

Luminaire Tested: DFN2DIP-4P4F0-030D030US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902277
REPORT IS A COMBINATION OF REPORTS P900600 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-030D030US830-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5202.9 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 50.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902277

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902277

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US830-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45			40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34			29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19			16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	758	758	758
5°	759	746	751
10°	752	732	727
15°	742	708	689
20°	728	675	643
25°	714	638	599
30°	695	600	542
35°	677	559	492
40°	658	516	435
45°	637	469	384
50°	614	421	333
55°	591	370	284
60°	563	317	234
65°	532	263	211
70°	494	212	192
75°	447	188	175
80°	378	158	153
85°	264	107	117

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 637 cd/sqm

TEST NUMBER: P902277

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	2.1
10°-20°	300.7	5.8
20°-30°	422.1	8.1
30°-40°	460.2	8.8
40°-50°	422.9	8.1
50°-60°	332.2	6.4
60°-70°	216.2	4.2
70°-80°	111.3	2.1
80°-90°	30.1	0.6
90°-100°	31.5	0.6
100°-110°	117.3	2.3
110°-120°	311.1	6.0
120°-130°	516.0	9.9
130°-140°	548.1	10.5
140°-150°	509.4	9.8
150°-160°	409.6	7.9
160°-170°	263.9	5.1
170°-180°	90.8	1.7
0°-30°	832.3	16.0
0°-40°	1292.5	24.8
0°-60°	2047.6	39.4
0°-90°	2405.2	46.2
90°-120°	459.9	8.8
90°-150°	2033.4	39.1
90°-180°	2798.0	53.8
0°-180°	5202.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	1	8	14	17	19	5
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	

TEST NUMBER: P902277

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6

TEST NUMBER: P902277

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3

TEST NUMBER: P902277

CATALOG NUMBER: DFN2DIP-4P4F0-030D030US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.84	6.64	6.84	7.64	8.97	1.80	2.60	2.80	3.60	4.93
	3H	7.52	8.24	8.53	9.25	10.60	2.99	3.71	4.00	4.72	6.06
	4H	8.13	8.81	9.15	9.82	11.18	3.44	4.12	4.46	5.13	6.49
	6H	8.56	9.18	9.59	10.20	11.57	3.76	4.38	4.79	5.40	6.77
	8H	8.69	9.28	9.72	10.31	11.68	3.85	4.44	4.89	5.48	6.84
	12H	8.75	9.31	9.79	10.34	11.73	3.90	4.46	4.93	5.49	6.87
4H	2H	5.86	6.53	6.88	7.55	8.90	2.40	3.07	3.42	4.09	5.44
	3H	7.69	8.25	8.72	9.29	10.66	3.75	4.31	4.78	5.35	6.72
	4H	8.38	8.90	9.42	9.93	11.33	4.29	4.81	5.34	5.84	7.24
	6H	8.90	9.34	9.95	10.40	11.79	4.71	5.16	5.76	6.21	7.60
	8H	9.08	9.49	10.13	10.54	11.95	4.84	5.26	5.90	6.31	7.71
	12H	9.18	9.55	10.25	10.62	12.02	4.91	5.28	5.98	6.35	7.75
8H	4H	8.35	8.76	9.40	9.81	11.22	4.58	4.99	5.63	6.04	7.44
	6H	8.92	9.26	10.00	10.35	11.75	5.10	5.44	6.17	6.53	7.93
	8H	9.14	9.44	10.22	10.52	11.94	5.29	5.59	6.37	6.67	8.08
	12H	9.28	9.55	10.37	10.62	12.08	5.41	5.67	6.49	6.74	8.20
12H	4H	8.30	8.67	9.37	9.74	11.15	4.58	4.95	5.65	6.02	7.43
	6H	8.90	9.20	9.98	10.27	11.69	5.15	5.45	6.23	6.52	7.94
	8H	9.12	9.38	10.20	10.45	11.92	5.36	5.62	6.44	6.69	8.15

END OF REPORT