

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902292

Luminaire Tested: DFN2DIP-4P4F0-030D070US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902292
REPORT IS A COMBINATION OF REPORTS P899128 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-030D070US830-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8242.6 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902292

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902292

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	32	32
2	85	78	72	68	76	70	66	61	56	52	49	42	40	38	29	28	27
3	78	69	62	57	70	62	56	52	49	45	42	37	35	32	26	25	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	24	22	20
5	65	54	47	41	59	49	43	38	39	35	31	30	27	24	21	19	18
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	20	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	33	27	46	36	30	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	758	758	758
5°	759	746	751
10°	752	732	727
15°	742	708	689
20°	728	675	643
25°	714	638	599
30°	695	600	542
35°	677	559	492
40°	658	516	435
45°	637	469	384
50°	614	421	333
55°	591	370	284
60°	563	317	234
65°	532	263	211
70°	494	212	192
75°	447	188	175
80°	378	158	153
85°	264	107	117

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1580 cd/sqm

TEST NUMBER: P902292

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	1.3
10°-20°	300.7	3.6
20°-30°	422.1	5.1
30°-40°	460.2	5.6
40°-50°	422.9	5.1
50°-60°	332.2	4.0
60°-70°	216.2	2.6
70°-80°	111.3	1.4
80°-90°	34.3	0.4
90°-100°	129.1	1.6
100°-110°	410.3	5.0
110°-120°	702.1	8.5
120°-130°	923.3	11.2
130°-140°	1036.4	12.6
140°-150°	1016.3	12.3
150°-160°	852.6	10.3
160°-170°	565.4	6.9
170°-180°	197.6	2.4
0°-30°	832.3	10.1
0°-40°	1292.5	15.7
0°-60°	2047.6	24.8
0°-90°	2409.4	29.2
90°-120°	1241.5	15.1
90°-150°	4217.6	51.2
90°-180°	5833.0	70.8
0°-180°	8242.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	2	23	62	58	60	8
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	

TEST NUMBER: P902292

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2

TEST NUMBER: P902292

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6

TEST NUMBER: P902292

CATALOG NUMBER: DFN2DIP-4P4F0-030D070US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.86	4.55	4.98	5.66	7.20	0.00	0.51	0.95	1.62	3.16
	3H	5.53	6.15	6.66	7.27	8.83	1.00	1.61	2.13	2.74	4.29
	4H	6.14	6.72	7.28	7.84	9.41	1.45	2.03	2.59	3.15	4.71
	6H	6.56	7.09	7.71	8.22	9.79	1.76	2.30	2.91	3.42	4.99
	8H	6.68	7.19	7.83	8.33	9.90	1.85	2.36	3.00	3.50	5.06
	12H	6.74	7.23	7.90	8.36	9.95	1.89	2.37	3.04	3.50	5.09
4H	2H	3.86	4.44	5.01	5.57	7.13	0.40	0.98	1.55	2.11	3.67
	3H	5.68	6.17	6.84	7.32	8.89	1.74	2.23	2.89	3.37	4.95
	4H	6.38	6.82	7.53	7.96	9.55	2.29	2.73	3.44	3.87	5.46
	6H	6.89	7.27	8.05	8.43	10.01	2.70	3.08	3.86	4.24	5.82
	8H	7.06	7.42	8.22	8.57	10.17	2.83	3.18	3.99	4.33	5.93
	12H	7.16	7.48	8.33	8.64	10.25	2.89	3.21	4.06	4.37	5.98
8H	4H	6.33	6.69	7.49	7.84	9.44	2.56	2.91	3.72	4.06	5.67
	6H	6.90	7.19	8.08	8.39	9.98	3.07	3.37	4.25	4.56	6.16
	8H	7.12	7.37	8.30	8.55	10.16	3.27	3.52	4.45	4.69	6.31
	12H	7.26	7.48	8.44	8.65	10.30	3.38	3.61	4.57	4.77	6.43
12H	4H	6.28	6.60	7.45	7.76	9.37	2.56	2.88	3.73	4.04	5.65
	6H	6.87	7.13	8.06	8.30	9.92	3.12	3.38	4.31	4.55	6.17
	8H	7.09	7.32	8.28	8.49	10.14	3.33	3.56	4.52	4.72	6.38

END OF REPORT