

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332893-940

Luminaire Tested: **SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332893-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4994.0 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332893-940

CATALOG NUMBER: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332893-940

CATALOG NUMBER: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				26
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22				22
2	84	77	71	67	75	69	64	60	54	50	48	40	37	36	26	25	24	18				18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16				16
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18	14				14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12				12
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14	11				11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9				9
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8				8
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8				8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4451	4451	4451
5°	4460	4406	4433
10°	4432	4353	4353
15°	4381	4262	4229
20°	4312	4141	4064
25°	4222	4000	3899
30°	4135	3852	3691
35°	4039	3698	3482
40°	3923	3523	3256
45°	3817	3350	3027
50°	3695	3149	2783
55°	3564	2940	2519
60°	3421	2713	2249
65°	3289	2428	1983
70°	3099	2110	1683
75°	2857	1753	1369
80°	2492	1334	1255
85°	2112	1213	1130



TEST NUMBER: P332893-940

CATALOG NUMBER: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	1.0
10°-20°	144.4	2.9
20°-30°	208.5	4.2
30°-40°	236.4	4.7
40°-50°	228.2	4.6
50°-60°	189.8	3.8
60°-70°	131.1	2.6
70°-80°	66.4	1.3
80°-90°	21.0	0.4
90°-100°	88.4	1.8
100°-110°	261.7	5.2
110°-120°	444.2	8.9
120°-130°	585.7	11.7
130°-140°	657.8	13.2
140°-150°	646.4	12.9
150°-160°	543.7	10.9
160°-170°	361.7	7.2
170°-180°	126.7	2.5
0°-30°	404.7	8.1
0°-40°	641.0	12.8
0°-60°	1059.1	21.2
0°-90°	1277.6	25.6
90°-120°	794.3	15.9
90°-150°	2684.3	53.8
90°-180°	3716.0	74.4
0°-180°	4994.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	548	544	548	547	52
15°	524	520	510	509	506	148
25°	474	466	449	442	438	218
35°	410	396	375	361	353	256
45°	334	318	293	273	265	258
55°	253	236	209	188	179	226
65°	172	154	127	110	104	170
75°	92	76	56	47	44	97
85°	23	15	13	12	12	26
90°	3	14	23	29	31	5
95°	62	71	79	82	82	69
105°	241	243	247	250	253	256
115°	452	452	450	449	448	445
125°	658	658	657	655	653	586
135°	848	854	855	853	850	656
145°	1031	1035	1036	1035	1032	645
155°	1181	1181	1180	1184	1180	543
165°	1286	1283	1280	1286	1282	362
175°	1338	1332	1331	1338	1331	127
180°	1340	1340	1340	1340	1340	



TEST NUMBER: P332893-940

CATALOG NUMBER: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	552.6	552.2	552.0	551.7	551.3	550.8	550.0	549.2	548.3	547.5	548.3
5°	550.4	550.0	549.7	549.3	548.8	548.1	547.0	545.9	544.7	543.7	544.6
7.5°	545.4	545.0	544.7	544.2	543.9	542.9	541.4	539.9	538.5	537.1	537.6
10°	540.6	540.2	539.8	539.3	538.8	537.7	536.0	534.3	532.6	531.0	531.4
12.5°	534.6	534.0	533.5	533.0	532.4	531.2	529.1	527.2	525.2	523.2	523.4
15°	524.2	523.3	522.5	521.7	520.8	519.2	516.9	514.5	512.2	509.9	509.7
17.5°	511.7	510.4	509.2	508.0	506.8	504.7	501.9	499.1	496.3	493.5	492.9
20°	501.9	500.6	499.4	498.2	497.0	494.8	491.6	488.4	485.2	482.0	481.3
22.5°	491.1	489.6	488.3	487.0	485.5	483.1	479.7	476.4	473.0	469.5	468.4
25°	474.0	472.3	470.6	469.0	467.3	464.5	460.7	456.8	452.9	449.1	447.5
27.5°	456.1	454.0	451.8	449.8	447.6	444.5	440.4	436.3	432.2	428.1	426.1
30°	443.6	441.2	438.9	436.6	434.3	430.9	426.4	422.0	417.6	413.2	410.9
32.5°	430.4	427.8	425.2	422.5	419.8	416.3	411.7	407.2	402.6	398.1	395.3
35°	409.8	406.8	403.9	400.8	397.8	394.0	389.3	384.6	380.0	375.2	372.0
37.5°	387.8	384.7	381.7	378.5	375.4	371.3	366.0	360.9	355.7	350.5	347.0
40°	372.3	369.2	366.0	363.0	359.9	355.7	350.4	345.0	339.7	334.3	330.4
42.5°	357.4	354.2	350.9	347.7	344.5	340.0	334.5	328.9	323.3	317.7	313.7
45°	334.3	330.8	327.3	323.9	320.4	315.8	310.2	304.6	299.0	293.4	288.7
47.5°	310.4	306.8	303.3	299.6	296.0	291.3	285.5	279.6	273.8	268.0	263.1
50°	294.2	290.5	286.9	283.2	279.6	274.7	268.8	262.7	256.7	250.7	246.0
52.5°	277.7	274.0	270.5	266.9	263.3	258.4	252.3	246.1	240.0	233.8	229.1
55°	253.2	249.5	245.8	242.0	238.3	233.3	227.2	221.1	215.0	208.9	204.0
57.5°	229.1	225.2	221.3	217.4	213.5	208.6	202.5	196.5	190.6	184.5	179.6
60°	211.9	208.1	204.4	200.6	196.9	192.0	186.0	179.9	174.0	168.0	163.1
62.5°	196.4	192.4	188.5	184.7	180.7	175.8	169.6	163.5	157.3	151.1	146.6
65°	172.2	168.2	164.2	160.2	156.0	151.1	145.1	139.0	133.0	127.1	123.1
67.5°	147.1	143.3	139.4	135.5	131.7	127.0	121.4	115.8	110.2	104.7	101.2
70°	131.3	127.3	123.4	119.5	115.5	110.8	105.5	100.1	94.8	89.4	86.4
72.5°	114.4	110.8	107.3	103.7	100.1	95.9	90.8	85.7	80.7	75.6	73.0
75°	91.6	88.1	84.6	81.1	77.7	73.7	69.4	64.9	60.5	56.2	53.9
77.5°	68.5	65.5	62.6	59.7	56.7	53.4	49.8	46.3	42.7	39.1	37.9
80°	53.6	50.9	48.2	45.5	42.7	39.9	37.2	34.3	31.5	28.7	28.4
82.5°	40.8	38.3	35.8	33.3	30.8	28.7	27.1	25.5	23.9	22.3	22.1
85°	22.8	21.0	19.1	17.1	15.2	14.2	13.9	13.6	13.4	13.1	12.9
87.5°	8.4	8.3	8.2	8.1	8.0	8.1	8.4	8.7	9.0	9.3	9.5
90°	3.1	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2
92.5°	22.2	25.1	28.0	30.9	33.8	35.8	37.2	38.4	39.8	41.0	41.8
95°	62.2	64.2	66.3	68.4	70.4	72.3	73.9	75.5	77.1	78.7	79.5
97.5°	108.6	110.2	111.9	113.5	115.2	117.0	118.9	120.7	122.6	124.5	125.4
100°	145.1	146.0	146.9	147.8	148.7	150.3	152.3	154.4	156.4	158.5	159.0
102.5°	183.2	183.5	183.9	184.2	184.7	185.7	187.6	189.6	191.5	193.3	193.9
105°	241.4	241.7	241.8	242.1	242.3	242.9	243.8	244.7	245.7	246.6	247.3
107.5°	302.5	302.8	303.1	303.4	303.6	303.8	304.0	304.1	304.3	304.3	305.1
110°	343.9	344.4	344.8	345.4	345.8	345.9	345.7	345.4	345.2	345.0	344.6



TEST NUMBER: P332893-940

CATALOG NUMBER: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	387.0	387.2	387.3	387.4	387.4	387.3	386.8	386.5	386.0	385.6	385.5
115°	451.7	451.7	451.7	451.7	451.7	451.5	451.0	450.6	450.0	449.6	449.4
117.5°	512.6	512.8	513.0	513.2	513.4	513.3	512.9	512.6	512.3	512.0	511.2
120°	553.2	554.1	555.1	556.0	556.9	557.1	556.3	555.6	554.9	554.3	553.1
122.5°	595.5	595.8	596.2	596.6	597.0	597.0	596.6	596.4	596.0	595.7	594.9
125°	657.8	657.8	657.8	657.8	657.8	657.7	657.5	657.3	657.0	656.8	656.4
127.5°	714.4	715.2	715.8	716.5	717.2	717.4	716.9	716.6	716.2	715.9	715.4
130°	754.2	754.9	755.5	756.3	757.0	757.3	757.3	757.3	757.3	757.3	756.9
132.5°	794.8	795.3	795.9	796.3	796.8	797.0	796.8	796.7	796.5	796.3	795.8
135°	848.5	849.9	851.2	852.7	854.0	854.7	854.7	854.7	854.7	854.7	854.3
137.5°	906.9	907.6	908.2	908.8	909.5	910.0	910.3	910.7	911.1	911.4	910.9
140°	945.8	946.3	946.8	947.3	947.7	947.9	947.9	947.9	947.9	947.9	947.7
142.5°	981.5	982.0	982.4	982.8	983.4	983.5	983.3	983.1	982.9	982.8	982.7
145°	1030.8	1031.7	1032.7	1033.6	1034.5	1035.1	1035.3	1035.5	1035.7	1036.0	1035.7
147.5°	1079.7	1080.8	1081.9	1083.0	1084.1	1084.6	1084.4	1084.2	1084.1	1083.9	1083.7
150°	1109.6	1110.4	1111.4	1112.3	1113.2	1113.7	1113.7	1113.7	1113.7	1113.7	1113.7
152.5°	1137.7	1138.3	1138.8	1139.3	1140.0	1140.3	1140.5	1140.7	1140.9	1141.0	1141.6
155°	1181.0	1181.0	1181.0	1181.0	1181.0	1180.9	1180.7	1180.4	1180.2	1180.0	1180.9
157.5°	1217.5	1217.1	1216.7	1216.3	1215.8	1215.6	1215.6	1215.5	1215.5	1215.4	1216.1
160°	1239.0	1238.9	1238.6	1238.3	1238.1	1237.9	1237.7	1237.4	1237.2	1237.0	1237.7
162.5°	1258.9	1258.3	1257.8	1257.1	1256.5	1256.2	1255.9	1255.7	1255.4	1255.2	1256.4
165°	1285.7	1285.0	1284.2	1283.6	1282.9	1282.3	1281.8	1281.4	1280.9	1280.5	1281.8
167.5°	1306.2	1305.2	1304.2	1303.2	1302.3	1301.8	1301.9	1301.9	1302.0	1302.0	1303.4
170°	1317.8	1316.6	1315.5	1314.3	1313.1	1312.7	1313.0	1313.1	1313.4	1313.7	1315.0
172.5°	1326.1	1325.1	1324.1	1323.1	1322.2	1321.7	1321.8	1321.9	1321.9	1322.0	1323.5
175°	1337.5	1336.3	1335.2	1334.0	1332.8	1332.1	1331.9	1331.7	1331.5	1331.2	1332.8
177.5°	1341.2	1340.2	1339.3	1338.5	1337.5	1337.0	1337.0	1337.0	1337.0	1337.0	1338.4
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5



TEST NUMBER: P332893-940

CATALOG NUMBER: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	549.2	550.0	550.8	551.2	551.1	551.1	551.0	550.9
5°	545.5	546.4	547.4	547.8	547.6	547.4	547.2	547.0
7.5°	538.2	538.9	539.5	539.6	539.3	539.0	538.7	538.4
10°	531.7	532.1	532.4	532.4	532.1	531.7	531.4	531.0
12.5°	523.6	523.9	524.1	524.0	523.4	522.9	522.4	521.8
15°	509.5	509.3	509.1	508.7	508.0	507.4	506.8	506.0
17.5°	492.4	492.0	491.4	490.6	489.6	488.7	487.7	486.7
20°	480.5	479.7	479.0	478.0	476.8	475.5	474.4	473.1
22.5°	467.3	466.1	465.0	464.0	463.0	462.0	461.0	459.9
25°	445.9	444.3	442.7	441.5	440.5	439.5	438.6	437.7
27.5°	424.1	422.1	420.2	418.6	417.1	415.8	414.5	413.1
30°	408.5	406.2	403.9	401.9	400.4	399.0	397.4	395.9
32.5°	392.6	389.9	387.2	385.0	383.6	382.2	380.8	379.3
35°	368.8	365.7	362.5	360.1	358.4	356.7	355.0	353.3
37.5°	343.4	339.8	336.3	333.6	331.9	330.2	328.5	326.8
40°	326.4	322.4	318.5	315.8	314.1	312.4	310.7	309.0
42.5°	309.7	305.7	301.7	298.8	297.0	295.2	293.5	291.8
45°	284.2	279.6	274.9	271.8	270.1	268.4	266.7	265.1
47.5°	258.4	253.6	248.9	245.6	243.7	241.8	240.0	238.2
50°	241.3	236.7	231.9	228.7	226.9	225.2	223.4	221.6
52.5°	224.3	219.5	214.8	211.4	209.6	207.8	205.9	204.0
55°	199.2	194.3	189.4	186.1	184.3	182.5	180.7	179.0
57.5°	174.6	169.7	164.7	161.6	160.2	158.9	157.5	156.1
60°	158.2	153.4	148.5	145.3	143.7	142.3	140.8	139.3
62.5°	142.1	137.6	133.1	130.3	129.0	127.9	126.6	125.5
65°	119.0	114.9	110.9	108.3	107.2	106.1	105.0	103.8
67.5°	97.7	94.3	90.8	88.5	87.2	86.0	84.7	83.5
70°	83.3	80.2	77.1	75.1	74.1	73.2	72.2	71.3
72.5°	70.4	67.7	65.1	63.3	62.4	61.6	60.7	59.8
75°	51.8	49.7	47.5	46.2	45.6	45.0	44.5	43.9
77.5°	36.6	35.4	34.2	33.4	33.3	33.1	32.9	32.7
80°	28.2	27.8	27.6	27.4	27.3	27.2	27.1	27.0
82.5°	21.8	21.7	21.5	21.3	21.2	21.1	21.0	21.0
85°	12.8	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	9.7	9.9	10.1	10.3	10.4	10.6	10.8	11.0
90°	25.6	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	42.7	43.5	44.3	44.9	45.2	45.5	45.7	46.0
95°	80.1	80.8	81.5	81.9	81.9	81.9	81.9	81.9
97.5°	126.2	127.0	127.9	128.2	128.2	128.2	128.2	128.2
100°	159.4	159.9	160.3	160.6	160.6	160.6	160.6	160.6
102.5°	194.6	195.3	195.9	196.3	196.5	196.7	196.9	197.1
105°	248.0	248.6	249.3	250.0	250.7	251.4	252.1	252.8
107.5°	305.7	306.3	306.9	307.3	307.2	307.2	307.1	307.1
110°	344.0	343.6	343.1	343.2	343.9	344.6	345.4	346.0



TEST NUMBER: P332893-940

CATALOG NUMBER: SA4XXRDIP-C350D1205U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	385.4	385.3	385.2	385.2	385.4	385.5	385.7	385.8
115°	449.2	448.9	448.7	448.4	448.3	448.0	447.8	447.5
117.5°	510.4	509.6	508.8	508.3	507.7	507.3	506.8	506.4
120°	552.0	550.8	549.7	549.3	549.7	550.2	550.7	551.2
122.5°	594.1	593.3	592.5	591.7	590.9	590.1	589.2	588.4
125°	655.9	655.4	655.0	654.5	654.1	653.6	653.1	652.6
127.5°	715.0	714.5	714.0	713.6	713.3	712.8	712.5	712.1
130°	756.3	755.9	755.5	754.7	753.9	753.0	752.0	751.1
132.5°	795.3	794.9	794.4	794.0	793.6	793.3	792.9	792.6
135°	853.8	853.3	852.8	852.3	851.6	850.9	850.2	849.5
137.5°	910.3	909.6	909.1	908.8	909.0	909.1	909.3	909.4
140°	947.4	947.3	947.0	946.8	946.6	946.3	946.1	945.8
142.5°	982.7	982.6	982.6	982.5	982.5	982.4	982.4	982.3
145°	1035.5	1035.3	1035.1	1034.6	1033.9	1033.2	1032.5	1031.9
147.5°	1083.5	1083.3	1083.1	1082.9	1082.7	1082.4	1082.2	1082.0
150°	1113.7	1113.7	1113.7	1113.6	1113.3	1113.1	1112.9	1112.7
152.5°	1142.1	1142.7	1143.3	1143.3	1142.6	1142.0	1141.4	1140.9
155°	1181.9	1182.8	1183.7	1183.7	1182.8	1181.9	1180.9	1180.0
157.5°	1216.8	1217.5	1218.2	1218.2	1217.4	1216.6	1215.8	1215.0
160°	1238.3	1239.0	1239.7	1239.5	1238.3	1237.2	1236.1	1234.9
162.5°	1257.7	1258.9	1260.2	1260.3	1259.1	1257.9	1256.8	1255.6
165°	1283.3	1284.6	1286.0	1286.2	1285.3	1284.4	1283.4	1282.5
167.5°	1304.8	1306.2	1307.5	1307.5	1306.1	1304.7	1303.2	1301.8
170°	1316.4	1317.8	1319.2	1319.0	1317.4	1315.8	1314.2	1312.6
172.5°	1325.1	1326.6	1328.2	1328.2	1326.5	1324.9	1323.3	1321.7
175°	1334.4	1336.1	1337.7	1337.7	1336.1	1334.4	1332.8	1331.2
177.5°	1339.6	1341.0	1342.2	1342.1	1340.6	1339.2	1337.7	1336.2
180°	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5	1339.5

(END OF REPORT)