

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902332

Luminaire Tested: DFN2DIP-4P4F0-050D050US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902332
REPORT IS A COMBINATION OF REPORTS P899108 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D050US830-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8176.6 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 90.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902332

CATALOG NUMBER: DFN2DIP-4P4F0-050D050US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902332

CATALOG NUMBER: DFN2DIP-4P4F0-050D050US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1264	1264	1264
5°	1266	1244	1252
10°	1253	1220	1212
15°	1236	1180	1149
20°	1213	1125	1072
25°	1190	1063	998
30°	1159	999	903
35°	1128	931	821
40°	1097	860	725
45°	1061	782	639
50°	1023	702	555
55°	984	617	474
60°	939	528	391
65°	887	438	352
70°	824	354	319
75°	745	313	292
80°	630	264	254
85°	441	179	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1128 cd/sqm

TEST NUMBER: P902332

CATALOG NUMBER: DFN2DIP-4P4F0-050D050US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	2.2
10°-20°	501.1	6.1
20°-30°	703.6	8.6
30°-40°	766.9	9.4
40°-50°	704.9	8.6
50°-60°	553.6	6.8
60°-70°	360.3	4.4
70°-80°	185.5	2.3
80°-90°	51.6	0.6
90°-100°	92.2	1.1
100°-110°	293.0	3.6
110°-120°	501.5	6.1
120°-130°	659.5	8.1
130°-140°	740.3	9.1
140°-150°	725.9	8.9
150°-160°	609.0	7.4
160°-170°	403.9	4.9
170°-180°	141.2	1.7
0°-30°	1387.2	17.0
0°-40°	2154.2	26.3
0°-60°	3412.7	41.7
0°-90°	4010.1	49.0
90°-120°	886.7	10.8
90°-150°	3012.5	36.8
90°-180°	4167.0	51.0
0°-180°	8176.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1853	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1185	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	1	16	44	41	43	8
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P902332

CATALOG NUMBER: DFN2DIP-4P4F0-050D050US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.8	1947.8	1947.8	1947.8	1947.8
2.5°	1956.5	1947.8	1928.3	1946.1	1942.5
5°	1947.8	1939.0	1916.0	1931.8	1926.7
7.5°	1931.8	1921.4	1896.7	1903.7	1894.8
10°	1910.7	1898.4	1863.2	1857.8	1847.3
12.5°	1884.3	1868.5	1820.8	1810.3	1790.8
15°	1852.6	1833.2	1773.3	1739.8	1722.2
17.5°	1815.5	1787.3	1713.3	1674.5	1646.2
20°	1773.3	1738.0	1649.8	1605.9	1567.0
22.5°	1727.5	1686.9	1584.6	1524.8	1498.4
25°	1681.6	1625.1	1508.8	1436.6	1410.0
27.5°	1627.0	1567.0	1438.3	1355.5	1314.9
30°	1568.9	1501.8	1360.7	1270.9	1223.2
32.5°	1512.4	1431.3	1286.9	1181.0	1136.9
35°	1449.0	1359.1	1204.0	1092.9	1054.0
37.5°	1387.2	1290.2	1126.4	1004.7	960.7
40°	1322.0	1216.4	1045.2	920.1	874.3
42.5°	1255.1	1142.3	964.2	833.7	789.8
45°	1184.6	1066.4	881.4	756.1	713.8
47.5°	1117.6	992.5	802.1	676.8	638.1
50°	1043.6	918.4	724.5	602.8	565.9
52.5°	971.2	839.0	650.4	534.1	500.7
55°	900.7	763.2	572.8	467.1	433.7
57.5°	828.5	687.5	504.2	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.9	241.5
67.5°	537.6	394.8	246.9	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.4
75°	324.3	200.9	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3



TEST NUMBER: P902332

CATALOG NUMBER: DFN2DIP-4P4F0-050D050US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P902332

CATALOG NUMBER: DFN2DIP-4P4F0-050D050US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.89	8.71	8.86	9.69	10.98	3.85	4.67	4.82	5.65	6.94
	3H	9.57	10.31	10.55	11.30	12.61	5.04	5.77	6.02	6.76	8.07
	4H	10.18	10.88	11.18	11.87	13.19	5.49	6.18	6.49	7.18	8.50
	6H	10.61	11.25	11.61	12.25	13.58	5.81	6.45	6.82	7.45	8.78
	8H	10.74	11.35	11.75	12.36	13.69	5.90	6.51	6.92	7.53	8.85
	12H	10.80	11.38	11.82	12.39	13.74	5.95	6.52	6.96	7.53	8.88
4H	2H	7.90	8.60	8.91	9.59	10.91	4.45	5.14	5.45	6.14	7.45
	3H	9.74	10.32	10.75	11.34	12.67	5.80	6.38	6.81	7.40	8.73
	4H	10.44	10.96	11.45	11.98	13.33	6.35	6.87	7.37	7.89	9.25
	6H	10.96	11.41	11.99	12.45	13.80	6.77	7.22	7.80	8.26	9.61
	8H	11.13	11.56	12.16	12.59	13.96	6.90	7.32	7.93	8.35	9.72
	12H	11.23	11.61	12.28	12.66	14.03	6.96	7.35	8.01	8.39	9.76
8H	4H	10.40	10.83	11.43	11.86	13.22	6.63	7.05	7.66	8.08	9.45
	6H	10.98	11.32	12.03	12.40	13.76	7.15	7.50	8.20	8.57	9.94
	8H	11.20	11.50	12.26	12.56	13.94	7.34	7.65	8.40	8.71	10.09
	12H	11.34	11.61	12.40	12.66	14.09	7.46	7.73	8.53	8.79	10.21
12H	4H	10.35	10.74	11.40	11.78	13.16	6.63	7.02	7.68	8.06	9.44
	6H	10.95	11.26	12.01	12.32	13.70	7.20	7.51	8.26	8.57	9.95
	8H	11.18	11.45	12.24	12.50	13.92	7.41	7.68	8.48	8.74	10.16

END OF REPORT