

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902340

Luminaire Tested: DFN2DIP-4P4F0-050D070US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902340
REPORT IS A COMBINATION OF REPORTS P899132 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D070US830-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9844.9 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 111.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902340

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902340

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1264	1264	1264
5°	1266	1244	1252
10°	1253	1220	1212
15°	1236	1180	1149
20°	1213	1125	1072
25°	1190	1063	998
30°	1159	999	903
35°	1128	931	821
40°	1097	860	725
45°	1061	782	639
50°	1023	702	555
55°	984	617	474
60°	939	528	391
65°	887	438	352
70°	824	354	319
75°	745	313	292
80°	630	264	254
85°	441	179	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1580 cd/sqm

TEST NUMBER: P902340

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	1.9
10°-20°	501.1	5.1
20°-30°	703.6	7.1
30°-40°	766.9	7.8
40°-50°	704.9	7.2
50°-60°	553.6	5.6
60°-70°	360.3	3.7
70°-80°	185.5	1.9
80°-90°	53.3	0.5
90°-100°	129.1	1.3
100°-110°	410.3	4.2
110°-120°	702.1	7.1
120°-130°	923.3	9.4
130°-140°	1036.4	10.5
140°-150°	1016.3	10.3
150°-160°	852.6	8.7
160°-170°	565.4	5.7
170°-180°	197.6	2.0
0°-30°	1387.2	14.1
0°-40°	2154.2	21.9
0°-60°	3412.7	34.7
0°-90°	4011.8	40.7
90°-120°	1241.5	12.6
90°-150°	4217.6	42.8
90°-180°	5833.0	59.2
0°-180°	9844.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1853	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1185	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	23	62	58	60	10
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	

TEST NUMBER: P902340

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.8	1947.8	1947.8	1947.8	1947.8
2.5°	1956.5	1947.8	1928.3	1946.1	1942.5
5°	1947.8	1939.0	1916.0	1931.8	1926.7
7.5°	1931.8	1921.4	1896.7	1903.7	1894.8
10°	1910.7	1898.4	1863.2	1857.8	1847.3
12.5°	1884.3	1868.5	1820.8	1810.3	1790.8
15°	1852.6	1833.2	1773.3	1739.8	1722.2
17.5°	1815.5	1787.3	1713.3	1674.5	1646.2
20°	1773.3	1738.0	1649.8	1605.9	1567.0
22.5°	1727.5	1686.9	1584.6	1524.8	1498.4
25°	1681.6	1625.1	1508.8	1436.6	1410.0
27.5°	1627.0	1567.0	1438.3	1355.5	1314.9
30°	1568.9	1501.8	1360.7	1270.9	1223.2
32.5°	1512.4	1431.3	1286.9	1181.0	1136.9
35°	1449.0	1359.1	1204.0	1092.9	1054.0
37.5°	1387.2	1290.2	1126.4	1004.7	960.7
40°	1322.0	1216.4	1045.2	920.1	874.3
42.5°	1255.1	1142.3	964.2	833.7	789.8
45°	1184.6	1066.4	881.4	756.1	713.8
47.5°	1117.6	992.5	802.1	676.8	638.1
50°	1043.6	918.4	724.5	602.8	565.9
52.5°	971.2	839.0	650.4	534.1	500.7
55°	900.7	763.2	572.8	467.1	433.7
57.5°	828.5	687.5	504.2	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.9	241.5
67.5°	537.6	394.8	246.9	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.4
75°	324.3	200.9	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2

TEST NUMBER: P902340

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6

TEST NUMBER: P902340

CATALOG NUMBER: DFN2DIP-4P4F0-050D070US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.05	7.81	8.09	8.85	10.25	3.01	3.77	4.05	4.81	6.21
	3H	8.73	9.40	9.77	10.45	11.87	4.19	4.87	5.24	5.92	7.34
	4H	9.33	9.98	10.39	11.03	12.46	4.64	5.29	5.70	6.34	7.76
	6H	9.76	10.35	10.83	11.40	12.84	4.96	5.55	6.03	6.61	8.05
	8H	9.88	10.45	10.96	11.52	12.95	5.05	5.61	6.12	6.68	8.12
	12H	9.95	10.48	11.03	11.55	13.00	5.09	5.63	6.17	6.69	8.15
4H	2H	7.06	7.70	8.12	8.75	10.18	3.60	4.24	4.67	5.29	6.72
	3H	8.89	9.42	9.96	10.50	11.94	4.94	5.48	6.02	6.56	8.00
	4H	9.58	10.07	10.66	11.14	12.60	5.49	5.98	6.57	7.05	8.51
	6H	10.10	10.52	11.19	11.61	13.07	5.91	6.33	7.00	7.42	8.88
	8H	10.27	10.67	11.36	11.75	13.22	6.04	6.43	7.13	7.52	8.99
	12H	10.37	10.72	11.47	11.82	13.30	6.10	6.45	7.21	7.55	9.03
8H	4H	9.54	9.94	10.63	11.02	12.49	5.77	6.16	6.86	7.25	8.72
	6H	10.11	10.44	11.22	11.56	13.03	6.29	6.61	7.40	7.74	9.21
	8H	10.33	10.62	11.45	11.73	13.21	6.48	6.76	7.60	7.87	9.36
	12H	10.47	10.72	11.59	11.83	13.35	6.60	6.85	7.72	7.95	9.48
12H	4H	9.49	9.85	10.60	10.95	12.42	5.77	6.13	6.88	7.23	8.70
	6H	10.09	10.37	11.21	11.48	12.97	6.34	6.62	7.46	7.73	9.22
	8H	10.31	10.56	11.43	11.66	13.19	6.55	6.80	7.67	7.90	9.43

END OF REPORT