

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332898-940

Luminaire Tested: **SA4XXRDIP-C575D365U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332898-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3398.3 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332898-940
CATALOG NUMBER: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332898-940

CATALOG NUMBER: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20				20				20	
RC	80									50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																			
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62	
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53	
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45	
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38	
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33	
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29	
6	66	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25	
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23	
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20	
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	20	18	
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P332898-940

CATALOG NUMBER: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	2.5
10°-20°	237.4	7.0
20°-30°	342.8	10.1
30°-40°	388.6	11.4
40°-50°	375.2	11.0
50°-60°	312.0	9.2
60°-70°	215.4	6.3
70°-80°	109.2	3.2
80°-90°	29.2	0.9
90°-100°	14.4	0.4
100°-110°	91.9	2.7
110°-120°	175.8	5.2
120°-130°	223.1	6.6
130°-140°	238.7	7.0
140°-150°	223.2	6.6
150°-160°	180.0	5.3
160°-170°	116.1	3.4
170°-180°	40.0	1.2
0°-30°	665.3	19.6
0°-40°	1053.9	31.0
0°-60°	1741.1	51.2
0°-90°	2095.0	61.6
90°-120°	282.1	8.3
90°-150°	967.2	28.5
90°-180°	1303.0	38.3
0°-180°	3398.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	1	4	7	9	10	3
95°	17	7	7	9	9	22
105°	95	97	98	100	90	99
115°	177	178	178	178	178	174
125°	249	250	250	250	251	222
135°	309	309	310	310	311	238
145°	356	357	357	357	358	222
155°	390	391	390	391	390	180
165°	412	410	410	413	410	116
175°	421	420	420	422	419	40
180°	421	421	421	421	421	



TEST NUMBER: P332898-940

CATALOG NUMBER: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	12.9	12.1	11.3	10.4	9.6	9.2	9.2	9.2	9.2	9.2	9.1
90°	1.0	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3
92.5°	4.0	4.0	4.0	4.1	4.1	4.5	5.0	5.5	6.2	6.7	7.1
95°	17.3	15.0	12.6	10.2	7.8	6.7	6.7	6.8	6.9	7.0	7.3
97.5°	36.8	38.3	39.8	41.3	42.7	39.6	31.7	24.0	16.1	8.3	8.4
100°	51.7	53.0	54.2	55.5	56.7	52.5	42.9	33.2	23.5	13.9	12.7
102.5°	68.3	69.3	70.2	71.1	72.1	71.9	70.6	69.4	68.0	66.8	53.9
105°	94.9	95.2	95.7	96.1	96.6	96.9	97.3	97.6	98.0	98.4	99.0
107.5°	119.5	119.7	119.9	120.1	120.4	120.6	121.2	121.6	122.1	122.6	122.9
110°	136.2	136.3	136.5	136.8	137.0	137.3	137.7	138.1	138.6	139.0	139.1



TEST NUMBER: P332898-940

CATALOG NUMBER: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.3	152.7	153.0	153.4	153.8	154.1	154.3	154.4	154.6	154.9	154.8
115°	177.1	177.4	177.5	177.7	178.0	178.0	178.0	177.9	177.8	177.7	177.9
117.5°	199.5	199.7	200.0	200.4	200.6	200.8	201.0	201.2	201.3	201.4	201.4
120°	214.6	214.9	215.2	215.4	215.7	215.8	215.8	215.7	215.6	215.5	215.7
122.5°	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	229.8	230.0	230.0
125°	249.0	249.2	249.5	249.8	250.1	250.1	250.0	249.9	249.8	249.6	249.8
127.5°	268.1	268.2	268.2	268.3	268.4	268.6	268.9	269.2	269.6	269.9	269.8
130°	280.4	280.5	280.6	280.7	280.8	280.9	281.1	281.3	281.5	281.8	281.8
132.5°	291.9	291.9	292.0	292.2	292.3	292.5	292.7	293.0	293.3	293.6	293.6
135°	308.8	308.8	308.7	308.6	308.5	308.6	309.0	309.2	309.5	309.8	310.0
137.5°	323.9	324.0	324.0	324.0	324.0	324.2	324.5	324.8	325.1	325.4	325.6
140°	333.8	333.9	334.0	334.1	334.3	334.4	334.6	334.7	334.8	335.0	335.2
142.5°	342.6	342.8	343.0	343.3	343.6	343.8	343.8	343.9	344.0	344.1	344.2
145°	356.1	356.3	356.5	356.8	357.0	357.0	357.0	357.0	357.0	357.0	357.1
147.5°	366.8	367.3	367.7	368.1	368.5	368.6	368.5	368.5	368.4	368.4	368.4
150°	374.7	375.0	375.2	375.6	375.9	375.9	375.9	375.8	375.7	375.7	375.7
152.5°	381.3	381.5	381.7	381.9	382.2	382.2	382.1	381.9	381.8	381.7	381.8
155°	390.5	390.6	390.6	390.7	390.7	390.7	390.5	390.2	390.0	389.9	390.1
157.5°	398.2	398.1	398.1	398.1	398.1	397.9	397.7	397.4	397.2	397.0	397.3
160°	402.8	402.5	402.3	402.2	401.9	401.8	401.7	401.6	401.5	401.4	401.9
162.5°	406.8	406.5	406.3	406.0	405.7	405.6	405.5	405.4	405.4	405.3	405.7
165°	411.9	411.5	411.2	410.8	410.5	410.3	410.3	410.3	410.3	410.3	410.9
167.5°	415.9	415.5	415.2	414.8	414.5	414.3	414.2	414.2	414.1	414.1	414.7
170°	418.2	417.8	417.3	417.0	416.5	416.3	416.4	416.5	416.5	416.6	417.1
172.5°	419.7	419.3	418.8	418.5	418.0	417.9	417.9	418.0	418.0	418.1	418.7
175°	421.3	420.9	420.5	420.1	419.6	419.5	419.5	419.6	419.7	419.7	420.4
177.5°	422.1	421.7	421.3	420.9	420.5	420.4	420.5	420.6	420.7	420.8	421.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332898-940

CATALOG NUMBER: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	9.1	9.0	9.0	9.1	9.2	9.4	9.5	9.6
90°	7.8	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	7.5	7.9	8.4	8.6	8.6	8.6	8.6	8.7
95°	7.8	8.2	8.6	8.8	8.9	9.0	9.1	9.1
97.5°	8.4	8.5	8.5	8.6	8.6	8.6	8.7	8.8
100°	11.5	10.3	9.1	8.6	8.6	8.6	8.7	8.8
102.5°	41.1	28.3	15.4	9.0	9.0	9.0	9.1	9.1
105°	99.6	100.2	100.9	99.9	97.4	94.9	92.3	89.8
107.5°	123.2	123.5	123.9	124.1	124.4	124.7	124.9	125.2
110°	139.3	139.4	139.6	139.7	139.9	140.2	140.4	140.5



TEST NUMBER: P332898-940

CATALOG NUMBER: SA4XXRDIP-C575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	154.8	154.8	154.7	154.9	155.2	155.4	155.7	156.0
115°	178.0	178.2	178.3	178.3	178.3	178.3	178.3	178.3
117.5°	201.3	201.3	201.3	201.3	201.3	201.3	201.3	201.2
120°	215.8	216.0	216.2	216.2	216.0	215.8	215.7	215.5
122.5°	230.1	230.2	230.2	230.2	230.1	230.0	229.8	229.7
125°	250.0	250.2	250.4	250.6	250.7	250.7	250.7	250.8
127.5°	269.8	269.7	269.7	269.7	269.7	269.6	269.5	269.5
130°	281.9	282.0	282.0	282.0	282.0	282.0	282.0	282.0
132.5°	293.7	293.8	293.9	293.9	293.8	293.7	293.7	293.6
135°	310.0	310.2	310.3	310.5	310.6	310.8	310.9	311.0
137.5°	325.7	325.9	326.0	326.1	326.0	326.0	325.9	325.9
140°	335.4	335.6	335.8	336.0	336.1	336.1	336.2	336.3
142.5°	344.4	344.6	344.6	344.7	344.8	344.8	344.8	344.8
145°	357.2	357.3	357.3	357.4	357.6	357.8	357.8	358.0
147.5°	368.5	368.5	368.5	368.6	368.7	368.7	368.8	368.9
150°	375.7	375.7	375.7	375.7	375.8	375.9	375.9	375.9
152.5°	381.9	382.0	382.2	382.2	382.1	382.1	382.1	382.0
155°	390.4	390.7	390.9	391.0	390.7	390.6	390.4	390.1
157.5°	397.7	398.1	398.4	398.4	398.1	397.7	397.3	397.0
160°	402.3	402.8	403.1	403.1	402.8	402.3	401.9	401.4
162.5°	406.1	406.5	407.0	406.9	406.4	406.0	405.5	405.0
165°	411.4	412.0	412.6	412.5	411.9	411.3	410.6	410.0
167.5°	415.4	416.0	416.5	416.5	415.8	415.1	414.4	413.8
170°	417.8	418.3	418.8	418.7	418.1	417.4	416.7	416.0
172.5°	419.3	419.8	420.4	420.3	419.5	418.7	418.0	417.2
175°	421.1	421.7	422.3	422.2	421.3	420.5	419.6	418.8
177.5°	421.8	422.2	422.7	422.5	421.9	421.2	420.5	419.8
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)