

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902389

Luminaire Tested: DFN2DIP-4P4F0-070D070US830-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902389
REPORT IS A COMBINATION OF REPORTS P900656 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D070US830-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12139.9 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 135.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902389

CATALOG NUMBER: DFN2DIP-4P4F0-070D070US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902389

CATALOG NUMBER: DFN2DIP-4P4F0-070D070US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	106	106	106	106		98	98	98	98		81	81	81		66	66	66		53	53	53
1	97	93	90	86		89	86	83	80		72	70	68		59	58	56		47	46	45
2	89	82	76	71		82	76	70	66		63	60	57		52	50	48		42	40	39
3	81	72	65	60		75	67	61	56		56	52	48		47	43	41		38	35	34
4	75	64	57	51		68	60	53	48		50	45	41		42	38	35		34	31	29
5	69	58	50	44		63	53	46	41		45	40	36		38	34	31		31	28	26
6	63	52	44	38		58	48	41	36		41	36	32		34	30	27		28	25	23
7	59	47	39	34		54	44	37	32		37	32	28		31	27	24		26	23	21
8	55	43	35	30		50	40	33	28		34	29	25		29	25	22		24	21	19
9	51	39	32	27		47	36	30	25		31	26	22		27	23	20		22	19	17
10	48	36	29	24		44	33	27	23		29	24	20		25	21	18		20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1769	1769	1769
5°	1772	1742	1753
10°	1755	1708	1696
15°	1731	1652	1609
20°	1699	1575	1501
25°	1666	1488	1397
30°	1622	1399	1265
35°	1579	1303	1149
40°	1536	1204	1016
45°	1485	1094	895
50°	1433	983	777
55°	1378	864	664
60°	1315	740	547
65°	1242	613	493
70°	1153	496	447
75°	1042	438	408
80°	882	370	356
85°	616	249	272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1485 cd/sqm

TEST NUMBER: P902389

CATALOG NUMBER: DFN2DIP-4P4F0-070D070US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.6	2.1
10°-20°	701.6	5.8
20°-30°	985.0	8.1
30°-40°	1073.7	8.8
40°-50°	986.9	8.1
50°-60°	775.0	6.4
60°-70°	504.5	4.2
70°-80°	259.7	2.1
80°-90°	70.2	0.6
90°-100°	73.4	0.6
100°-110°	273.7	2.3
110°-120°	725.9	6.0
120°-130°	1204.0	9.9
130°-140°	1278.9	10.5
140°-150°	1188.6	9.8
150°-160°	955.6	7.9
160°-170°	615.8	5.1
170°-180°	211.9	1.7
0°-30°	1942.1	16.0
0°-40°	3015.8	24.8
0°-60°	4777.7	39.4
0°-90°	5612.0	46.2
90°-120°	1073.0	8.8
90°-150°	4744.6	39.1
90°-180°	6528.0	53.8
0°-180°	12139.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2727	2727	2727	2727	2727	
5°	2727	2714	2682	2705	2697	259
15°	2594	2566	2483	2436	2411	731
25°	2354	2275	2112	2011	1974	1083
35°	2028	1903	1686	1530	1476	1270
45°	1658	1493	1234	1059	999	1281
55°	1261	1068	802	654	607	1127
65°	851	651	429	346	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	122
90°	2	19	32	40	44	11
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1362	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2182	2172	2177	2188	2177	616
175°	2232	2220	2224	2235	2219	212
180°	2227	2227	2227	2227	2227	

TEST NUMBER: P902389

CATALOG NUMBER: DFN2DIP-4P4F0-070D070US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.9	2726.9	2726.9	2726.9	2726.9
2.5°	2739.1	2726.9	2699.6	2724.5	2719.5
5°	2726.9	2714.5	2682.4	2704.6	2697.3
7.5°	2704.6	2689.9	2655.4	2665.0	2652.8
10°	2675.0	2657.8	2608.5	2600.9	2586.2
12.5°	2638.1	2615.8	2549.1	2534.4	2507.2
15°	2593.6	2566.4	2482.6	2435.7	2411.1
17.5°	2541.8	2502.3	2398.6	2344.3	2304.8
20°	2482.6	2433.1	2309.8	2248.2	2193.8
22.5°	2418.5	2361.6	2218.4	2134.6	2097.7
25°	2354.3	2275.2	2112.3	2011.3	1974.2
27.5°	2277.8	2193.8	2013.6	1897.7	1840.9
30°	2196.4	2102.4	1905.0	1779.3	1712.6
32.5°	2117.3	2003.8	1801.6	1653.4	1591.6
35°	2028.5	1902.6	1685.6	1530.1	1475.6
37.5°	1942.2	1806.3	1577.0	1406.5	1345.0
40°	1850.8	1702.9	1463.3	1288.2	1224.0
42.5°	1757.1	1599.2	1349.9	1167.2	1105.7
45°	1658.4	1492.9	1234.0	1058.6	999.4
47.5°	1564.6	1389.5	1122.9	947.5	893.3
50°	1460.9	1285.8	1014.3	843.9	792.3
52.5°	1359.6	1174.5	910.6	747.7	700.9
55°	1260.9	1068.5	801.9	654.0	607.2
57.5°	1159.9	962.4	705.9	567.6	528.1
60°	1056.2	858.8	604.5	478.9	439.3
62.5°	955.1	757.7	518.1	399.8	380.1
65°	851.4	651.4	429.4	345.6	338.0
67.5°	752.7	552.7	345.6	303.4	296.1
70°	649.0	456.6	286.2	261.6	251.6
72.5°	550.4	367.6	239.3	219.7	214.7
75°	454.0	281.2	197.4	180.1	177.8
77.5°	357.9	199.7	155.5	145.5	140.6
80°	268.9	143.2	118.4	108.7	108.7
82.5°	187.5	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	1.5	19.3	32.1	40.3	43.5
92.5°	40.3	33.8	38.6	41.9	43.5
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.2	644.4	101.6	119.2	125.7
110°	713.9	747.5	282.0	120.9	127.2

TEST NUMBER: P902389

CATALOG NUMBER: DFN2DIP-4P4F0-070D070US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.8	994.1	248.2	132.2
117.5°	1021.5	1053.7	1081.2	850.6	428.6
120°	1127.8	1152.0	1181.1	1200.4	982.9
122.5°	1218.0	1243.8	1276.2	1285.7	1287.4
125°	1309.9	1330.9	1361.5	1372.8	1377.5
127.5°	1393.6	1416.2	1440.5	1456.6	1458.1
130°	1472.6	1498.5	1516.1	1533.9	1532.4
132.5°	1553.2	1574.2	1591.9	1606.4	1604.9
135°	1620.9	1646.7	1661.1	1677.3	1674.1
137.5°	1691.7	1711.1	1727.3	1743.4	1738.6
140°	1761.0	1774.0	1791.6	1806.1	1798.1
142.5°	1819.1	1830.4	1851.2	1864.1	1856.1
145°	1880.4	1878.7	1906.0	1917.3	1909.3
147.5°	1933.3	1928.6	1956.0	1964.0	1957.7
150°	1985.0	1973.8	1999.6	2009.1	2001.1
152.5°	2028.4	2015.6	2039.8	2049.5	2038.2
155°	2070.4	2056.0	2075.3	2084.9	2072.1
157.5°	2104.2	2091.4	2105.9	2117.2	2104.2
160°	2133.4	2123.5	2133.4	2142.9	2131.6
162.5°	2159.0	2149.4	2157.4	2168.7	2154.2
165°	2181.5	2172.0	2176.7	2188.0	2176.7
167.5°	2199.3	2189.5	2194.5	2205.8	2191.3
170°	2213.8	2204.1	2207.3	2218.7	2204.1
172.5°	2223.5	2213.8	2217.1	2228.4	2213.8
175°	2231.5	2220.2	2223.5	2234.7	2218.7
177.5°	2234.7	2223.5	2225.2	2236.5	2221.9
180°	2226.7	2226.7	2226.7	2226.7	2226.7

TEST NUMBER: P902389

CATALOG NUMBER: DFN2DIP-4P4F0-070D070US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.78	9.59	9.78	10.59	11.91	4.75	5.55	5.74	6.55	7.87
	3H	10.47	11.18	11.47	12.19	13.54	5.93	6.65	6.94	7.66	9.01
	4H	11.08	11.75	12.10	12.77	14.12	6.38	7.06	7.40	8.07	9.43
	6H	11.50	12.12	12.53	13.14	14.51	6.70	7.33	7.73	8.35	9.71
	8H	11.63	12.22	12.66	13.26	14.62	6.80	7.39	7.83	8.42	9.79
	12H	11.69	12.26	12.73	13.28	14.67	6.84	7.40	7.88	8.43	9.82
4H	2H	8.80	9.48	9.82	10.49	11.85	5.34	6.02	6.37	7.03	8.39
	3H	10.63	11.19	11.67	12.24	13.61	6.69	7.25	7.72	8.30	9.66
	4H	11.33	11.84	12.37	12.88	14.27	7.24	7.75	8.28	8.79	10.18
	6H	11.85	12.29	12.90	13.35	14.73	7.66	8.10	8.71	9.16	10.55
	8H	12.02	12.44	13.08	13.49	14.89	7.79	8.20	8.84	9.25	10.65
	12H	12.12	12.49	13.19	13.56	14.97	7.85	8.22	8.92	9.29	10.70
8H	4H	11.29	11.71	12.34	12.76	14.16	7.52	7.93	8.57	8.98	10.39
	6H	11.86	12.20	12.94	13.30	14.70	8.04	8.38	9.11	9.47	10.87
	8H	12.09	12.38	13.17	13.46	14.88	8.23	8.53	9.31	9.61	11.03
	12H	12.23	12.49	13.31	13.56	15.02	8.35	8.61	9.44	9.69	11.15
12H	4H	11.24	11.62	12.31	12.68	14.09	7.52	7.90	8.59	8.96	10.37
	6H	11.84	12.14	12.92	13.22	14.64	8.09	8.39	9.17	9.47	10.89
	8H	12.06	12.33	13.15	13.40	14.86	8.30	8.56	9.39	9.64	11.10