

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332946-940

Luminaire Tested: **SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332946-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6546.9 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332946-940

CATALOG NUMBER: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332946-940

CATALOG NUMBER: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44				
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32				
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31	27				
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23				
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20				
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P332946-940

CATALOG NUMBER: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	1.8
10°-20°	324.5	5.0
20°-30°	468.6	7.2
30°-40°	531.1	8.1
40°-50°	512.9	7.8
50°-60°	426.5	6.5
60°-70°	294.5	4.5
70°-80°	149.3	2.3
80°-90°	41.7	0.6
90°-100°	40.7	0.6
100°-110°	259.5	4.0
110°-120°	496.5	7.6
120°-130°	630.3	9.6
130°-140°	674.3	10.3
140°-150°	630.6	9.6
150°-160°	508.5	7.8
160°-170°	328.0	5.0
170°-180°	113.0	1.7
0°-30°	909.4	13.9
0°-40°	1440.5	22.0
0°-60°	2379.9	36.4
0°-90°	2865.4	43.8
90°-120°	796.7	12.2
90°-150°	2731.9	41.7
90°-180°	3681.0	56.2
0°-180°	6546.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	3	12	20	25	27	5
95°	49	20	20	25	26	63
105°	268	273	278	284	254	280
115°	500	503	502	504	504	492
125°	703	706	705	708	709	628
135°	872	872	875	877	879	672
145°	1006	1008	1008	1010	1011	628
155°	1103	1104	1101	1104	1102	508
165°	1163	1159	1159	1165	1158	329
175°	1190	1185	1186	1193	1183	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P332946-940

CATALOG NUMBER: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	18.0	17.0	16.1	15.2	14.4	13.9	14.1	14.3	14.4	14.5	14.6
90°	2.7	4.8	7.0	9.2	11.4	13.3	14.8	16.4	18.0	19.6	20.8
92.5°	11.2	11.3	11.4	11.6	11.7	12.6	14.1	15.7	17.3	18.9	20.1
95°	49.0	42.3	35.5	28.8	22.0	18.8	19.0	19.2	19.4	19.6	20.8
97.5°	104.0	108.2	112.4	116.5	120.7	111.8	89.7	67.7	45.6	23.5	23.6
100°	146.0	149.5	153.1	156.7	160.2	148.4	121.1	93.8	66.4	39.1	35.8
102.5°	193.0	195.6	198.2	200.8	203.4	203.0	199.4	195.8	192.3	188.7	152.4
105°	268.0	269.1	270.3	271.5	272.7	273.8	274.7	275.7	276.8	277.8	279.6
107.5°	337.5	338.1	338.8	339.3	339.9	340.9	342.2	343.6	344.9	346.3	347.1
110°	384.6	385.1	385.8	386.3	386.9	387.8	389.0	390.2	391.4	392.5	393.0



TEST NUMBER: P332946-940

CATALOG NUMBER: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.2	431.2	432.3	433.4	434.4	435.2	435.8	436.3	436.8	437.4	437.4
115°	500.2	500.9	501.5	502.0	502.7	502.8	502.7	502.5	502.2	502.0	502.5
117.5°	563.5	564.3	565.1	565.9	566.7	567.2	567.7	568.1	568.6	569.0	568.9
120°	606.2	607.0	607.8	608.6	609.4	609.7	609.5	609.3	609.0	608.9	609.3
122.5°	646.0	646.6	647.0	647.5	648.0	648.4	648.6	648.9	649.2	649.4	649.7
125°	703.2	704.0	704.8	705.6	706.4	706.6	706.2	705.8	705.4	705.0	705.6
127.5°	757.3	757.5	757.8	758.0	758.1	758.7	759.6	760.5	761.4	762.3	762.2
130°	792.3	792.5	792.6	792.8	793.0	793.4	794.1	794.6	795.2	795.9	796.0
132.5°	824.3	824.7	825.0	825.4	825.7	826.3	827.1	827.8	828.5	829.3	829.5
135°	872.4	872.2	872.0	871.7	871.6	871.8	872.6	873.4	874.2	875.0	875.4
137.5°	914.9	915.0	915.1	915.2	915.3	915.7	916.6	917.5	918.3	919.2	919.6
140°	942.7	943.1	943.5	943.9	944.2	944.7	945.0	945.5	945.8	946.3	946.8
142.5°	967.6	968.3	969.0	969.7	970.4	970.9	971.2	971.4	971.6	971.9	972.3
145°	1005.8	1006.5	1007.1	1007.6	1008.3	1008.5	1008.5	1008.5	1008.5	1008.5	1008.8
147.5°	1036.3	1037.4	1038.6	1039.6	1040.8	1041.3	1041.0	1040.8	1040.6	1040.4	1040.6
150°	1058.4	1059.2	1060.0	1060.8	1061.6	1061.8	1061.7	1061.5	1061.3	1061.0	1061.0
152.5°	1076.9	1077.5	1078.2	1078.8	1079.4	1079.6	1079.2	1078.9	1078.5	1078.2	1078.5
155°	1103.0	1103.1	1103.3	1103.5	1103.7	1103.5	1103.0	1102.3	1101.7	1101.2	1101.9
157.5°	1124.8	1124.7	1124.5	1124.4	1124.4	1123.9	1123.3	1122.6	1122.0	1121.2	1122.3
160°	1137.6	1137.0	1136.5	1135.9	1135.2	1134.9	1134.7	1134.4	1134.3	1134.1	1135.2
162.5°	1149.1	1148.3	1147.5	1146.7	1146.0	1145.6	1145.3	1145.1	1145.0	1144.8	1145.9
165°	1163.4	1162.4	1161.5	1160.5	1159.5	1159.0	1159.0	1159.0	1159.0	1159.0	1160.6
167.5°	1174.8	1173.8	1172.8	1171.8	1170.7	1170.2	1170.0	1169.9	1169.8	1169.7	1171.4
170°	1181.2	1180.1	1178.8	1177.7	1176.5	1176.0	1176.2	1176.4	1176.6	1176.8	1178.4
172.5°	1185.5	1184.4	1183.1	1182.0	1180.8	1180.3	1180.4	1180.7	1180.9	1181.1	1182.7
175°	1190.2	1189.0	1187.8	1186.6	1185.4	1184.9	1185.1	1185.4	1185.5	1185.7	1187.5
177.5°	1192.3	1191.1	1190.1	1189.0	1187.8	1187.5	1187.8	1188.1	1188.4	1188.7	1190.0
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2



TEST NUMBER: P332946-940

CATALOG NUMBER: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	14.7	14.7	14.8	15.0	15.2	15.4	15.7	16.0
90°	21.9	23.2	24.3	25.1	25.5	25.9	26.3	26.7
92.5°	21.2	22.5	23.6	24.3	24.3	24.4	24.5	24.6
95°	21.9	23.2	24.3	25.1	25.2	25.4	25.6	25.8
97.5°	23.7	23.9	24.0	24.2	24.3	24.5	24.7	25.0
100°	32.5	29.1	25.7	24.2	24.3	24.5	24.7	25.0
102.5°	116.2	79.9	43.6	25.5	25.5	25.6	25.6	25.7
105°	281.3	283.0	284.8	282.2	275.1	268.0	260.8	253.7
107.5°	348.0	348.9	349.7	350.5	351.3	352.0	352.8	353.6
110°	393.3	393.8	394.1	394.7	395.2	395.8	396.5	397.0



TEST NUMBER: P332946-940

CATALOG NUMBER: SA4XXRDIP-C795D1035U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	437.3	437.2	437.1	437.5	438.2	439.0	439.7	440.4
115°	502.8	503.3	503.6	503.8	503.8	503.8	503.8	503.8
117.5°	568.8	568.7	568.6	568.6	568.6	568.5	568.4	568.3
120°	609.7	610.0	610.5	610.5	610.0	609.7	609.3	608.9
122.5°	650.0	650.1	650.4	650.3	650.0	649.5	649.2	648.7
125°	706.2	706.8	707.4	707.8	708.0	708.2	708.4	708.6
127.5°	762.1	762.0	761.9	761.7	761.6	761.4	761.3	761.1
130°	796.2	796.4	796.6	796.7	796.7	796.7	796.7	796.7
132.5°	829.6	829.9	830.1	830.1	829.9	829.7	829.6	829.5
135°	875.8	876.2	876.6	877.0	877.4	877.8	878.2	878.6
137.5°	920.1	920.5	921.0	921.0	921.0	920.9	920.7	920.6
140°	947.4	948.1	948.6	949.0	949.2	949.4	949.6	949.9
142.5°	972.8	973.2	973.7	973.8	973.9	973.9	974.0	974.0
145°	1009.0	1009.1	1009.3	1009.7	1010.0	1010.4	1010.8	1011.2
147.5°	1040.7	1040.9	1041.1	1041.3	1041.4	1041.6	1041.9	1042.1
150°	1061.0	1061.0	1061.0	1061.1	1061.4	1061.6	1061.8	1061.9
152.5°	1078.8	1079.1	1079.4	1079.5	1079.4	1079.3	1079.1	1079.1
155°	1102.7	1103.5	1104.3	1104.4	1103.8	1103.2	1102.6	1102.1
157.5°	1123.3	1124.4	1125.3	1125.3	1124.4	1123.3	1122.3	1121.2
160°	1136.5	1137.6	1138.8	1138.8	1137.6	1136.5	1135.2	1134.1
162.5°	1147.1	1148.3	1149.5	1149.4	1148.1	1146.7	1145.4	1144.1
165°	1162.2	1163.8	1165.3	1165.2	1163.4	1161.6	1159.8	1158.1
167.5°	1173.1	1174.9	1176.6	1176.5	1174.6	1172.6	1170.5	1168.6
170°	1180.0	1181.5	1183.1	1182.9	1181.0	1179.0	1177.0	1175.0
172.5°	1184.3	1185.8	1187.4	1187.1	1185.0	1182.9	1180.7	1178.6
175°	1189.3	1191.1	1192.8	1192.5	1190.2	1187.8	1185.4	1183.0
177.5°	1191.2	1192.5	1193.8	1193.5	1191.6	1189.7	1187.8	1185.9
180°	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2	1190.2

(END OF REPORT)