

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902412

Luminaire Tested: DFN2DIP-4P4F0-080D070US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902412
REPORT IS A COMBINATION OF REPORTS P899138 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D070US830-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12248.4 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 146.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902412

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902412

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50
2	90	83	77	72	83	77	72	68	66	63	59	56	53	51	47	45	43
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	24	21	19
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2022	2022	2022
5°	2025	1990	2003
10°	2005	1952	1939
15°	1978	1888	1839
20°	1941	1800	1716
25°	1904	1700	1597
30°	1854	1599	1446
35°	1805	1489	1313
40°	1755	1376	1161
45°	1697	1250	1023
50°	1637	1123	888
55°	1575	988	758
60°	1502	846	625
65°	1419	701	563
70°	1318	566	511
75°	1191	501	467
80°	1008	422	407
85°	704	285	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1697 cd/sqm

TEST NUMBER: P902412

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	2.4
10°-20°	801.8	6.5
20°-30°	1125.7	9.2
30°-40°	1227.1	10.0
40°-50°	1127.8	9.2
50°-60°	885.7	7.2
60°-70°	576.5	4.7
70°-80°	296.8	2.4
80°-90°	81.7	0.7
90°-100°	129.1	1.1
100°-110°	410.3	3.3
110°-120°	702.1	5.7
120°-130°	923.3	7.5
130°-140°	1036.4	8.5
140°-150°	1016.3	8.3
150°-160°	852.6	7.0
160°-170°	565.4	4.6
170°-180°	197.6	1.6
0°-30°	2219.6	18.1
0°-40°	3446.7	28.1
0°-60°	5460.2	44.6
0°-90°	6415.2	52.4
90°-120°	1241.5	10.1
90°-150°	4217.6	34.4
90°-180°	5833.0	47.6
0°-180°	12248.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	2	23	62	58	60	12
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	

TEST NUMBER: P902412

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2

TEST NUMBER: P902412

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6

TEST NUMBER: P902412

CATALOG NUMBER: DFN2DIP-4P4F0-080D070US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.83	10.68	10.77	11.64	12.87	5.79	6.64	6.73	7.60	8.84
	3H	11.51	12.28	12.47	13.24	14.50	6.98	7.74	7.94	8.71	9.97
	4H	12.13	12.85	13.10	13.82	15.09	7.44	8.15	8.40	9.12	10.39
	6H	12.56	13.22	13.54	14.19	15.48	7.76	8.42	8.74	9.39	10.68
	8H	12.69	13.31	13.67	14.30	15.59	7.85	8.48	8.84	9.47	10.75
	12H	12.75	13.35	13.74	14.33	15.64	7.90	8.49	8.89	9.48	10.78
4H	2H	9.85	10.57	10.83	11.54	12.81	6.39	7.11	7.37	8.08	9.35
	3H	11.69	12.29	12.67	13.28	14.57	7.75	8.34	8.73	9.34	10.63
	4H	12.39	12.93	13.38	13.92	15.23	8.30	8.84	9.29	9.83	11.14
	6H	12.91	13.38	13.91	14.39	15.70	8.72	9.19	9.72	10.20	11.51
	8H	13.09	13.52	14.09	14.53	15.85	8.85	9.29	9.85	10.29	11.62
	12H	13.19	13.58	14.21	14.60	15.93	8.92	9.31	9.94	10.33	11.66
8H	4H	12.36	12.79	13.36	13.80	15.12	8.58	9.02	9.59	10.03	11.35
	6H	12.93	13.29	13.96	14.34	15.66	9.10	9.46	10.13	10.51	11.83
	8H	13.15	13.47	14.19	14.50	15.84	9.30	9.61	10.33	10.65	11.99
	12H	13.29	13.57	14.33	14.60	15.99	9.42	9.70	10.46	10.73	12.11
12H	4H	12.31	12.70	13.33	13.73	15.05	8.59	8.98	9.61	10.01	11.33
	6H	12.90	13.22	13.94	14.26	15.60	9.15	9.47	10.19	10.51	11.85
	8H	13.13	13.41	14.17	14.44	15.82	9.37	9.65	10.41	10.68	12.06

END OF REPORT