

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332954-940

Luminaire Tested: **SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332954-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6700.7 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332954-940
CATALOG NUMBER: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332954-940

CATALOG NUMBER: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	96	92	88	85	88	84	81	78	70	68	66	56	55	54	44	43	42	36
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	74	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	25	23	20
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	23	21	18	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P332954-940

CATALOG NUMBER: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	1.7
10°-20°	324.5	4.8
20°-30°	468.6	7.0
30°-40°	531.1	7.9
40°-50°	512.9	7.7
50°-60°	426.5	6.4
60°-70°	294.5	4.4
70°-80°	149.3	2.2
80°-90°	41.2	0.6
90°-100°	380.9	5.7
100°-110°	792.8	11.8
110°-120°	710.1	10.6
120°-130°	597.3	8.9
130°-140°	498.1	7.4
140°-150°	380.5	5.7
150°-160°	267.5	4.0
160°-170°	157.3	2.3
170°-180°	51.2	0.8
0°-30°	909.4	13.6
0°-40°	1440.5	21.5
0°-60°	2379.9	35.5
0°-90°	2864.9	42.8
90°-120°	1883.9	28.1
90°-150°	3359.8	50.1
90°-180°	3836.0	57.2
0°-180°	6700.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	1	8	19	21	22	4
95°	34	108	844	418	253	38
105°	121	176	680	1464	1458	129
115°	214	268	606	1165	1400	212
125°	297	353	603	991	1117	265
135°	353	421	598	880	999	273
145°	407	466	595	742	816	256
155°	463	500	578	655	683	213
165°	505	520	554	587	596	142
175°	526	527	532	539	537	50
180°	527	527	527	527	527	



TEST NUMBER: P332954-940

CATALOG NUMBER: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	17.7	16.8	16.0	14.9	13.7	12.9	14.0	13.8	14.1	14.4	14.0
90°	1.1	3.1	6.2	7.2	8.3	8.3	14.5	14.5	16.6	18.6	17.7
92.5°	11.8	17.2	26.9	39.6	54.8	76.2	128.9	209.3	287.7	328.7	273.8
95°	34.2	37.3	47.7	61.2	86.0	129.6	219.6	389.6	637.2	844.5	868.3
97.5°	61.3	61.3	70.3	82.7	104.1	140.5	209.9	350.3	596.4	889.5	1090.9
100°	78.7	78.7	86.0	98.4	118.2	151.3	212.4	329.5	540.9	833.0	1098.3
102.5°	95.3	97.0	103.4	115.0	133.8	165.4	220.7	323.7	503.5	762.6	1036.2
105°	121.3	124.3	129.6	142.0	160.6	190.6	240.4	326.4	471.4	679.8	923.2
107.5°	149.8	151.9	157.1	170.3	188.2	217.8	263.4	341.7	465.7	633.3	832.1
110°	168.9	170.9	176.1	188.6	207.2	235.2	280.8	353.3	467.3	617.6	786.5



TEST NUMBER: P332954-940

CATALOG NUMBER: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.2	189.2	195.2	206.8	225.5	253.4	297.4	365.8	472.3	610.1	760.7
115°	213.5	216.6	223.8	234.2	253.9	281.9	323.2	385.5	481.8	606.2	736.7
117.5°	240.8	243.7	250.1	261.5	280.0	309.0	348.4	405.6	492.0	605.1	725.9
120°	259.0	261.1	268.4	279.7	297.4	326.4	365.8	419.6	499.4	605.1	720.1
122.5°	275.6	277.7	285.0	295.5	314.8	343.0	382.4	432.9	506.9	604.3	713.5
125°	297.4	301.5	307.7	319.1	338.9	367.8	405.1	452.8	518.1	603.1	702.5
127.5°	316.6	319.9	327.4	340.5	361.0	390.2	426.2	470.0	527.0	600.7	687.8
130°	327.4	331.5	339.8	355.4	375.1	405.1	440.4	480.8	533.6	599.9	678.7
132.5°	338.2	341.5	352.3	367.0	388.3	416.8	452.0	491.6	539.4	599.1	670.4
135°	353.3	357.5	367.8	385.5	407.2	434.2	468.3	505.7	548.1	597.9	658.0
137.5°	368.5	372.4	383.8	400.6	423.2	448.9	480.8	515.6	553.3	597.6	647.2
140°	379.2	382.4	393.8	411.3	433.1	458.0	489.1	522.2	557.5	596.8	641.4
142.5°	390.8	394.0	404.5	421.3	442.2	466.3	496.5	527.2	560.8	596.8	636.4
145°	407.2	410.4	420.7	435.2	454.9	477.7	504.6	532.6	562.7	594.8	627.9
147.5°	425.6	426.7	435.8	450.8	467.1	487.6	512.9	537.3	563.7	591.0	620.3
150°	437.3	438.3	446.6	459.1	474.6	494.3	517.0	539.8	563.7	588.5	614.5
152.5°	448.0	448.3	456.6	468.1	482.1	500.1	520.4	541.5	562.0	584.4	607.8
155°	463.2	464.2	470.4	480.8	492.2	507.7	525.3	543.0	559.5	578.2	597.9
157.5°	477.9	477.9	483.7	491.8	501.7	514.0	528.9	543.0	556.9	571.8	587.7
160°	487.0	487.0	491.2	498.4	506.7	518.1	530.5	543.0	554.4	566.8	580.2
162.5°	495.3	494.5	497.8	504.2	511.7	520.6	532.2	543.0	551.9	561.8	573.6
165°	504.6	504.6	506.7	511.8	517.0	523.3	532.6	540.9	547.1	554.4	562.7
167.5°	514.0	512.9	514.0	517.9	520.8	525.6	532.4	538.4	542.2	546.9	552.7
170°	518.1	517.0	518.1	521.2	523.3	526.4	531.5	536.7	538.8	541.9	546.1
172.5°	522.2	521.2	521.4	523.7	525.0	527.2	530.7	535.1	535.5	536.9	540.3
175°	526.4	525.3	525.3	526.4	527.4	527.4	529.5	532.6	531.5	531.5	533.6
177.5°	528.2	527.4	526.6	527.4	527.4	527.4	528.2	529.9	528.2	528.2	529.1
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332954-940

CATALOG NUMBER: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	14.0	14.1	14.1	14.1	14.4	14.8	14.8	15.0
90°	18.6	19.7	20.7	20.7	21.8	22.8	21.8	21.8
92.5°	203.5	153.1	121.9	101.1	88.9	83.3	79.8	79.8
95°	767.8	607.2	468.3	367.8	317.1	285.0	266.3	252.8
97.5°	1134.4	1074.7	973.4	865.2	790.8	728.4	697.3	675.8
100°	1249.6	1270.3	1219.6	1142.9	1052.8	989.5	958.5	950.2
102.5°	1243.8	1346.6	1361.3	1329.4	1274.1	1228.2	1195.5	1188.9
105°	1160.5	1339.8	1442.3	1484.8	1486.9	1478.6	1464.1	1457.9
107.5°	1042.1	1233.1	1377.5	1469.9	1521.1	1544.7	1555.1	1557.8
110°	970.9	1150.1	1300.4	1414.3	1487.9	1531.4	1550.2	1559.4



TEST NUMBER: P332954-940

CATALOG NUMBER: SA4XXRDIP-C795D1205U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	918.6	1077.2	1219.1	1333.1	1416.7	1469.3	1495.4	1510.6
115°	866.2	993.7	1114.9	1214.4	1296.3	1358.4	1391.6	1399.9
117.5°	840.5	946.0	1041.3	1125.7	1195.5	1247.8	1281.3	1287.7
120°	828.9	925.3	1008.2	1081.7	1140.9	1186.4	1213.4	1224.8
122.5°	818.9	912.0	987.5	1052.0	1101.9	1140.9	1163.6	1175.0
125°	802.0	891.1	962.6	1019.6	1061.0	1091.1	1110.8	1117.0
127.5°	781.2	866.5	937.7	991.8	1033.5	1060.2	1076.8	1083.0
130°	764.7	846.6	917.0	972.0	1014.4	1040.3	1056.9	1063.1
132.5°	747.3	824.2	893.0	947.9	989.5	1018.8	1034.5	1040.7
135°	723.3	790.6	853.8	905.6	947.1	976.1	992.7	998.9
137.5°	701.5	758.5	811.7	858.5	897.3	926.0	939.6	947.1
140°	689.0	737.7	784.3	827.9	864.2	887.0	901.4	909.7
142.5°	677.4	720.3	760.4	798.1	830.2	851.3	864.2	870.0
145°	661.1	696.3	727.4	756.4	782.3	800.0	810.3	815.5
147.5°	647.6	675.6	700.4	723.3	742.3	757.4	765.4	767.1
150°	639.4	663.2	683.9	702.5	719.1	732.5	738.8	739.9
152.5°	630.2	650.7	669.8	685.1	699.2	710.2	713.9	715.0
155°	616.5	633.1	648.6	661.1	671.5	679.8	682.9	682.9
157.5°	601.8	615.7	628.7	638.7	646.6	652.8	654.7	654.7
160°	592.7	604.0	615.5	623.8	630.0	636.2	637.2	637.2
162.5°	583.5	593.3	602.3	609.7	614.2	620.5	621.5	620.6
165°	571.0	577.1	584.4	589.6	593.7	597.9	596.8	595.8
167.5°	558.7	563.5	569.3	572.4	574.4	577.1	576.9	576.1
170°	551.3	554.4	558.5	561.6	563.7	564.7	563.7	563.7
172.5°	544.6	546.9	549.4	551.6	552.9	553.9	552.9	551.3
175°	535.7	536.7	538.8	538.8	538.8	540.9	538.8	536.7
177.5°	529.9	530.7	530.7	531.5	530.7	531.5	529.9	528.2
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4

(END OF REPORT)