

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334246

Luminaire Tested: **SA4XXRDP-C575D927-4F0-1E-UDD-F**

Issue Date: 10/11/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P334246  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)  
Test Lab: INNOVATIONS CENTER  
Issue Date: 10/11/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XRDP-C575D927-4F0-1E-UDD-F  
Description: DEFINE 4 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER  
PENDANT/SURFACE/WALL MOUNT, 575 LUMENS PER FOOT  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1716.5 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 18.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P334246

CATALOG NUMBER: SA4XXRDP-C575D927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P334246

CATALOG NUMBER: SA4XXRDP-C575D927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85																																				
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	74	72																																				
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62																																				
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	54																																				
5	78	66	57	51	76	65	56	50	62	55	50	61	54	49	59	53	49	47																																				
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41																																				
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	37																																				
8	63	50	41	36	61	49	41	36	48	40	35	46	40	35	45	39	35	33																																				
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																																				
10	55	42	35	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5997	5997	5997
5°	6011	5937	5974
10°	5973	5866	5866
15°	5905	5743	5700
20°	5810	5581	5478
25°	5690	5391	5255
30°	5573	5191	4973
35°	5443	4984	4692
40°	5287	4748	4388
45°	5143	4513	4078
50°	4980	4244	3750
55°	4804	3963	3395
60°	4610	3655	3031
65°	4434	3270	2672
70°	4175	2847	2268
75°	3849	2361	1847
80°	3357	1799	1692
85°	2844	1630	1528



TEST NUMBER: P334246

CATALOG NUMBER: SA4XXRDP-C575D927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.9	4.1
10°-20°	194.8	11.3
20°-30°	281.2	16.4
30°-40°	318.7	18.6
40°-50°	307.7	17.9
50°-60°	255.8	14.9
60°-70°	176.6	10.3
70°-80°	89.2	5.2
80°-90°	22.7	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.8	31.8
0°-40°	864.5	50.4
0°-60°	1428.0	83.2
0°-90°	1716.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1716.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	743	743	743	743	743	
5°	742	739	733	738	737	70
15°	706	701	687	686	682	199
25°	639	628	605	596	590	294
35°	552	534	506	486	476	345
45°	450	429	395	367	357	347
55°	341	318	282	252	241	305
65°	232	208	171	147	140	229
75°	123	102	76	63	59	130
85°	31	19	18	16	16	35
90°	0	0	0	0	0	



TEST NUMBER: P334246

CATALOG NUMBER: SA4XXRDP-C575D927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	742.9	742.9	742.9	742.9	742.9
2.5°	745.1	742.9	736.6	742.9	742.3
5°	741.7	739.4	732.6	738.3	737.2
7.5°	736.6	734.3	725.8	729.8	728.1
10°	728.6	725.8	715.6	717.8	715.6
12.5°	718.4	715.0	702.5	703.6	700.2
15°	706.5	701.3	687.1	686.0	682.0
17.5°	692.8	685.4	668.9	666.1	660.4
20°	676.3	668.9	649.6	645.0	637.6
22.5°	658.1	649.6	628.5	621.1	615.4
25°	638.8	628.5	605.2	595.5	589.9
27.5°	618.9	606.3	581.9	570.5	562.6
30°	597.8	583.6	556.9	542.6	533.5
32.5°	575.6	559.1	531.3	514.2	505.7
35°	552.3	534.1	505.7	486.3	476.1
37.5°	527.9	509.1	477.8	456.8	446.5
40°	501.7	482.9	450.5	426.6	416.4
42.5°	476.7	456.8	422.6	398.2	387.4
45°	450.5	429.4	395.3	367.4	357.2
47.5°	423.8	402.1	366.9	337.9	326.5
50°	396.5	374.3	337.9	309.4	298.6
52.5°	368.6	347.0	309.4	280.4	269.0
55°	341.3	318.5	281.6	252.0	241.2
57.5°	314.6	290.7	254.3	224.1	216.1
60°	285.5	262.8	226.4	196.8	187.7
62.5°	259.4	235.5	197.9	171.2	164.4
65°	232.1	207.6	171.2	146.8	139.9
67.5°	203.6	180.3	146.2	124.6	116.6
70°	176.9	153.0	120.6	101.8	96.1
72.5°	148.5	127.4	97.3	81.9	76.8
75°	123.4	102.4	75.7	62.6	59.2
77.5°	97.3	79.1	56.3	47.2	46.1
80°	72.2	55.7	38.7	37.0	36.4
82.5°	50.6	35.8	27.9	26.7	26.2
85°	30.7	19.3	17.6	16.5	16.5
87.5°	13.1	8.5	8.0	7.4	8.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)