

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334247

Luminaire Tested: **SA4XXRDP-C795D927-4F0-1E-UDD-F**

Issue Date: 10/11/2019

Test Information

Test Method: LM-79-08
Report Number: P334247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)
Test Lab: INNOVATIONS CENTER
Issue Date: 10/11/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDP-C795D927-4F0-1E-UDD-F
Description: DEFINE 4 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 795 LUMENS PER FOOT
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2390.5 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334247

CATALOG NUMBER: SA4XXRDP-C795D927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P334247

CATALOG NUMBER: SA4XXRDP-C795D927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85				
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	74	72				
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62				
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	54				
5	78	66	57	51	76	65	56	50	62	55	50	61	54	49	59	53	49	47				
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41				
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	37				
8	63	50	41	36	61	49	41	36	48	40	35	46	40	35	45	39	35	33				
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				
10	55	42	35	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8352	8352	8352
5°	8371	8268	8320
10°	8319	8170	8170
15°	8223	7998	7938
20°	8092	7772	7629
25°	7924	7508	7318
30°	7761	7229	6927
35°	7581	6940	6535
40°	7363	6612	6111
45°	7163	6286	5680
50°	6935	5910	5223
55°	6690	5519	4728
60°	6421	5091	4221
65°	6174	4554	3723
70°	5816	3963	3161
75°	5362	3288	2570
80°	4677	2506	2357
85°	3964	2279	2130



TEST NUMBER: P334247

CATALOG NUMBER: SA4XXRDP-C795D927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.3	4.1
10°-20°	271.3	11.3
20°-30°	391.6	16.4
30°-40°	443.8	18.6
40°-50°	428.5	17.9
50°-60°	356.3	14.9
60°-70°	245.9	10.3
70°-80°	124.3	5.2
80°-90°	31.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	760.2	31.8
0°-40°	1204.0	50.4
0°-60°	1988.8	83.2
0°-90°	2390.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2390.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1035	1035	1035	1035	1035	
5°	1033	1030	1020	1028	1027	98
15°	984	977	957	955	950	277
25°	890	875	843	829	822	410
35°	769	744	704	677	663	481
45°	627	598	551	512	498	484
55°	475	444	392	351	336	425
65°	323	289	238	204	195	319
75°	172	143	105	87	82	181
85°	43	27	25	23	23	49
90°	0	0	0	0	0	



TEST NUMBER: P334247

CATALOG NUMBER: SA4XXRDP-C795D927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1034.6	1034.6	1034.6	1034.6	1034.6
2.5°	1037.8	1034.6	1025.9	1034.6	1033.8
5°	1033.0	1029.8	1020.3	1028.3	1026.7
7.5°	1025.9	1022.7	1010.8	1016.4	1014.0
10°	1014.8	1010.8	996.6	999.7	996.6
12.5°	1000.5	995.8	978.3	979.9	975.2
15°	983.9	976.8	957.0	955.4	949.8
17.5°	964.9	954.6	931.6	927.6	919.7
20°	941.9	931.6	904.7	898.3	888.0
22.5°	916.6	904.7	875.4	865.1	857.1
25°	889.6	875.4	842.9	829.4	821.5
27.5°	861.9	844.5	810.4	794.6	783.5
30°	832.6	812.8	775.5	755.7	743.1
32.5°	801.7	778.7	739.9	716.1	704.2
35°	769.2	743.9	704.2	677.3	663.1
37.5°	735.1	709.0	665.4	636.1	621.9
40°	698.7	672.6	627.4	594.1	579.9
42.5°	663.8	636.1	588.6	554.5	539.5
45°	627.4	598.1	550.6	511.7	497.5
47.5°	590.2	560.1	511.0	470.6	454.7
50°	552.2	521.3	470.6	430.9	415.9
52.5°	513.3	483.2	430.9	390.5	374.7
55°	475.3	443.6	392.1	350.9	335.9
57.5°	438.1	404.8	354.1	312.1	301.0
60°	397.7	366.0	315.3	274.1	261.4
62.5°	361.2	328.0	275.7	238.4	228.9
65°	323.2	289.1	238.4	204.4	194.9
67.5°	283.6	251.1	203.6	173.5	162.4
70°	246.4	213.1	167.9	141.8	133.9
72.5°	206.8	177.4	135.5	114.1	106.9
75°	171.9	142.6	105.4	87.1	82.4
77.5°	135.5	110.1	78.4	65.8	64.2
80°	100.6	77.6	53.9	51.5	50.7
82.5°	70.5	49.9	38.8	37.2	36.4
85°	42.8	26.9	24.6	23.0	23.0
87.5°	18.2	11.9	11.1	10.3	11.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)