

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905105

Luminaire Tested: DFN2DIP-4P4F0-070D040US835-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905105
REPORT IS A COMBINATION OF REPORTS P900620 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-070D040US835-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open
No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9909.9 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 105.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905105

CATALOG NUMBER: DFN2DIP-4P4F0-070D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905105

CATALOG NUMBER: DFN2DIP-4P4F0-070D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	57	56
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	32	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1877	1877	1877
5°	1880	1848	1860
10°	1862	1812	1800
15°	1836	1753	1707
20°	1802	1671	1593
25°	1768	1579	1482
30°	1721	1484	1342
35°	1676	1383	1219
40°	1629	1278	1078
45°	1576	1161	949
50°	1520	1043	824
55°	1462	917	704
60°	1395	785	580
65°	1317	651	523
70°	1224	526	474
75°	1106	465	433
80°	936	392	378
85°	654	265	289

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1576 cd/sqm

TEST NUMBER: P905105

CATALOG NUMBER: DFN2DIP-4P4F0-070D040US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	2.7
10°-20°	744.3	7.5
20°-30°	1045.0	10.5
30°-40°	1139.2	11.5
40°-50°	1047.0	10.6
50°-60°	822.3	8.3
60°-70°	535.2	5.4
70°-80°	275.5	2.8
80°-90°	72.7	0.7
90°-100°	44.5	0.4
100°-110°	165.9	1.7
110°-120°	440.1	4.4
120°-130°	729.9	7.4
130°-140°	775.4	7.8
140°-150°	720.6	7.3
150°-160°	579.4	5.8
160°-170°	373.3	3.8
170°-180°	128.5	1.3
0°-30°	2060.5	20.8
0°-40°	3199.7	32.3
0°-60°	5068.9	51.1
0°-90°	5952.3	60.1
90°-120°	650.5	6.6
90°-150°	2876.4	29.0
90°-180°	3958.0	39.9
0°-180°	9909.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	129
90°	1	12	20	24	26	9
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P905105

CATALOG NUMBER: DFN2DIP-4P4F0-070D040US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P905105

CATALOG NUMBER: DFN2DIP-4P4F0-070D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P905105

CATALOG NUMBER: DFN2DIP-4P4F0-070D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.24	11.16	11.12	12.05	13.18	6.20	7.12	7.08	8.01	9.14
	3H	11.93	12.76	12.82	13.66	14.80	7.40	8.22	8.29	9.12	10.27
	4H	12.55	13.33	13.45	14.23	15.39	7.86	8.63	8.76	9.54	10.70
	6H	12.98	13.70	13.89	14.61	15.78	8.19	8.90	9.10	9.81	10.98
	8H	13.11	13.79	14.03	14.72	15.89	8.28	8.96	9.20	9.89	11.06
	12H	13.18	13.83	14.11	14.75	15.94	8.33	8.97	9.25	9.89	11.09
4H	2H	10.27	11.05	11.18	11.95	13.11	6.81	7.59	7.72	8.50	9.65
	3H	12.12	12.76	13.03	13.70	14.87	8.18	8.82	9.09	9.76	10.93
	4H	12.82	13.40	13.74	14.34	15.54	8.73	9.32	9.66	10.25	11.45
	6H	13.34	13.85	14.28	14.80	16.00	9.15	9.66	10.10	10.61	11.81
	8H	13.52	14.00	14.47	14.94	16.16	9.29	9.76	10.23	10.71	11.92
	12H	13.63	14.05	14.59	15.02	16.24	9.36	9.78	10.32	10.75	11.97
8H	4H	12.79	13.26	13.74	14.21	15.43	9.02	9.49	9.96	10.44	11.65
	6H	13.37	13.76	14.34	14.75	15.96	9.54	9.93	10.51	10.92	12.14
	8H	13.59	13.93	14.57	14.91	16.14	9.74	10.08	10.71	11.06	12.29
	12H	13.74	14.04	14.72	15.01	16.29	9.86	10.16	10.84	11.14	12.42
12H	4H	12.75	13.17	13.71	14.14	15.36	9.03	9.45	9.99	10.42	11.64
	6H	13.34	13.69	14.32	14.67	15.90	9.59	9.94	10.57	10.92	12.15
	8H	13.57	13.88	14.55	14.85	16.13	9.81	10.11	10.79	11.09	12.37

END OF REPORT