

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902142

Luminaire Tested: DFN2DIP-4P2F0-020D030US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902142
REPORT IS A COMBINATION OF REPORTS P899017 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US830-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4368.7 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 40
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902142
CATALOG NUMBER: DFN2DIP-4P2F0-020D030US830-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P902142

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	49	49	49	43
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42	44	43	42	36
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35	38	37	35	30
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30	34	32	30	26
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26	30	28	26	22
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22	27	25	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1836	1806	1820
10°	1818	1778	1793
15°	1787	1744	1751
20°	1747	1698	1708
25°	1708	1645	1660
30°	1659	1595	1599
35°	1612	1537	1535
40°	1555	1478	1473
45°	1499	1419	1410
50°	1437	1357	1338
55°	1371	1285	1270
60°	1297	1201	1193
65°	1216	1112	1102
70°	1113	1004	1003
75°	972	875	908
80°	799	711	734
85°	533	444	457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1499 cd/sqm



TEST NUMBER: P902142

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	1.6
10°-20°	194.2	4.4
20°-30°	285.5	6.5
30°-40°	331.5	7.6
40°-50°	331.1	7.6
50°-60°	288.7	6.6
60°-70°	213.4	4.9
70°-80°	120.8	2.8
80°-90°	34.4	0.8
90°-100°	55.3	1.3
100°-110°	175.8	4.0
110°-120°	300.9	6.9
120°-130°	395.7	9.1
130°-140°	444.2	10.2
140°-150°	435.6	10.0
150°-160°	365.4	8.4
160°-170°	242.3	5.5
170°-180°	84.7	1.9
0°-30°	548.7	12.6
0°-40°	880.3	20.2
0°-60°	1500.2	34.3
0°-90°	1868.8	42.8
90°-120°	532.1	12.2
90°-150°	1807.5	41.4
90°-180°	2500.0	57.2
0°-180°	4368.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	10	26	25	26	4
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	



TEST NUMBER: P902142

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4



TEST NUMBER: P902142

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3



TEST NUMBER: P902142
 CATALOG NUMBER: DFN2DIP-4P2F0-020D030US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.54	9.34	9.56	10.37	11.74	8.10	8.90	9.11	9.92	11.29
	3H	10.17	10.89	11.20	11.93	13.32	9.68	10.40	10.71	11.44	12.83
	4H	10.74	11.42	11.78	12.46	13.86	10.25	10.93	11.29	11.97	13.37
	6H	11.12	11.75	12.17	12.79	14.20	10.62	11.25	11.67	12.29	13.70
	8H	11.22	11.81	12.27	12.87	14.28	10.72	11.31	11.77	12.37	13.78
	12H	11.26	11.82	12.31	12.87	14.30	10.75	11.31	11.81	12.36	13.79
4H	2H	8.98	9.66	10.03	10.70	12.10	8.63	9.31	9.67	10.34	11.74
	3H	10.82	11.38	11.87	12.45	13.86	10.41	10.98	11.46	12.04	13.45
	4H	11.51	12.03	12.57	13.09	14.52	11.09	11.61	12.15	12.66	14.09
	6H	12.00	12.45	13.07	13.53	14.95	11.57	12.01	12.64	13.09	14.52
	8H	12.14	12.55	13.21	13.63	15.07	11.70	12.12	12.77	13.19	14.63
	12H	12.20	12.57	13.28	13.66	15.11	11.75	12.13	12.84	13.21	14.66
8H	4H	11.69	12.11	12.76	13.18	14.62	11.31	11.73	12.38	12.80	14.24
	6H	12.29	12.63	13.38	13.75	15.19	11.90	12.25	13.00	13.36	14.80
	8H	12.49	12.80	13.59	13.89	15.35	12.10	12.40	13.20	13.50	14.96
	12H	12.61	12.87	13.71	13.97	15.47	12.20	12.46	13.30	13.56	15.06
12H	4H	11.67	12.05	12.76	13.13	14.58	11.30	11.67	12.39	12.76	14.21
	6H	12.31	12.62	13.41	13.71	15.17	11.94	12.24	13.04	13.34	14.80
	8H	12.53	12.80	13.64	13.89	15.39	12.15	12.42	13.26	13.51	15.01