

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902147

Luminaire Tested: DFN2DIP-4P2F0-020D040US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902147
REPORT IS A COMBINATION OF REPORTS P900543 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D040US830-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5598.7 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 49.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902147

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902147

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1836	1806	1820
10°	1818	1778	1793
15°	1787	1744	1751
20°	1747	1698	1708
25°	1708	1645	1660
30°	1659	1595	1599
35°	1612	1537	1535
40°	1555	1478	1473
45°	1499	1419	1410
50°	1437	1357	1338
55°	1371	1285	1270
60°	1297	1201	1193
65°	1216	1112	1102
70°	1113	1004	1003
75°	972	875	908
80°	799	711	734
85°	533	444	457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1499 cd/sqm

TEST NUMBER: P902147

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	1.2
10°-20°	194.2	3.5
20°-30°	285.5	5.1
30°-40°	331.5	5.9
40°-50°	331.1	5.9
50°-60°	288.7	5.2
60°-70°	213.4	3.8
70°-80°	120.8	2.2
80°-90°	34.1	0.6
90°-100°	41.9	0.7
100°-110°	156.4	2.8
110°-120°	414.8	7.4
120°-130°	688.0	12.3
130°-140°	730.8	13.1
140°-150°	679.2	12.1
150°-160°	546.1	9.8
160°-170°	351.9	6.3
170°-180°	121.1	2.2
0°-30°	548.7	9.8
0°-40°	880.3	15.7
0°-60°	1500.2	26.8
0°-90°	1868.5	33.4
90°-120°	613.2	11.0
90°-150°	2711.2	48.4
90°-180°	3730.0	66.6
0°-180°	5598.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	11	18	23	25	5
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	

TEST NUMBER: P902147

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7

TEST NUMBER: P902147

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4

TEST NUMBER: P902147

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.48	8.21	8.56	9.29	10.78	7.03	7.76	8.12	8.85	10.34
	3H	9.10	9.76	10.20	10.85	12.36	8.62	9.27	9.71	10.36	11.87
	4H	9.67	10.29	10.78	11.39	12.90	9.18	9.80	10.28	10.89	12.41
	6H	10.05	10.62	11.16	11.72	13.24	9.55	10.12	10.66	11.22	12.74
	8H	10.14	10.68	11.26	11.80	13.32	9.64	10.18	10.76	11.30	12.81
	12H	10.17	10.69	11.30	11.80	13.34	9.67	10.18	10.79	11.29	12.83
4H	2H	7.91	8.53	9.02	9.63	11.14	7.55	8.17	8.67	9.27	10.78
	3H	9.74	10.25	10.86	11.38	12.90	9.33	9.85	10.45	10.97	12.50
	4H	10.43	10.90	11.55	12.02	13.56	10.00	10.48	11.13	11.59	13.14
	6H	10.91	11.32	12.04	12.46	13.99	10.48	10.89	11.61	12.02	13.56
	8H	11.05	11.43	12.18	12.56	14.11	10.61	10.99	11.74	12.12	13.67
	12H	11.10	11.45	12.25	12.59	14.15	10.66	11.00	11.80	12.14	13.70
8H	4H	10.60	10.98	11.73	12.11	13.66	10.22	10.60	11.35	11.73	13.28
	6H	11.20	11.51	12.35	12.68	14.23	10.81	11.13	11.96	12.30	13.85
	8H	11.40	11.68	12.56	12.83	14.40	11.01	11.28	12.17	12.43	14.00
	12H	11.51	11.75	12.67	12.90	14.51	11.10	11.34	12.26	12.49	14.10
12H	4H	10.58	10.92	11.72	12.06	13.62	10.21	10.55	11.35	11.69	13.25
	6H	11.22	11.50	12.38	12.64	14.22	10.85	11.12	12.00	12.27	13.84
	8H	11.44	11.68	12.60	12.83	14.43	11.06	11.30	12.22	12.44	14.05