

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907780

Luminaire Tested: DFN2DIP-4P4F0-050D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907780
REPORT IS A COMBINATION OF REPORTS P899084 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-050D030US840-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6973.2 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 73.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907780

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907780

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	58
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	41	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1354	1354	1354
5°	1356	1333	1341
10°	1343	1307	1298
15°	1324	1264	1231
20°	1300	1205	1149
25°	1275	1139	1069
30°	1242	1071	968
35°	1209	997	879
40°	1175	921	777
45°	1137	837	685
50°	1096	752	595
55°	1054	661	508
60°	1006	566	418
65°	950	469	377
70°	883	379	342
75°	798	335	312
80°	675	283	273
85°	472	191	209

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1137 cd/sqm

TEST NUMBER: P907780

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	2.8
10°-20°	536.9	7.7
20°-30°	753.8	10.8
30°-40°	821.7	11.8
40°-50°	755.2	10.8
50°-60°	593.1	8.5
60°-70°	386.1	5.5
70°-80°	198.7	2.9
80°-90°	53.5	0.8
90°-100°	59.3	0.9
100°-110°	188.4	2.7
110°-120°	322.4	4.6
120°-130°	424.0	6.1
130°-140°	475.9	6.8
140°-150°	466.7	6.7
150°-160°	391.5	5.6
160°-170°	259.6	3.7
170°-180°	90.7	1.3
0°-30°	1486.3	21.3
0°-40°	2308.0	33.1
0°-60°	3656.4	52.4
0°-90°	4294.7	61.6
90°-120°	570.1	8.2
90°-150°	1936.6	27.8
90°-180°	2678.0	38.4
0°-180°	6973.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2078	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1617	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1143	944	810	765	980
55°	965	818	614	500	465	862
65°	652	499	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	1	10	28	27	28	7
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P907780

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2086.9	2086.9	2086.9	2086.9	2086.9
2.5°	2096.3	2086.9	2066.1	2085.1	2081.2
5°	2086.9	2077.5	2052.9	2069.8	2064.3
7.5°	2069.8	2058.6	2032.2	2039.6	2030.1
10°	2047.2	2034.0	1996.3	1990.5	1979.2
12.5°	2018.9	2002.0	1950.9	1939.6	1918.7
15°	1984.9	1964.1	1900.0	1864.1	1845.2
17.5°	1945.2	1915.0	1835.6	1794.1	1763.8
20°	1900.0	1862.1	1767.7	1720.6	1678.9
22.5°	1850.9	1807.4	1697.8	1633.7	1605.4
25°	1801.7	1741.2	1616.6	1539.2	1510.8
27.5°	1743.2	1678.9	1541.1	1452.3	1408.9
30°	1680.9	1609.0	1457.9	1361.7	1310.6
32.5°	1620.4	1533.5	1378.8	1265.4	1218.1
35°	1552.5	1456.1	1290.0	1170.9	1129.3
37.5°	1486.3	1382.4	1206.9	1076.4	1029.4
40°	1416.4	1303.2	1119.8	985.8	936.8
42.5°	1344.7	1223.9	1033.1	893.2	846.2
45°	1269.2	1142.6	944.3	810.1	764.8
47.5°	1197.4	1063.4	859.4	725.2	683.7
50°	1118.1	984.0	776.3	645.8	606.3
52.5°	1040.6	898.9	696.9	572.3	536.4
55°	965.0	817.7	613.7	500.5	464.6
57.5°	887.7	736.6	540.2	434.4	404.1
60°	808.3	657.2	462.6	366.5	336.2
62.5°	730.9	579.9	396.6	306.0	290.9
65°	651.6	498.6	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.8	349.4	219.0	200.2	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.6
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.9	35.9	35.9
87.5°	30.3	15.0	15.0	13.2	13.2
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0



TEST NUMBER: P907780

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P907780

CATALOG NUMBER: DFN2DIP-4P4F0-050D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.24	10.17	10.09	11.05	12.14	5.20	6.13	6.05	7.01	8.10
	3H	10.93	11.76	11.80	12.65	13.77	6.39	7.23	7.27	8.11	9.24
	4H	11.54	12.33	12.43	13.22	14.36	6.85	7.64	7.74	8.53	9.67
	6H	11.98	12.70	12.87	13.60	14.75	7.18	7.90	8.08	8.80	9.95
	8H	12.11	12.80	13.01	13.71	14.86	7.27	7.96	8.18	8.88	10.03
	12H	12.18	12.83	13.09	13.74	14.91	7.32	7.98	8.23	8.89	10.06
4H	2H	9.27	10.06	10.16	10.95	12.08	5.81	6.60	6.70	7.49	8.62
	3H	11.11	11.77	12.01	12.69	13.84	7.17	7.82	8.07	8.75	9.90
	4H	11.81	12.41	12.73	13.33	14.50	7.72	8.32	8.64	9.24	10.41
	6H	12.34	12.85	13.27	13.79	14.97	8.15	8.66	9.08	9.61	10.78
	8H	12.52	13.00	13.45	13.94	15.13	8.28	8.76	9.21	9.70	10.89
	12H	12.62	13.05	13.57	14.01	15.20	8.35	8.78	9.30	9.74	10.93
8H	4H	11.79	12.27	12.72	13.20	14.39	8.01	8.49	8.94	9.43	10.62
	6H	12.36	12.76	13.32	13.74	14.93	8.54	8.94	9.49	9.91	11.10
	8H	12.59	12.94	13.55	13.90	15.11	8.73	9.08	9.70	10.05	11.26
	12H	12.73	13.04	13.70	14.00	15.26	8.86	9.17	9.83	10.13	11.38
12H	4H	11.75	12.18	12.69	13.13	14.33	8.02	8.46	8.97	9.41	10.61
	6H	12.34	12.69	13.31	13.66	14.87	8.59	8.94	9.56	9.91	11.12
	8H	12.57	12.88	13.54	13.84	15.10	8.81	9.12	9.77	10.08	11.33

END OF REPORT