

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902149

Luminaire Tested: DFN2DIP-4P2F0-020D040US830-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902149
REPORT IS A COMBINATION OF REPORTS P900544 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D040US830-RLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5334.8 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 49.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902149

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902149

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1951	1951	1951
5°	1950	1915	1929
10°	1927	1872	1863
15°	1896	1806	1763
20°	1857	1716	1641
25°	1818	1616	1524
30°	1765	1514	1376
35°	1714	1405	1247
40°	1661	1293	1099
45°	1601	1169	964
50°	1538	1044	834
55°	1471	911	708
60°	1395	774	580
65°	1306	634	519
70°	1199	504	465
75°	1063	435	417
80°	870	351	351
85°	561	216	248

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1601 cd/sqm

TEST NUMBER: P902149

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.4
10°-20°	200.4	3.8
20°-30°	281.4	5.3
30°-40°	306.8	5.8
40°-50°	282.0	5.3
50°-60°	221.4	4.2
60°-70°	144.1	2.7
70°-80°	74.2	1.4
80°-90°	21.2	0.4
90°-100°	41.9	0.8
100°-110°	156.4	2.9
110°-120°	414.8	7.8
120°-130°	688.0	12.9
130°-140°	730.8	13.7
140°-150°	679.2	12.7
150°-160°	546.1	10.2
160°-170°	351.9	6.6
170°-180°	121.1	2.3
0°-30°	554.9	10.4
0°-40°	861.7	16.2
0°-60°	1365.1	25.6
0°-90°	1604.6	30.1
90°-120°	613.2	11.5
90°-150°	2711.2	50.8
90°-180°	3730.0	69.9
0°-180°	5334.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	766	773	771	74
15°	741	733	709	696	689	209
25°	673	650	604	575	564	309
35°	580	544	482	437	422	363
45°	474	426	353	302	286	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	52	51	137
85°	30	16	13	13	13	35
90°	1	11	18	23	25	5
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	

TEST NUMBER: P902149

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	779.1	779.1	779.1	779.1	779.1
2.5°	782.6	779.1	771.3	778.4	777.0
5°	779.1	775.6	766.4	772.8	770.6
7.5°	772.8	768.5	758.7	761.5	757.9
10°	764.3	759.3	745.3	743.1	739.0
12.5°	753.8	747.3	728.3	724.2	716.3
15°	741.0	733.2	709.3	695.9	688.9
17.5°	726.2	714.9	685.3	669.8	658.6
20°	709.3	695.1	660.0	642.3	626.8
22.5°	691.0	674.8	633.9	609.9	599.4
25°	672.7	650.1	603.5	574.7	564.0
27.5°	650.8	626.8	575.3	542.2	525.9
30°	627.5	600.7	544.3	508.4	489.3
32.5°	604.9	572.5	514.7	472.4	454.8
35°	579.6	543.7	481.6	437.2	421.6
37.5°	554.9	516.0	450.5	401.9	384.3
40°	528.8	486.5	418.1	368.1	349.7
42.5°	502.0	456.9	385.7	333.5	315.9
45°	473.8	426.5	352.6	302.5	285.5
47.5°	447.0	397.0	320.8	270.7	255.2
50°	417.5	367.4	289.8	241.1	226.4
52.5°	388.4	335.5	260.1	213.7	200.3
55°	360.2	305.3	229.1	186.9	173.4
57.5°	331.4	274.9	201.7	162.2	150.9
60°	301.8	245.3	172.8	136.9	125.5
62.5°	272.9	216.5	148.1	114.2	108.6
65°	243.3	186.2	122.7	98.8	96.6
67.5°	215.1	157.9	98.8	86.7	84.6
70°	185.4	130.4	81.7	74.7	71.9
72.5°	157.2	105.0	68.3	62.8	61.4
75°	129.7	80.3	56.4	51.5	50.8
77.5°	102.3	57.1	44.4	41.6	40.2
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.3	15.5	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7

TEST NUMBER: P902149

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4

TEST NUMBER: P902149

CATALOG NUMBER: DFN2DIP-4P2F0-020D040US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.11	7.80	8.23	8.91	10.44	3.07	3.77	4.19	4.87	6.40
	3H	8.76	9.37	9.88	10.49	12.04	4.23	4.85	5.36	5.96	7.51
	4H	9.34	9.93	10.48	11.04	12.60	4.66	5.25	5.79	6.36	7.92
	6H	9.74	10.28	10.88	11.40	12.96	4.96	5.49	6.10	6.61	8.18
	8H	9.85	10.36	11.00	11.50	13.05	5.03	5.54	6.18	6.68	8.24
	12H	9.90	10.38	11.05	11.51	13.09	5.06	5.55	6.21	6.68	8.26
4H	2H	7.11	7.69	8.25	8.81	10.36	3.64	4.23	4.78	5.34	6.90
	3H	8.90	9.38	10.04	10.53	12.09	4.95	5.44	6.10	6.58	8.15
	4H	9.57	10.01	10.72	11.14	12.73	5.48	5.93	6.63	7.06	8.64
	6H	10.05	10.43	11.21	11.59	13.17	5.87	6.25	7.02	7.40	8.98
	8H	10.21	10.57	11.37	11.71	13.31	5.98	6.34	7.14	7.48	9.08
	12H	10.29	10.61	11.46	11.77	13.37	6.03	6.35	7.20	7.51	9.11
8H	4H	9.52	9.88	10.67	11.02	12.61	5.73	6.09	6.89	7.24	8.83
	6H	10.05	10.35	11.23	11.54	13.13	6.22	6.51	7.39	7.70	9.29
	8H	10.25	10.51	11.43	11.68	13.29	6.39	6.65	7.57	7.82	9.43
	12H	10.37	10.60	11.55	11.76	13.40	6.49	6.72	7.67	7.88	9.52
12H	4H	9.46	9.79	10.63	10.94	12.54	5.73	6.05	6.90	7.21	8.81
	6H	10.03	10.28	11.21	11.45	13.06	6.26	6.52	7.44	7.68	9.29
	8H	10.22	10.45	11.41	11.61	13.26	6.45	6.67	7.63	7.84	9.48

END OF REPORT