

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902150

Luminaire Tested: DFN2DIP-4P2F0-030D020US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902150
REPORT IS A COMBINATION OF REPORTS P899013 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D020US830-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4467.7 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 43.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902150

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902150

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US830-FLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2755	2755	2755
5°	2754	2710	2730
10°	2726	2666	2689
15°	2681	2615	2626
20°	2621	2547	2563
25°	2561	2467	2490
30°	2488	2393	2399
35°	2418	2306	2302
40°	2333	2218	2210
45°	2248	2129	2116
50°	2155	2036	2007
55°	2057	1928	1906
60°	1946	1801	1790
65°	1824	1668	1653
70°	1669	1507	1505
75°	1457	1313	1363
80°	1198	1066	1103
85°	804	667	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2248 cd/sqm

TEST NUMBER: P902150

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	2.3
10°-20°	291.4	6.5
20°-30°	428.2	9.6
30°-40°	497.3	11.1
40°-50°	496.7	11.1
50°-60°	433.1	9.7
60°-70°	320.2	7.2
70°-80°	181.1	4.1
80°-90°	49.5	1.1
90°-100°	36.9	0.8
100°-110°	117.2	2.6
110°-120°	200.6	4.5
120°-130°	263.8	5.9
130°-140°	296.1	6.6
140°-150°	290.4	6.5
150°-160°	243.6	5.5
160°-170°	161.5	3.6
170°-180°	56.5	1.3
0°-30°	823.1	18.4
0°-40°	1320.4	29.6
0°-60°	2250.3	50.4
0°-90°	2801.1	62.7
90°-120°	354.7	7.9
90°-150°	1205.0	27.0
90°-180°	1667.0	37.3
0°-180°	4467.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1100	1096	1084	1093	1091	104
15°	1047	1041	1027	1032	1026	295
25°	948	940	922	924	922	436
35°	818	807	790	784	779	511
45°	666	658	642	631	626	514
55°	504	497	485	472	467	450
65°	340	333	323	313	308	336
75°	178	176	170	164	166	190
85°	43	42	41	38	37	48
90°	1	6	18	16	17	4
95°	26	31	32	32	31	29
105°	108	110	111	112	112	114
115°	201	204	203	203	201	199
125°	293	297	296	294	294	262
135°	379	384	385	385	383	293
145°	460	463	466	467	465	287
155°	526	527	529	531	530	242
165°	572	571	571	575	572	161
175°	595	594	593	596	593	57
180°	596	596	596	596	596	

TEST NUMBER: P902150

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1100.2	1100.2	1100.2	1100.2	1100.2
2.5°	1106.6	1101.4	1089.7	1100.2	1098.3
5°	1100.2	1096.1	1084.4	1092.9	1090.8
7.5°	1092.9	1086.6	1074.9	1083.5	1081.3
10°	1081.3	1073.8	1061.2	1069.6	1066.5
12.5°	1065.4	1059.0	1046.4	1051.6	1049.5
15°	1047.4	1041.1	1027.3	1031.5	1026.2
17.5°	1025.1	1018.9	1005.0	1010.3	1005.0
20°	1000.8	994.5	979.7	982.8	978.6
22.5°	976.6	967.0	953.2	953.2	951.0
25°	947.9	939.5	921.5	923.6	921.5
27.5°	916.2	908.7	895.0	891.9	886.6
30°	884.5	876.0	860.2	857.0	852.7
32.5°	850.6	844.3	827.4	821.0	816.7
35°	817.8	807.3	790.3	783.9	778.6
37.5°	780.8	771.3	754.3	746.9	741.6
40°	742.7	734.2	717.3	707.8	703.6
42.5°	705.7	697.2	680.3	669.7	663.4
45°	665.5	658.1	642.2	630.6	626.3
47.5°	626.3	619.0	602.0	590.3	584.0
50°	585.0	579.8	565.0	550.2	544.9
52.5°	544.9	537.4	523.8	512.1	504.6
55°	503.7	497.3	484.6	471.9	466.7
57.5°	462.3	457.0	443.3	430.6	426.3
60°	421.0	416.9	402.1	390.4	387.3
62.5°	380.9	373.4	362.9	352.3	348.1
65°	339.7	333.3	322.7	313.2	307.9
67.5°	297.4	292.0	282.5	275.1	270.9
70°	258.2	253.9	244.4	237.0	232.8
72.5°	218.0	213.7	208.4	201.0	197.9
75°	177.7	175.7	170.3	164.0	166.2
77.5°	141.8	137.5	135.3	132.2	129.1
80°	105.8	104.7	102.5	99.4	97.4
82.5°	71.9	71.9	71.0	66.6	66.6
85°	43.4	42.3	41.3	38.1	37.0
87.5°	19.0	17.0	14.8	11.7	10.6
90°	0.6	6.5	17.6	16.5	17.1
92.5°	11.1	15.1	15.6	16.2	16.2
95°	26.2	31.3	32.1	32.1	31.3
97.5°	43.6	48.4	50.3	50.3	50.3
100°	63.8	68.0	69.4	69.4	68.8
102.5°	85.0	88.0	90.0	90.6	90.0
105°	108.2	109.6	110.7	111.6	111.6
107.5°	131.2	133.4	133.4	133.7	131.2
110°	153.5	156.4	156.4	156.4	155.0

TEST NUMBER: P902150

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.6	180.6	180.1	178.6	177.6
115°	201.3	204.2	203.3	202.7	201.3
117.5°	224.9	228.8	226.3	224.9	223.4
120°	248.5	252.5	248.5	248.5	246.9
122.5°	270.1	275.1	272.7	271.3	270.1
125°	292.8	297.3	295.9	294.3	293.7
127.5°	314.9	320.5	318.5	316.3	314.9
130°	335.5	342.0	341.1	340.1	338.1
132.5°	358.7	363.8	364.1	361.7	360.1
135°	378.7	384.3	385.3	384.8	383.3
137.5°	401.0	405.5	406.4	406.0	403.9
140°	420.6	425.1	427.6	427.6	425.7
142.5°	440.7	445.2	446.7	447.1	445.2
145°	459.8	463.4	466.3	466.7	464.8
147.5°	476.8	481.4	483.5	484.4	482.4
150°	494.5	497.5	499.5	501.1	499.5
152.5°	510.1	513.1	515.7	517.6	515.7
155°	525.8	527.2	528.8	531.3	529.7
157.5°	539.2	540.3	541.2	544.8	542.2
160°	551.3	552.3	552.9	555.9	553.7
162.5°	562.4	562.4	562.9	566.4	563.8
165°	571.9	571.4	571.4	575.0	572.5
167.5°	580.5	578.9	578.9	582.5	580.0
170°	587.0	585.6	585.0	588.6	585.6
172.5°	591.5	590.0	589.6	593.1	590.0
175°	595.1	593.7	592.6	596.2	593.1
177.5°	597.1	595.7	594.6	597.6	594.6
180°	596.2	596.2	596.2	596.2	596.2

TEST NUMBER: P902150

CATALOG NUMBER: DFN2DIP-4P2F0-030D020US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.75	12.74	12.59	13.60	14.68	11.31	12.30	12.15	13.16	14.24
	3H	13.40	14.29	14.25	15.16	16.26	12.91	13.80	13.76	14.67	15.77
	4H	13.98	14.82	14.85	15.70	16.81	13.49	14.32	14.35	15.20	16.32
	6H	14.37	15.14	15.25	16.03	17.15	13.87	14.64	14.75	15.53	16.66
	8H	14.47	15.20	15.36	16.11	17.23	13.97	14.70	14.86	15.61	16.73
	12H	14.51	15.21	15.41	16.11	17.26	14.00	14.70	14.90	15.60	16.76
4H	2H	12.22	13.05	13.09	13.93	15.05	11.86	12.70	12.73	13.58	14.69
	3H	14.07	14.77	14.95	15.68	16.81	13.66	14.36	14.54	15.27	16.40
	4H	14.77	15.41	15.67	16.31	17.47	14.34	14.98	15.24	15.89	17.05
	6H	15.27	15.82	16.18	16.75	17.91	14.84	15.39	15.75	16.32	17.48
	8H	15.41	15.93	16.32	16.85	18.02	14.97	15.49	15.89	16.41	17.59
	12H	15.48	15.94	16.41	16.89	18.06	15.03	15.50	15.96	16.44	17.62
8H	4H	14.96	15.48	15.88	16.40	17.57	14.58	15.10	15.50	16.02	17.20
	6H	15.57	16.00	16.51	16.96	18.13	15.19	15.61	16.13	16.58	17.75
	8H	15.78	16.15	16.73	17.11	18.30	15.38	15.76	16.33	16.72	17.91
	12H	15.90	16.23	16.85	17.18	18.42	15.49	15.82	16.44	16.77	18.01
12H	4H	14.95	15.42	15.88	16.36	17.54	14.58	15.05	15.51	15.99	17.17
	6H	15.60	15.97	16.55	16.93	18.12	15.22	15.60	16.17	16.56	17.75
	8H	15.83	16.16	16.78	17.11	18.35	15.44	15.78	16.40	16.73	17.97