

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907852

Luminaire Tested: DFN2DIP-4P4F0-080D030US840-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907852
REPORT IS A COMBINATION OF REPORTS P899090 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D030US840-RLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9548.3 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 108.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907852

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907852

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	96	96	96	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	49	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2166	2166	2166
5°	2170	2132	2146
10°	2148	2091	2077
15°	2119	2023	1970
20°	2080	1928	1838
25°	2040	1822	1711
30°	1987	1713	1549
35°	1934	1596	1407
40°	1881	1474	1244
45°	1818	1340	1096
50°	1754	1204	951
55°	1687	1058	812
60°	1609	906	670
65°	1520	751	603
70°	1412	607	547
75°	1276	537	500
80°	1080	452	436
85°	755	306	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1818 cd/sqm

TEST NUMBER: P907852

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.9	3.3
10°-20°	859.1	9.0
20°-30°	1206.1	12.6
30°-40°	1314.7	13.8
40°-50°	1208.4	12.7
50°-60°	949.0	9.9
60°-70°	617.7	6.5
70°-80°	318.0	3.3
80°-90°	83.9	0.9
90°-100°	59.3	0.6
100°-110°	188.4	2.0
110°-120°	322.4	3.4
120°-130°	424.0	4.4
130°-140°	475.9	5.0
140°-150°	466.7	4.9
150°-160°	391.5	4.1
160°-170°	259.6	2.7
170°-180°	90.7	1.0
0°-30°	2378.1	24.9
0°-40°	3692.9	38.7
0°-60°	5850.2	61.3
0°-90°	6869.8	71.9
90°-120°	570.1	6.0
90°-150°	1936.6	20.3
90°-180°	2678.0	28.0
0°-180°	9548.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3339	3339	3339	3339	3339	
5°	3339	3324	3284	3312	3303	317
15°	3176	3142	3040	2982	2952	895
25°	2883	2786	2587	2463	2417	1326
35°	2484	2330	2064	1874	1807	1555
45°	2031	1828	1511	1296	1224	1568
55°	1544	1308	982	801	744	1380
65°	1043	798	526	423	414	1034
75°	556	344	242	221	218	588
85°	130	66	57	57	57	149
90°	1	10	28	27	28	9
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P907852

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3339.0	3339.0	3339.0	3339.0	3339.0
2.5°	3354.1	3339.0	3305.7	3336.1	3330.0
5°	3339.0	3324.0	3284.5	3311.8	3302.8
7.5°	3311.8	3293.8	3251.5	3263.4	3248.2
10°	3275.5	3254.4	3194.1	3184.8	3166.8
12.5°	3230.4	3203.1	3121.3	3103.3	3070.0
15°	3175.8	3142.5	3039.9	2982.5	2952.3
17.5°	3112.3	3063.9	2937.0	2870.6	2822.2
20°	3039.9	2979.3	2828.3	2753.0	2686.2
22.5°	2961.3	2891.7	2716.4	2613.8	2568.6
25°	2882.8	2786.0	2586.6	2462.9	2417.3
27.5°	2789.1	2686.2	2465.7	2323.7	2254.1
30°	2689.5	2574.3	2332.7	2178.8	2097.0
32.5°	2592.6	2453.6	2206.1	2024.6	1948.9
35°	2484.0	2329.8	2064.0	1873.6	1806.9
37.5°	2378.1	2211.8	1931.0	1722.2	1646.9
40°	2266.3	2085.2	1791.8	1577.3	1498.7
42.5°	2151.5	1958.2	1652.9	1429.3	1353.8
45°	2030.6	1828.1	1511.0	1296.2	1223.8
47.5°	1915.9	1701.4	1375.0	1160.2	1093.9
50°	1788.9	1574.5	1242.0	1033.3	970.1
52.5°	1664.9	1438.1	1115.0	915.6	858.3
55°	1544.0	1308.4	982.0	800.8	743.5
57.5°	1420.3	1178.5	864.3	695.1	646.6
60°	1293.2	1051.6	740.2	586.3	538.0
62.5°	1169.5	927.8	634.5	489.6	465.5
65°	1042.6	797.6	525.7	423.2	413.8
67.5°	921.7	676.8	423.2	371.5	362.6
70°	794.8	559.2	350.4	320.2	308.1
72.5°	673.9	450.1	293.1	269.0	262.9
75°	555.9	344.4	241.8	220.6	217.7
77.5°	438.3	244.6	190.5	178.2	172.2
80°	329.2	175.4	144.9	133.0	133.0
82.5°	229.5	118.0	99.7	93.6	93.6
85°	129.9	66.3	57.4	57.4	57.4
87.5°	48.4	24.0	24.0	21.2	21.2
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0

TEST NUMBER: P907852

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P907852

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.69	12.74	12.44	13.51	14.43	7.66	8.70	8.41	9.47	10.39
	3H	13.39	14.33	14.16	15.11	16.06	8.86	9.80	9.63	10.58	11.53
	4H	14.02	14.90	14.80	15.69	16.65	9.32	10.21	10.11	10.99	11.96
	6H	14.45	15.27	15.25	16.06	17.04	9.66	10.47	10.45	11.27	12.24
	8H	14.59	15.36	15.39	16.18	17.16	9.75	10.53	10.56	11.34	12.32
	12H	14.66	15.40	15.47	16.20	17.21	9.81	10.54	10.61	11.35	12.36
4H	2H	11.74	12.62	12.52	13.41	14.37	8.28	9.16	9.07	9.95	10.91
	3H	13.59	14.33	14.39	15.15	16.13	9.65	10.39	10.45	11.21	12.19
	4H	14.30	14.97	15.11	15.78	16.79	10.21	10.88	11.02	11.70	12.71
	6H	14.83	15.41	15.66	16.25	17.27	10.64	11.22	11.47	12.06	13.08
	8H	15.01	15.55	15.85	16.39	17.42	10.78	11.31	11.61	12.15	13.18
	12H	15.12	15.60	15.97	16.47	17.50	10.85	11.34	11.70	12.20	13.23
8H	4H	14.28	14.82	15.12	15.66	16.69	10.51	11.05	11.34	11.89	12.91
	6H	14.86	15.31	15.72	16.19	17.22	11.04	11.48	11.90	12.36	13.39
	8H	15.08	15.48	15.96	16.36	17.40	11.23	11.63	12.10	12.50	13.55
	12H	15.24	15.58	16.11	16.45	17.55	11.36	11.71	12.23	12.58	13.68
12H	4H	14.25	14.73	15.10	15.59	16.62	10.53	11.01	11.38	11.87	12.90
	6H	14.84	15.23	15.71	16.11	17.16	11.09	11.48	11.96	12.36	13.41
	8H	15.07	15.42	15.95	16.29	17.39	11.31	11.66	12.18	12.53	13.63