

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907596

Luminaire Tested: DFN2DIP-4P2F0-020D020US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907596
REPORT IS A COMBINATION OF REPORTS P899012 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D020US840-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3504.2 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907596

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907596

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2090	2090	2090
5°	2089	2052	2067
10°	2065	2006	1996
15°	2032	1935	1889
20°	1990	1839	1759
25°	1947	1731	1633
30°	1891	1622	1475
35°	1836	1505	1336
40°	1780	1385	1177
45°	1715	1252	1033
50°	1648	1119	894
55°	1577	977	759
60°	1495	829	622
65°	1399	680	556
70°	1284	540	498
75°	1140	466	446
80°	932	377	376
85°	600	231	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1715 cd/sqm

TEST NUMBER: P907596

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	2.2
10°-20°	214.8	6.1
20°-30°	301.5	8.6
30°-40°	328.7	9.4
40°-50°	302.1	8.6
50°-60°	237.3	6.8
60°-70°	154.4	4.4
70°-80°	79.5	2.3
80°-90°	22.1	0.6
90°-100°	39.5	1.1
100°-110°	125.6	3.6
110°-120°	214.9	6.1
120°-130°	282.7	8.1
130°-140°	317.3	9.1
140°-150°	311.1	8.9
150°-160°	261.0	7.4
160°-170°	173.1	4.9
170°-180°	60.5	1.7
0°-30°	594.5	17.0
0°-40°	923.2	26.3
0°-60°	1462.6	41.7
0°-90°	1718.6	49.0
90°-120°	380.0	10.8
90°-150°	1291.1	36.8
90°-180°	1786.0	51.0
0°-180°	3504.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	835	835	835	835	835	
5°	835	831	821	828	826	79
15°	794	786	760	746	738	224
25°	721	696	647	616	604	331
35°	621	582	516	468	452	389
45°	508	457	378	324	306	392
55°	386	327	246	200	186	345
65°	261	199	132	106	104	258
75°	139	86	60	55	54	147
85°	32	17	14	14	14	37
90°	1	7	19	18	18	3
95°	28	34	34	34	34	31
105°	116	117	119	120	120	122
115°	216	219	218	217	216	213
125°	314	318	317	315	315	280
135°	406	412	413	412	411	314
145°	493	496	500	500	498	308
155°	563	565	566	569	568	259
165°	613	612	612	616	613	173
175°	638	636	635	639	636	61
180°	639	639	639	639	639	

TEST NUMBER: P907596

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	834.8	834.8	834.8	834.8	834.8
2.5°	838.5	834.8	826.4	834.0	832.5
5°	834.8	831.0	821.1	828.0	825.7
7.5°	828.0	823.4	812.8	815.9	812.0
10°	818.9	813.5	798.5	796.2	791.7
12.5°	807.6	800.7	780.3	775.9	767.5
15°	794.0	785.6	759.9	745.6	738.1
17.5°	778.1	766.0	734.3	717.6	705.6
20°	759.9	744.8	707.1	688.2	671.6
22.5°	740.3	723.0	679.1	653.5	642.2
25°	720.7	696.5	646.6	615.7	604.3
27.5°	697.3	671.6	616.4	580.9	563.5
30°	672.4	643.6	583.2	544.7	524.2
32.5°	648.1	613.4	551.5	506.1	487.3
35°	621.0	582.5	516.0	468.4	451.7
37.5°	594.5	552.9	482.7	430.6	411.7
40°	566.5	521.3	448.0	394.4	374.7
42.5°	537.9	489.6	413.2	357.3	338.5
45°	507.7	457.0	377.8	324.1	305.9
47.5°	479.0	425.4	343.8	290.0	273.5
50°	447.3	393.6	310.5	258.3	242.6
52.5°	416.2	359.5	278.7	228.9	214.6
55°	386.0	327.1	245.5	200.3	185.8
57.5°	355.1	294.6	216.1	173.8	161.7
60°	323.4	262.9	185.1	146.6	134.5
62.5°	292.4	232.0	158.6	122.4	116.3
65°	260.6	199.4	131.5	105.8	103.5
67.5°	230.5	169.2	105.8	92.9	90.7
70°	198.6	139.8	87.6	80.1	77.1
72.5°	168.4	112.5	73.2	67.3	65.7
75°	139.0	86.0	60.4	55.1	54.4
77.5°	109.6	61.2	47.6	44.5	43.0
80°	82.3	43.8	36.3	33.2	33.2
82.5°	57.4	29.5	24.9	23.4	23.4
85°	32.4	16.6	14.3	14.3	14.3
87.5°	12.1	6.1	6.1	5.3	5.3
90°	0.6	7.0	18.9	17.7	18.3
92.5°	11.9	16.2	16.8	17.4	17.4
95°	28.1	33.5	34.4	34.4	33.5
97.5°	46.8	51.8	53.9	53.9	53.9
100°	68.4	72.8	74.3	74.3	73.7
102.5°	91.1	94.3	96.4	97.0	96.4
105°	115.9	117.4	118.7	119.6	119.6
107.5°	140.6	142.9	142.9	143.3	140.6
110°	164.5	167.5	167.5	167.5	166.0



TEST NUMBER: P907596

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	190.3	193.5	193.0	191.4	190.3
115°	215.7	218.7	217.8	217.2	215.7
117.5°	241.0	245.2	242.5	241.0	239.3
120°	266.3	270.5	266.3	266.3	264.6
122.5°	289.4	294.8	292.2	290.6	289.4
125°	313.7	318.5	317.0	315.3	314.7
127.5°	337.4	343.4	341.2	338.9	337.4
130°	359.5	366.5	365.5	364.4	362.2
132.5°	384.4	389.8	390.1	387.5	385.9
135°	405.8	411.7	412.8	412.3	410.7
137.5°	429.6	434.4	435.5	435.1	432.7
140°	450.6	455.4	458.2	458.2	456.1
142.5°	472.2	477.0	478.6	479.1	477.0
145°	492.6	496.4	499.6	500.1	498.0
147.5°	510.9	515.7	518.1	519.0	516.8
150°	529.8	533.0	535.1	536.8	535.1
152.5°	546.5	549.8	552.5	554.6	552.5
155°	563.3	564.8	566.5	569.3	567.5
157.5°	577.7	578.9	579.9	583.7	581.0
160°	590.7	591.8	592.4	595.6	593.3
162.5°	602.6	602.6	603.1	606.8	604.1
165°	612.8	612.2	612.2	616.0	613.4
167.5°	622.0	620.3	620.3	624.1	621.5
170°	628.9	627.4	626.8	630.7	627.4
172.5°	633.8	632.2	631.7	635.5	632.2
175°	637.6	636.1	634.9	638.7	635.5
177.5°	639.7	638.2	637.0	640.3	637.0
180°	638.7	638.7	638.7	638.7	638.7

TEST NUMBER: P907596

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.48	10.30	10.45	11.29	12.57	5.44	6.27	6.42	7.25	8.54
	3H	11.14	11.87	12.12	12.86	14.17	6.61	7.35	7.60	8.34	9.65
	4H	11.73	12.42	12.73	13.42	14.74	7.05	7.74	8.04	8.74	10.05
	6H	12.13	12.77	13.14	13.77	15.10	7.35	7.99	8.35	8.99	10.32
	8H	12.25	12.86	13.26	13.87	15.20	7.43	8.04	8.44	9.05	10.38
	12H	12.30	12.88	13.32	13.89	15.24	7.46	8.04	8.48	9.05	10.40
4H	2H	9.49	10.19	10.50	11.18	12.50	6.03	6.72	7.03	7.72	9.03
	3H	11.30	11.87	12.31	12.90	14.23	7.35	7.93	8.36	8.95	10.28
	4H	11.97	12.50	12.99	13.51	14.87	7.88	8.41	8.90	9.42	10.78
	6H	12.46	12.92	13.49	13.96	15.31	8.28	8.73	9.31	9.77	11.12
	8H	12.62	13.05	13.66	14.08	15.45	8.39	8.82	9.42	9.85	11.21
	12H	12.71	13.09	13.76	14.14	15.51	8.44	8.83	9.49	9.87	11.25
8H	4H	11.93	12.36	12.96	13.39	14.75	8.15	8.57	9.18	9.60	10.97
	6H	12.47	12.82	13.53	13.90	15.26	8.64	8.98	9.69	10.06	11.42
	8H	12.67	12.98	13.74	14.04	15.42	8.81	9.12	9.87	10.18	11.56
	12H	12.80	13.07	13.86	14.12	15.54	8.91	9.18	9.98	10.24	11.66
12H	4H	11.88	12.26	12.93	13.31	14.68	8.15	8.53	9.20	9.58	10.95
	6H	12.45	12.75	13.51	13.81	15.20	8.68	8.99	9.74	10.04	11.43
	8H	12.65	12.92	13.71	13.97	15.40	8.87	9.14	9.93	10.19	11.62