

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907599

Luminaire Tested: DFN2DIP-4P2F0-020D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907599
REPORT IS A COMBINATION OF REPORTS P900537 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D030US840-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4998.9 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 40
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907599
CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907599
 CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	41	40	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	24	21
5	67	55	47	41	60	50	44	38	42	37	33	34	30	27	26	23	21	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	15	13	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1968	1968	1968
5°	1967	1935	1950
10°	1947	1904	1920
15°	1915	1868	1876
20°	1872	1819	1830
25°	1830	1762	1779
30°	1777	1709	1713
35°	1727	1647	1644
40°	1667	1584	1579
45°	1606	1521	1511
50°	1539	1454	1434
55°	1469	1377	1361
60°	1390	1286	1278
65°	1303	1192	1181
70°	1192	1076	1075
75°	1040	938	973
80°	856	762	787
85°	572	476	491

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1606 cd/sqm



TEST NUMBER: P907599

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.0	1.5
10°-20°	208.1	4.2
20°-30°	305.8	6.1
30°-40°	355.2	7.1
40°-50°	354.8	7.1
50°-60°	309.4	6.2
60°-70°	228.7	4.6
70°-80°	129.4	2.6
80°-90°	36.0	0.7
90°-100°	33.7	0.7
100°-110°	125.7	2.5
110°-120°	333.3	6.7
120°-130°	552.9	11.1
130°-140°	587.3	11.7
140°-150°	545.8	10.9
150°-160°	438.8	8.8
160°-170°	282.8	5.7
170°-180°	97.3	1.9
0°-30°	587.9	11.8
0°-40°	943.2	18.9
0°-60°	1607.3	32.2
0°-90°	2001.3	40.0
90°-120°	492.7	9.9
90°-150°	2178.7	43.6
90°-180°	2998.0	60.0
0°-180°	4998.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	786	783	775	781	779	75
15°	748	744	734	737	733	211
25°	677	671	658	660	658	312
35°	584	577	564	560	556	365
45°	475	470	459	450	447	367
55°	360	355	346	337	333	322
65°	243	238	231	224	220	240
75°	127	126	122	117	119	135
85°	31	30	30	27	26	35
90°	1	9	15	19	20	5
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P907599

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	785.9	785.9	785.9	785.9	785.9
2.5°	790.4	786.7	778.3	785.9	784.5
5°	785.9	782.9	774.6	780.6	779.1
7.5°	780.6	776.1	767.8	773.9	772.3
10°	772.3	767.1	758.0	764.0	761.7
12.5°	760.9	756.5	747.4	751.1	749.6
15°	748.1	743.7	733.8	736.8	733.1
17.5°	732.3	727.8	717.9	721.6	717.9
20°	714.9	710.3	699.7	702.1	699.0
22.5°	697.5	690.7	680.9	680.9	679.3
25°	677.1	671.1	658.2	659.6	658.2
27.5°	654.4	649.1	639.3	637.1	633.3
30°	631.8	625.7	614.4	612.2	609.0
32.5°	607.5	603.1	591.0	586.4	583.4
35°	584.2	576.6	564.5	560.0	556.1
37.5°	557.7	550.9	538.8	533.5	529.7
40°	530.5	524.4	512.3	505.6	502.5
42.5°	504.0	498.0	485.9	478.4	473.8
45°	475.3	470.1	458.7	450.4	447.4
47.5°	447.4	442.1	430.0	421.6	417.2
50°	417.9	414.1	403.5	392.9	389.2
52.5°	389.2	383.8	374.1	365.8	360.5
55°	359.7	355.2	346.1	337.1	333.3
57.5°	330.2	326.5	316.6	307.6	304.5
60°	300.7	297.8	287.2	278.8	276.6
62.5°	272.1	266.7	259.2	251.7	248.6
65°	242.6	238.0	230.6	223.7	219.9
67.5°	212.4	208.5	201.8	196.5	193.5
70°	184.4	181.4	174.5	169.3	166.3
72.5°	155.7	152.7	148.9	143.6	141.4
75°	126.9	125.5	121.6	117.1	118.7
77.5°	101.3	98.3	96.6	94.4	92.2
80°	75.6	74.8	73.3	71.0	69.5
82.5°	51.4	51.4	50.7	47.7	47.7
85°	30.9	30.2	29.5	27.2	26.5
87.5°	13.6	12.1	10.6	8.4	7.6
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P907599

CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P907599
 CATALOG NUMBER: DFN2DIP-4P2F0-020D030US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.49	9.27	9.53	10.32	11.72	8.05	8.83	9.09	9.87	11.28
	3H	10.12	10.82	11.17	11.87	13.30	9.63	10.33	10.68	11.39	12.81
	4H	10.69	11.35	11.75	12.41	13.84	10.20	10.86	11.26	11.92	13.35
	6H	11.07	11.68	12.14	12.74	14.18	10.57	11.18	11.64	12.24	13.68
	8H	11.16	11.74	12.24	12.82	14.26	10.66	11.24	11.74	12.32	13.76
	12H	11.20	11.75	12.28	12.82	14.28	10.69	11.24	11.77	12.31	13.78
4H	2H	8.93	9.59	10.00	10.65	12.08	8.58	9.24	9.64	10.29	11.73
	3H	10.76	11.31	11.84	12.40	13.84	10.35	10.91	11.43	11.99	13.44
	4H	11.46	11.96	12.53	13.03	14.50	11.03	11.54	12.11	12.61	14.08
	6H	11.94	12.38	13.03	13.48	14.94	11.51	11.95	12.60	13.04	14.50
	8H	12.08	12.49	13.17	13.58	15.05	11.64	12.05	12.73	13.14	14.62
	12H	12.14	12.51	13.25	13.61	15.09	11.69	12.06	12.80	13.16	14.64
8H	4H	11.63	12.04	12.72	13.13	14.60	11.25	11.66	12.34	12.75	14.23
	6H	12.23	12.57	13.34	13.70	15.17	11.85	12.18	12.96	13.31	14.79
	8H	12.44	12.73	13.55	13.84	15.34	12.04	12.34	13.16	13.45	14.94
	12H	12.55	12.81	13.67	13.92	15.45	12.14	12.40	13.26	13.51	15.04
12H	4H	11.61	11.98	12.72	13.08	14.56	11.24	11.61	12.35	12.71	14.19
	6H	12.26	12.55	13.37	13.66	15.16	11.88	12.18	13.00	13.29	14.78
	8H	12.48	12.73	13.60	13.84	15.37	12.09	12.35	13.22	13.46	14.99