

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907613

Luminaire Tested: DFN2DIP-4P2F0-030D030US840-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907613
REPORT IS A COMBINATION OF REPORTS P900540 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D030US840-RLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5574.5 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907613

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907613

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3135	3135	3135
5°	3134	3078	3100
10°	3097	3009	2994
15°	3048	2902	2833
20°	2985	2758	2638
25°	2921	2597	2449
30°	2837	2433	2212
35°	2754	2258	2004
40°	2670	2078	1766
45°	2573	1878	1550
50°	2471	1678	1340
55°	2365	1465	1139
60°	2241	1243	933
65°	2099	1019	833
70°	1926	810	747
75°	1709	699	669
80°	1398	565	565
85°	902	347	398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2573 cd/sqm

TEST NUMBER: P907613

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	2.1
10°-20°	322.1	5.8
20°-30°	452.3	8.1
30°-40°	493.0	8.8
40°-50°	453.1	8.1
50°-60°	355.9	6.4
60°-70°	231.6	4.2
70°-80°	119.2	2.1
80°-90°	32.2	0.6
90°-100°	33.7	0.6
100°-110°	125.7	2.3
110°-120°	333.3	6.0
120°-130°	552.9	9.9
130°-140°	587.3	10.5
140°-150°	545.8	9.8
150°-160°	438.8	7.9
160°-170°	282.8	5.1
170°-180°	97.3	1.7
0°-30°	891.8	16.0
0°-40°	1384.8	24.8
0°-60°	2193.8	39.4
0°-90°	2576.9	46.2
90°-120°	492.7	8.8
90°-150°	2178.7	39.1
90°-180°	2998.0	53.8
0°-180°	5574.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	9	15	19	20	5
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P907613

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5

TEST NUMBER: P907613

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5

TEST NUMBER: P907613

CATALOG NUMBER: DFN2DIP-4P2F0-030D030US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.62	11.42	11.61	12.42	13.75	6.58	7.38	7.57	8.38	9.71
	3H	12.27	12.99	13.28	14.00	15.35	7.75	8.46	8.75	9.47	10.82
	4H	12.86	13.54	13.88	14.55	15.91	8.18	8.86	9.20	9.87	11.23
	6H	13.27	13.89	14.29	14.91	16.27	8.48	9.10	9.51	10.12	11.49
	8H	13.38	13.97	14.41	15.01	16.37	8.56	9.15	9.59	10.19	11.55
	12H	13.43	13.99	14.47	15.02	16.41	8.59	9.16	9.63	10.18	11.57
4H	2H	10.63	11.31	11.65	12.32	13.68	7.16	7.84	8.18	8.85	10.21
	3H	12.43	12.99	13.46	14.03	15.40	8.48	9.04	9.52	10.09	11.46
	4H	13.10	13.62	14.14	14.65	16.04	9.01	9.53	10.05	10.56	11.95
	6H	13.59	14.03	14.64	15.09	16.48	9.41	9.85	10.46	10.91	12.29
	8H	13.75	14.17	14.81	15.22	16.62	9.52	9.94	10.57	10.99	12.39
	12H	13.84	14.21	14.90	15.27	16.68	9.57	9.95	10.64	11.01	12.42
8H	4H	13.06	13.47	14.11	14.53	15.93	9.28	9.69	10.33	10.74	12.14
	6H	13.60	13.94	14.68	15.03	16.43	9.76	10.11	10.84	11.20	12.60
	8H	13.80	14.10	14.88	15.18	16.60	9.94	10.24	11.02	11.32	12.73
	12H	13.92	14.19	15.01	15.26	16.72	10.04	10.30	11.12	11.38	12.84
12H	4H	13.01	13.38	14.08	14.45	15.86	9.28	9.65	10.34	10.71	12.12
	6H	13.57	13.87	14.66	14.95	16.37	9.81	10.11	10.89	11.18	12.60
	8H	13.78	14.04	14.86	15.11	16.57	10.00	10.26	11.08	11.33	12.79

END OF REPORT