

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907623

Luminaire Tested: DFN2DIP-4P2F0-040D030US840-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907623
REPORT IS A COMBINATION OF REPORTS P900541 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-040D030US840-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6998.4 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907623
CATALOG NUMBER: DFN2DIP-4P2F0-040D030US840-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907623

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57	57	57	57
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53	48	48	48	48
2	91	83	77	72	84	77	72	67	67	63	59	58	55	52	49	47	45	40	40	40	40
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	40	38	34	34	34	34
4	76	65	57	50	70	61	53	48	53	47	43	45	41	38	39	35	33	29	29	29	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26	26	26	26
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25	22	22	22	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20	20	20	20
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18	18	18	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16	16	16	16
10	48	36	28	24	45	34	27	22	30	24	20	26	22	18	23	19	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3936	3936	3936
5°	3934	3871	3900
10°	3894	3809	3841
15°	3829	3736	3752
20°	3744	3639	3661
25°	3659	3525	3557
30°	3554	3418	3427
35°	3455	3294	3289
40°	3334	3168	3158
45°	3212	3041	3023
50°	3079	2908	2867
55°	2939	2754	2723
60°	2780	2573	2557
65°	2605	2383	2362
70°	2384	2152	2149
75°	2082	1876	1946
80°	1712	1523	1575
85°	1146	952	980

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3212 cd/sqm



TEST NUMBER: P907623

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	2.1
10°-20°	416.2	5.9
20°-30°	611.7	8.7
30°-40°	710.5	10.2
40°-50°	709.6	10.1
50°-60°	618.7	8.8
60°-70°	457.4	6.5
70°-80°	258.8	3.7
80°-90°	70.1	1.0
90°-100°	33.7	0.5
100°-110°	125.7	1.8
110°-120°	333.3	4.8
120°-130°	552.9	7.9
130°-140°	587.3	8.4
140°-150°	545.8	7.8
150°-160°	438.8	6.3
160°-170°	282.8	4.0
170°-180°	97.3	1.4
0°-30°	1175.9	16.8
0°-40°	1886.3	27.0
0°-60°	3214.6	45.9
0°-90°	4000.8	57.2
90°-120°	492.7	7.0
90°-150°	2178.7	31.1
90°-180°	2998.0	42.8
0°-180°	6998.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1468	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	1	9	15	19	20	6
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P907623

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.8	1571.8	1571.8	1571.8	1571.8
2.5°	1580.9	1573.4	1556.7	1571.8	1568.9
5°	1571.8	1565.8	1549.1	1561.2	1558.3
7.5°	1561.2	1552.2	1535.5	1547.7	1544.7
10°	1544.7	1534.1	1516.0	1528.0	1523.5
12.5°	1521.9	1512.9	1494.8	1502.4	1499.2
15°	1496.2	1487.2	1467.5	1473.6	1466.1
17.5°	1464.5	1455.5	1435.8	1443.3	1435.8
20°	1429.7	1420.7	1399.6	1404.0	1398.2
22.5°	1395.0	1381.4	1361.7	1361.7	1358.7
25°	1354.1	1342.1	1316.5	1319.4	1316.5
27.5°	1308.8	1298.2	1278.7	1274.1	1266.7
30°	1263.5	1251.4	1228.8	1224.3	1218.2
32.5°	1215.2	1206.2	1181.9	1172.9	1166.7
35°	1168.3	1153.3	1129.0	1119.9	1112.4
37.5°	1115.4	1101.8	1077.5	1067.0	1059.4
40°	1061.1	1048.8	1024.6	1011.2	1005.1
42.5°	1008.1	995.9	971.9	956.6	947.7
45°	950.7	940.2	917.4	900.9	894.7
47.5°	894.7	884.1	860.0	843.3	834.4
50°	835.8	828.2	807.1	785.9	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.3	674.1	666.6
57.5°	660.5	653.0	633.2	615.1	609.0
60°	601.5	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.5	503.3	497.3
65°	485.2	476.1	461.0	447.4	439.9
67.5°	424.7	417.1	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.7
75°	253.9	251.0	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.1
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P907623

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P907623
 CATALOG NUMBER: DFN2DIP-4P2F0-040D030US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.53	13.46	13.43	14.38	15.54	12.09	13.02	12.98	13.93	15.10
	3H	14.18	15.01	15.08	15.93	17.12	13.69	14.52	14.59	15.44	16.63
	4H	14.75	15.54	15.67	16.47	17.67	14.26	15.05	15.18	15.98	17.18
	6H	15.14	15.87	16.07	16.80	18.01	14.64	15.37	15.57	16.30	17.51
	8H	15.24	15.93	16.18	16.88	18.09	14.74	15.43	15.67	16.38	17.59
	12H	15.28	15.94	16.22	16.88	18.12	14.77	15.43	15.72	16.38	17.61
4H	2H	12.99	13.78	13.92	14.71	15.91	12.64	13.42	13.56	14.35	15.55
	3H	14.84	15.50	15.77	16.45	17.67	14.43	15.09	15.36	16.05	17.26
	4H	15.54	16.14	16.48	17.09	18.33	15.11	15.71	16.06	16.67	17.90
	6H	16.03	16.55	16.99	17.53	18.77	15.60	16.12	16.56	17.10	18.33
	8H	16.17	16.66	17.13	17.63	18.88	15.74	16.22	16.70	17.19	18.44
	12H	16.24	16.68	17.22	17.66	18.92	15.79	16.23	16.77	17.22	18.47
8H	4H	15.72	16.21	16.69	17.18	18.43	15.35	15.83	16.31	16.80	18.05
	6H	16.33	16.73	17.32	17.74	19.00	15.95	16.35	16.93	17.36	18.61
	8H	16.54	16.89	17.53	17.89	19.16	16.14	16.50	17.14	17.50	18.77
	12H	16.66	16.97	17.66	17.96	19.28	16.25	16.56	17.25	17.55	18.87
12H	4H	15.71	16.15	16.69	17.14	18.39	15.34	15.78	16.32	16.77	18.02
	6H	16.36	16.71	17.35	17.71	18.98	15.98	16.34	16.98	17.34	18.61
	8H	16.58	16.89	17.58	17.89	19.21	16.20	16.51	17.20	17.51	18.82