

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910493

Luminaire Tested: DFN2DIP-4P4F0-040D050US850-RLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P910493  
REPORT IS A COMBINATION OF REPORTS P900626 AND P897523  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-040D050US850-RLLONL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9260.2 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 79  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P910493

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLONL

### Luminous Intensity Polar Plot



TEST NUMBER: P910493

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 105 | 105 | 105 | 105 | 96 | 96 | 96 | 96 | 78 | 78 | 78 | 62 | 62 | 62 | 48 | 48 | 48 |
| 1   | 96  | 92  | 88  | 85  | 87 | 84 | 81 | 78 | 69 | 67 | 65 | 55 | 54 | 53 | 43 | 42 | 41 |
| 2   | 88  | 81  | 75  | 70  | 80 | 74 | 69 | 65 | 61 | 57 | 54 | 49 | 47 | 44 | 38 | 36 | 35 |
| 3   | 80  | 71  | 64  | 59  | 73 | 65 | 59 | 54 | 54 | 50 | 46 | 44 | 41 | 38 | 34 | 32 | 30 |
| 4   | 74  | 63  | 56  | 50  | 67 | 58 | 52 | 46 | 48 | 43 | 40 | 39 | 36 | 33 | 31 | 28 | 26 |
| 5   | 68  | 57  | 49  | 43  | 62 | 52 | 45 | 40 | 43 | 38 | 34 | 35 | 32 | 29 | 28 | 25 | 23 |
| 6   | 62  | 51  | 43  | 37  | 57 | 47 | 40 | 35 | 39 | 34 | 30 | 32 | 28 | 25 | 25 | 23 | 21 |
| 7   | 58  | 46  | 38  | 33  | 53 | 42 | 36 | 31 | 36 | 30 | 27 | 29 | 25 | 23 | 23 | 21 | 19 |
| 8   | 54  | 42  | 34  | 29  | 49 | 39 | 32 | 27 | 33 | 27 | 24 | 27 | 23 | 20 | 21 | 19 | 17 |
| 9   | 50  | 38  | 31  | 26  | 46 | 35 | 29 | 24 | 30 | 25 | 21 | 25 | 21 | 18 | 20 | 17 | 15 |
| 10  | 47  | 35  | 28  | 23  | 43 | 32 | 26 | 22 | 28 | 23 | 19 | 23 | 19 | 17 | 18 | 16 | 14 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1189 | 1189 | 1189 |
| 5°  | 1191 | 1171 | 1178 |
| 10° | 1180 | 1148 | 1141 |
| 15° | 1164 | 1111 | 1082 |
| 20° | 1142 | 1059 | 1009 |
| 25° | 1120 | 1000 | 939  |
| 30° | 1091 | 941  | 851  |
| 35° | 1062 | 876  | 772  |
| 40° | 1033 | 810  | 683  |
| 45° | 998  | 736  | 602  |
| 50° | 963  | 661  | 522  |
| 55° | 926  | 581  | 446  |
| 60° | 884  | 497  | 368  |
| 65° | 835  | 412  | 331  |
| 70° | 775  | 333  | 300  |
| 75° | 701  | 294  | 275  |
| 80° | 593  | 248  | 240  |
| 85° | 414  | 168  | 183  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 998 cd/sqm

TEST NUMBER: P910493

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLONL

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 171.8  | 1.9       |
| 10°-20°   | 471.7  | 5.1       |
| 20°-30°   | 662.3  | 7.2       |
| 30°-40°   | 721.9  | 7.8       |
| 40°-50°   | 663.5  | 7.2       |
| 50°-60°   | 521.1  | 5.6       |
| 60°-70°   | 339.2  | 3.7       |
| 70°-80°   | 174.6  | 1.9       |
| 80°-90°   | 47.9   | 0.5       |
| 90°-100°  | 61.7   | 0.7       |
| 100°-110° | 230.0  | 2.5       |
| 110°-120° | 610.1  | 6.6       |
| 120°-130° | 1011.9 | 10.9      |
| 130°-140° | 1074.8 | 11.6      |
| 140°-150° | 999.0  | 10.8      |
| 150°-160° | 803.1  | 8.7       |
| 160°-170° | 517.5  | 5.6       |
| 170°-180° | 178.1  | 1.9       |
| 0°-30°    | 1305.8 | 14.1      |
| 0°-40°    | 2027.7 | 21.9      |
| 0°-60°    | 3212.2 | 34.7      |
| 0°-90°    | 3773.9 | 40.8      |
| 90°-120°  | 901.9  | 9.7       |
| 90°-150°  | 3987.5 | 43.1      |
| 90°-180°  | 5486.0 | 59.2      |
| 0°-180°   | 9260.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 1833 | 1833  | 1833 | 1833  | 1833 |      |
| 5°   | 1833 | 1825  | 1804 | 1818  | 1814 | 174  |
| 15°  | 1744 | 1726  | 1669 | 1638  | 1621 | 491  |
| 25°  | 1583 | 1530  | 1420 | 1352  | 1327 | 728  |
| 35°  | 1364 | 1279  | 1133 | 1029  | 992  | 854  |
| 45°  | 1115 | 1004  | 830  | 712   | 672  | 861  |
| 55°  | 848  | 718   | 539  | 440   | 408  | 758  |
| 65°  | 572  | 438   | 289  | 232   | 227  | 568  |
| 75°  | 305  | 189   | 133  | 121   | 120  | 323  |
| 85°  | 71   | 36    | 32   | 32    | 32   | 82   |
| 90°  | 1    | 16    | 27   | 34    | 36   | 9    |
| 95°  | 88   | 43    | 53   | 60    | 58   | 104  |
| 105° | 412  | 452   | 83   | 98    | 103  | 440  |
| 115° | 779  | 802   | 836  | 209   | 111  | 767  |
| 125° | 1101 | 1118  | 1144 | 1154  | 1158 | 982  |
| 135° | 1362 | 1384  | 1396 | 1410  | 1407 | 1052 |
| 145° | 1580 | 1579  | 1602 | 1611  | 1605 | 988  |
| 155° | 1740 | 1728  | 1744 | 1752  | 1742 | 802  |
| 165° | 1833 | 1825  | 1829 | 1839  | 1829 | 518  |
| 175° | 1875 | 1866  | 1869 | 1878  | 1865 | 178  |
| 180° | 1871 | 1871  | 1871 | 1871  | 1871 |      |

TEST NUMBER: P910493

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLONL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 1833.4 | 1833.4 | 1833.4 | 1833.4 | 1833.4 |
| 2.5°   | 1841.7 | 1833.4 | 1815.1 | 1831.8 | 1828.4 |
| 5°     | 1833.4 | 1825.1 | 1803.5 | 1818.4 | 1813.5 |
| 7.5°   | 1818.4 | 1808.6 | 1785.4 | 1791.8 | 1783.6 |
| 10°    | 1798.6 | 1786.9 | 1753.8 | 1748.7 | 1738.9 |
| 12.5°  | 1773.7 | 1758.8 | 1713.8 | 1704.0 | 1685.7 |
| 15°    | 1743.8 | 1725.5 | 1669.2 | 1637.7 | 1621.1 |
| 17.5°  | 1709.0 | 1682.4 | 1612.6 | 1576.2 | 1549.6 |
| 20°    | 1669.2 | 1635.9 | 1552.9 | 1511.6 | 1475.0 |
| 22.5°  | 1626.0 | 1587.9 | 1491.5 | 1435.2 | 1410.4 |
| 25°    | 1582.9 | 1529.8 | 1420.2 | 1352.3 | 1327.3 |
| 27.5°  | 1531.5 | 1475.0 | 1353.9 | 1275.9 | 1237.6 |
| 30°    | 1476.7 | 1413.5 | 1280.8 | 1196.3 | 1151.5 |
| 32.5°  | 1423.6 | 1347.2 | 1211.2 | 1111.7 | 1070.1 |
| 35°    | 1364.0 | 1279.2 | 1133.3 | 1028.7 | 992.1  |
| 37.5°  | 1305.8 | 1214.5 | 1060.2 | 945.6  | 904.3  |
| 40°    | 1244.4 | 1144.9 | 983.9  | 866.1  | 823.0  |
| 42.5°  | 1181.3 | 1075.2 | 907.6  | 784.7  | 743.4  |
| 45°    | 1115.0 | 1003.8 | 829.6  | 711.8  | 671.9  |
| 47.5°  | 1052.0 | 934.2  | 755.0  | 637.1  | 600.6  |
| 50°    | 982.2  | 864.5  | 681.9  | 567.4  | 532.7  |
| 52.5°  | 914.1  | 789.7  | 612.3  | 502.7  | 471.2  |
| 55°    | 847.8  | 718.4  | 539.2  | 439.7  | 408.2  |
| 57.5°  | 779.8  | 647.1  | 474.5  | 381.6  | 355.1  |
| 60°    | 710.1  | 577.3  | 406.4  | 321.9  | 295.4  |
| 62.5°  | 642.2  | 509.5  | 348.3  | 268.8  | 255.6  |
| 65°    | 572.5  | 437.9  | 288.7  | 232.3  | 227.2  |
| 67.5°  | 506.1  | 371.6  | 232.3  | 204.1  | 199.1  |
| 70°    | 436.4  | 307.0  | 192.4  | 175.9  | 169.1  |
| 72.5°  | 370.1  | 247.2  | 160.9  | 147.7  | 144.4  |
| 75°    | 305.2  | 189.1  | 132.7  | 121.1  | 119.6  |
| 77.5°  | 240.7  | 134.3  | 104.6  | 97.9   | 94.5   |
| 80°    | 180.8  | 96.3   | 79.5   | 73.1   | 73.1   |
| 82.5°  | 126.1  | 64.8   | 54.8   | 51.3   | 51.3   |
| 85°    | 71.3   | 36.5   | 31.5   | 31.5   | 31.5   |
| 87.5°  | 26.6   | 13.2   | 13.2   | 11.6   | 11.6   |
| 90°    | 1.3    | 16.2   | 27.1   | 33.9   | 36.5   |
| 92.5°  | 33.9   | 28.5   | 32.5   | 35.3   | 36.5   |
| 95°    | 87.9   | 43.3   | 52.8   | 59.7   | 58.2   |
| 97.5°  | 158.4  | 47.5   | 69.0   | 73.2   | 74.4   |
| 100°   | 239.8  | 54.2   | 77.2   | 87.9   | 90.7   |
| 102.5° | 329.0  | 326.4  | 80.0   | 94.7   | 98.9   |
| 105°   | 411.7  | 452.4  | 82.6   | 97.5   | 102.9  |
| 107.5° | 507.8  | 541.5  | 85.4   | 100.1  | 105.7  |
| 110°   | 600.0  | 628.2  | 237.0  | 101.6  | 106.9  |



TEST NUMBER: P910493

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLONL

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 686.6  | 710.9  | 687.9  | 104.2  | 108.3  |
| 115°   | 778.6  | 801.6  | 835.5  | 208.6  | 111.1  |
| 117.5° | 858.5  | 885.5  | 908.7  | 714.9  | 360.2  |
| 120°   | 947.9  | 968.2  | 992.6  | 1008.9 | 826.0  |
| 122.5° | 1023.6 | 1045.3 | 1072.5 | 1080.6 | 1082.1 |
| 125°   | 1100.8 | 1118.5 | 1144.3 | 1153.7 | 1157.8 |
| 127.5° | 1171.2 | 1190.2 | 1210.7 | 1224.1 | 1225.4 |
| 130°   | 1237.6 | 1259.4 | 1274.1 | 1289.1 | 1287.9 |
| 132.5° | 1305.4 | 1323.0 | 1337.8 | 1350.1 | 1348.8 |
| 135°   | 1362.3 | 1384.0 | 1396.0 | 1409.8 | 1407.0 |
| 137.5° | 1421.7 | 1438.0 | 1451.7 | 1465.2 | 1461.2 |
| 140°   | 1480.0 | 1490.9 | 1505.7 | 1517.9 | 1511.2 |
| 142.5° | 1528.9 | 1538.4 | 1555.9 | 1566.7 | 1559.9 |
| 145°   | 1580.3 | 1578.9 | 1601.8 | 1611.4 | 1604.6 |
| 147.5° | 1624.9 | 1620.8 | 1643.9 | 1650.6 | 1645.3 |
| 150°   | 1668.3 | 1658.8 | 1680.5 | 1688.6 | 1681.8 |
| 152.5° | 1704.8 | 1694.0 | 1714.3 | 1722.5 | 1713.0 |
| 155°   | 1740.0 | 1727.9 | 1744.1 | 1752.2 | 1741.5 |
| 157.5° | 1768.4 | 1757.7 | 1769.9 | 1779.4 | 1768.4 |
| 160°   | 1792.9 | 1784.7 | 1792.9 | 1800.9 | 1791.5 |
| 162.5° | 1814.4 | 1806.5 | 1813.1 | 1822.6 | 1810.4 |
| 165°   | 1833.4 | 1825.4 | 1829.4 | 1838.8 | 1829.4 |
| 167.5° | 1848.4 | 1840.2 | 1844.4 | 1853.8 | 1841.6 |
| 170°   | 1860.6 | 1852.4 | 1855.1 | 1864.6 | 1852.4 |
| 172.5° | 1868.7 | 1860.6 | 1863.3 | 1872.8 | 1860.6 |
| 175°   | 1875.4 | 1865.9 | 1868.7 | 1878.1 | 1864.6 |
| 177.5° | 1878.1 | 1868.7 | 1870.1 | 1879.5 | 1867.3 |
| 180°   | 1871.3 | 1871.3 | 1871.3 | 1871.3 | 1871.3 |

TEST NUMBER: P910493

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLONL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |      |      |      |      |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 6.84             | 7.60  | 7.88  | 8.64  | 10.04 | 2.80           | 3.56 | 3.84 | 4.60 | 6.00 |
|                 | 3H   | 8.52             | 9.20  | 9.57  | 10.25 | 11.67 | 3.99           | 4.66 | 5.03 | 5.71 | 7.13 |
|                 | 4H   | 9.13             | 9.77  | 10.19 | 10.82 | 12.25 | 4.43           | 5.08 | 5.49 | 6.13 | 7.56 |
|                 | 6H   | 9.55             | 10.14 | 10.62 | 11.20 | 12.64 | 4.75           | 5.34 | 5.82 | 6.40 | 7.84 |
|                 | 8H   | 9.68             | 10.24 | 10.75 | 11.31 | 12.74 | 4.84           | 5.40 | 5.92 | 6.48 | 7.91 |
|                 | 12H  | 9.74             | 10.27 | 10.82 | 11.34 | 12.80 | 4.88           | 5.42 | 5.96 | 6.48 | 7.94 |
| 4H              | 2H   | 6.85             | 7.49  | 7.92  | 8.54  | 9.97  | 3.39           | 4.03 | 4.46 | 5.09 | 6.51 |
|                 | 3H   | 8.68             | 9.21  | 9.75  | 10.29 | 11.73 | 4.74           | 5.27 | 5.81 | 6.35 | 7.79 |
|                 | 4H   | 9.37             | 9.86  | 10.45 | 10.93 | 12.39 | 5.28           | 5.77 | 6.36 | 6.84 | 8.30 |
|                 | 6H   | 9.89             | 10.31 | 10.98 | 11.40 | 12.86 | 5.70           | 6.12 | 6.79 | 7.21 | 8.67 |
|                 | 8H   | 10.07            | 10.46 | 11.16 | 11.54 | 13.02 | 5.83           | 6.22 | 6.92 | 7.31 | 8.78 |
|                 | 12H  | 10.16            | 10.52 | 11.27 | 11.62 | 13.09 | 5.89           | 6.25 | 7.00 | 7.35 | 8.82 |
| 8H              | 4H   | 9.34             | 9.73  | 10.42 | 10.81 | 12.28 | 5.56           | 5.95 | 6.65 | 7.04 | 8.51 |
|                 | 6H   | 9.91             | 10.23 | 11.02 | 11.36 | 12.82 | 6.08           | 6.40 | 7.19 | 7.53 | 9.00 |
|                 | 8H   | 10.13            | 10.41 | 11.24 | 11.52 | 13.01 | 6.27           | 6.56 | 7.39 | 7.67 | 9.15 |
|                 | 12H  | 10.27            | 10.52 | 11.39 | 11.62 | 13.15 | 6.39           | 6.64 | 7.51 | 7.74 | 9.27 |
| 12H             | 4H   | 9.28             | 9.64  | 10.39 | 10.74 | 12.21 | 5.56           | 5.92 | 6.67 | 7.02 | 8.49 |
|                 | 6H   | 9.88             | 10.16 | 11.00 | 11.27 | 12.76 | 6.13           | 6.41 | 7.25 | 7.52 | 9.01 |
|                 | 8H   | 10.10            | 10.35 | 11.22 | 11.46 | 12.98 | 6.34           | 6.59 | 7.46 | 7.69 | 9.22 |

END OF REPORT