

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910505

Luminaire Tested: DFN2DIP-4P4F0-040D080US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910505
REPORT IS A COMBINATION OF REPORTS P900662 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-040D080US850-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12553.9 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 112.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910505

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910505

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1189	1189	1189
5°	1191	1171	1178
10°	1180	1148	1141
15°	1164	1111	1082
20°	1142	1059	1009
25°	1120	1000	939
30°	1091	941	851
35°	1062	876	772
40°	1033	810	683
45°	998	736	602
50°	963	661	522
55°	926	581	446
60°	884	497	368
65°	835	412	331
70°	775	333	300
75°	701	294	275
80°	593	248	240
85°	414	168	183

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1543 cd/sqm

TEST NUMBER: P910505

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.8	1.4
10°-20°	471.7	3.8
20°-30°	662.3	5.3
30°-40°	721.9	5.8
40°-50°	663.5	5.3
50°-60°	521.1	4.2
60°-70°	339.2	2.7
70°-80°	174.6	1.4
80°-90°	49.8	0.4
90°-100°	98.7	0.8
100°-110°	368.1	2.9
110°-120°	976.2	7.8
120°-130°	1619.0	12.9
130°-140°	1719.8	13.7
140°-150°	1598.3	12.7
150°-160°	1285.0	10.2
160°-170°	828.0	6.6
170°-180°	285.0	2.3
0°-30°	1305.8	10.4
0°-40°	2027.7	16.2
0°-60°	3212.2	25.6
0°-90°	3775.8	30.1
90°-120°	1442.9	11.5
90°-150°	6380.0	50.8
90°-180°	8778.0	69.9
0°-180°	12553.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1825	1804	1818	1814	174
15°	1744	1726	1669	1638	1621	491
25°	1583	1530	1420	1352	1327	728
35°	1364	1279	1133	1029	992	854
45°	1115	1004	830	712	672	861
55°	848	718	539	440	408	758
65°	572	438	289	232	227	568
75°	305	189	133	121	120	323
85°	71	36	32	32	32	82
90°	2	26	43	54	58	12
95°	141	69	84	96	93	167
105°	659	724	132	156	165	704
115°	1246	1283	1337	334	178	1226
125°	1761	1790	1831	1846	1852	1571
135°	2180	2214	2234	2256	2251	1684
145°	2528	2526	2563	2578	2567	1581
155°	2784	2765	2791	2804	2786	1283
165°	2934	2921	2927	2942	2927	829
175°	3001	2985	2990	3005	2983	286
180°	2994	2994	2994	2994	2994	

TEST NUMBER: P910505

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.4	1833.4	1833.4	1833.4	1833.4
2.5°	1841.7	1833.4	1815.1	1831.8	1828.4
5°	1833.4	1825.1	1803.5	1818.4	1813.5
7.5°	1818.4	1808.6	1785.4	1791.8	1783.6
10°	1798.6	1786.9	1753.8	1748.7	1738.9
12.5°	1773.7	1758.8	1713.8	1704.0	1685.7
15°	1743.8	1725.5	1669.2	1637.7	1621.1
17.5°	1709.0	1682.4	1612.6	1576.2	1549.6
20°	1669.2	1635.9	1552.9	1511.6	1475.0
22.5°	1626.0	1587.9	1491.5	1435.2	1410.4
25°	1582.9	1529.8	1420.2	1352.3	1327.3
27.5°	1531.5	1475.0	1353.9	1275.9	1237.6
30°	1476.7	1413.5	1280.8	1196.3	1151.5
32.5°	1423.6	1347.2	1211.2	1111.7	1070.1
35°	1364.0	1279.2	1133.3	1028.7	992.1
37.5°	1305.8	1214.5	1060.2	945.6	904.3
40°	1244.4	1144.9	983.9	866.1	823.0
42.5°	1181.3	1075.2	907.6	784.7	743.4
45°	1115.0	1003.8	829.6	711.8	671.9
47.5°	1052.0	934.2	755.0	637.1	600.6
50°	982.2	864.5	681.9	567.4	532.7
52.5°	914.1	789.7	612.3	502.7	471.2
55°	847.8	718.4	539.2	439.7	408.2
57.5°	779.8	647.1	474.5	381.6	355.1
60°	710.1	577.3	406.4	321.9	295.4
62.5°	642.2	509.5	348.3	268.8	255.6
65°	572.5	437.9	288.7	232.3	227.2
67.5°	506.1	371.6	232.3	204.1	199.1
70°	436.4	307.0	192.4	175.9	169.1
72.5°	370.1	247.2	160.9	147.7	144.4
75°	305.2	189.1	132.7	121.1	119.6
77.5°	240.7	134.3	104.6	97.9	94.5
80°	180.8	96.3	79.5	73.1	73.1
82.5°	126.1	64.8	54.8	51.3	51.3
85°	71.3	36.5	31.5	31.5	31.5
87.5°	26.6	13.2	13.2	11.6	11.6
90°	2.1	26.0	43.3	54.2	58.4
92.5°	54.2	45.6	52.0	56.3	58.4
95°	140.7	69.2	84.4	95.5	93.2
97.5°	253.4	75.9	110.3	117.1	119.1
100°	383.6	86.7	123.5	140.7	145.1
102.5°	526.4	522.2	127.9	151.5	158.3
105°	658.6	723.7	132.2	155.9	164.7
107.5°	812.5	866.5	136.6	160.3	169.0
110°	960.0	1005.2	379.3	162.6	171.1

TEST NUMBER: P910505

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1098.6	1137.4	1100.7	166.7	173.4
115°	1245.7	1282.6	1336.8	333.7	177.8
117.5°	1373.6	1416.9	1453.9	1143.8	576.3
120°	1516.7	1549.1	1588.2	1614.1	1321.6
122.5°	1637.8	1672.6	1716.1	1728.9	1731.3
125°	1761.3	1789.6	1830.7	1845.9	1852.4
127.5°	1874.0	1904.4	1937.1	1958.6	1960.7
130°	1980.2	2014.9	2038.7	2062.6	2060.5
132.5°	2088.6	2116.9	2140.6	2160.1	2158.0
135°	2179.6	2214.3	2233.6	2255.6	2251.2
137.5°	2274.9	2300.8	2322.7	2344.3	2337.9
140°	2367.9	2385.5	2409.2	2428.7	2417.8
142.5°	2446.2	2461.3	2489.4	2506.7	2495.8
145°	2528.5	2526.2	2563.0	2578.2	2567.3
147.5°	2599.8	2593.4	2630.1	2641.0	2632.4
150°	2669.3	2654.1	2688.8	2701.6	2690.9
152.5°	2727.7	2710.4	2742.8	2756.0	2740.8
155°	2784.0	2764.7	2790.7	2803.6	2786.4
157.5°	2829.5	2812.3	2831.8	2847.0	2829.5
160°	2868.7	2855.6	2868.7	2881.5	2866.3
162.5°	2903.1	2890.3	2901.0	2916.2	2896.7
165°	2933.5	2920.7	2927.1	2942.2	2927.1
167.5°	2957.4	2944.3	2950.9	2966.1	2946.6
170°	2977.0	2963.8	2968.2	2983.4	2963.8
172.5°	2989.9	2977.0	2981.3	2996.5	2977.0
175°	3000.6	2985.4	2989.9	3004.9	2983.4
177.5°	3004.9	2989.9	2992.1	3007.3	2987.8
180°	2994.2	2994.2	2994.2	2994.2	2994.2

TEST NUMBER: P910505

CATALOG NUMBER: DFN2DIP-4P4F0-040D080US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.55	6.24	6.66	7.34	8.88	1.51	2.20	2.62	3.30	4.84
	3H	7.22	7.84	8.34	8.95	10.50	2.69	3.30	3.81	4.42	5.97
	4H	7.83	8.41	8.96	9.53	11.08	3.13	3.72	4.27	4.83	6.39
	6H	8.25	8.78	9.39	9.90	11.47	3.45	3.99	4.59	5.11	6.67
	8H	8.37	8.88	9.52	10.02	11.57	3.54	4.05	4.68	5.18	6.74
	12H	8.43	8.92	9.58	10.04	11.62	3.57	4.06	4.72	5.19	6.77
4H	2H	5.55	6.13	6.69	7.25	8.80	2.09	2.67	3.23	3.79	5.34
	3H	7.37	7.86	8.52	9.00	10.57	3.43	3.92	4.58	5.06	6.62
	4H	8.06	8.51	9.21	9.64	11.23	3.97	4.42	5.12	5.55	7.14
	6H	8.58	8.96	9.73	10.11	11.69	4.39	4.77	5.54	5.92	7.50
	8H	8.75	9.11	9.91	10.25	11.85	4.51	4.87	5.67	6.02	7.61
	12H	8.84	9.17	10.01	10.32	11.92	4.57	4.90	5.74	6.05	7.65
8H	4H	8.02	8.38	9.17	9.52	11.12	4.25	4.60	5.40	5.75	7.34
	6H	8.59	8.88	9.76	10.07	11.66	4.76	5.06	5.94	6.25	7.83
	8H	8.81	9.06	9.99	10.23	11.84	4.95	5.21	6.13	6.38	7.99
	12H	8.94	9.17	10.13	10.33	11.98	5.07	5.29	6.25	6.46	8.10
12H	4H	7.97	8.29	9.14	9.45	11.04	4.25	4.57	5.42	5.73	7.32
	6H	8.56	8.82	9.74	9.99	11.60	4.81	5.07	5.99	6.24	7.85
	8H	8.78	9.01	9.96	10.17	11.81	5.02	5.24	6.20	6.41	8.05

END OF REPORT