

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910354

Luminaire Tested: DFN2DIP-4P2F0-040D040US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910354
REPORT IS A COMBINATION OF REPORTS P899027 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-040D040US850-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8317.5 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 73.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910354

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910354

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4322	4322	4322
5°	4320	4251	4283
10°	4277	4183	4218
15°	4205	4103	4120
20°	4111	3996	4021
25°	4018	3871	3906
30°	3903	3754	3763
35°	3794	3617	3612
40°	3661	3479	3468
45°	3527	3340	3319
50°	3381	3193	3149
55°	3227	3024	2990
60°	3053	2825	2808
65°	2861	2617	2594
70°	2618	2364	2361
75°	2286	2061	2137
80°	1880	1673	1729
85°	1259	1046	1076

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3527 cd/sqm

TEST NUMBER: P910354

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.0
10°-20°	457.1	5.5
20°-30°	671.7	8.1
30°-40°	780.2	9.4
40°-50°	779.2	9.4
50°-60°	679.5	8.2
60°-70°	502.3	6.0
70°-80°	284.2	3.4
80°-90°	79.0	0.9
90°-100°	86.8	1.0
100°-110°	275.8	3.3
110°-120°	472.0	5.7
120°-130°	620.8	7.5
130°-140°	696.8	8.4
140°-150°	683.3	8.2
150°-160°	573.2	6.9
160°-170°	380.1	4.6
170°-180°	132.9	1.6
0°-30°	1291.3	15.5
0°-40°	2071.5	24.9
0°-60°	3530.2	42.4
0°-90°	4395.6	52.8
90°-120°	834.7	10.0
90°-150°	2835.6	34.1
90°-180°	3922.0	47.2
0°-180°	8317.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	76
90°	1	15	42	39	40	8
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	

TEST NUMBER: P910354

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US850-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6

TEST NUMBER: P910354

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9

TEST NUMBER: P910354

CATALOG NUMBER: DFN2DIP-4P2F0-040D040US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.48	13.37	13.41	14.32	15.55	12.04	12.92	12.97	13.87	15.10
	3H	14.12	14.92	15.06	15.88	17.13	13.63	14.43	14.57	15.39	16.64
	4H	14.69	15.45	15.65	16.41	17.67	14.20	14.95	15.16	15.92	17.18
	6H	15.08	15.77	16.05	16.74	18.02	14.58	15.27	15.55	16.24	17.52
	8H	15.17	15.84	16.15	16.82	18.09	14.67	15.33	15.65	16.32	17.59
	12H	15.22	15.85	16.20	16.82	18.12	14.71	15.34	15.69	16.32	17.61
4H	2H	12.93	13.69	13.90	14.65	15.91	12.58	13.33	13.54	14.29	15.56
	3H	14.77	15.40	15.75	16.40	17.67	14.37	15.00	15.34	15.99	17.26
	4H	15.47	16.05	16.45	17.03	18.33	15.05	15.62	16.03	16.61	17.91
	6H	15.97	16.46	16.96	17.47	18.77	15.53	16.03	16.53	17.04	18.34
	8H	16.11	16.57	17.10	17.57	18.89	15.67	16.13	16.67	17.14	18.45
	12H	16.17	16.59	17.18	17.61	18.93	15.72	16.14	16.74	17.16	18.48
8H	4H	15.66	16.12	16.65	17.12	18.44	15.28	15.74	16.28	16.75	18.06
	6H	16.26	16.64	17.28	17.69	19.00	15.88	16.26	16.90	17.30	18.62
	8H	16.47	16.80	17.50	17.84	19.17	16.07	16.41	17.10	17.44	18.77
	12H	16.58	16.88	17.62	17.91	19.28	16.17	16.47	17.21	17.50	18.87
12H	4H	15.64	16.06	16.66	17.08	18.40	15.27	15.69	16.29	16.71	18.03
	6H	16.29	16.62	17.32	17.66	18.99	15.91	16.25	16.94	17.28	18.61
	8H	16.51	16.81	17.54	17.83	19.21	16.13	16.43	17.16	17.45	18.83