

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913071

Luminaire Tested: DFN2DIP-4P2F0-030D040US927-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913071
REPORT IS A COMBINATION OF REPORTS P900545 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-030D040US927-FLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5489.8 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 60.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913071

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913071

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	32	52	41	34	29	35	29	25	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2315	2315	2315
5°	2315	2277	2295
10°	2291	2241	2260
15°	2253	2198	2207
20°	2203	2141	2154
25°	2153	2074	2093
30°	2091	2011	2016
35°	2033	1938	1935
40°	1961	1864	1858
45°	1890	1789	1778
50°	1811	1711	1687
55°	1729	1620	1602
60°	1636	1513	1504
65°	1533	1402	1390
70°	1403	1266	1265
75°	1224	1104	1145
80°	1008	896	926
85°	674	560	576

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1890 cd/sqm

TEST NUMBER: P913071

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.6
10°-20°	244.9	4.5
20°-30°	359.9	6.6
30°-40°	418.0	7.6
40°-50°	417.5	7.6
50°-60°	364.0	6.6
60°-70°	269.1	4.9
70°-80°	152.3	2.8
80°-90°	42.1	0.8
90°-100°	35.2	0.6
100°-110°	131.5	2.4
110°-120°	348.6	6.4
120°-130°	578.2	10.5
130°-140°	614.2	11.2
140°-150°	570.9	10.4
150°-160°	458.9	8.4
160°-170°	295.7	5.4
170°-180°	101.8	1.9
0°-30°	691.8	12.6
0°-40°	1109.8	20.2
0°-60°	1891.3	34.5
0°-90°	2354.7	42.9
90°-120°	515.3	9.4
90°-150°	2278.7	41.5
90°-180°	3135.0	57.1
0°-180°	5489.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	925	921	911	918	917	88
15°	880	875	863	867	862	248
25°	797	790	774	776	774	367
35°	687	678	664	659	654	429
45°	559	553	540	530	526	432
55°	423	418	407	397	392	378
65°	286	280	271	263	259	282
75°	149	148	143	138	140	159
85°	36	36	35	32	31	41
90°	1	9	15	19	21	5
95°	50	25	30	34	33	60
105°	235	258	47	56	59	251
115°	445	458	477	119	64	438
125°	629	639	654	659	662	561
135°	778	791	798	806	804	601
145°	903	902	915	921	917	565
155°	994	988	997	1001	995	458
165°	1048	1043	1045	1051	1045	296
175°	1072	1066	1068	1073	1066	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P913071

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	924.7	924.7	924.7	924.7	924.7
2.5°	930.1	925.7	915.8	924.7	923.0
5°	924.7	921.2	911.4	918.5	916.8
7.5°	918.5	913.2	903.4	910.6	908.8
10°	908.8	902.5	891.9	899.0	896.4
12.5°	895.4	890.1	879.5	883.8	882.1
15°	880.3	875.0	863.4	867.0	862.5
17.5°	861.6	856.3	844.7	849.1	844.7
20°	841.1	835.8	823.4	826.0	822.5
22.5°	820.8	812.8	801.1	801.1	799.3
25°	796.7	789.6	774.5	776.3	774.5
27.5°	770.0	763.7	752.3	749.6	745.2
30°	743.4	736.3	722.9	720.3	716.7
32.5°	714.9	709.6	695.4	690.0	686.4
35°	687.4	678.5	664.2	658.9	654.4
37.5°	656.2	648.2	634.0	627.7	623.3
40°	624.2	617.1	602.8	594.9	591.4
42.5°	593.1	586.0	571.8	562.8	557.5
45°	559.4	553.1	539.7	530.0	526.4
47.5°	526.4	520.2	506.0	496.1	490.8
50°	491.7	487.3	474.8	462.4	458.0
52.5°	458.0	451.7	440.2	430.4	424.1
55°	423.3	418.0	407.3	396.6	392.2
57.5°	388.6	384.1	372.6	361.9	358.3
60°	353.9	350.4	337.9	328.1	325.5
62.5°	320.1	313.9	305.0	296.1	292.6
65°	285.5	280.1	271.2	263.2	258.8
67.5°	249.9	245.4	237.4	231.2	227.7
70°	217.0	213.4	205.4	199.2	195.7
72.5°	183.2	179.6	175.2	169.0	166.4
75°	149.3	147.7	143.1	137.8	139.7
77.5°	119.1	115.6	113.8	111.1	108.5
80°	89.0	88.0	86.2	83.6	81.8
82.5°	60.4	60.4	59.7	56.0	56.0
85°	36.4	35.6	34.7	32.0	31.1
87.5°	16.0	14.3	12.4	9.8	8.9
90°	0.7	9.3	15.4	19.4	20.8
92.5°	19.4	16.2	18.5	20.1	20.8
95°	50.2	24.7	30.1	34.1	33.3
97.5°	90.5	27.1	39.5	41.8	42.5
100°	137.0	31.0	44.1	50.2	51.8
102.5°	188.0	186.6	45.6	54.1	56.5
105°	235.2	258.5	47.2	55.7	58.8
107.5°	290.2	309.5	48.8	57.3	60.4
110°	342.9	359.0	135.5	58.1	61.1



TEST NUMBER: P913071

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.4	406.2	393.1	59.6	61.9
115°	444.9	458.0	477.4	119.1	63.5
117.5°	490.6	506.0	519.3	408.5	205.8
120°	541.7	553.3	567.2	576.5	472.1
122.5°	584.9	597.4	612.9	617.5	618.3
125°	629.1	639.2	653.9	659.3	661.6
127.5°	669.3	680.2	691.8	699.6	700.3
130°	707.3	719.7	728.1	736.6	735.9
132.5°	745.9	756.1	764.5	771.5	770.8
135°	778.5	790.9	797.8	805.6	804.1
137.5°	812.5	821.7	829.6	837.3	835.0
140°	845.7	852.0	860.5	867.4	863.6
142.5°	873.7	879.1	889.1	895.2	891.4
145°	903.1	902.3	915.4	920.8	916.9
147.5°	928.5	926.2	939.4	943.3	940.2
150°	953.3	947.9	960.4	965.0	961.1
152.5°	974.2	968.0	979.6	984.3	978.9
155°	994.3	987.5	996.7	1001.3	995.1
157.5°	1010.6	1004.4	1011.5	1016.8	1010.6
160°	1024.5	1019.9	1024.5	1029.1	1023.7
162.5°	1036.9	1032.3	1036.2	1041.6	1034.6
165°	1047.7	1043.1	1045.4	1050.8	1045.4
167.5°	1056.3	1051.5	1054.0	1059.4	1052.4
170°	1063.3	1058.6	1060.1	1065.6	1058.6
172.5°	1067.9	1063.3	1064.8	1070.2	1063.3
175°	1071.7	1066.3	1067.9	1073.2	1065.6
177.5°	1073.2	1067.9	1068.7	1074.1	1067.1
180°	1069.4	1069.4	1069.4	1069.4	1069.4

TEST NUMBER: P913071

CATALOG NUMBER: DFN2DIP-4P2F0-030D040US927-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.36	10.16	10.38	11.19	12.55	8.92	9.72	9.93	10.74	12.11
	3H	10.99	11.71	12.02	12.74	14.13	10.50	11.22	11.53	12.26	13.64
	4H	11.56	12.24	12.60	13.28	14.68	11.07	11.75	12.11	12.79	14.18
	6H	11.94	12.57	12.99	13.61	15.02	11.44	12.07	12.49	13.11	14.52
	8H	12.04	12.63	13.09	13.69	15.09	11.54	12.13	12.59	13.19	14.59
	12H	12.07	12.64	13.13	13.69	15.12	11.57	12.13	12.62	13.18	14.61
4H	2H	9.80	10.48	10.85	11.52	12.91	9.45	10.13	10.49	11.16	12.56
	3H	11.63	12.20	12.69	13.27	14.68	11.23	11.79	12.28	12.86	14.27
	4H	12.33	12.85	13.39	13.90	15.34	11.90	12.42	12.96	13.48	14.91
	6H	12.82	13.27	13.89	14.34	15.77	12.39	12.83	13.46	13.91	15.34
	8H	12.96	13.37	14.02	14.44	15.89	12.52	12.94	13.59	14.01	15.45
	12H	13.01	13.39	14.10	14.48	15.92	12.57	12.94	13.65	14.03	15.48
8H	4H	12.51	12.92	13.58	14.00	15.44	12.13	12.55	13.20	13.62	15.06
	6H	13.11	13.45	14.20	14.57	16.01	12.72	13.07	13.82	14.18	15.62
	8H	13.31	13.61	14.41	14.71	16.17	12.92	13.22	14.02	14.32	15.78
	12H	13.43	13.69	14.53	14.78	16.28	13.02	13.28	14.12	14.37	15.87
12H	4H	12.49	12.86	13.57	13.95	15.40	12.12	12.49	13.20	13.58	15.03
	6H	13.13	13.43	14.23	14.53	15.99	12.76	13.06	13.86	14.16	15.62
	8H	13.35	13.62	14.46	14.71	16.21	12.97	13.24	14.07	14.33	15.83