

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915805

Luminaire Tested: DFN2DIP-4P2F0-040D020US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915805
REPORT IS A COMBINATION OF REPORTS P900536 AND P897455
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-040D020US930-RLLONL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4386.3 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915805

CATALOG NUMBER: DFN2DIP-4P2F0-040D020US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915805

CATALOG NUMBER: DFN2DIP-4P2F0-040D020US930-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3375	3375	3375
5°	3374	3313	3337
10°	3334	3239	3223
15°	3281	3124	3050
20°	3213	2969	2839
25°	3144	2796	2636
30°	3054	2619	2381
35°	2965	2431	2157
40°	2874	2236	1901
45°	2769	2022	1669
50°	2660	1806	1443
55°	2546	1577	1226
60°	2413	1338	1004
65°	2260	1097	897
70°	2074	872	804
75°	1840	753	721
80°	1505	608	608
85°	970	375	430

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2769 cd/sqm

TEST NUMBER: P915805

CATALOG NUMBER: DFN2DIP-4P2F0-040D020US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.9
10°-20°	346.8	7.9
20°-30°	486.9	11.1
30°-40°	530.7	12.1
40°-50°	487.8	11.1
50°-60°	383.1	8.7
60°-70°	249.3	5.7
70°-80°	128.4	2.9
80°-90°	33.7	0.8
90°-100°	18.1	0.4
100°-110°	67.6	1.5
110°-120°	179.4	4.1
120°-130°	297.6	6.8
130°-140°	316.1	7.2
140°-150°	293.8	6.7
150°-160°	236.2	5.4
160°-170°	152.2	3.5
170°-180°	52.4	1.2
0°-30°	960.0	21.9
0°-40°	1490.7	34.0
0°-60°	2361.5	53.8
0°-90°	2773.0	63.2
90°-120°	265.2	6.0
90°-150°	1172.6	26.7
90°-180°	1613.0	36.8
0°-180°	4386.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	0	5	8	10	11	4
95°	26	13	16	18	17	31
105°	121	133	24	29	30	129
115°	229	236	246	61	33	225
125°	324	329	336	339	340	289
135°	401	407	410	415	414	309
145°	465	464	471	474	472	291
155°	512	508	513	515	512	236
165°	539	537	538	541	538	152
175°	552	549	550	552	548	52
180°	550	550	550	550	550	

TEST NUMBER: P915805

CATALOG NUMBER: DFN2DIP-4P2F0-040D020US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	0.4	4.8	7.9	9.9	10.8
92.5°	9.9	8.4	9.5	10.4	10.8
95°	25.8	12.7	15.5	17.5	17.1
97.5°	46.6	13.9	20.3	21.5	21.9
100°	70.5	15.9	22.7	25.8	26.7
102.5°	96.8	96.0	23.5	27.9	29.1
105°	121.1	133.0	24.3	28.6	30.2
107.5°	149.4	159.2	25.1	29.4	31.1
110°	176.4	184.7	69.7	29.9	31.5



TEST NUMBER: P915805

CATALOG NUMBER: DFN2DIP-4P2F0-040D020US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.9	209.0	202.3	30.7	31.9
115°	228.9	235.7	245.7	61.3	32.7
117.5°	252.4	260.4	267.2	210.3	105.9
120°	278.8	284.7	291.9	296.7	242.9
122.5°	301.0	307.4	315.4	317.7	318.2
125°	323.8	328.9	336.5	339.2	340.5
127.5°	344.5	350.0	356.0	360.0	360.4
130°	363.9	370.3	374.7	379.1	378.7
132.5°	383.8	389.1	393.4	397.0	396.6
135°	400.6	407.0	410.5	414.6	413.8
137.5°	418.1	422.9	426.9	430.9	429.7
140°	435.2	438.5	442.8	446.4	444.4
142.5°	449.6	452.4	457.5	460.7	458.7
145°	464.7	464.3	471.1	473.9	471.9
147.5°	477.8	476.6	483.4	485.3	483.8
150°	490.6	487.8	494.2	496.5	494.6
152.5°	501.3	498.1	504.1	506.5	503.7
155°	511.7	508.1	512.9	515.3	512.1
157.5°	520.1	516.9	520.5	523.3	520.1
160°	527.3	524.8	527.3	529.6	526.8
162.5°	533.5	531.2	533.2	536.0	532.4
165°	539.2	536.8	537.9	540.8	537.9
167.5°	543.6	541.1	542.3	545.2	541.5
170°	547.1	544.7	545.5	548.3	544.7
172.5°	549.5	547.1	548.0	550.7	547.1
175°	551.5	548.7	549.5	552.3	548.3
177.5°	552.3	549.5	549.9	552.7	549.1
180°	550.3	550.3	550.3	550.3	550.3

TEST NUMBER: P915805

CATALOG NUMBER: DFN2DIP-4P2F0-040D020US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.39	13.34	13.23	14.20	15.27	8.35	9.30	9.19	10.16	11.23
	3H	14.05	14.91	14.91	15.77	16.87	9.53	10.38	10.38	11.25	12.35
	4H	14.65	15.46	15.53	16.33	17.44	9.97	10.77	10.84	11.65	12.76
	6H	15.06	15.80	15.95	16.68	17.81	10.28	11.02	11.16	11.90	13.02
	8H	15.18	15.89	16.07	16.79	17.91	10.36	11.06	11.25	11.96	13.09
	12H	15.24	15.91	16.14	16.80	17.95	10.40	11.07	11.30	11.96	13.11
4H	2H	12.42	13.22	13.29	14.10	15.21	8.95	9.75	9.82	10.63	11.74
	3H	14.23	14.90	15.12	15.81	16.93	10.29	10.95	11.17	11.86	12.98
	4H	14.91	15.52	15.81	16.42	17.57	10.82	11.43	11.72	12.33	13.48
	6H	15.41	15.93	16.32	16.86	18.01	11.22	11.75	12.14	12.67	13.83
	8H	15.58	16.06	16.49	16.99	18.15	11.34	11.83	12.26	12.75	13.92
	12H	15.66	16.10	16.60	17.04	18.21	11.40	11.84	12.34	12.78	13.95
8H	4H	14.88	15.37	15.80	16.29	17.46	11.10	11.58	12.01	12.51	13.67
	6H	15.43	15.83	16.37	16.79	17.96	11.59	11.99	12.53	12.96	14.12
	8H	15.63	15.99	16.58	16.94	18.12	11.77	12.12	12.72	13.08	14.26
	12H	15.76	16.07	16.71	17.02	18.25	11.87	12.19	12.83	13.13	14.37
12H	4H	14.84	15.28	15.77	16.22	17.39	11.10	11.54	12.04	12.48	13.65
	6H	15.40	15.76	16.35	16.71	17.90	11.63	11.99	12.59	12.95	14.13
	8H	15.61	15.93	16.57	16.87	18.11	11.83	12.15	12.79	13.09	14.33