

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913213

Luminaire Tested: DFN2DIP-4P4F0-040D030US927-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913213
REPORT IS A COMBINATION OF REPORTS P900602 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-040D030US927-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5046.2 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 61.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913213
CATALOG NUMBER: DFN2DIP-4P4F0-040D030US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P913213

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59	53
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	53	52	51	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	42	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	27	24	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	23	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	850	850	850
5°	851	836	842
10°	843	820	815
15°	831	793	773
20°	816	756	721
25°	800	715	671
30°	779	672	608
35°	759	626	552
40°	738	578	488
45°	713	525	430
50°	688	472	373
55°	662	415	319
60°	631	355	263
65°	596	295	237
70°	554	238	215
75°	501	210	196
80°	423	177	171
85°	296	120	131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 713 cd/sqm



TEST NUMBER: P913213

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US927-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	2.4
10°-20°	336.9	6.7
20°-30°	473.1	9.4
30°-40°	515.7	10.2
40°-50°	473.9	9.4
50°-60°	372.2	7.4
60°-70°	242.3	4.8
70°-80°	124.7	2.5
80°-90°	33.3	0.7
90°-100°	26.5	0.5
100°-110°	98.6	2.0
110°-120°	261.5	5.2
120°-130°	433.7	8.6
130°-140°	460.7	9.1
140°-150°	428.1	8.5
150°-160°	344.2	6.8
160°-170°	221.8	4.4
170°-180°	76.3	1.5
0°-30°	932.7	18.5
0°-40°	1448.4	28.7
0°-60°	2294.6	45.5
0°-90°	2694.8	53.4
90°-120°	386.5	7.7
90°-150°	1709.0	33.9
90°-180°	2351.0	46.6
0°-180°	5046.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	7	12	15	16	5
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	



TEST NUMBER: P913213

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9



TEST NUMBER: P913213

CATALOG NUMBER: DFN2DIP-4P4F0-040D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1



TEST NUMBER: P913213
 CATALOG NUMBER: DFN2DIP-4P4F0-040D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.91	7.77	7.85	8.72	9.94	2.87	3.73	3.81	4.68	5.90
	3H	8.60	9.37	9.54	10.32	11.57	4.07	4.83	5.01	5.79	7.04
	4H	9.21	9.94	10.17	10.90	12.16	4.52	5.24	5.48	6.20	7.46
	6H	9.64	10.31	10.61	11.27	12.54	4.84	5.51	5.81	6.48	7.75
	8H	9.77	10.40	10.75	11.39	12.65	4.93	5.57	5.91	6.55	7.82
	12H	9.84	10.44	10.82	11.42	12.71	4.98	5.58	5.96	6.56	7.85
4H	2H	6.93	7.66	7.90	8.62	9.88	3.48	4.20	4.44	5.16	6.42
	3H	8.77	9.38	9.75	10.37	11.64	4.83	5.43	5.81	6.42	7.69
	4H	9.47	10.02	10.45	11.00	12.30	5.38	5.93	6.36	6.91	8.21
	6H	9.99	10.47	10.99	11.47	12.77	5.80	6.28	6.80	7.28	8.58
	8H	10.17	10.61	11.17	11.61	12.92	5.93	6.38	6.93	7.38	8.68
	12H	10.27	10.67	11.29	11.69	13.00	6.00	6.40	7.02	7.42	8.73
8H	4H	9.44	9.88	10.44	10.88	12.19	5.67	6.11	6.66	7.11	8.42
	6H	10.01	10.38	11.04	11.42	12.73	6.19	6.55	7.21	7.60	8.90
	8H	10.23	10.56	11.27	11.59	12.91	6.38	6.70	7.41	7.73	9.06
	12H	10.38	10.66	11.41	11.68	13.05	6.50	6.79	7.54	7.81	9.18
12H	4H	9.39	9.79	10.41	10.81	12.12	5.67	6.07	6.69	7.09	8.40
	6H	9.99	10.31	11.02	11.34	12.66	6.24	6.56	7.27	7.59	8.91
	8H	10.22	10.50	11.25	11.52	12.89	6.45	6.74	7.49	7.76	9.13