

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915806

Luminaire Tested: DFN2DIP-4P2F0-040D030US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915806
REPORT IS A COMBINATION OF REPORTS P899021 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-040D030US930-FLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5393.2 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 63.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915806
CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P915806

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55	55	55	55	50
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	46	46	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	40	40	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	34	34	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	30	30	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	26	26	26	23
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	23	23	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3177	3177	3177
5°	3176	3125	3149
10°	3144	3075	3101
15°	3091	3016	3029
20°	3023	2938	2956
25°	2954	2846	2872
30°	2870	2760	2767
35°	2789	2659	2656
40°	2691	2558	2549
45°	2593	2455	2440
50°	2485	2347	2315
55°	2373	2223	2198
60°	2244	2077	2064
65°	2104	1924	1907
70°	1924	1737	1736
75°	1681	1515	1571
80°	1383	1230	1272
85°	926	768	791

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2593 cd/sqm



TEST NUMBER: P915806

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	2.2
10°-20°	336.0	6.2
20°-30°	493.8	9.2
30°-40°	573.6	10.6
40°-50°	572.9	10.6
50°-60°	499.5	9.3
60°-70°	369.3	6.8
70°-80°	208.9	3.9
80°-90°	57.3	1.1
90°-100°	47.9	0.9
100°-110°	152.1	2.8
110°-120°	260.3	4.8
120°-130°	342.3	6.3
130°-140°	384.2	7.1
140°-150°	376.8	7.0
150°-160°	316.1	5.9
160°-170°	209.6	3.9
170°-180°	73.3	1.4
0°-30°	949.3	17.6
0°-40°	1522.9	28.2
0°-60°	2595.3	48.1
0°-90°	3230.8	59.9
90°-120°	460.2	8.5
90°-150°	1563.5	29.0
90°-180°	2162.0	40.1
0°-180°	5393.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	1	8	23	21	22	5
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	



TEST NUMBER: P915806

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1



TEST NUMBER: P915806

CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6



TEST NUMBER: P915806
 CATALOG NUMBER: DFN2DIP-4P2F0-040D030US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.02	12.98	12.89	13.87	14.99	11.58	12.53	12.44	13.42	14.54
	3H	13.66	14.52	14.54	15.42	16.57	13.17	14.03	14.05	14.93	16.08
	4H	14.24	15.05	15.14	15.96	17.12	13.75	14.56	14.64	15.46	16.62
	6H	14.63	15.38	15.54	16.29	17.46	14.13	14.88	15.04	15.79	16.96
	8H	14.73	15.44	15.64	16.37	17.54	14.23	14.94	15.14	15.87	17.04
	12H	14.77	15.45	15.69	16.37	17.57	14.26	14.94	15.18	15.86	17.06
4H	2H	12.48	13.29	13.38	14.20	15.36	12.12	12.94	13.02	13.84	15.00
	3H	14.33	15.01	15.24	15.94	17.12	13.92	14.60	14.83	15.53	16.71
	4H	15.03	15.65	15.95	16.58	17.78	14.60	15.22	15.53	16.15	17.35
	6H	15.53	16.06	16.46	17.02	18.22	15.09	15.63	16.03	16.58	17.78
	8H	15.67	16.17	16.61	17.12	18.33	15.23	15.73	16.17	16.68	17.89
	12H	15.74	16.19	16.69	17.15	18.37	15.29	15.74	16.24	16.70	17.92
8H	4H	15.22	15.72	16.16	16.67	17.88	14.84	15.34	15.78	16.29	17.50
	6H	15.83	16.24	16.79	17.23	18.44	15.44	15.86	16.41	16.85	18.06
	8H	16.03	16.40	17.01	17.38	18.61	15.64	16.01	16.61	16.98	18.22
	12H	16.15	16.48	17.13	17.45	18.73	15.74	16.07	16.72	17.04	18.32
12H	4H	15.21	15.66	16.16	16.62	17.84	14.84	15.29	15.79	16.25	17.47
	6H	15.85	16.22	16.83	17.20	18.43	15.48	15.84	16.45	16.82	18.05
	8H	16.08	16.40	17.06	17.38	18.65	15.70	16.02	16.68	16.99	18.27