

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918508

Luminaire Tested: DFN2DIP-4P2F0-020D020US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918508
REPORT IS A COMBINATION OF REPORTS P899012 AND P895899
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P2F0-020D020US935-RLLFLL
Description: 2 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2987.7 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.07' x L: 2.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918508

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918508

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1782	1782	1782
5°	1781	1749	1762
10°	1760	1710	1702
15°	1732	1649	1611
20°	1697	1568	1499
25°	1660	1476	1392
30°	1613	1383	1257
35°	1565	1284	1139
40°	1517	1181	1003
45°	1462	1068	881
50°	1405	954	762
55°	1344	833	647
60°	1274	707	530
65°	1193	579	474
70°	1095	460	425
75°	972	397	380
80°	795	321	320
85°	511	197	226

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1462 cd/sqm

TEST NUMBER: P918508

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	2.2
10°-20°	183.1	6.1
20°-30°	257.1	8.6
30°-40°	280.2	9.4
40°-50°	257.6	8.6
50°-60°	202.3	6.8
60°-70°	131.7	4.4
70°-80°	67.8	2.3
80°-90°	18.8	0.6
90°-100°	33.7	1.1
100°-110°	107.1	3.6
110°-120°	183.2	6.1
120°-130°	241.0	8.1
130°-140°	270.5	9.1
140°-150°	265.3	8.9
150°-160°	222.5	7.4
160°-170°	147.6	4.9
170°-180°	51.6	1.7
0°-30°	506.9	17.0
0°-40°	787.1	26.3
0°-60°	1247.0	41.7
0°-90°	1465.3	49.0
90°-120°	324.0	10.8
90°-150°	1100.8	36.8
90°-180°	1522.0	50.9
0°-180°	2987.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	0	6	16	15	16	3
95°	24	29	29	29	29	27
105°	99	100	101	102	102	104
115°	184	186	186	185	184	182
125°	267	272	270	269	268	239
135°	346	351	352	352	350	267
145°	420	423	426	426	425	262
155°	480	482	483	485	484	221
165°	522	522	522	525	523	147
175°	544	542	541	545	542	52
180°	545	545	545	545	545	

TEST NUMBER: P918508

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	0.5	5.9	16.1	15.1	15.6
92.5°	10.2	13.8	14.3	14.8	14.8
95°	23.9	28.6	29.4	29.4	28.6
97.5°	39.9	44.2	46.0	46.0	46.0
100°	58.3	62.1	63.4	63.4	62.9
102.5°	77.7	80.4	82.2	82.7	82.2
105°	98.8	100.1	101.2	101.9	101.9
107.5°	119.9	121.8	121.8	122.2	119.9
110°	140.3	142.8	142.8	142.8	141.5



TEST NUMBER: P918508

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	162.2	165.0	164.5	163.2	162.2
115°	183.9	186.5	185.7	185.2	183.9
117.5°	205.4	209.1	206.7	205.4	204.1
120°	227.0	230.7	227.0	227.0	225.6
122.5°	246.8	251.3	249.1	247.8	246.8
125°	267.4	271.6	270.3	268.8	268.3
127.5°	287.7	292.7	290.9	289.0	287.7
130°	306.5	312.5	311.6	310.6	308.8
132.5°	327.7	332.3	332.6	330.4	329.0
135°	345.9	351.0	352.0	351.5	350.2
137.5°	366.3	370.4	371.3	370.9	368.9
140°	384.2	388.3	390.6	390.6	388.8
142.5°	402.6	406.6	408.0	408.5	406.6
145°	420.0	423.3	425.9	426.4	424.6
147.5°	435.6	439.7	441.7	442.5	440.7
150°	451.7	454.4	456.2	457.7	456.2
152.5°	466.0	468.7	471.1	472.9	471.1
155°	480.3	481.6	483.0	485.3	483.9
157.5°	492.6	493.5	494.4	497.7	495.3
160°	503.6	504.5	505.1	507.8	505.8
162.5°	513.8	513.8	514.2	517.4	515.0
165°	522.5	521.9	521.9	525.2	523.0
167.5°	530.3	528.8	528.8	532.1	529.9
170°	536.2	534.9	534.4	537.7	534.9
172.5°	540.4	539.0	538.6	541.8	539.0
175°	543.6	542.3	541.3	544.6	541.8
177.5°	545.4	544.2	543.1	545.9	543.1
180°	544.6	544.6	544.6	544.6	544.6

TEST NUMBER: P918508

CATALOG NUMBER: DFN2DIP-4P2F0-020D020US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.93	9.75	9.90	10.73	12.02	4.89	5.71	5.86	6.69	7.98
	3H	10.58	11.32	11.57	12.31	13.62	6.06	6.79	7.04	7.78	9.09
	4H	11.17	11.87	12.17	12.86	14.18	6.49	7.19	7.49	8.18	9.50
	6H	11.58	12.22	12.58	13.22	14.55	6.79	7.43	7.80	8.43	9.76
	8H	11.69	12.30	12.71	13.32	14.64	6.87	7.48	7.89	8.50	9.83
	12H	11.75	12.32	12.76	13.33	14.68	6.91	7.49	7.93	8.50	9.85
4H	2H	8.94	9.64	9.94	10.63	11.95	5.47	6.17	6.48	7.16	8.48
	3H	10.74	11.32	11.75	12.34	13.67	6.80	7.38	7.81	8.40	9.73
	4H	11.42	11.94	12.43	12.96	14.31	7.33	7.86	8.35	8.87	10.23
	6H	11.91	12.36	12.94	13.40	14.75	7.72	8.18	8.75	9.22	10.57
	8H	12.07	12.49	13.10	13.53	14.89	7.84	8.26	8.87	9.29	10.66
	12H	12.15	12.53	13.20	13.58	14.95	7.89	8.27	8.94	9.32	10.69
8H	4H	11.38	11.80	12.41	12.83	14.20	7.59	8.02	8.62	9.05	10.41
	6H	11.92	12.27	12.97	13.34	14.71	8.08	8.43	9.14	9.51	10.87
	8H	12.12	12.43	13.18	13.49	14.87	8.26	8.56	9.32	9.62	11.01
	12H	12.24	12.51	13.31	13.57	14.99	8.36	8.63	9.42	9.68	11.11
12H	4H	11.33	11.71	12.38	12.76	14.13	7.59	7.98	8.64	9.02	10.39
	6H	11.89	12.20	12.95	13.26	14.64	8.12	8.43	9.19	9.49	10.87
	8H	12.10	12.37	13.16	13.42	14.84	8.32	8.59	9.38	9.64	11.07